

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009337

Luminaire Tested: S122DIP-B675D530UB50-4F0-XX-W2A-D1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009337
REPORT IS A COMBINATION OF REPORTS P984593 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D530UB50-4F0-XX-W2A-D1
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4420.0 lumens
Efficiency: N/A
Efficacy: 86.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009337

CATALOG NUMBER: S122DIP-B675D530UB50-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1009337

CATALOG NUMBER: S122DIP-B675D530UB50-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58
1	97	92	87	83	89	85	81	77	72	69	66	60	58	56	49	47	46
2	87	79	72	67	80	73	67	62	62	58	54	52	48	45	42	40	38
3	79	69	61	55	73	64	57	51	54	49	44	45	41	38	37	34	31
4	72	61	52	46	66	56	49	43	48	42	37	40	35	32	33	29	27
5	66	54	45	39	61	50	42	37	43	37	32	36	31	27	29	26	23
6	61	48	40	34	56	45	37	32	38	32	28	32	27	24	26	23	20
7	56	43	35	29	52	40	33	28	35	29	24	29	24	21	24	20	18
8	52	39	31	26	48	37	29	24	31	26	21	27	22	19	22	18	16
9	49	36	28	23	45	33	26	22	29	23	19	24	20	17	20	17	14
10	45	33	25	20	42	31	24	19	27	21	17	23	18	15	19	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10778	10778	10778
5°	10827	10318	10260
10°	10754	9961	9815
15°	10602	9592	9359
20°	10410	9202	8927
25°	10222	8832	8535
30°	9957	8454	8146
35°	9689	8089	7860
40°	9407	7774	7577
45°	9138	7489	7329
50°	8848	7225	7085
55°	8545	6945	6838
60°	8175	6655	6577
65°	7789	6319	6275
70°	7349	5960	5953
75°	6791	5601	5646
80°	5908	5226	5331
85°	5015	4876	5058

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9138 cd/sqm

TEST NUMBER: P1009337

CATALOG NUMBER: S122DIP-B675D530UB50-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.5	1.5
10°-20°	185.1	4.2
20°-30°	280.5	6.3
30°-40°	341.6	7.7
40°-50°	367.5	8.3
50°-60°	356.9	8.1
60°-70°	311.7	7.1
70°-80°	239.9	5.4
80°-90°	162.5	3.7
90°-100°	151.1	3.4
100°-110°	209.0	4.7
110°-120°	272.5	6.2
120°-130°	317.9	7.2
130°-140°	335.9	7.6
140°-150°	319.3	7.2
150°-160°	266.0	6.0
160°-170°	176.4	4.0
170°-180°	61.7	1.4
0°-30°	530.2	12.0
0°-40°	871.7	19.7
0°-60°	1596.1	36.1
0°-90°	2310.2	52.3
90°-120°	632.6	14.3
90°-150°	1605.7	36.3
90°-180°	2110.0	47.7
0°-180°	4420.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	681	681	681	681	681	
5°	683	680	674	680	679	65
15°	651	653	653	662	661	183
25°	592	599	608	620	623	272
35°	510	527	546	567	574	319
45°	418	445	480	510	520	323
55°	321	356	408	443	456	287
65°	219	267	326	366	379	218
75°	121	177	240	282	295	128
85°	36	97	160	201	215	37
90°	10	74	150	188	200	9
95°	36	88	149	186	197	38
105°	123	153	206	241	252	130
115°	224	238	281	310	320	221
125°	322	327	357	382	390	288
135°	415	421	432	452	458	321
145°	502	506	509	516	518	314
155°	574	576	577	580	578	264
165°	625	624	624	628	625	176
175°	650	648	647	651	648	62
180°	651	651	651	651	651	

TEST NUMBER: P1009337

CATALOG NUMBER: S122DIP-B675D530UB50-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	680.9	680.9	680.9	680.9	680.9
2.5°	685.8	682.9	675.9	680.9	678.9
5°	682.9	679.9	674.0	679.9	678.9
7.5°	677.9	675.9	671.0	677.9	676.9
10°	672.0	670.0	667.1	675.0	674.0
12.5°	662.1	663.1	661.1	669.0	668.1
15°	651.3	653.3	653.3	662.1	661.1
17.5°	637.5	641.4	644.4	653.3	653.3
20°	623.6	628.6	632.5	643.4	643.4
22.5°	608.8	614.8	620.7	631.5	633.5
25°	592.1	599.0	607.9	619.7	622.7
27.5°	572.3	583.2	593.1	607.9	609.8
30°	552.6	565.4	578.3	594.0	597.0
32.5°	530.9	545.7	561.5	580.2	586.1
35°	510.2	526.9	545.7	567.4	574.3
37.5°	487.5	506.2	529.9	553.6	560.5
40°	464.8	486.5	513.1	538.8	547.7
42.5°	443.1	464.8	496.4	525.0	533.8
45°	418.4	445.0	479.6	510.2	520.0
47.5°	394.7	423.3	462.8	494.4	505.2
50°	370.0	400.6	445.0	478.6	489.4
52.5°	346.4	378.9	426.3	460.8	472.7
55°	320.7	356.2	407.5	443.1	455.9
57.5°	296.0	335.5	386.8	425.3	438.1
60°	269.4	311.8	368.1	405.6	419.4
62.5°	245.7	290.1	346.4	386.8	399.6
65°	219.1	267.4	325.6	366.1	378.9
67.5°	195.4	245.7	304.9	345.4	359.2
70°	169.7	221.0	282.2	324.7	336.5
72.5°	146.0	199.3	261.5	302.9	317.7
75°	121.4	176.6	239.8	282.2	295.0
77.5°	97.7	154.9	219.1	261.5	275.3
80°	74.0	134.2	198.3	239.8	253.6
82.5°	54.3	113.5	178.6	220.1	232.9
85°	35.5	96.7	159.9	201.3	215.1
87.5°	21.7	80.9	144.1	184.5	197.4
90°	10.4	74.2	149.5	187.8	200.3
92.5°	21.0	77.7	138.4	177.5	189.3
95°	36.5	88.4	148.7	186.2	196.9
97.5°	54.7	102.0	161.5	198.0	209.8
100°	76.7	117.6	174.5	211.0	221.3
102.5°	98.7	134.6	190.1	226.2	236.4
105°	123.0	153.4	205.8	241.4	252.3
107.5°	148.3	174.2	223.6	257.6	265.8
110°	171.5	194.6	242.9	274.5	283.7

TEST NUMBER: P1009337

CATALOG NUMBER: S122DIP-B675D530UB50-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	197.8	216.9	261.8	291.7	301.5
115°	223.7	237.9	281.2	310.2	319.5
117.5°	248.6	260.9	299.5	327.5	335.7
120°	274.4	282.7	317.8	345.4	354.7
122.5°	298.0	304.4	338.3	363.2	371.0
125°	321.7	326.7	356.6	381.6	389.9
127.5°	345.9	351.0	375.4	397.9	405.1
130°	368.4	374.6	394.2	416.8	422.5
132.5°	393.7	398.2	413.6	433.5	439.8
135°	414.7	420.7	431.7	451.9	458.1
137.5°	438.9	443.8	449.8	468.1	472.8
140°	460.3	464.2	469.0	484.8	488.5
142.5°	482.3	486.2	487.9	500.2	503.0
145°	502.1	506.0	509.3	515.7	518.5
147.5°	520.8	525.8	528.0	530.1	530.8
150°	540.1	543.3	545.5	547.2	545.5
152.5°	557.1	560.4	563.1	565.3	563.1
155°	574.1	575.8	577.4	580.2	578.5
157.5°	588.9	590.0	591.1	595.0	592.2
160°	602.1	603.2	603.8	607.1	604.9
162.5°	614.2	614.2	614.8	618.6	615.9
165°	624.7	624.1	624.1	628.0	625.2
167.5°	634.0	632.3	632.3	636.2	633.4
170°	641.1	639.5	638.9	642.8	639.5
172.5°	646.1	644.4	643.9	647.7	644.4
175°	649.9	648.3	647.2	651.0	647.7
177.5°	652.1	650.5	649.4	652.7	649.4
180°	651.0	651.0	651.0	651.0	651.0

(END OF REPORT)