

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009982

Luminaire Tested: S122RDIP-B485D330UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009982
REPORT IS A COMBINATION OF REPORTS P988262 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B485D330UB27-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2844.9 lumens
Efficiency: N/A
Efficacy: 85.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009982

CATALOG NUMBER: S122RDIP-B485D330UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1009982

CATALOG NUMBER: S122RDIP-B485D330UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	55
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	52	49	48
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	43	41
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	42	39	36
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	34	32
6	66	54	46	40	61	51	44	38	45	39	35	40	35	32	35	31	28
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23
9	53	41	34	29	50	39	32	27	35	29	25	31	26	23	27	23	21
10	50	38	31	26	46	36	29	25	32	27	23	29	24	21	25	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12899	12899	12899
5°	12920	12273	12182
10°	12793	11639	11256
15°	12618	10892	10200
20°	12385	10043	9096
25°	12147	9172	8087
30°	11827	8322	6983
35°	11513	7466	6036
40°	11194	6626	5061
45°	10824	5757	4210
50°	10441	4921	3427
55°	10043	4085	2721
60°	9577	3267	2059
65°	9044	2490	1673
70°	8402	1806	1330
75°	7591	1378	1016
80°	6419	933	681
85°	4478	427	329

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10824 cd/sqm

TEST NUMBER: P1009982

CATALOG NUMBER: S122RDIP-B485D330UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.4	2.7
10°-20°	209.7	7.4
20°-30°	294.4	10.3
30°-40°	320.9	11.3
40°-50°	294.9	10.4
50°-60°	231.6	8.1
60°-70°	150.7	5.3
70°-80°	77.6	2.7
80°-90°	21.0	0.7
90°-100°	25.8	0.9
100°-110°	82.1	2.9
110°-120°	140.6	4.9
120°-130°	184.8	6.5
130°-140°	207.5	7.3
140°-150°	203.5	7.2
150°-160°	170.7	6.0
160°-170°	113.2	4.0
170°-180°	39.6	1.4
0°-30°	580.4	20.4
0°-40°	901.3	31.7
0°-60°	1427.8	50.2
0°-90°	1677.2	59.0
90°-120°	248.5	8.7
90°-150°	844.4	29.7
90°-180°	1168.0	41.1
0°-180°	2844.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	815	815	815	815	815	
5°	815	811	802	808	806	77
15°	775	767	742	728	720	218
25°	704	680	631	601	590	324
35°	606	569	504	457	441	379
45°	496	446	369	316	299	383
55°	377	319	240	195	181	337
65°	254	195	128	103	101	252
75°	136	84	59	54	53	144
85°	32	16	14	14	14	36
90°	0	5	12	12	12	3
95°	18	22	23	23	22	20
105°	76	77	78	78	78	80
115°	141	143	142	142	141	139
125°	205	208	207	206	206	183
135°	265	269	270	270	269	205
145°	322	325	327	327	326	201
155°	368	369	370	372	371	170
165°	401	400	400	403	401	113
175°	417	416	415	418	416	40
180°	418	418	418	418	418	

TEST NUMBER: P1009982

CATALOG NUMBER: S122RDIP-B485D330UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	814.9	814.9	814.9	814.9	814.9
2.5°	818.6	814.9	806.8	814.2	812.7
5°	814.9	811.2	801.7	808.3	806.1
7.5°	808.3	803.9	793.5	796.5	792.8
10°	799.4	794.3	779.5	777.3	772.9
12.5°	788.4	781.7	761.8	757.4	749.3
15°	775.1	767.0	741.9	727.9	720.5
17.5°	759.6	747.8	716.8	700.6	688.8
20°	741.9	727.2	690.3	671.9	655.6
22.5°	722.7	705.8	663.0	637.9	626.9
25°	703.6	680.0	631.3	601.1	590.0
27.5°	680.7	655.6	601.8	567.1	550.2
30°	656.4	628.3	569.3	531.7	511.8
32.5°	632.8	598.8	538.4	494.1	475.7
35°	606.2	568.6	503.7	457.2	441.0
37.5°	580.4	539.8	471.3	420.4	401.9
40°	553.1	508.9	437.3	385.0	365.8
42.5°	525.1	477.9	403.4	348.8	330.4
45°	495.6	446.2	368.7	316.4	298.7
47.5°	467.6	415.2	335.6	283.2	267.0
50°	436.6	384.2	303.1	252.2	236.7
52.5°	406.4	351.0	272.1	223.5	209.4
55°	376.9	319.3	239.7	195.4	181.4
57.5°	346.6	287.6	210.9	169.6	157.8
60°	315.6	256.6	180.7	143.1	131.3
62.5°	285.4	226.4	154.9	119.5	113.6
65°	254.4	194.7	128.3	103.2	101.0
67.5°	224.9	165.2	103.2	90.7	88.5
70°	194.0	136.4	85.5	78.2	75.2
72.5°	164.5	109.9	71.5	65.6	64.2
75°	135.7	84.1	59.0	53.8	53.1
77.5°	106.9	59.7	46.5	43.5	42.0
80°	80.4	42.8	35.4	32.4	32.4
82.5°	56.0	28.8	24.3	22.9	22.9
85°	31.7	16.2	14.0	14.0	14.0
87.5°	11.8	5.9	5.9	5.2	5.2
90°	0.4	4.6	12.3	11.6	12.0
92.5°	7.8	10.6	10.9	11.3	11.3
95°	18.3	21.9	22.6	22.6	21.9
97.5°	30.7	33.8	35.2	35.2	35.2
100°	44.8	47.6	48.6	48.6	48.3
102.5°	59.6	61.7	63.1	63.4	63.1
105°	75.8	76.8	77.5	78.3	78.3
107.5°	92.0	93.4	93.4	93.8	92.0
110°	107.5	109.6	109.6	109.6	108.6

TEST NUMBER: P1009982

CATALOG NUMBER: S122RDIP-B485D330UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	124.4	126.5	126.2	125.1	124.4
115°	141.0	143.1	142.4	142.1	141.0
117.5°	157.6	160.4	158.6	157.6	156.5
120°	174.1	176.9	174.1	174.1	173.1
122.5°	189.3	192.8	191.0	190.0	189.3
125°	205.1	208.3	207.3	206.2	205.9
127.5°	220.7	224.5	223.1	221.7	220.7
130°	235.1	239.7	239.0	238.3	236.9
132.5°	251.3	254.9	255.2	253.4	252.4
135°	265.4	269.3	270.0	269.7	268.6
137.5°	280.9	284.1	284.8	284.5	283.0
140°	294.7	297.9	299.6	299.6	298.2
142.5°	308.8	312.0	313.0	313.4	312.0
145°	322.2	324.6	326.8	327.1	325.7
147.5°	334.2	337.3	338.7	339.4	338.0
150°	346.5	348.6	350.0	351.1	350.0
152.5°	357.4	359.5	361.3	362.7	361.3
155°	368.4	369.4	370.5	372.2	371.2
157.5°	377.9	378.6	379.3	381.7	380.0
160°	386.3	387.0	387.4	389.5	388.1
162.5°	394.1	394.1	394.4	396.9	395.1
165°	400.8	400.4	400.4	402.9	401.1
167.5°	406.8	405.7	405.7	408.2	406.4
170°	411.4	410.3	409.9	412.4	410.3
172.5°	414.5	413.5	413.1	415.6	413.5
175°	417.0	415.9	415.2	417.7	415.6
177.5°	418.4	417.3	416.6	418.8	416.6
180°	417.7	417.7	417.7	417.7	417.7

(END OF REPORT)