

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010012

Luminaire Tested: S122RDIP-B485D530UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010012
REPORT IS A COMBINATION OF REPORTS P988302 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B485D530UB27-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3555.0 lumens
Efficiency: N/A
Efficacy: 90.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010012

CATALOG NUMBER: S122RDIP-B485D530UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1010012

CATALOG NUMBER: S122RDIP-B485D530UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54	47	47	47
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41	41	41
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	40	35	35	35
3	82	73	66	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30	30	30
4	75	65	57	51	69	60	53	48	51	46	42	42	39	36	35	32	30	26	26	26
5	69	58	50	44	63	54	47	41	46	40	36	38	34	31	31	29	26	23	23	23
6	64	52	44	38	58	48	41	36	41	36	32	35	31	28	29	26	23	20	20	20
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	26	23	21	18	18	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	17	17	17
9	51	39	32	27	47	37	30	25	32	26	23	27	23	20	22	19	17	15	15	15
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	21	18	16	14	14	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12899	12899	12899
5°	12920	12273	12182
10°	12793	11639	11256
15°	12618	10892	10200
20°	12385	10043	9096
25°	12147	9172	8087
30°	11827	8322	6983
35°	11513	7466	6036
40°	11194	6626	5061
45°	10824	5757	4210
50°	10441	4921	3427
55°	10043	4085	2721
60°	9577	3267	2059
65°	9044	2490	1673
70°	8402	1806	1330
75°	7591	1378	1016
80°	6419	933	681
85°	4478	427	329

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10824 cd/sqm

TEST NUMBER: P1010012

CATALOG NUMBER: S122RDIP-B485D530UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.4	2.1
10°-20°	209.7	5.9
20°-30°	294.4	8.3
30°-40°	320.9	9.0
40°-50°	294.9	8.3
50°-60°	231.6	6.5
60°-70°	150.7	4.2
70°-80°	77.6	2.2
80°-90°	21.7	0.6
90°-100°	41.5	1.2
100°-110°	132.0	3.7
110°-120°	225.9	6.4
120°-130°	297.1	8.4
130°-140°	333.5	9.4
140°-150°	327.1	9.2
150°-160°	274.3	7.7
160°-170°	182.0	5.1
170°-180°	63.6	1.8
0°-30°	580.4	16.3
0°-40°	901.3	25.4
0°-60°	1427.8	40.2
0°-90°	1677.9	47.2
90°-120°	399.5	11.2
90°-150°	1357.2	38.2
90°-180°	1877.0	52.8
0°-180°	3555.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	815	815	815	815	815	
5°	815	811	802	808	806	77
15°	775	767	742	728	720	218
25°	704	680	631	601	590	324
35°	606	569	504	457	441	379
45°	496	446	369	316	299	383
55°	377	319	240	195	181	337
65°	254	195	128	103	101	252
75°	136	84	59	54	53	144
85°	32	16	14	14	14	36
90°	1	7	20	19	19	3
95°	30	35	36	36	35	33
105°	122	124	125	126	126	129
115°	227	230	229	228	227	224
125°	330	335	333	331	331	295
135°	427	433	434	433	432	330
145°	518	522	525	526	524	324
155°	592	594	596	598	597	273
165°	644	644	644	648	645	182
175°	670	669	667	671	668	64
180°	671	671	671	671	671	

TEST NUMBER: P1010012

CATALOG NUMBER: S122RDIP-B485D530UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	814.9	814.9	814.9	814.9	814.9
2.5°	818.6	814.9	806.8	814.2	812.7
5°	814.9	811.2	801.7	808.3	806.1
7.5°	808.3	803.9	793.5	796.5	792.8
10°	799.4	794.3	779.5	777.3	772.9
12.5°	788.4	781.7	761.8	757.4	749.3
15°	775.1	767.0	741.9	727.9	720.5
17.5°	759.6	747.8	716.8	700.6	688.8
20°	741.9	727.2	690.3	671.9	655.6
22.5°	722.7	705.8	663.0	637.9	626.9
25°	703.6	680.0	631.3	601.1	590.0
27.5°	680.7	655.6	601.8	567.1	550.2
30°	656.4	628.3	569.3	531.7	511.8
32.5°	632.8	598.8	538.4	494.1	475.7
35°	606.2	568.6	503.7	457.2	441.0
37.5°	580.4	539.8	471.3	420.4	401.9
40°	553.1	508.9	437.3	385.0	365.8
42.5°	525.1	477.9	403.4	348.8	330.4
45°	495.6	446.2	368.7	316.4	298.7
47.5°	467.6	415.2	335.6	283.2	267.0
50°	436.6	384.2	303.1	252.2	236.7
52.5°	406.4	351.0	272.1	223.5	209.4
55°	376.9	319.3	239.7	195.4	181.4
57.5°	346.6	287.6	210.9	169.6	157.8
60°	315.6	256.6	180.7	143.1	131.3
62.5°	285.4	226.4	154.9	119.5	113.6
65°	254.4	194.7	128.3	103.2	101.0
67.5°	224.9	165.2	103.2	90.7	88.5
70°	194.0	136.4	85.5	78.2	75.2
72.5°	164.5	109.9	71.5	65.6	64.2
75°	135.7	84.1	59.0	53.8	53.1
77.5°	106.9	59.7	46.5	43.5	42.0
80°	80.4	42.8	35.4	32.4	32.4
82.5°	56.0	28.8	24.3	22.9	22.9
85°	31.7	16.2	14.0	14.0	14.0
87.5°	11.8	5.9	5.9	5.2	5.2
90°	0.6	7.4	19.8	18.7	19.3
92.5°	12.5	17.0	17.6	18.1	18.1
95°	29.5	35.1	36.3	36.3	35.1
97.5°	49.3	54.4	56.7	56.7	56.7
100°	72.0	76.5	78.2	78.2	77.6
102.5°	95.8	99.2	101.4	102.0	101.4
105°	121.8	123.5	124.6	125.8	125.8
107.5°	147.9	150.1	150.1	150.7	147.9
110°	172.8	176.2	176.2	176.2	174.5

TEST NUMBER: P1010012

CATALOG NUMBER: S122RDIP-B485D530UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	200.0	203.4	202.8	201.1	200.0
115°	226.6	230.0	228.9	228.3	226.6
117.5°	253.3	257.8	255.0	253.3	251.6
120°	279.9	284.4	279.9	279.9	278.2
122.5°	304.3	309.9	307.1	305.4	304.3
125°	329.7	334.8	333.1	331.4	330.9
127.5°	354.7	360.9	358.6	356.4	354.7
130°	377.9	385.3	384.1	383.0	380.7
132.5°	404.0	409.6	410.2	407.4	405.7
135°	426.6	432.9	434.0	433.4	431.7
137.5°	451.6	456.7	457.8	457.2	455.0
140°	473.7	478.8	481.6	481.6	479.3
142.5°	496.3	501.4	503.1	503.7	501.4
145°	517.9	521.8	525.2	525.8	523.5
147.5°	537.1	542.2	544.5	545.6	543.3
150°	556.9	560.3	562.6	564.3	562.6
152.5°	574.5	577.9	580.7	583.0	580.7
155°	592.1	593.8	595.5	598.3	596.6
157.5°	607.4	608.5	609.6	613.6	610.8
160°	621.0	622.1	622.7	626.1	623.8
162.5°	633.4	633.4	634.0	638.0	635.1
165°	644.2	643.6	643.6	647.6	644.8
167.5°	653.8	652.1	652.1	656.1	653.3
170°	661.2	659.5	658.9	662.9	659.5
172.5°	666.3	664.6	664.0	668.0	664.6
175°	670.3	668.6	667.4	671.4	668.0
177.5°	672.5	670.8	669.7	673.1	669.7
180°	671.4	671.4	671.4	671.4	671.4

(END OF REPORT)