

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009340

Luminaire Tested: S122DIP-B675D530UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009340
REPORT IS A COMBINATION OF REPORTS P984596 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D530UB50-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4433.0 lumens
Efficiency: N/A
Efficacy: 86.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009340

CATALOG NUMBER: S122DIP-B675D530UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1009340

CATALOG NUMBER: S122DIP-B675D530UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	100	95	91	88	93	89	86	83	77	75	73	67	65	63	57	56	54
2	91	83	77	72	85	78	72	68	68	64	60	59	56	53	50	48	46
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	44	41	39
4	76	65	57	51	71	61	54	48	53	48	43	46	42	38	40	36	34
5	70	58	50	44	65	54	47	41	48	42	37	42	37	33	36	32	29
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	32	29	26
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23
8	55	43	35	29	51	40	33	28	36	30	26	31	27	23	27	23	21
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16246	16246	16246
5°	16272	15485	15375
10°	16139	14779	14486
15°	15903	14068	13550
20°	15583	13295	12665
25°	15265	12487	11780
30°	14865	11728	10853
35°	14487	10926	9941
40°	14020	10138	9078
45°	13556	9353	8234
50°	13050	8556	7357
55°	12516	7703	6527
60°	11916	6780	5664
65°	11262	5842	4757
70°	10428	4815	3841
75°	9275	3712	2965
80°	7880	2522	1909
85°	5721	1174	811

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13556 cd/sqm

TEST NUMBER: P1009340

CATALOG NUMBER: S122DIP-B675D530UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.6	2.2
10°-20°	271.8	6.1
20°-30°	399.4	9.0
30°-40°	463.9	10.5
40°-50°	463.3	10.5
50°-60°	404.0	9.1
60°-70°	298.6	6.7
70°-80°	169.0	3.8
80°-90°	46.4	1.0
90°-100°	40.3	0.9
100°-110°	128.0	2.9
110°-120°	219.1	4.9
120°-130°	288.1	6.5
130°-140°	323.4	7.3
140°-150°	317.1	7.2
150°-160°	266.0	6.0
160°-170°	176.4	4.0
170°-180°	61.7	1.4
0°-30°	767.7	17.3
0°-40°	1231.6	27.8
0°-60°	2098.9	47.3
0°-90°	2612.9	58.9
90°-120°	387.4	8.7
90°-150°	1316.0	29.7
90°-180°	1820.0	41.1
0°-180°	4433.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1026	1026	1026	1026	1026	
5°	1026	1022	1012	1019	1017	97
15°	977	971	958	962	957	275
25°	884	876	860	862	860	407
35°	763	753	737	731	726	476
45°	621	614	599	588	584	479
55°	470	464	452	440	435	420
65°	317	311	301	292	287	313
75°	166	164	159	153	155	177
85°	40	40	38	36	34	45
90°	0	7	19	18	19	4
95°	29	34	35	35	34	32
105°	118	120	121	122	122	125
115°	220	223	222	221	220	217
125°	320	325	323	321	321	286
135°	414	420	421	420	419	320
145°	502	506	509	510	508	314
155°	574	576	577	580	578	264
165°	625	624	624	628	625	176
175°	650	648	647	651	648	62
180°	651	651	651	651	651	

TEST NUMBER: P1009340

CATALOG NUMBER: S122DIP-B675D530UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1026.3	1026.3	1026.3	1026.3	1026.3
2.5°	1032.2	1027.3	1016.4	1026.3	1024.3
5°	1026.3	1022.3	1011.5	1019.4	1017.4
7.5°	1019.4	1013.4	1002.6	1010.5	1008.5
10°	1008.5	1001.6	989.8	997.7	994.7
12.5°	993.7	987.8	975.9	980.9	978.9
15°	976.9	971.0	958.2	962.1	957.2
17.5°	956.2	950.3	937.5	942.4	937.5
20°	933.5	927.6	913.8	916.7	912.8
22.5°	910.8	901.9	889.1	889.1	887.1
25°	884.2	876.3	859.5	861.5	859.5
27.5°	854.6	847.7	834.8	831.9	826.9
30°	825.0	817.1	802.3	799.3	795.4
32.5°	793.4	787.5	771.7	765.8	761.8
35°	762.8	752.9	737.1	731.2	726.3
37.5°	728.3	719.4	703.6	696.7	691.7
40°	692.7	684.8	669.1	660.2	656.2
42.5°	658.2	650.3	634.5	624.6	618.7
45°	620.7	613.8	599.0	588.1	584.2
47.5°	584.2	577.3	561.5	550.6	544.7
50°	545.7	540.8	527.0	513.1	508.2
52.5°	508.2	501.3	488.5	477.6	470.7
55°	469.7	463.8	452.0	440.1	435.2
57.5°	431.2	426.3	413.5	401.6	397.7
60°	392.7	388.8	375.0	364.1	361.2
62.5°	355.2	348.3	338.5	328.6	324.7
65°	316.8	310.8	301.0	292.1	287.2
67.5°	277.3	272.4	263.5	256.6	252.6
70°	240.8	236.8	228.0	221.0	217.1
72.5°	203.3	199.3	194.4	187.5	184.5
75°	165.8	163.8	158.9	153.0	154.9
77.5°	132.2	128.3	126.3	123.3	120.4
80°	98.7	97.7	95.7	92.8	90.8
82.5°	67.1	67.1	66.1	62.2	62.2
85°	40.5	39.5	38.5	35.5	34.5
87.5°	17.8	15.8	13.8	10.9	9.9
90°	0.5	7.1	19.2	18.1	18.7
92.5°	12.1	16.5	17.0	17.6	17.6
95°	28.6	34.1	35.2	35.2	34.1
97.5°	47.8	52.7	54.9	54.9	54.9
100°	69.8	74.2	75.8	75.8	75.3
102.5°	92.8	96.1	98.3	98.9	98.3
105°	118.1	119.8	120.9	122.0	122.0
107.5°	143.4	145.6	145.6	146.1	143.4
110°	167.6	170.9	170.9	170.9	169.2

TEST NUMBER: P1009340

CATALOG NUMBER: S122DIP-B675D530UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	193.9	197.2	196.7	195.0	193.9
115°	219.8	223.1	222.0	221.4	219.8
117.5°	245.6	250.0	247.2	245.6	243.9
120°	271.4	275.8	271.4	271.4	269.8
122.5°	295.0	300.5	297.8	296.1	295.0
125°	319.7	324.7	323.0	321.4	320.8
127.5°	343.9	350.0	347.8	345.6	343.9
130°	366.4	373.6	372.5	371.4	369.2
132.5°	391.7	397.2	397.8	395.0	393.4
135°	413.7	419.7	420.8	420.3	418.6
137.5°	437.9	442.8	443.9	443.4	441.2
140°	459.3	464.2	467.0	467.0	464.8
142.5°	481.3	486.2	487.9	488.4	486.2
145°	502.1	506.0	509.3	509.8	507.6
147.5°	520.8	525.8	528.0	529.1	526.9
150°	540.1	543.3	545.5	547.2	545.5
152.5°	557.1	560.4	563.1	565.3	563.1
155°	574.1	575.8	577.4	580.2	578.5
157.5°	588.9	590.0	591.1	595.0	592.2
160°	602.1	603.2	603.8	607.1	604.9
162.5°	614.2	614.2	614.8	618.6	615.9
165°	624.7	624.1	624.1	628.0	625.2
167.5°	634.0	632.3	632.3	636.2	633.4
170°	641.1	639.5	638.9	642.8	639.5
172.5°	646.1	644.4	643.9	647.7	644.4
175°	649.9	648.3	647.2	651.0	647.7
177.5°	652.1	650.5	649.4	652.7	649.4
180°	651.0	651.0	651.0	651.0	651.0

(END OF REPORT)