

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009368

Luminaire Tested: S122DIP-B675D725UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009368
REPORT IS A COMBINATION OF REPORTS P984639 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D725UB35-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5509.2 lumens
Efficiency: N/A
Efficacy: 96.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009368

CATALOG NUMBER: S122DIP-B675D725UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1009368

CATALOG NUMBER: S122DIP-B675D725UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	89	86	90	86	83	80	73	70	68	61	59	57	49	48	47
2	89	82	75	70	82	75	70	66	64	60	56	53	50	48	43	41	40
3	81	72	64	58	75	66	60	55	56	51	47	47	43	40	38	36	34
4	74	63	56	49	68	59	52	46	50	45	40	42	38	35	34	31	29
5	68	57	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25
6	63	51	43	37	58	47	40	35	40	35	30	34	30	26	28	25	22
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	22	20
8	54	42	34	28	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	18	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16967	16967	16967
5°	16995	16172	16058
10°	16856	15435	15129
15°	16609	14694	14152
20°	16276	13886	13227
25°	15944	13042	12304
30°	15524	12249	11334
35°	15131	11412	10383
40°	14643	10587	9482
45°	14159	9769	8599
50°	13628	8936	7684
55°	13073	8044	6817
60°	12447	7080	5915
65°	11760	6100	4967
70°	10892	5029	4010
75°	9683	3875	3097
80°	8231	2635	1993
85°	5975	1226	849

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14159 cd/sqm

TEST NUMBER: P1009368

CATALOG NUMBER: S122DIP-B675D725UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.9	1.8
10°-20°	283.8	5.2
20°-30°	417.1	7.6
30°-40°	484.5	8.8
40°-50°	483.9	8.8
50°-60°	421.9	7.7
60°-70°	311.9	5.7
70°-80°	176.5	3.2
80°-90°	49.1	0.9
90°-100°	161.6	2.9
100°-110°	546.4	9.9
110°-120°	574.3	10.4
120°-130°	472.3	8.6
130°-140°	379.5	6.9
140°-150°	286.7	5.2
150°-160°	201.6	3.7
160°-170°	118.7	2.2
170°-180°	38.6	0.7
0°-30°	801.8	14.6
0°-40°	1286.3	23.3
0°-60°	2192.1	39.8
0°-90°	2729.5	49.5
90°-120°	1282.3	23.3
90°-150°	2420.8	43.9
90°-180°	2780.0	50.5
0°-180°	5509.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1072	1072	1072	1072	1072	
5°	1072	1068	1056	1065	1063	102
15°	1020	1014	1001	1005	1000	287
25°	924	915	898	900	898	425
35°	797	786	770	764	759	497
45°	648	641	626	614	610	500
55°	491	484	472	460	454	439
65°	331	325	314	305	300	327
75°	173	171	166	160	162	185
85°	42	41	40	37	36	47
90°	1	10	26	25	25	4
95°	27	66	300	113	87	28
105°	94	141	568	1015	864	99
115°	165	208	475	981	1137	163
125°	230	272	457	795	922	204
135°	270	322	452	668	764	208
145°	308	354	449	558	610	193
155°	350	378	436	493	513	161
165°	382	393	418	443	450	108
175°	398	398	402	407	406	38
180°	399	399	399	399	399	

TEST NUMBER: P1009368

CATALOG NUMBER: S122DIP-B675D725UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1071.9	1071.9	1071.9	1071.9	1071.9
2.5°	1078.1	1072.9	1061.6	1071.9	1069.8
5°	1071.9	1067.7	1056.4	1064.7	1062.6
7.5°	1064.7	1058.5	1047.1	1055.4	1053.3
10°	1053.3	1046.1	1033.7	1042.0	1038.9
12.5°	1037.9	1031.7	1019.3	1024.5	1022.4
15°	1020.3	1014.2	1000.8	1004.9	999.7
17.5°	998.7	992.5	979.1	984.3	979.1
20°	975.0	968.8	954.4	957.5	953.3
22.5°	951.3	942.0	928.6	928.6	926.5
25°	923.5	915.2	897.7	899.7	897.7
27.5°	892.5	885.3	871.9	868.8	863.7
30°	861.6	853.4	837.9	834.8	830.7
32.5°	828.6	822.5	806.0	799.8	795.7
35°	796.7	786.4	769.9	763.7	758.6
37.5°	760.6	751.3	734.8	727.6	722.5
40°	723.5	715.3	698.8	689.5	685.4
42.5°	687.4	679.2	662.7	652.4	646.2
45°	648.3	641.1	625.6	614.3	610.1
47.5°	610.1	602.9	586.4	575.1	568.9
50°	569.9	564.8	550.4	535.9	530.8
52.5°	530.8	523.6	510.2	498.8	491.6
55°	490.6	484.4	472.0	459.7	454.5
57.5°	450.4	445.2	431.8	419.5	415.3
60°	410.2	406.1	391.6	380.3	377.2
62.5°	371.0	363.8	353.5	343.2	339.1
65°	330.8	324.7	314.3	305.1	299.9
67.5°	289.6	284.5	275.2	268.0	263.8
70°	251.5	247.4	238.1	230.9	226.7
72.5°	212.3	208.2	203.0	195.8	192.7
75°	173.1	171.1	165.9	159.7	161.8
77.5°	138.1	134.0	131.9	128.8	125.7
80°	103.1	102.0	100.0	96.9	94.8
82.5°	70.1	70.1	69.1	64.9	64.9
85°	42.3	41.2	40.2	37.1	36.1
87.5°	18.6	16.5	14.4	11.3	10.3
90°	0.8	10.4	26.1	24.9	25.3
92.5°	11.5	36.4	118.1	54.4	46.8
95°	26.8	65.9	300.5	113.4	87.4
97.5°	39.9	87.1	489.9	227.7	146.4
100°	59.0	106.6	605.7	453.5	274.5
102.5°	76.7	124.2	609.5	766.7	535.2
105°	93.5	141.0	568.1	1015.4	864.1
107.5°	111.9	158.0	529.8	1105.6	1085.6
110°	130.3	175.2	503.7	1091.0	1176.1

TEST NUMBER: P1009368

CATALOG NUMBER: S122DIP-B675D725UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	147.2	191.7	486.9	1041.6	1174.6
115°	164.8	208.2	475.4	981.0	1137.0
117.5°	183.2	224.6	469.2	923.1	1080.3
120°	200.1	240.8	463.9	871.4	1025.8
122.5°	216.2	257.2	460.8	831.1	969.1
125°	230.0	272.2	457.0	794.6	922.3
127.5°	241.5	286.4	454.7	763.6	878.6
130°	251.5	299.0	453.1	732.2	842.6
132.5°	260.7	311.2	452.4	699.6	805.0
135°	269.9	322.0	451.6	667.8	764.4
137.5°	278.3	331.2	451.6	635.6	725.3
140°	288.3	339.6	450.8	607.2	684.7
142.5°	298.2	346.5	450.8	580.0	644.0
145°	308.2	354.2	449.3	557.8	610.3
147.5°	318.9	360.4	447.0	538.2	580.4
150°	329.7	366.5	444.7	521.4	554.3
152.5°	340.4	372.6	440.9	507.2	532.1
155°	350.4	378.4	436.3	493.4	512.9
157.5°	358.8	383.0	431.7	480.4	496.1
160°	367.2	387.6	427.1	467.3	480.0
162.5°	375.7	391.0	423.2	455.0	464.6
165°	381.8	393.3	417.9	443.2	450.1
167.5°	387.2	395.6	413.3	432.4	436.3
170°	392.5	396.8	409.4	422.4	424.0
172.5°	395.6	397.9	404.8	413.6	414.0
175°	397.9	398.3	401.7	406.7	405.6
177.5°	399.4	398.7	398.7	401.7	399.4
180°	398.7	398.7	398.7	398.7	398.7

(END OF REPORT)