

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009377

Luminaire Tested: S122DIP-B675D725UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009377
REPORT IS A COMBINATION OF REPORTS P984648 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D725UB40-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5455.1 lumens
Efficiency: N/A
Efficacy: 95.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009377

CATALOG NUMBER: S122DIP-B675D725UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1009377

CATALOG NUMBER: S122DIP-B675D725UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	89	86	90	86	83	80	73	70	68	61	59	57	49	48	47
2	89	82	75	70	82	75	70	66	64	60	56	53	50	48	43	41	40
3	81	72	64	58	75	66	60	55	56	51	47	47	43	40	38	36	34
4	74	63	56	49	68	59	52	46	50	45	40	42	38	35	34	31	29
5	68	57	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25
6	63	51	43	37	58	47	40	35	40	35	30	34	30	26	28	25	22
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	22	20
8	54	42	34	28	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	18	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16800	16800	16800
5°	16827	16012	15899
10°	16689	15283	14979
15°	16445	14547	14012
20°	16114	13747	13096
25°	15785	12913	12182
30°	15371	12127	11222
35°	14981	11300	10279
40°	14497	10483	9388
45°	14019	9672	8515
50°	13494	8847	7608
55°	12942	7966	6749
60°	12323	7011	5857
65°	11646	6040	4917
70°	10783	4978	3972
75°	9588	3838	3066
80°	8143	2609	1974
85°	5905	1214	839

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14019 cd/sqm

TEST NUMBER: P1009377

CATALOG NUMBER: S122DIP-B675D725UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.9	1.8
10°-20°	281.0	5.2
20°-30°	413.0	7.6
30°-40°	479.7	8.8
40°-50°	479.1	8.8
50°-60°	417.7	7.7
60°-70°	308.8	5.7
70°-80°	174.7	3.2
80°-90°	48.6	0.9
90°-100°	160.1	2.9
100°-110°	541.1	9.9
110°-120°	568.7	10.4
120°-130°	467.7	8.6
130°-140°	375.8	6.9
140°-150°	283.9	5.2
150°-160°	199.6	3.7
160°-170°	117.5	2.2
170°-180°	38.2	0.7
0°-30°	793.9	14.6
0°-40°	1273.6	23.3
0°-60°	2170.4	39.8
0°-90°	2702.5	49.5
90°-120°	1269.9	23.3
90°-150°	2397.3	43.9
90°-180°	2753.0	50.5
0°-180°	5455.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1061	1061	1061	1061	1061	
5°	1061	1057	1046	1054	1052	101
15°	1010	1004	991	995	990	285
25°	914	906	889	891	889	421
35°	789	779	762	756	751	493
45°	642	635	619	608	604	495
55°	486	480	467	455	450	434
65°	328	321	311	302	297	324
75°	171	169	164	158	160	183
85°	42	41	40	37	36	47
90°	1	10	26	25	25	4
95°	27	65	298	112	87	27
105°	93	140	563	1006	856	98
115°	163	206	471	972	1126	162
125°	228	270	452	787	913	202
135°	267	319	447	661	757	206
145°	305	351	445	552	604	191
155°	347	375	432	489	508	160
165°	378	390	414	439	446	107
175°	394	394	398	403	402	37
180°	395	395	395	395	395	

TEST NUMBER: P1009377

CATALOG NUMBER: S122DIP-B675D725UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1067.4	1062.3	1051.0	1061.3	1059.2
5°	1061.3	1057.2	1045.9	1054.1	1052.1
7.5°	1054.1	1048.0	1036.8	1044.9	1042.9
10°	1042.9	1035.7	1023.5	1031.7	1028.6
12.5°	1027.6	1021.5	1009.2	1014.3	1012.3
15°	1010.2	1004.1	990.8	994.9	989.8
17.5°	988.8	982.7	969.4	974.5	969.4
20°	965.3	959.2	944.9	948.0	943.9
22.5°	941.9	932.7	919.4	919.4	917.4
25°	914.3	906.1	888.8	890.8	888.8
27.5°	883.7	876.6	863.3	860.2	855.1
30°	853.1	844.9	829.6	826.6	822.5
32.5°	820.4	814.3	798.0	791.9	787.8
35°	788.8	778.6	762.3	756.1	751.0
37.5°	753.1	743.9	727.6	720.4	715.3
40°	716.3	708.2	691.9	682.7	678.6
42.5°	680.6	672.5	656.1	645.9	639.8
45°	641.9	634.7	619.4	608.2	604.1
47.5°	604.1	597.0	580.6	569.4	563.3
50°	564.3	559.2	544.9	530.6	525.5
52.5°	525.5	518.4	505.1	493.9	486.7
55°	485.7	479.6	467.4	455.1	450.0
57.5°	445.9	440.8	427.6	415.3	411.2
60°	406.1	402.1	387.8	376.5	373.5
62.5°	367.4	360.2	350.0	339.8	335.7
65°	327.6	321.4	311.2	302.0	296.9
67.5°	286.7	281.6	272.5	265.3	261.2
70°	249.0	244.9	235.7	228.6	224.5
72.5°	210.2	206.1	201.0	193.9	190.8
75°	171.4	169.4	164.3	158.2	160.2
77.5°	136.7	132.7	130.6	127.6	124.5
80°	102.0	101.0	99.0	95.9	93.9
82.5°	69.4	69.4	68.4	64.3	64.3
85°	41.8	40.8	39.8	36.7	35.7
87.5°	18.4	16.3	14.3	11.2	10.2
90°	0.8	10.2	25.8	24.7	25.1
92.5°	11.4	36.0	116.9	53.9	46.3
95°	26.6	65.3	297.6	112.4	86.6
97.5°	39.5	86.2	485.2	225.5	145.0
100°	58.5	105.6	599.8	449.1	271.8
102.5°	75.9	123.0	603.6	759.2	530.0
105°	92.6	139.7	562.6	1005.6	855.7
107.5°	110.9	156.4	524.6	1094.8	1075.1
110°	129.1	173.5	498.8	1080.4	1164.7

TEST NUMBER: P1009377

CATALOG NUMBER: S122DIP-B675D725UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	145.8	189.8	482.1	1031.4	1163.2
115°	163.2	206.2	470.7	971.5	1126.0
117.5°	181.5	222.4	464.7	914.1	1069.8
120°	198.2	238.4	459.3	862.8	1015.9
122.5°	214.1	254.7	456.3	823.0	959.7
125°	227.8	269.5	452.5	787.0	913.4
127.5°	239.2	283.6	450.2	756.2	870.1
130°	249.0	296.1	448.7	725.0	834.4
132.5°	258.1	308.2	448.0	692.8	797.2
135°	267.3	318.9	447.2	661.3	757.0
137.5°	275.6	328.0	447.2	629.4	718.2
140°	285.5	336.4	446.4	601.3	678.0
142.5°	295.3	343.2	446.4	574.4	637.8
145°	305.2	350.8	444.9	552.3	604.4
147.5°	315.8	356.8	442.6	533.0	574.8
150°	326.5	363.0	440.4	516.3	548.9
152.5°	337.1	369.0	436.6	502.2	526.9
155°	347.0	374.7	432.0	488.6	507.9
157.5°	355.3	379.2	427.5	475.7	491.2
160°	363.7	383.8	422.9	462.8	475.3
162.5°	372.0	387.2	419.1	450.6	460.1
165°	378.1	389.5	413.8	438.8	445.7
167.5°	383.4	391.8	409.2	428.2	432.0
170°	388.7	393.0	405.4	418.4	419.9
172.5°	391.8	394.0	400.9	409.6	410.0
175°	394.1	394.5	397.8	402.8	401.6
177.5°	395.6	394.8	394.8	397.8	395.6
180°	394.8	394.8	394.8	394.8	394.8

(END OF REPORT)