

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009385

Luminaire Tested: S122DIP-B675D725UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009385
REPORT IS A COMBINATION OF REPORTS P984656 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D725UB50-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5045.1 lumens
Efficiency: N/A
Efficacy: 88.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009385

CATALOG NUMBER: S122DIP-B675D725UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1009385

CATALOG NUMBER: S122DIP-B675D725UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	108	108	108	108	99	99	99	99	84	84	84		70	70	70		58
1	98	94	90	86	91	87	84	81	74	72	69		62	60	59		51
2	89	82	76	71	82	76	71	66	65	61	57		54	52	49		45
3	82	72	65	59	75	67	60	55	57	52	48		48	45	41		40
4	75	64	56	50	69	59	52	47	51	45	41		43	39	36		36
5	69	57	49	43	63	53	46	40	45	40	35		39	34	31		32
6	63	51	43	37	58	48	40	35	41	35	31		35	30	27		29
7	58	46	38	32	54	43	36	31	37	31	27		32	27	24		27
8	54	42	34	29	50	39	32	27	34	28	24		29	25	21		24
9	50	38	31	26	47	36	29	24	31	26	22		27	22	19		23
10	47	35	28	23	44	33	26	22	29	23	20		25	20	17		21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16246	16246	16246
5°	16272	15485	15375
10°	16139	14779	14486
15°	15903	14068	13550
20°	15583	13295	12665
25°	15265	12487	11780
30°	14865	11728	10853
35°	14487	10926	9941
40°	14020	10138	9078
45°	13556	9353	8234
50°	13050	8556	7357
55°	12516	7703	6527
60°	11916	6780	5664
65°	11262	5842	4757
70°	10428	4815	3841
75°	9275	3712	2965
80°	7880	2522	1909
85°	5721	1174	811

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13556 cd/sqm

TEST NUMBER: P1009385

CATALOG NUMBER: S122DIP-B675D725UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.6	1.9
10°-20°	271.8	5.4
20°-30°	399.4	7.9
30°-40°	463.9	9.2
40°-50°	463.3	9.2
50°-60°	404.0	8.0
60°-70°	298.6	5.9
70°-80°	169.0	3.3
80°-90°	47.1	0.9
90°-100°	53.8	1.1
100°-110°	171.0	3.4
110°-120°	292.7	5.8
120°-130°	384.9	7.6
130°-140°	432.0	8.6
140°-150°	423.7	8.4
150°-160°	355.4	7.0
160°-170°	235.7	4.7
170°-180°	82.4	1.6
0°-30°	767.7	15.2
0°-40°	1231.6	24.4
0°-60°	2098.9	41.6
0°-90°	2613.5	51.8
90°-120°	517.5	10.3
90°-150°	1758.1	34.8
90°-180°	2432.0	48.2
0°-180°	5045.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1026	1026	1026	1026	1026	
5°	1026	1022	1012	1019	1017	97
15°	977	971	958	962	957	275
25°	884	876	860	862	860	407
35°	763	753	737	731	726	476
45°	621	614	599	588	584	479
55°	470	464	452	440	435	420
65°	317	311	301	292	287	313
75°	166	164	159	153	155	177
85°	40	40	38	36	34	45
90°	1	10	26	24	25	5
95°	38	46	47	47	46	43
105°	158	160	162	163	163	167
115°	294	298	296	296	294	290
125°	427	434	432	429	429	382
135°	553	561	562	562	559	427
145°	671	676	680	681	678	419
155°	767	769	771	775	773	353
165°	834	834	834	839	835	235
175°	868	866	865	870	865	82
180°	870	870	870	870	870	

TEST NUMBER: P1009385

CATALOG NUMBER: S122DIP-B675D725UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1026.3	1026.3	1026.3	1026.3	1026.3
2.5°	1032.2	1027.3	1016.4	1026.3	1024.3
5°	1026.3	1022.3	1011.5	1019.4	1017.4
7.5°	1019.4	1013.4	1002.6	1010.5	1008.5
10°	1008.5	1001.6	989.8	997.7	994.7
12.5°	993.7	987.8	975.9	980.9	978.9
15°	976.9	971.0	958.2	962.1	957.2
17.5°	956.2	950.3	937.5	942.4	937.5
20°	933.5	927.6	913.8	916.7	912.8
22.5°	910.8	901.9	889.1	889.1	887.1
25°	884.2	876.3	859.5	861.5	859.5
27.5°	854.6	847.7	834.8	831.9	826.9
30°	825.0	817.1	802.3	799.3	795.4
32.5°	793.4	787.5	771.7	765.8	761.8
35°	762.8	752.9	737.1	731.2	726.3
37.5°	728.3	719.4	703.6	696.7	691.7
40°	692.7	684.8	669.1	660.2	656.2
42.5°	658.2	650.3	634.5	624.6	618.7
45°	620.7	613.8	599.0	588.1	584.2
47.5°	584.2	577.3	561.5	550.6	544.7
50°	545.7	540.8	527.0	513.1	508.2
52.5°	508.2	501.3	488.5	477.6	470.7
55°	469.7	463.8	452.0	440.1	435.2
57.5°	431.2	426.3	413.5	401.6	397.7
60°	392.7	388.8	375.0	364.1	361.2
62.5°	355.2	348.3	338.5	328.6	324.7
65°	316.8	310.8	301.0	292.1	287.2
67.5°	277.3	272.4	263.5	256.6	252.6
70°	240.8	236.8	228.0	221.0	217.1
72.5°	203.3	199.3	194.4	187.5	184.5
75°	165.8	163.8	158.9	153.0	154.9
77.5°	132.2	128.3	126.3	123.3	120.4
80°	98.7	97.7	95.7	92.8	90.8
82.5°	67.1	67.1	66.1	62.2	62.2
85°	40.5	39.5	38.5	35.5	34.5
87.5°	17.8	15.8	13.8	10.9	9.9
90°	0.7	9.5	25.7	24.2	25.0
92.5°	16.1	22.0	22.8	23.5	23.5
95°	38.2	45.5	47.0	47.0	45.5
97.5°	63.9	70.5	73.4	73.4	73.4
100°	93.2	99.1	101.3	101.3	100.5
102.5°	124.0	128.4	131.4	132.1	131.4
105°	157.8	160.0	161.5	162.9	162.9
107.5°	191.6	194.5	194.5	195.2	191.6
110°	223.8	228.3	228.3	228.3	226.0



TEST NUMBER: P1009385

CATALOG NUMBER: S122DIP-B675D725UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	259.1	263.5	262.7	260.5	259.1
115°	293.6	298.0	296.5	295.8	293.6
117.5°	328.1	333.9	330.3	328.1	325.9
120°	362.6	368.4	362.6	362.6	360.4
122.5°	394.1	401.5	397.8	395.6	394.1
125°	427.1	433.8	431.5	429.3	428.6
127.5°	459.4	467.5	464.6	461.6	459.4
130°	489.5	499.1	497.6	496.1	493.2
132.5°	523.3	530.6	531.4	527.7	525.5
135°	552.6	560.7	562.2	561.5	559.3
137.5°	584.9	591.5	593.0	592.3	589.3
140°	613.6	620.2	623.8	623.8	620.9
142.5°	642.9	649.5	651.7	652.5	649.5
145°	670.8	675.9	680.4	681.1	678.1
147.5°	695.8	702.4	705.3	706.8	703.8
150°	721.4	725.9	728.8	731.0	728.8
152.5°	744.2	748.6	752.3	755.2	752.3
155°	767.0	769.2	771.4	775.0	772.8
157.5°	786.8	788.2	789.7	794.8	791.2
160°	804.4	805.9	806.6	811.0	808.1
162.5°	820.5	820.5	821.3	826.4	822.7
165°	834.5	833.7	833.7	838.9	835.2
167.5°	847.0	844.7	844.7	849.9	846.2
170°	856.5	854.3	853.6	858.7	854.3
172.5°	863.1	860.9	860.2	865.3	860.9
175°	868.2	866.0	864.6	869.7	865.3
177.5°	871.2	869.0	867.5	871.9	867.5
180°	869.7	869.7	869.7	869.7	869.7

(END OF REPORT)