

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009386

Luminaire Tested: S122DIP-B675D725UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009386
REPORT IS A COMBINATION OF REPORTS P984657 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D725UB50-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5275.0 lumens
Efficiency: N/A
Efficacy: 92.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009386

CATALOG NUMBER: S122DIP-B675D725UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1009386

CATALOG NUMBER: S122DIP-B675D725UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	89	86	90	86	83	80	73	70	68	61	59	57	49	48	47
2	89	82	75	70	82	75	70	66	64	60	56	53	50	48	43	41	40
3	81	72	64	58	75	66	60	55	56	51	47	47	43	40	38	36	34
4	74	63	56	49	68	59	52	46	50	45	40	42	38	35	34	31	29
5	68	57	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25
6	63	51	43	37	58	47	40	35	40	35	30	34	30	26	28	25	22
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	22	20
8	54	42	34	28	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	18	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16246	16246	16246
5°	16272	15485	15375
10°	16139	14779	14486
15°	15903	14068	13550
20°	15583	13295	12665
25°	15265	12487	11780
30°	14865	11728	10853
35°	14487	10926	9941
40°	14020	10138	9078
45°	13556	9353	8234
50°	13050	8556	7357
55°	12516	7703	6527
60°	11916	6780	5664
65°	11262	5842	4757
70°	10428	4815	3841
75°	9275	3712	2965
80°	7880	2522	1909
85°	5721	1174	811

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13556 cd/sqm

TEST NUMBER: P1009386

CATALOG NUMBER: S122DIP-B675D725UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.6	1.8
10°-20°	271.8	5.2
20°-30°	399.4	7.6
30°-40°	463.9	8.8
40°-50°	463.3	8.8
50°-60°	404.0	7.7
60°-70°	298.6	5.7
70°-80°	169.0	3.2
80°-90°	47.0	0.9
90°-100°	154.7	2.9
100°-110°	523.2	9.9
110°-120°	549.9	10.4
120°-130°	452.2	8.6
130°-140°	363.4	6.9
140°-150°	274.5	5.2
150°-160°	193.0	3.7
160°-170°	113.6	2.2
170°-180°	37.0	0.7
0°-30°	767.7	14.6
0°-40°	1231.6	23.3
0°-60°	2098.9	39.8
0°-90°	2613.5	49.5
90°-120°	1227.9	23.3
90°-150°	2318.0	43.9
90°-180°	2662.0	50.5
0°-180°	5275.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1026	1026	1026	1026	1026	
5°	1026	1022	1012	1019	1017	97
15°	977	971	958	962	957	275
25°	884	876	860	862	860	407
35°	763	753	737	731	726	476
45°	621	614	599	588	584	479
55°	470	464	452	440	435	420
65°	317	311	301	292	287	313
75°	166	164	159	153	155	177
85°	40	40	38	36	34	45
90°	1	10	25	24	24	4
95°	26	63	288	109	84	27
105°	90	135	544	972	827	95
115°	158	199	455	939	1089	157
125°	220	261	438	761	883	196
135°	258	308	432	639	732	200
145°	295	339	430	534	584	185
155°	336	362	418	472	491	154
165°	366	377	400	424	431	103
175°	381	381	385	390	388	36
180°	382	382	382	382	382	

TEST NUMBER: P1009386

CATALOG NUMBER: S122DIP-B675D725UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1026.3	1026.3	1026.3	1026.3	1026.3
2.5°	1032.2	1027.3	1016.4	1026.3	1024.3
5°	1026.3	1022.3	1011.5	1019.4	1017.4
7.5°	1019.4	1013.4	1002.6	1010.5	1008.5
10°	1008.5	1001.6	989.8	997.7	994.7
12.5°	993.7	987.8	975.9	980.9	978.9
15°	976.9	971.0	958.2	962.1	957.2
17.5°	956.2	950.3	937.5	942.4	937.5
20°	933.5	927.6	913.8	916.7	912.8
22.5°	910.8	901.9	889.1	889.1	887.1
25°	884.2	876.3	859.5	861.5	859.5
27.5°	854.6	847.7	834.8	831.9	826.9
30°	825.0	817.1	802.3	799.3	795.4
32.5°	793.4	787.5	771.7	765.8	761.8
35°	762.8	752.9	737.1	731.2	726.3
37.5°	728.3	719.4	703.6	696.7	691.7
40°	692.7	684.8	669.1	660.2	656.2
42.5°	658.2	650.3	634.5	624.6	618.7
45°	620.7	613.8	599.0	588.1	584.2
47.5°	584.2	577.3	561.5	550.6	544.7
50°	545.7	540.8	527.0	513.1	508.2
52.5°	508.2	501.3	488.5	477.6	470.7
55°	469.7	463.8	452.0	440.1	435.2
57.5°	431.2	426.3	413.5	401.6	397.7
60°	392.7	388.8	375.0	364.1	361.2
62.5°	355.2	348.3	338.5	328.6	324.7
65°	316.8	310.8	301.0	292.1	287.2
67.5°	277.3	272.4	263.5	256.6	252.6
70°	240.8	236.8	228.0	221.0	217.1
72.5°	203.3	199.3	194.4	187.5	184.5
75°	165.8	163.8	158.9	153.0	154.9
77.5°	132.2	128.3	126.3	123.3	120.4
80°	98.7	97.7	95.7	92.8	90.8
82.5°	67.1	67.1	66.1	62.2	62.2
85°	40.5	39.5	38.5	35.5	34.5
87.5°	17.8	15.8	13.8	10.9	9.9
90°	0.7	9.9	25.0	23.8	24.2
92.5°	11.0	34.8	113.1	52.2	44.8
95°	25.7	63.1	287.8	108.6	83.7
97.5°	38.2	83.3	469.1	218.0	140.2
100°	56.5	102.0	580.0	434.2	262.8
102.5°	73.4	119.0	583.6	734.2	512.4
105°	89.6	135.1	544.0	972.4	827.4
107.5°	107.2	151.2	507.3	1058.6	1039.5
110°	124.8	167.8	482.3	1044.7	1126.2

TEST NUMBER: P1009386

CATALOG NUMBER: S122DIP-B675D725UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	141.0	183.5	466.2	997.3	1124.7
115°	157.8	199.3	455.2	939.3	1088.7
117.5°	175.5	215.1	449.3	883.9	1034.4
120°	191.6	230.5	444.2	834.4	982.3
122.5°	207.0	246.3	441.2	795.8	928.0
125°	220.2	260.6	437.5	761.0	883.2
127.5°	231.3	274.2	435.3	731.2	841.3
130°	240.8	286.3	433.9	701.1	806.8
132.5°	249.6	298.0	433.1	669.9	770.8
135°	258.4	308.4	432.4	639.4	731.9
137.5°	266.5	317.2	432.4	608.6	694.5
140°	276.0	325.2	431.7	581.4	655.6
142.5°	285.6	331.8	431.7	555.4	616.7
145°	295.1	339.2	430.2	534.0	584.4
147.5°	305.4	345.0	428.0	515.4	555.7
150°	315.7	350.9	425.8	499.2	530.8
152.5°	326.0	356.8	422.1	485.6	509.5
155°	335.5	362.3	417.7	472.4	491.1
157.5°	343.6	366.7	413.3	459.9	475.0
160°	351.7	371.1	408.9	447.4	459.6
162.5°	359.7	374.4	405.2	435.7	444.9
165°	365.6	376.6	400.1	424.4	430.9
167.5°	370.7	378.8	395.7	414.0	417.7
170°	375.9	379.9	392.0	404.5	406.0
172.5°	378.8	381.0	387.6	396.0	396.4
175°	381.0	381.4	384.7	389.5	388.4
177.5°	382.5	381.8	381.8	384.7	382.5
180°	381.8	381.8	381.8	381.8	381.8

(END OF REPORT)