

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010309

Luminaire Tested: S122RDIP-B865D530UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010309
REPORT IS A COMBINATION OF REPORTS P988704 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B865D530UB27-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5027.4 lumens
Efficiency: N/A
Efficacy: 80.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010309

CATALOG NUMBER: S122RDIP-B865D530UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1010309

CATALOG NUMBER: S122RDIP-B865D530UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	56
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	52	50	48
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	44	41
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	42	39	36
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	35	32
6	66	54	46	40	61	51	44	39	45	39	35	40	35	32	35	31	28
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23
9	53	41	34	29	50	39	32	27	35	29	25	31	26	23	27	24	21
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	25	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22875	22875	22875
5°	22912	21762	21601
10°	22686	20640	19959
15°	22375	19315	18088
20°	21962	17809	16131
25°	21539	16263	14339
30°	20971	14759	12384
35°	20416	13240	10703
40°	19851	11750	8975
45°	19193	10211	7465
50°	18514	8727	6077
55°	17808	7243	4825
60°	16984	5793	3651
65°	16040	4417	2968
70°	14893	3204	2360
75°	13459	2443	1803
80°	11377	1655	1209
85°	7939	756	583

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19193 cd/sqm

TEST NUMBER: P1010309

CATALOG NUMBER: S122RDIP-B865D530UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.4	2.7
10°-20°	371.8	7.4
20°-30°	522.0	10.4
30°-40°	569.0	11.3
40°-50°	523.0	10.4
50°-60°	410.7	8.2
60°-70°	267.3	5.3
70°-80°	137.6	2.7
80°-90°	37.0	0.7
90°-100°	119.4	2.4
100°-110°	403.6	8.0
110°-120°	424.3	8.4
120°-130°	348.9	6.9
130°-140°	280.4	5.6
140°-150°	211.8	4.2
150°-160°	148.9	3.0
160°-170°	87.7	1.7
170°-180°	28.5	0.6
0°-30°	1029.2	20.5
0°-40°	1598.2	31.8
0°-60°	2531.9	50.4
0°-90°	2973.9	59.2
90°-120°	947.3	18.8
90°-150°	1788.4	35.6
90°-180°	2053.0	40.8
0°-180°	5027.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1445	1445	1445	1445	1445	
5°	1445	1438	1422	1433	1429	137
15°	1374	1360	1316	1291	1278	387
25°	1248	1206	1119	1066	1046	574
35°	1075	1008	893	811	782	673
45°	879	791	654	561	530	679
55°	668	566	425	347	322	597
65°	451	345	228	183	179	447
75°	241	149	105	96	94	254
85°	56	29	25	25	25	65
90°	1	8	19	18	19	4
95°	20	49	222	84	65	20
105°	69	104	420	750	638	73
115°	122	154	351	725	840	121
125°	170	201	338	587	681	151
135°	199	238	334	493	565	154
145°	228	262	332	412	451	143
155°	259	280	322	364	379	119
165°	282	291	309	327	332	80
175°	294	294	297	300	300	28
180°	294	294	294	294	294	

TEST NUMBER: P1010309

CATALOG NUMBER: S122RDIP-B865D530UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1445.1	1445.1	1445.1	1445.1	1445.1
2.5°	1451.6	1445.1	1430.7	1443.8	1441.2
5°	1445.1	1438.5	1421.5	1433.3	1429.4
7.5°	1433.3	1425.5	1407.2	1412.4	1405.9
10°	1417.6	1408.5	1382.3	1378.4	1370.5
12.5°	1398.0	1386.2	1350.9	1343.1	1328.7
15°	1374.5	1360.1	1315.6	1290.8	1277.7
17.5°	1347.0	1326.1	1271.2	1242.4	1221.5
20°	1315.6	1289.5	1224.1	1191.4	1162.6
22.5°	1281.6	1251.5	1175.7	1131.2	1111.6
25°	1247.6	1205.8	1119.4	1065.8	1046.2
27.5°	1207.1	1162.6	1067.1	1005.7	975.6
30°	1163.9	1114.2	1009.6	942.9	907.6
32.5°	1122.1	1061.9	954.7	876.2	843.5
35°	1075.0	1008.3	893.2	810.8	782.0
37.5°	1029.2	957.3	835.7	745.4	712.7
40°	980.8	902.4	775.5	682.7	648.7
42.5°	931.1	847.4	715.3	618.6	585.9
45°	878.8	791.2	653.9	561.0	529.6
47.5°	829.1	736.3	595.0	502.2	473.4
50°	774.2	681.3	537.5	447.3	419.8
52.5°	720.6	622.5	482.6	396.3	371.4
55°	668.3	566.3	425.0	346.6	321.7
57.5°	614.7	510.0	374.0	300.8	279.9
60°	559.7	455.1	320.4	253.7	232.8
62.5°	506.1	401.5	274.6	211.9	201.4
65°	451.2	345.3	227.6	183.1	179.2
67.5°	398.9	292.9	183.1	160.9	156.9
70°	343.9	241.9	151.7	138.6	133.4
72.5°	291.6	194.9	126.9	116.4	113.8
75°	240.6	149.1	104.6	95.5	94.2
77.5°	189.6	105.9	82.4	77.2	74.5
80°	142.5	75.9	62.8	57.5	57.5
82.5°	99.4	51.0	43.2	40.5	40.5
85°	56.2	28.8	24.8	24.8	24.8
87.5°	20.9	10.5	10.5	9.2	9.2
90°	0.6	7.6	19.3	18.4	18.7
92.5°	8.5	26.9	87.2	40.2	34.6
95°	19.8	48.7	222.0	83.8	64.6
97.5°	29.5	64.2	361.9	168.2	108.2
100°	43.6	78.8	447.5	335.0	202.8
102.5°	56.6	91.8	450.3	566.4	395.3
105°	69.1	104.2	419.7	750.2	638.3
107.5°	82.7	116.6	391.4	816.8	802.0
110°	96.3	129.4	372.1	806.0	868.9

TEST NUMBER: P1010309

CATALOG NUMBER: S122RDIP-B865D530UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	108.7	141.6	359.7	769.4	867.7
115°	121.8	153.8	351.2	724.7	840.0
117.5°	135.4	166.0	346.6	682.0	798.1
120°	147.8	177.9	342.7	643.7	757.8
122.5°	159.7	190.0	340.4	614.0	715.9
125°	169.9	201.0	337.6	587.0	681.4
127.5°	178.4	211.6	335.9	564.2	649.1
130°	185.8	220.9	334.7	540.9	622.5
132.5°	192.6	230.0	334.2	516.8	594.7
135°	199.4	237.9	333.6	493.4	564.7
137.5°	205.6	244.6	333.6	469.6	535.8
140°	213.0	251.0	333.0	448.6	505.8
142.5°	220.3	256.0	333.0	428.5	475.8
145°	227.7	261.6	331.9	412.0	450.9
147.5°	235.6	266.2	330.2	397.6	428.8
150°	243.6	270.7	328.5	385.2	409.5
152.5°	251.5	275.2	325.7	374.6	393.1
155°	258.8	279.6	322.3	364.5	378.9
157.5°	265.1	282.9	318.9	354.8	366.5
160°	271.3	286.3	315.5	345.2	354.6
162.5°	277.5	288.8	312.7	336.2	343.2
165°	282.1	290.6	308.7	327.4	332.5
167.5°	286.0	292.2	305.3	319.5	322.3
170°	290.0	293.2	302.5	312.1	313.2
172.5°	292.3	294.0	299.1	305.6	305.9
175°	294.0	294.2	296.8	300.5	299.6
177.5°	295.1	294.5	294.5	296.8	295.1
180°	294.5	294.5	294.5	294.5	294.5

(END OF REPORT)