

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010365

Luminaire Tested: S122RDIP-B865D925UB27-4F0-XX-W2A-A1

Issue Date: 5/6/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P1010365  
REPORT IS A COMBINATION OF REPORTS P988780 AND P1007351  
Test Lab: INNOVATION CENTER  
Issue Date: 5/6/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-B865D925UB27-4F0-XX-W2A-A1  
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}  
{m-EER=0.52}  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6500.0 lumens  
Efficiency: N/A  
Efficacy: 86.3 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01  
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')  
CIE Type: General Diffuse

Input Watts (W): 75.3  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1010365

CATALOG NUMBER: S122RDIP-B865D925UB27-4F0-XX-W2A-A1

### Luminous Intensity Polar Plot



TEST NUMBER: P1010365

CATALOG NUMBER: S122RDIP-B865D925UB27-4F0-XX-W2A-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |
|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|
| RF  | 20  |     |     |     | 20 |    |    |    |    | 20 |    |    |    |    | 20 |    |    |    |    | 20 |
| RC  | 80  |     |     |     | 70 |    |    |    |    | 50 |    |    |    |    | 30 |    |    |    |    | 0  |
| RW  | 70  | 50  | 30  | 10  | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 |
| RCR |     |     |     |     |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |
| 0   | 107 | 107 | 107 | 107 | 99 | 99 | 99 | 99 | 83 | 83 | 83 | 69 | 69 | 69 | 56 | 56 | 56 | 56 | 56 | 56 |
| 1   | 99  | 95  | 91  | 88  | 91 | 87 | 84 | 82 | 74 | 72 | 70 | 62 | 61 | 59 | 51 | 50 | 49 | 49 | 49 | 44 |
| 2   | 90  | 83  | 78  | 73  | 83 | 77 | 72 | 68 | 66 | 62 | 59 | 55 | 53 | 51 | 46 | 44 | 42 | 42 | 42 | 38 |
| 3   | 83  | 74  | 67  | 62  | 77 | 69 | 63 | 58 | 59 | 55 | 51 | 50 | 47 | 44 | 41 | 39 | 37 | 37 | 37 | 33 |
| 4   | 76  | 66  | 59  | 53  | 70 | 62 | 55 | 50 | 53 | 48 | 44 | 45 | 41 | 38 | 38 | 35 | 33 | 33 | 33 | 29 |
| 5   | 71  | 60  | 52  | 46  | 65 | 56 | 49 | 44 | 48 | 43 | 39 | 41 | 37 | 34 | 34 | 31 | 29 | 29 | 29 | 26 |
| 6   | 65  | 54  | 46  | 41  | 60 | 50 | 43 | 38 | 44 | 38 | 34 | 37 | 33 | 30 | 32 | 29 | 26 | 26 | 26 | 23 |
| 7   | 61  | 49  | 41  | 36  | 56 | 46 | 39 | 34 | 40 | 35 | 31 | 34 | 30 | 27 | 29 | 26 | 24 | 24 | 24 | 21 |
| 8   | 56  | 45  | 37  | 32  | 52 | 42 | 35 | 31 | 37 | 31 | 28 | 32 | 28 | 25 | 27 | 24 | 22 | 22 | 22 | 19 |
| 9   | 53  | 41  | 34  | 29  | 49 | 39 | 32 | 28 | 34 | 29 | 25 | 29 | 25 | 22 | 25 | 22 | 20 | 20 | 20 | 18 |
| 10  | 49  | 38  | 31  | 26  | 46 | 36 | 29 | 25 | 31 | 26 | 23 | 27 | 23 | 20 | 23 | 20 | 18 | 18 | 18 | 16 |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°    | 90°   | 180°  | 270°  |
|-----|-------|-------|-------|-------|
| 0°  | 29788 | 29788 | 29788 | 29788 |
| 5°  | 29857 | 31640 | 29961 | 25276 |
| 10° | 29529 | 33442 | 29738 | 20873 |
| 15° | 28888 | 33453 | 29378 | 15680 |
| 20° | 28116 | 27652 | 28729 | 12937 |
| 25° | 27183 | 17278 | 27770 | 11005 |
| 30° | 25989 | 11063 | 26695 | 9475  |
| 35° | 24537 | 8502  | 25333 | 8108  |
| 40° | 22921 | 7146  | 23900 | 7092  |
| 45° | 21191 | 6082  | 22078 | 5954  |
| 50° | 19420 | 5168  | 20326 | 5150  |
| 55° | 17459 | 4492  | 18399 | 4432  |
| 60° | 15715 | 3425  | 16547 | 3384  |
| 65° | 14085 | 2577  | 14924 | 2923  |
| 70° | 12291 | 2059  | 13252 | 2383  |
| 75° | 10388 | 1577  | 11339 | 1803  |
| 80° | 8247  | 1072  | 8878  | 1181  |
| 85° | 5721  | 553   | 6286  | 583   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 27250 cd/sqm

TEST NUMBER: P1010365

CATALOG NUMBER: S122RDIP-B865D925UB27-4F0-XX-W2A-A1

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 178.5  | 2.7       |
| 10°-20°   | 498.2  | 7.7       |
| 20°-30°   | 641.2  | 9.9       |
| 30°-40°   | 608.3  | 9.4       |
| 40°-50°   | 521.3  | 8.0       |
| 50°-60°   | 397.0  | 6.1       |
| 60°-70°   | 250.4  | 3.9       |
| 70°-80°   | 124.9  | 1.9       |
| 80°-90°   | 35.4   | 0.5       |
| 90°-100°  | 71.8   | 1.1       |
| 100°-110° | 228.2  | 3.5       |
| 110°-120° | 390.5  | 6.0       |
| 120°-130° | 513.6  | 7.9       |
| 130°-140° | 576.5  | 8.9       |
| 140°-150° | 565.4  | 8.7       |
| 150°-160° | 474.2  | 7.3       |
| 160°-170° | 314.5  | 4.8       |
| 170°-180° | 109.9  | 1.7       |
| 0°-30°    | 1317.9 | 20.3      |
| 0°-40°    | 1926.2 | 29.6      |
| 0°-60°    | 2844.6 | 43.8      |
| 0°-90°    | 3255.3 | 50.1      |
| 90°-120°  | 690.5  | 10.6      |
| 90°-150°  | 2346.0 | 36.1      |
| 90°-180°  | 3245.0 | 49.9      |
| 0°-180°   | 6500.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|      | 0°   | 90°  | 180° | 270° | 360° | Flux |
|------|------|------|------|------|------|------|
| 0°   | 1882 | 1882 | 1882 | 1882 | 1882 |      |
| 5°   | 1883 | 2094 | 1890 | 1673 | 1883 | 179  |
| 15°  | 1775 | 2363 | 1805 | 1108 | 1775 | 499  |
| 25°  | 1574 | 1261 | 1608 | 803  | 1574 | 723  |
| 35°  | 1292 | 621  | 1334 | 592  | 1292 | 808  |
| 45°  | 970  | 432  | 1011 | 422  | 970  | 749  |
| 55°  | 655  | 300  | 690  | 296  | 655  | 590  |
| 65°  | 396  | 156  | 420  | 176  | 396  | 393  |
| 75°  | 186  | 82   | 203  | 94   | 186  | 201  |
| 85°  | 40   | 24   | 44   | 25   | 40   | 46   |
| 90°  | 1    | 33   | 1    | 33   | 1    | 6    |
| 95°  | 51   | 61   | 51   | 61   | 51   | 57   |
| 105° | 211  | 217  | 211  | 217  | 211  | 222  |
| 115° | 392  | 392  | 392  | 392  | 392  | 388  |
| 125° | 570  | 572  | 570  | 572  | 570  | 509  |
| 135° | 738  | 746  | 738  | 746  | 738  | 570  |
| 145° | 895  | 905  | 895  | 905  | 895  | 559  |
| 155° | 1023 | 1031 | 1023 | 1031 | 1023 | 471  |
| 165° | 1114 | 1114 | 1114 | 1114 | 1114 | 314  |
| 175° | 1159 | 1155 | 1159 | 1155 | 1159 | 110  |
| 180° | 1161 | 1161 | 1161 | 1161 | 1161 |      |

TEST NUMBER: P1010365

CATALOG NUMBER: S122RDIP-B865D925UB27-4F0-XX-W2A-A1

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 5°     | 10°    | 15°    | 20°    | 22.5°  | 25°    | 30°    | 35°    | 40°    | 45°    |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 |
| 2.5°   | 1893.6 | 1901.4 | 1905.3 | 1910.6 | 1922.3 | 1930.2 | 1942.0 | 1944.6 | 1943.3 | 1948.5 | 1934.1 |
| 5°     | 1883.1 | 1900.1 | 1915.8 | 1928.9 | 1949.8 | 1962.9 | 1977.3 | 1994.3 | 1998.2 | 2017.8 | 2006.0 |
| 7.5°   | 1868.7 | 1893.6 | 1915.8 | 1942.0 | 1973.3 | 1990.4 | 2012.6 | 2038.7 | 2050.5 | 2074.0 | 2080.6 |
| 10°    | 1845.2 | 1880.5 | 1918.4 | 1945.9 | 1989.0 | 2019.1 | 2040.0 | 2081.9 | 2109.4 | 2144.7 | 2139.4 |
| 12.5°  | 1807.3 | 1853.0 | 1904.0 | 1949.8 | 2006.0 | 2025.7 | 2064.9 | 2108.0 | 2143.4 | 2176.0 | 2204.8 |
| 15°    | 1774.6 | 1826.9 | 1883.1 | 1939.3 | 2003.4 | 2040.0 | 2079.3 | 2135.5 | 2173.4 | 2231.0 | 2255.8 |
| 17.5°  | 1730.1 | 1796.8 | 1863.5 | 1926.3 | 2002.1 | 2044.0 | 2092.4 | 2147.3 | 2203.5 | 2258.4 | 2278.0 |
| 20°    | 1684.3 | 1756.3 | 1828.2 | 1913.2 | 1999.5 | 2040.0 | 2089.7 | 2157.7 | 2212.7 | 2255.8 | 2255.8 |
| 22.5°  | 1629.4 | 1717.0 | 1799.4 | 1880.5 | 1974.7 | 2033.5 | 2084.5 | 2164.3 | 2203.5 | 2212.7 | 2177.4 |
| 25°    | 1574.5 | 1662.1 | 1752.3 | 1853.0 | 1960.3 | 2012.6 | 2070.1 | 2144.7 | 2157.7 | 2121.1 | 2029.6 |
| 27.5°  | 1509.1 | 1607.2 | 1709.2 | 1817.7 | 1930.2 | 1995.6 | 2047.9 | 2097.6 | 2072.7 | 1974.7 | 1832.1 |
| 30°    | 1442.4 | 1548.3 | 1663.4 | 1766.7 | 1902.7 | 1962.9 | 2007.4 | 2021.7 | 1943.3 | 1783.7 | 1599.3 |
| 32.5°  | 1373.1 | 1476.4 | 1598.0 | 1722.3 | 1859.6 | 1917.1 | 1945.9 | 1908.0 | 1764.1 | 1562.7 | 1337.8 |
| 35°    | 1292.0 | 1408.4 | 1535.3 | 1664.7 | 1800.7 | 1843.9 | 1860.9 | 1768.0 | 1583.6 | 1323.4 | 1099.8 |
| 37.5°  | 1218.8 | 1335.2 | 1471.2 | 1603.3 | 1735.3 | 1758.9 | 1741.9 | 1596.7 | 1362.6 | 1105.0 | 886.6  |
| 40°    | 1132.5 | 1256.7 | 1390.1 | 1537.9 | 1646.4 | 1653.0 | 1611.1 | 1422.8 | 1132.5 | 890.6  | 755.9  |
| 42.5°  | 1052.7 | 1178.3 | 1311.6 | 1462.0 | 1544.4 | 1522.2 | 1466.0 | 1218.8 | 945.5  | 767.6  | 659.1  |
| 45°    | 970.3  | 1089.3 | 1233.2 | 1366.6 | 1425.4 | 1373.1 | 1288.1 | 1025.3 | 793.8  | 660.4  | 576.7  |
| 47.5°  | 890.6  | 1001.7 | 1144.3 | 1272.4 | 1282.9 | 1224.0 | 1123.3 | 859.2  | 687.9  | 580.6  | 512.6  |
| 50°    | 812.1  | 923.3  | 1056.6 | 1162.6 | 1152.1 | 1071.0 | 957.3  | 746.7  | 597.6  | 512.6  | 456.4  |
| 52.5°  | 733.6  | 834.3  | 963.8  | 1047.5 | 1003.0 | 924.6  | 812.1  | 632.9  | 521.8  | 447.2  | 404.1  |
| 55°    | 655.2  | 749.3  | 860.5  | 929.8  | 859.2  | 768.9  | 689.2  | 542.7  | 452.5  | 392.3  | 359.6  |
| 57.5°  | 589.8  | 664.3  | 766.3  | 808.2  | 723.2  | 652.6  | 583.2  | 466.9  | 392.3  | 349.2  | 311.2  |
| 60°    | 517.9  | 585.9  | 669.6  | 694.4  | 606.8  | 549.2  | 490.4  | 394.9  | 336.1  | 298.2  | 273.3  |
| 62.5°  | 456.4  | 512.6  | 576.7  | 576.7  | 499.5  | 456.4  | 411.9  | 330.9  | 282.5  | 252.4  | 240.6  |
| 65°    | 396.2  | 436.8  | 482.5  | 477.3  | 411.9  | 374.0  | 338.7  | 273.3  | 236.7  | 215.8  | 204.0  |
| 67.5°  | 337.4  | 368.8  | 398.9  | 380.5  | 333.5  | 300.8  | 268.1  | 221.0  | 196.2  | 181.8  | 166.1  |
| 70°    | 283.8  | 308.6  | 324.3  | 307.3  | 260.2  | 232.8  | 209.2  | 177.8  | 158.2  | 139.9  | 130.8  |
| 72.5°  | 238.0  | 248.5  | 253.7  | 232.8  | 193.5  | 177.8  | 160.8  | 138.6  | 121.6  | 112.5  | 109.8  |
| 75°    | 185.7  | 194.9  | 190.9  | 175.2  | 142.5  | 130.8  | 117.7  | 102.0  | 98.1   | 92.8   | 90.2   |
| 77.5°  | 145.2  | 145.2  | 138.6  | 124.2  | 102.0  | 92.8   | 87.6   | 79.8   | 75.8   | 74.5   | 71.9   |
| 80°    | 103.3  | 102.0  | 98.1   | 82.4   | 69.3   | 64.1   | 64.1   | 58.8   | 57.5   | 54.9   | 54.9   |
| 82.5°  | 68.0   | 68.0   | 62.8   | 49.7   | 45.8   | 44.5   | 43.2   | 40.5   | 40.5   | 39.2   | 39.2   |
| 85°    | 40.5   | 37.9   | 31.4   | 27.5   | 26.2   | 26.2   | 24.8   | 23.5   | 24.8   | 23.5   | 23.5   |
| 87.5°  | 18.3   | 14.4   | 10.5   | 10.5   | 10.5   | 10.5   | 10.5   | 10.5   | 10.5   | 10.5   | 10.5   |
| 90°    | 1.0    | 3.6    | 6.2    | 8.8    | 11.4   | 12.7   | 15.1   | 19.9   | 24.7   | 29.5   | 34.3   |
| 92.5°  | 21.5   | 23.3   | 25.0   | 26.8   | 28.5   | 29.4   | 29.5   | 29.7   | 30.0   | 30.2   | 30.4   |
| 95°    | 50.9   | 53.1   | 55.3   | 57.4   | 59.6   | 60.7   | 60.9   | 61.4   | 61.8   | 62.3   | 62.7   |
| 97.5°  | 85.2   | 87.2   | 89.1   | 91.1   | 93.0   | 94.0   | 94.4   | 95.3   | 96.2   | 97.0   | 97.9   |
| 100°   | 124.4  | 126.1  | 127.9  | 129.6  | 131.3  | 132.2  | 132.5  | 133.2  | 133.9  | 134.5  | 135.2  |
| 102.5° | 165.5  | 166.8  | 168.1  | 169.4  | 170.7  | 171.4  | 171.8  | 172.7  | 173.6  | 174.4  | 175.3  |
| 105°   | 210.6  | 211.2  | 211.9  | 212.5  | 213.2  | 213.5  | 213.7  | 214.2  | 214.6  | 215.1  | 215.5  |
| 107.5° | 255.6  | 256.5  | 257.3  | 258.2  | 259.1  | 259.5  | 259.5  | 259.5  | 259.5  | 259.5  | 259.5  |
| 110°   | 298.7  | 300.0  | 301.3  | 302.6  | 303.9  | 304.6  | 304.6  | 304.6  | 304.6  | 304.6  | 304.6  |

TEST NUMBER: P1010365

CATALOG NUMBER: S122RDIP-B865D925UB27-4F0-XX-W2A-A1

**CANDELA DISTRIBUTION (continued):**

|        | 0°     | 5°     | 10°    | 15°    | 20°    | 22.5°  | 25°    | 30°    | 35°    | 40°    | 45°    |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 112.5° | 345.7  | 347.0  | 348.3  | 349.6  | 350.9  | 351.6  | 351.5  | 351.3  | 351.0  | 350.8  | 350.6  |
| 115°   | 391.7  | 393.0  | 394.3  | 395.6  | 396.9  | 397.6  | 397.4  | 397.0  | 396.5  | 396.1  | 395.7  |
| 117.5° | 437.8  | 439.5  | 441.3  | 443.0  | 444.7  | 445.6  | 445.1  | 444.0  | 442.9  | 441.8  | 440.7  |
| 120°   | 483.8  | 485.5  | 487.3  | 489.0  | 490.7  | 491.6  | 490.7  | 489.0  | 487.3  | 485.5  | 483.8  |
| 122.5° | 525.9  | 528.1  | 530.3  | 532.4  | 534.6  | 535.7  | 535.2  | 534.1  | 533.0  | 531.9  | 530.8  |
| 125°   | 570.0  | 572.0  | 573.9  | 575.9  | 577.8  | 578.8  | 578.5  | 577.8  | 577.2  | 576.5  | 575.9  |
| 127.5° | 613.1  | 615.5  | 617.9  | 620.3  | 622.7  | 623.9  | 623.5  | 622.6  | 621.7  | 620.8  | 619.9  |
| 130°   | 653.2  | 656.0  | 658.9  | 661.7  | 664.6  | 666.0  | 665.8  | 665.3  | 664.9  | 664.4  | 664.0  |
| 132.5° | 698.3  | 700.5  | 702.7  | 704.8  | 707.0  | 708.1  | 708.2  | 708.4  | 708.7  | 708.9  | 709.1  |
| 135°   | 737.5  | 739.9  | 742.3  | 744.6  | 747.0  | 748.2  | 748.4  | 748.9  | 749.3  | 749.8  | 750.2  |
| 137.5° | 780.6  | 782.6  | 784.5  | 786.5  | 788.4  | 789.4  | 789.6  | 790.0  | 790.5  | 790.9  | 791.3  |
| 140°   | 818.8  | 820.8  | 822.7  | 824.7  | 826.6  | 827.6  | 828.1  | 829.2  | 830.3  | 831.4  | 832.5  |
| 142.5° | 857.9  | 859.9  | 861.8  | 863.8  | 865.7  | 866.7  | 867.0  | 867.7  | 868.4  | 869.0  | 869.7  |
| 145°   | 895.1  | 896.6  | 898.2  | 899.7  | 901.2  | 902.0  | 902.7  | 904.0  | 905.3  | 906.6  | 907.9  |
| 147.5° | 928.4  | 930.4  | 932.4  | 934.3  | 936.3  | 937.3  | 937.7  | 938.6  | 939.5  | 940.3  | 941.2  |
| 150°   | 962.7  | 964.0  | 965.3  | 966.6  | 967.9  | 968.6  | 969.0  | 969.9  | 970.8  | 971.6  | 972.5  |
| 152.5° | 993.1  | 994.4  | 995.7  | 997.0  | 998.3  | 999.0  | 999.5  | 1000.6 | 1001.7 | 1002.8 | 1003.9 |
| 155°   | 1023.4 | 1024.1 | 1024.7 | 1025.4 | 1026.1 | 1026.4 | 1026.7 | 1027.4 | 1028.0 | 1028.7 | 1029.3 |
| 157.5° | 1049.9 | 1050.3 | 1050.7 | 1051.2 | 1051.6 | 1051.8 | 1052.0 | 1052.5 | 1052.9 | 1053.4 | 1053.8 |
| 160°   | 1073.4 | 1073.8 | 1074.3 | 1074.7 | 1075.2 | 1075.4 | 1075.5 | 1075.7 | 1075.9 | 1076.1 | 1076.3 |
| 162.5° | 1094.9 | 1094.9 | 1094.9 | 1094.9 | 1094.9 | 1094.9 | 1095.0 | 1095.2 | 1095.5 | 1095.7 | 1095.9 |
| 165°   | 1113.5 | 1113.3 | 1113.1 | 1112.9 | 1112.7 | 1112.6 | 1112.6 | 1112.6 | 1112.6 | 1112.6 | 1112.6 |
| 167.5° | 1130.2 | 1129.6 | 1128.9 | 1128.3 | 1127.6 | 1127.3 | 1127.3 | 1127.3 | 1127.3 | 1127.3 | 1127.3 |
| 170°   | 1142.9 | 1142.3 | 1141.6 | 1141.0 | 1140.3 | 1140.0 | 1139.9 | 1139.7 | 1139.4 | 1139.2 | 1139.0 |
| 172.5° | 1151.7 | 1151.1 | 1150.4 | 1149.8 | 1149.1 | 1148.8 | 1148.7 | 1148.5 | 1148.2 | 1148.0 | 1147.8 |
| 175°   | 1158.6 | 1158.0 | 1157.3 | 1156.7 | 1156.0 | 1155.7 | 1155.5 | 1155.0 | 1154.6 | 1154.1 | 1153.7 |
| 177.5° | 1162.5 | 1161.9 | 1161.2 | 1160.6 | 1159.9 | 1159.6 | 1159.4 | 1158.9 | 1158.5 | 1158.0 | 1157.6 |
| 180°   | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 |

TEST NUMBER: P1010365

CATALOG NUMBER: S122RDIP-B865D925UB27-4F0-XX-W2A-A1

**CANDELA DISTRIBUTION (continued):**

|        | 50°    | 55°    | 60°    | 65°    | 67.5°  | 70°    | 75°    | 80°    | 85°    | 90°    | 95°    |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 |
| 2.5°   | 1948.5 | 1951.1 | 1955.0 | 1973.3 | 1976.0 | 1981.2 | 1978.6 | 1978.6 | 1979.9 | 1977.3 | 1978.6 |
| 5°     | 2032.2 | 2036.1 | 2055.7 | 2078.0 | 2083.2 | 2078.0 | 2084.5 | 2093.7 | 2093.7 | 2093.7 | 2091.0 |
| 7.5°   | 2110.7 | 2125.0 | 2147.3 | 2180.0 | 2186.5 | 2193.0 | 2204.8 | 2197.0 | 2199.6 | 2211.4 | 2207.4 |
| 10°    | 2186.5 | 2207.4 | 2232.3 | 2259.7 | 2274.1 | 2283.3 | 2288.5 | 2300.3 | 2327.7 | 2296.4 | 2308.1 |
| 12.5°  | 2258.4 | 2288.5 | 2314.7 | 2344.7 | 2355.2 | 2367.0 | 2370.9 | 2381.4 | 2381.4 | 2380.1 | 2389.2 |
| 15°    | 2305.5 | 2333.0 | 2356.5 | 2376.1 | 2378.7 | 2376.1 | 2373.5 | 2374.8 | 2378.7 | 2363.1 | 2372.2 |
| 17.5°  | 2316.0 | 2318.6 | 2326.4 | 2318.6 | 2319.9 | 2292.4 | 2276.7 | 2272.8 | 2236.2 | 2237.5 | 2267.6 |
| 20°    | 2265.0 | 2220.5 | 2208.7 | 2165.6 | 2139.4 | 2068.8 | 2066.2 | 2046.6 | 1969.4 | 1993.0 | 1987.7 |
| 22.5°  | 2125.0 | 2049.2 | 1948.5 | 1898.8 | 1874.0 | 1799.4 | 1741.9 | 1701.3 | 1673.9 | 1646.4 | 1634.7 |
| 25°    | 1940.7 | 1817.7 | 1675.2 | 1577.1 | 1562.7 | 1493.4 | 1387.5 | 1337.8 | 1279.0 | 1260.6 | 1292.0 |
| 27.5°  | 1702.7 | 1543.1 | 1382.3 | 1231.9 | 1204.4 | 1141.6 | 1088.0 | 1052.7 | 984.7  | 980.8  | 983.4  |
| 30°    | 1379.6 | 1218.8 | 1084.1 | 986.0  | 918.0  | 889.2  | 853.9  | 827.8  | 800.3  | 810.8  | 813.4  |
| 32.5°  | 1133.8 | 980.8  | 855.2  | 802.9  | 771.6  | 753.2  | 723.2  | 706.2  | 694.4  | 690.5  | 689.2  |
| 35°    | 901.0  | 799.0  | 742.8  | 691.8  | 673.5  | 660.4  | 638.2  | 630.3  | 619.9  | 621.2  | 621.2  |
| 37.5°  | 771.6  | 686.6  | 644.7  | 618.6  | 601.6  | 595.0  | 580.6  | 572.8  | 566.2  | 563.6  | 567.6  |
| 40°    | 665.6  | 606.8  | 580.6  | 557.1  | 542.7  | 540.1  | 532.2  | 523.1  | 515.2  | 516.5  | 520.5  |
| 42.5°  | 588.5  | 554.5  | 523.1  | 504.8  | 494.3  | 490.4  | 483.9  | 477.3  | 477.3  | 473.4  | 472.1  |
| 45°    | 527.0  | 499.5  | 473.4  | 456.4  | 449.9  | 444.6  | 436.8  | 435.5  | 430.2  | 431.5  | 432.9  |
| 47.5°  | 472.1  | 449.9  | 430.2  | 413.2  | 406.7  | 405.4  | 397.5  | 392.3  | 392.3  | 391.0  | 389.7  |
| 50°    | 422.4  | 400.2  | 383.2  | 374.0  | 364.9  | 362.2  | 360.9  | 359.6  | 357.0  | 357.0  | 358.3  |
| 52.5°  | 381.9  | 359.6  | 346.5  | 338.7  | 333.5  | 330.9  | 330.9  | 329.5  | 329.5  | 329.5  | 328.2  |
| 55°    | 337.4  | 319.1  | 308.6  | 306.0  | 303.4  | 302.1  | 300.8  | 298.2  | 296.9  | 299.5  | 296.9  |
| 57.5°  | 295.5  | 289.0  | 279.9  | 277.2  | 270.7  | 270.7  | 266.8  | 264.2  | 261.5  | 264.2  | 264.2  |
| 60°    | 262.9  | 253.7  | 248.5  | 240.6  | 235.4  | 230.2  | 223.6  | 222.3  | 219.7  | 218.4  | 217.1  |
| 62.5°  | 228.9  | 221.0  | 207.9  | 196.2  | 188.3  | 183.1  | 180.5  | 179.2  | 179.2  | 177.8  | 177.8  |
| 65°    | 190.9  | 172.6  | 166.1  | 162.2  | 160.8  | 159.5  | 156.9  | 155.6  | 156.9  | 155.6  | 156.9  |
| 67.5°  | 149.1  | 146.5  | 142.5  | 139.9  | 138.6  | 137.3  | 137.3  | 136.0  | 136.0  | 136.0  | 136.0  |
| 70°    | 129.5  | 122.9  | 121.6  | 119.0  | 119.0  | 117.7  | 117.7  | 117.7  | 117.7  | 116.4  | 119.0  |
| 72.5°  | 107.2  | 103.3  | 102.0  | 100.7  | 100.7  | 100.7  | 99.4   | 99.4   | 99.4   | 98.1   | 99.4   |
| 75°    | 87.6   | 86.3   | 83.7   | 83.7   | 82.4   | 83.7   | 82.4   | 82.4   | 81.1   | 82.4   | 82.4   |
| 77.5°  | 70.6   | 69.3   | 68.0   | 68.0   | 66.7   | 66.7   | 66.7   | 66.7   | 66.7   | 66.7   | 68.0   |
| 80°    | 53.6   | 52.3   | 51.0   | 52.3   | 51.0   | 52.3   | 51.0   | 51.0   | 52.3   | 51.0   | 51.0   |
| 82.5°  | 39.2   | 37.9   | 37.9   | 36.6   | 36.6   | 36.6   | 36.6   | 36.6   | 36.6   | 36.6   | 36.6   |
| 85°    | 23.5   | 22.2   | 22.2   | 23.5   | 22.2   | 23.5   | 22.2   | 22.2   | 22.2   | 23.5   | 23.5   |
| 87.5°  | 10.5   | 11.8   | 10.5   | 10.5   | 10.5   | 10.5   | 10.5   | 10.5   | 10.5   | 10.5   | 11.8   |
| 90°    | 33.9   | 33.4   | 33.0   | 32.5   | 32.3   | 32.4   | 32.6   | 32.9   | 33.1   | 33.3   | 33.1   |
| 92.5°  | 30.6   | 30.8   | 31.0   | 31.2   | 31.3   | 31.3   | 31.3   | 31.3   | 31.3   | 31.3   | 31.3   |
| 95°    | 62.7   | 62.7   | 62.7   | 62.7   | 62.7   | 62.5   | 62.0   | 61.6   | 61.1   | 60.7   | 61.1   |
| 97.5°  | 97.9   | 97.9   | 97.9   | 97.9   | 97.9   | 97.9   | 97.9   | 97.9   | 97.9   | 97.9   | 97.9   |
| 100°   | 135.2  | 135.2  | 135.2  | 135.2  | 135.2  | 135.1  | 134.9  | 134.6  | 134.4  | 134.2  | 134.4  |
| 102.5° | 175.5  | 175.7  | 176.0  | 176.2  | 176.3  | 176.2  | 176.0  | 175.7  | 175.5  | 175.3  | 175.5  |
| 105°   | 215.9  | 216.3  | 216.8  | 217.2  | 217.4  | 217.4  | 217.4  | 217.4  | 217.4  | 217.4  | 217.4  |
| 107.5° | 259.7  | 259.9  | 260.2  | 260.4  | 260.5  | 260.0  | 258.9  | 257.8  | 256.7  | 255.6  | 256.7  |
| 110°   | 304.6  | 304.6  | 304.6  | 304.6  | 304.6  | 304.3  | 303.6  | 302.9  | 302.3  | 301.6  | 302.3  |



TEST NUMBER: P1010365

CATALOG NUMBER: S122RDIP-B865D925UB27-4F0-XX-W2A-A1

**CANDELA DISTRIBUTION (continued):**

|        | 50°    | 55°    | 60°    | 65°    | 67.5°  | 70°    | 75°    | 80°    | 85°    | 90°    | 95°    |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 112.5° | 350.0  | 349.3  | 348.7  | 348.0  | 347.7  | 347.5  | 347.0  | 346.6  | 346.1  | 345.7  | 346.1  |
| 115°   | 395.5  | 395.3  | 395.0  | 394.8  | 394.7  | 394.4  | 393.7  | 393.0  | 392.4  | 391.7  | 392.4  |
| 117.5° | 440.1  | 439.4  | 438.8  | 438.1  | 437.8  | 437.5  | 436.8  | 436.1  | 435.5  | 434.8  | 435.5  |
| 120°   | 483.8  | 483.8  | 483.8  | 483.8  | 483.8  | 483.5  | 482.8  | 482.2  | 481.5  | 480.9  | 481.5  |
| 122.5° | 530.2  | 529.5  | 528.9  | 528.2  | 527.9  | 527.7  | 527.2  | 526.8  | 526.3  | 525.9  | 526.3  |
| 125°   | 575.2  | 574.6  | 573.9  | 573.2  | 572.9  | 572.8  | 572.6  | 572.4  | 572.2  | 572.0  | 572.2  |
| 127.5° | 619.0  | 618.2  | 617.3  | 616.4  | 616.0  | 615.7  | 615.0  | 614.4  | 613.7  | 613.1  | 613.7  |
| 130°   | 663.6  | 663.2  | 662.7  | 662.3  | 662.1  | 661.7  | 660.8  | 659.9  | 659.0  | 658.1  | 659.0  |
| 132.5° | 708.0  | 706.9  | 705.8  | 704.7  | 704.2  | 703.9  | 703.2  | 702.5  | 701.9  | 701.2  | 701.9  |
| 135°   | 750.0  | 749.8  | 749.5  | 749.3  | 749.2  | 748.9  | 748.2  | 747.6  | 746.9  | 746.3  | 746.9  |
| 137.5° | 791.1  | 790.9  | 790.7  | 790.5  | 790.4  | 790.0  | 789.1  | 788.2  | 787.3  | 786.4  | 787.3  |
| 140°   | 832.5  | 832.5  | 832.5  | 832.5  | 832.5  | 832.1  | 831.2  | 830.3  | 829.4  | 828.5  | 829.4  |
| 142.5° | 869.9  | 870.1  | 870.4  | 870.6  | 870.7  | 870.3  | 869.4  | 868.5  | 867.6  | 866.7  | 867.6  |
| 145°   | 908.1  | 908.3  | 908.6  | 908.8  | 908.9  | 908.5  | 907.6  | 906.7  | 905.8  | 904.9  | 905.8  |
| 147.5° | 941.6  | 942.0  | 942.5  | 942.9  | 943.1  | 942.7  | 941.8  | 940.9  | 940.1  | 939.2  | 940.1  |
| 150°   | 973.2  | 973.8  | 974.5  | 975.2  | 975.5  | 975.2  | 974.5  | 973.8  | 973.2  | 972.5  | 973.2  |
| 152.5° | 1004.8 | 1005.6 | 1006.5 | 1007.4 | 1007.8 | 1007.4 | 1006.5 | 1005.6 | 1004.8 | 1003.9 | 1004.8 |
| 155°   | 1030.4 | 1031.5 | 1032.6 | 1033.7 | 1034.2 | 1033.9 | 1033.2 | 1032.6 | 1031.9 | 1031.3 | 1031.9 |
| 157.5° | 1055.3 | 1056.9 | 1058.4 | 1059.9 | 1060.7 | 1060.2 | 1059.1 | 1058.0 | 1056.9 | 1055.8 | 1056.9 |
| 160°   | 1077.6 | 1078.9 | 1080.2 | 1081.5 | 1082.2 | 1081.8 | 1080.9 | 1080.0 | 1079.2 | 1078.3 | 1079.2 |
| 162.5° | 1097.4 | 1099.0 | 1100.5 | 1102.0 | 1102.8 | 1102.3 | 1101.2 | 1100.1 | 1099.0 | 1097.9 | 1099.0 |
| 165°   | 1114.1 | 1115.6 | 1117.1 | 1118.6 | 1119.4 | 1118.9 | 1117.8 | 1116.7 | 1115.6 | 1114.5 | 1115.6 |
| 167.5° | 1128.8 | 1130.3 | 1131.8 | 1133.3 | 1134.1 | 1133.6 | 1132.5 | 1131.4 | 1130.3 | 1129.2 | 1130.3 |
| 170°   | 1140.5 | 1142.1 | 1143.6 | 1145.1 | 1145.9 | 1145.2 | 1143.9 | 1142.6 | 1141.3 | 1140.0 | 1141.3 |
| 172.5° | 1149.3 | 1150.9 | 1152.4 | 1153.9 | 1154.7 | 1154.0 | 1152.7 | 1151.4 | 1150.1 | 1148.8 | 1150.1 |
| 175°   | 1155.2 | 1156.8 | 1158.3 | 1159.8 | 1160.6 | 1159.9 | 1158.6 | 1157.3 | 1156.0 | 1154.7 | 1156.0 |
| 177.5° | 1158.9 | 1160.2 | 1161.5 | 1162.8 | 1163.5 | 1162.8 | 1161.5 | 1160.2 | 1158.9 | 1157.6 | 1158.9 |
| 180°   | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 |

TEST NUMBER: P1010365

CATALOG NUMBER: S122RDIP-B865D925UB27-4F0-XX-W2A-A1

**CANDELA DISTRIBUTION (continued):**

|        | 100°   | 105°   | 110°   | 112.5° | 115°   | 120°   | 125°   | 130°   | 135°   | 140°   | 145°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 |
| 2.5°   | 1983.8 | 1974.7 | 1972.0 | 1974.7 | 1972.0 | 1973.3 | 1964.2 | 1930.2 | 1939.3 | 1925.0 | 1932.8 |
| 5°     | 2096.3 | 2088.4 | 2071.4 | 2068.8 | 2066.2 | 2063.6 | 2050.5 | 2020.4 | 2008.7 | 1989.0 | 1987.7 |
| 7.5°   | 2203.5 | 2203.5 | 2190.4 | 2181.3 | 2169.5 | 2160.4 | 2143.4 | 2098.9 | 2080.6 | 2057.0 | 2044.0 |
| 10°    | 2309.4 | 2275.4 | 2289.8 | 2280.7 | 2251.9 | 2246.7 | 2215.3 | 2189.1 | 2153.8 | 2130.3 | 2109.4 |
| 12.5°  | 2385.3 | 2374.8 | 2361.7 | 2353.9 | 2346.0 | 2329.0 | 2308.1 | 2241.4 | 2223.1 | 2176.0 | 2152.5 |
| 15°    | 2382.7 | 2376.1 | 2380.1 | 2380.1 | 2377.4 | 2373.5 | 2356.5 | 2308.1 | 2276.7 | 2231.0 | 2190.4 |
| 17.5°  | 2254.5 | 2271.5 | 2288.5 | 2300.3 | 2326.4 | 2338.2 | 2353.9 | 2325.1 | 2305.5 | 2266.3 | 2223.1 |
| 20°    | 2030.9 | 2072.7 | 2122.4 | 2132.9 | 2156.4 | 2225.7 | 2257.1 | 2282.0 | 2289.8 | 2276.7 | 2241.4 |
| 22.5°  | 1719.7 | 1755.0 | 1875.3 | 1872.7 | 1906.7 | 1989.0 | 2080.6 | 2155.1 | 2214.0 | 2246.7 | 2233.6 |
| 25°    | 1347.0 | 1396.6 | 1460.7 | 1509.1 | 1620.3 | 1743.2 | 1857.0 | 1976.0 | 2078.0 | 2168.2 | 2190.4 |
| 27.5°  | 1018.7 | 1084.1 | 1135.1 | 1199.2 | 1255.4 | 1400.6 | 1547.0 | 1732.7 | 1851.7 | 2023.0 | 2112.0 |
| 30°    | 823.9  | 853.9  | 904.9  | 935.0  | 962.5  | 1073.6 | 1239.7 | 1422.8 | 1632.0 | 1829.5 | 1982.5 |
| 32.5°  | 703.6  | 724.5  | 762.4  | 775.5  | 804.2  | 878.8  | 983.4  | 1150.8 | 1366.6 | 1605.9 | 1807.3 |
| 35°    | 631.6  | 653.9  | 661.7  | 673.5  | 697.0  | 744.1  | 816.0  | 937.6  | 1132.5 | 1366.6 | 1607.2 |
| 37.5°  | 570.2  | 581.9  | 604.2  | 612.0  | 619.9  | 655.2  | 703.6  | 788.6  | 918.0  | 1110.3 | 1377.0 |
| 40°    | 527.0  | 533.5  | 545.3  | 551.9  | 557.1  | 581.9  | 625.1  | 682.6  | 778.1  | 924.6  | 1170.4 |
| 42.5°  | 481.2  | 489.1  | 496.9  | 504.8  | 511.3  | 530.9  | 557.1  | 612.0  | 676.1  | 787.2  | 965.1  |
| 45°    | 436.8  | 442.0  | 451.2  | 456.4  | 465.5  | 481.2  | 504.8  | 542.7  | 600.2  | 670.9  | 814.7  |
| 47.5°  | 396.2  | 402.8  | 406.7  | 413.2  | 419.8  | 436.8  | 459.0  | 483.9  | 530.9  | 600.2  | 704.9  |
| 50°    | 359.6  | 367.5  | 372.7  | 374.0  | 379.2  | 394.9  | 413.2  | 440.7  | 470.8  | 524.4  | 615.9  |
| 52.5°  | 333.5  | 334.8  | 338.7  | 343.9  | 342.6  | 351.8  | 368.8  | 389.7  | 421.1  | 464.2  | 530.9  |
| 55°    | 303.4  | 307.3  | 309.9  | 311.2  | 311.2  | 319.1  | 328.2  | 347.9  | 372.7  | 408.0  | 464.2  |
| 57.5°  | 265.5  | 269.4  | 277.2  | 279.9  | 283.8  | 287.7  | 291.6  | 304.7  | 325.6  | 359.6  | 405.4  |
| 60°    | 226.2  | 228.9  | 236.7  | 241.9  | 244.5  | 255.0  | 260.2  | 270.7  | 282.5  | 307.3  | 350.5  |
| 62.5°  | 181.8  | 184.4  | 188.3  | 193.5  | 198.8  | 214.5  | 227.5  | 238.0  | 247.2  | 264.2  | 299.5  |
| 65°    | 158.2  | 159.5  | 162.2  | 163.5  | 164.8  | 171.3  | 183.1  | 197.5  | 214.5  | 227.5  | 248.5  |
| 67.5°  | 137.3  | 138.6  | 139.9  | 142.5  | 143.8  | 145.2  | 150.4  | 154.3  | 171.3  | 189.6  | 205.3  |
| 70°    | 117.7  | 120.3  | 121.6  | 121.6  | 122.9  | 125.5  | 128.2  | 133.4  | 138.6  | 147.8  | 167.4  |
| 72.5°  | 99.4   | 100.7  | 103.3  | 103.3  | 103.3  | 105.9  | 108.5  | 111.2  | 113.8  | 119.0  | 126.8  |
| 75°    | 82.4   | 85.0   | 85.0   | 85.0   | 86.3   | 86.3   | 88.9   | 91.5   | 94.2   | 98.1   | 100.7  |
| 77.5°  | 68.0   | 68.0   | 68.0   | 68.0   | 69.3   | 69.3   | 70.6   | 73.2   | 74.5   | 75.8   | 78.5   |
| 80°    | 51.0   | 52.3   | 52.3   | 52.3   | 53.6   | 53.6   | 53.6   | 56.2   | 57.5   | 57.5   | 60.2   |
| 82.5°  | 37.9   | 37.9   | 37.9   | 39.2   | 37.9   | 39.2   | 39.2   | 40.5   | 39.2   | 40.5   | 41.8   |
| 85°    | 23.5   | 23.5   | 23.5   | 24.8   | 24.8   | 24.8   | 24.8   | 24.8   | 24.8   | 24.8   | 26.2   |
| 87.5°  | 11.8   | 11.8   | 11.8   | 11.8   | 11.8   | 11.8   | 11.8   | 11.8   | 13.1   | 11.8   | 11.8   |
| 90°    | 32.9   | 32.6   | 32.4   | 32.3   | 32.5   | 33.0   | 33.4   | 33.9   | 34.3   | 29.5   | 24.7   |
| 92.5°  | 31.3   | 31.3   | 31.3   | 31.3   | 31.2   | 31.0   | 30.8   | 30.6   | 30.4   | 30.2   | 30.0   |
| 95°    | 61.6   | 62.0   | 62.5   | 62.7   | 62.7   | 62.7   | 62.7   | 62.7   | 62.7   | 62.3   | 61.8   |
| 97.5°  | 97.9   | 97.9   | 97.9   | 97.9   | 97.9   | 97.9   | 97.9   | 97.9   | 97.9   | 97.0   | 96.2   |
| 100°   | 134.6  | 134.9  | 135.1  | 135.2  | 135.2  | 135.2  | 135.2  | 135.2  | 135.2  | 134.5  | 133.9  |
| 102.5° | 175.7  | 176.0  | 176.2  | 176.3  | 176.2  | 176.0  | 175.7  | 175.5  | 175.3  | 174.4  | 173.6  |
| 105°   | 217.4  | 217.4  | 217.4  | 217.4  | 217.2  | 216.8  | 216.3  | 215.9  | 215.5  | 215.1  | 214.6  |
| 107.5° | 257.8  | 258.9  | 260.0  | 260.5  | 260.4  | 260.2  | 259.9  | 259.7  | 259.5  | 259.5  | 259.5  |
| 110°   | 302.9  | 303.6  | 304.3  | 304.6  | 304.6  | 304.6  | 304.6  | 304.6  | 304.6  | 304.6  | 304.6  |

TEST NUMBER: P1010365

CATALOG NUMBER: S122RDIP-B865D925UB27-4F0-XX-W2A-A1

**CANDELA DISTRIBUTION (continued):**

|        | 100°   | 105°   | 110°   | 112.5° | 115°   | 120°   | 125°   | 130°   | 135°   | 140°   | 145°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 112.5° | 346.6  | 347.0  | 347.5  | 347.7  | 348.0  | 348.7  | 349.3  | 350.0  | 350.6  | 350.8  | 351.0  |
| 115°   | 393.0  | 393.7  | 394.4  | 394.7  | 394.8  | 395.0  | 395.3  | 395.5  | 395.7  | 396.1  | 396.5  |
| 117.5° | 436.1  | 436.8  | 437.5  | 437.8  | 438.1  | 438.8  | 439.4  | 440.1  | 440.7  | 441.8  | 442.9  |
| 120°   | 482.2  | 482.8  | 483.5  | 483.8  | 483.8  | 483.8  | 483.8  | 483.8  | 483.8  | 485.5  | 487.3  |
| 122.5° | 526.8  | 527.2  | 527.7  | 527.9  | 528.2  | 528.9  | 529.5  | 530.2  | 530.8  | 531.9  | 533.0  |
| 125°   | 572.4  | 572.6  | 572.8  | 572.9  | 573.2  | 573.9  | 574.6  | 575.2  | 575.9  | 576.5  | 577.2  |
| 127.5° | 614.4  | 615.0  | 615.7  | 616.0  | 616.4  | 617.3  | 618.2  | 619.0  | 619.9  | 620.8  | 621.7  |
| 130°   | 659.9  | 660.8  | 661.7  | 662.1  | 662.3  | 662.7  | 663.2  | 663.6  | 664.0  | 664.4  | 664.9  |
| 132.5° | 702.5  | 703.2  | 703.9  | 704.2  | 704.7  | 705.8  | 706.9  | 708.0  | 709.1  | 708.9  | 708.7  |
| 135°   | 747.6  | 748.2  | 748.9  | 749.2  | 749.3  | 749.5  | 749.8  | 750.0  | 750.2  | 749.8  | 749.3  |
| 137.5° | 788.2  | 789.1  | 790.0  | 790.4  | 790.5  | 790.7  | 790.9  | 791.1  | 791.3  | 790.9  | 790.5  |
| 140°   | 830.3  | 831.2  | 832.1  | 832.5  | 832.5  | 832.5  | 832.5  | 832.5  | 832.5  | 831.4  | 830.3  |
| 142.5° | 868.5  | 869.4  | 870.3  | 870.7  | 870.6  | 870.4  | 870.1  | 869.9  | 869.7  | 869.0  | 868.4  |
| 145°   | 906.7  | 907.6  | 908.5  | 908.9  | 908.8  | 908.6  | 908.3  | 908.1  | 907.9  | 906.6  | 905.3  |
| 147.5° | 940.9  | 941.8  | 942.7  | 943.1  | 942.9  | 942.5  | 942.0  | 941.6  | 941.2  | 940.3  | 939.5  |
| 150°   | 973.8  | 974.5  | 975.2  | 975.5  | 975.2  | 974.5  | 973.8  | 973.2  | 972.5  | 971.6  | 970.8  |
| 152.5° | 1005.6 | 1006.5 | 1007.4 | 1007.8 | 1007.4 | 1006.5 | 1005.6 | 1004.8 | 1003.9 | 1002.8 | 1001.7 |
| 155°   | 1032.6 | 1033.2 | 1033.9 | 1034.2 | 1033.7 | 1032.6 | 1031.5 | 1030.4 | 1029.3 | 1028.7 | 1028.0 |
| 157.5° | 1058.0 | 1059.1 | 1060.2 | 1060.7 | 1059.9 | 1058.4 | 1056.9 | 1055.3 | 1053.8 | 1053.4 | 1052.9 |
| 160°   | 1080.0 | 1080.9 | 1081.8 | 1082.2 | 1081.5 | 1080.2 | 1078.9 | 1077.6 | 1076.3 | 1076.1 | 1075.9 |
| 162.5° | 1100.1 | 1101.2 | 1102.3 | 1102.8 | 1102.0 | 1100.5 | 1099.0 | 1097.4 | 1095.9 | 1095.7 | 1095.5 |
| 165°   | 1116.7 | 1117.8 | 1118.9 | 1119.4 | 1118.6 | 1117.1 | 1115.6 | 1114.1 | 1112.6 | 1112.6 | 1112.6 |
| 167.5° | 1131.4 | 1132.5 | 1133.6 | 1134.1 | 1133.3 | 1131.8 | 1130.3 | 1128.8 | 1127.3 | 1127.3 | 1127.3 |
| 170°   | 1142.6 | 1143.9 | 1145.2 | 1145.9 | 1145.1 | 1143.6 | 1142.1 | 1140.5 | 1139.0 | 1139.2 | 1139.4 |
| 172.5° | 1151.4 | 1152.7 | 1154.0 | 1154.7 | 1153.9 | 1152.4 | 1150.9 | 1149.3 | 1147.8 | 1148.0 | 1148.2 |
| 175°   | 1157.3 | 1158.6 | 1159.9 | 1160.6 | 1159.8 | 1158.3 | 1156.8 | 1155.2 | 1153.7 | 1154.1 | 1154.6 |
| 177.5° | 1160.2 | 1161.5 | 1162.8 | 1163.5 | 1162.8 | 1161.5 | 1160.2 | 1158.9 | 1157.6 | 1158.0 | 1158.5 |
| 180°   | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 |

TEST NUMBER: P1010365

CATALOG NUMBER: S122RDIP-B865D925UB27-4F0-XX-W2A-A1

**CANDELA DISTRIBUTION (continued):**

|        | 150°   | 155°   | 157.5° | 160°   | 165°   | 170°   | 175°   | 180°   | 185°   | 190°   | 195°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 |
| 2.5°   | 1921.0 | 1914.5 | 1914.5 | 1910.6 | 1910.6 | 1889.7 | 1889.7 | 1896.2 | 1888.3 | 1879.2 | 1866.1 |
| 5°     | 1970.7 | 1956.3 | 1952.4 | 1947.2 | 1930.2 | 1904.0 | 1893.6 | 1889.7 | 1874.0 | 1854.3 | 1832.1 |
| 7.5°   | 2017.8 | 1994.3 | 1982.5 | 1970.7 | 1948.5 | 1911.9 | 1891.0 | 1876.6 | 1853.0 | 1823.0 | 1794.2 |
| 10°    | 2063.6 | 2033.5 | 2003.4 | 1989.0 | 1957.7 | 1911.9 | 1881.8 | 1858.3 | 1824.3 | 1783.7 | 1743.2 |
| 12.5°  | 2105.4 | 2042.7 | 2037.4 | 2008.7 | 1962.9 | 1910.6 | 1864.8 | 1830.8 | 1787.7 | 1740.6 | 1693.5 |
| 15°    | 2142.0 | 2078.0 | 2046.6 | 2020.4 | 1960.3 | 1894.9 | 1846.5 | 1804.7 | 1747.1 | 1693.5 | 1636.0 |
| 17.5°  | 2160.4 | 2091.0 | 2070.1 | 2027.0 | 1965.5 | 1880.5 | 1815.1 | 1764.1 | 1701.3 | 1637.3 | 1571.9 |
| 20°    | 2178.7 | 2097.6 | 2063.6 | 2033.5 | 1949.8 | 1853.0 | 1779.8 | 1721.0 | 1651.7 | 1575.8 | 1503.9 |
| 22.5°  | 2187.8 | 2097.6 | 2057.0 | 2015.2 | 1934.1 | 1823.0 | 1736.7 | 1667.3 | 1586.3 | 1509.1 | 1422.8 |
| 25°    | 2172.1 | 2089.7 | 2041.4 | 1998.2 | 1906.7 | 1786.3 | 1687.0 | 1608.5 | 1522.2 | 1434.6 | 1347.0 |
| 27.5°  | 2132.9 | 2071.4 | 2015.2 | 1970.7 | 1868.7 | 1739.3 | 1634.7 | 1545.7 | 1456.8 | 1358.7 | 1269.8 |
| 30°    | 2059.7 | 2032.2 | 1987.7 | 1938.0 | 1826.9 | 1697.4 | 1573.2 | 1481.6 | 1383.6 | 1285.5 | 1192.6 |
| 32.5°  | 1945.9 | 1969.4 | 1940.7 | 1897.5 | 1777.2 | 1639.9 | 1507.8 | 1415.0 | 1307.7 | 1201.8 | 1116.8 |
| 35°    | 1807.3 | 1891.0 | 1875.3 | 1845.2 | 1724.9 | 1578.4 | 1446.3 | 1333.9 | 1226.6 | 1119.4 | 1034.4 |
| 37.5°  | 1655.6 | 1782.4 | 1795.5 | 1777.2 | 1664.7 | 1515.6 | 1370.5 | 1260.6 | 1150.8 | 1042.3 | 955.9  |
| 40°    | 1447.6 | 1642.5 | 1684.3 | 1692.2 | 1602.0 | 1439.8 | 1288.1 | 1180.9 | 1072.3 | 966.4  | 861.8  |
| 42.5°  | 1256.7 | 1502.6 | 1554.9 | 1587.6 | 1522.2 | 1365.3 | 1212.3 | 1093.3 | 986.0  | 890.6  | 785.9  |
| 45°    | 1077.6 | 1333.9 | 1418.9 | 1460.7 | 1432.0 | 1280.3 | 1122.0 | 1010.9 | 912.8  | 825.2  | 724.5  |
| 47.5°  | 893.2  | 1150.8 | 1269.8 | 1336.5 | 1336.5 | 1193.9 | 1035.7 | 925.9  | 831.7  | 757.2  | 668.2  |
| 50°    | 770.2  | 984.7  | 1107.6 | 1195.3 | 1218.8 | 1106.3 | 957.3  | 850.0  | 761.1  | 680.0  | 612.0  |
| 52.5°  | 656.5  | 848.7  | 950.7  | 1042.3 | 1110.3 | 1012.2 | 869.6  | 772.9  | 685.2  | 609.4  | 555.8  |
| 55°    | 567.6  | 711.4  | 804.2  | 904.9  | 980.8  | 916.7  | 784.6  | 690.5  | 614.6  | 551.9  | 506.1  |
| 57.5°  | 482.5  | 608.1  | 683.9  | 772.9  | 853.9  | 805.6  | 699.6  | 618.6  | 551.9  | 496.9  | 456.4  |
| 60°    | 410.6  | 512.6  | 571.5  | 640.8  | 741.5  | 707.5  | 619.9  | 545.3  | 491.7  | 442.0  | 408.0  |
| 62.5°  | 349.2  | 430.2  | 479.9  | 529.6  | 621.2  | 605.5  | 537.5  | 479.9  | 434.2  | 392.3  | 363.5  |
| 65°    | 286.4  | 353.1  | 392.3  | 435.5  | 508.7  | 515.2  | 460.3  | 419.8  | 377.9  | 341.3  | 315.2  |
| 67.5°  | 231.5  | 283.8  | 319.1  | 355.7  | 414.5  | 432.9  | 394.9  | 360.9  | 325.6  | 295.5  | 272.0  |
| 70°    | 187.0  | 223.6  | 249.8  | 278.5  | 326.9  | 349.2  | 329.5  | 306.0  | 277.2  | 252.4  | 231.5  |
| 72.5°  | 147.8  | 171.3  | 187.0  | 209.2  | 248.5  | 270.7  | 269.4  | 248.5  | 227.5  | 210.5  | 193.5  |
| 75°    | 108.5  | 126.8  | 139.9  | 154.3  | 185.7  | 206.6  | 211.9  | 202.7  | 181.8  | 168.7  | 155.6  |
| 77.5°  | 82.4   | 92.8   | 99.4   | 109.8  | 132.1  | 150.4  | 158.2  | 155.6  | 141.2  | 130.8  | 121.6  |
| 80°    | 62.8   | 65.4   | 68.0   | 71.9   | 90.2   | 107.2  | 112.5  | 111.2  | 103.3  | 99.4   | 88.9   |
| 82.5°  | 44.5   | 45.8   | 47.1   | 48.4   | 54.9   | 69.3   | 74.5   | 77.2   | 70.6   | 66.7   | 57.5   |
| 85°    | 26.2   | 27.5   | 27.5   | 30.1   | 31.4   | 35.3   | 44.5   | 44.5   | 43.2   | 37.9   | 36.6   |
| 87.5°  | 13.1   | 13.1   | 11.8   | 11.8   | 13.1   | 14.4   | 17.0   | 19.6   | 17.0   | 15.7   | 14.4   |
| 90°    | 19.9   | 15.1   | 12.7   | 11.4   | 8.8    | 6.2    | 3.6    | 1.0    | 3.6    | 6.2    | 8.8    |
| 92.5°  | 29.7   | 29.5   | 29.4   | 28.5   | 26.8   | 25.0   | 23.3   | 21.5   | 23.3   | 25.0   | 26.8   |
| 95°    | 61.4   | 60.9   | 60.7   | 59.6   | 57.4   | 55.3   | 53.1   | 50.9   | 53.1   | 55.3   | 57.4   |
| 97.5°  | 95.3   | 94.4   | 94.0   | 93.0   | 91.1   | 89.1   | 87.2   | 85.2   | 87.2   | 89.1   | 91.1   |
| 100°   | 133.2  | 132.5  | 132.2  | 131.3  | 129.6  | 127.9  | 126.1  | 124.4  | 126.1  | 127.9  | 129.6  |
| 102.5° | 172.7  | 171.8  | 171.4  | 170.7  | 169.4  | 168.1  | 166.8  | 165.5  | 166.8  | 168.1  | 169.4  |
| 105°   | 214.2  | 213.7  | 213.5  | 213.2  | 212.5  | 211.9  | 211.2  | 210.6  | 211.2  | 211.9  | 212.5  |
| 107.5° | 259.5  | 259.5  | 259.5  | 259.1  | 258.2  | 257.3  | 256.5  | 255.6  | 256.5  | 257.3  | 258.2  |
| 110°   | 304.6  | 304.6  | 304.6  | 303.9  | 302.6  | 301.3  | 300.0  | 298.7  | 300.0  | 301.3  | 302.6  |

TEST NUMBER: P1010365

CATALOG NUMBER: S122RDIP-B865D925UB27-4F0-XX-W2A-A1

**CANDELA DISTRIBUTION (continued):**

|        | 150°   | 155°   | 157.5° | 160°   | 165°   | 170°   | 175°   | 180°   | 185°   | 190°   | 195°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 112.5° | 351.3  | 351.5  | 351.6  | 350.9  | 349.6  | 348.3  | 347.0  | 345.7  | 347.0  | 348.3  | 349.6  |
| 115°   | 397.0  | 397.4  | 397.6  | 396.9  | 395.6  | 394.3  | 393.0  | 391.7  | 393.0  | 394.3  | 395.6  |
| 117.5° | 444.0  | 445.1  | 445.6  | 444.7  | 443.0  | 441.3  | 439.5  | 437.8  | 439.5  | 441.3  | 443.0  |
| 120°   | 489.0  | 490.7  | 491.6  | 490.7  | 489.0  | 487.3  | 485.5  | 483.8  | 485.5  | 487.3  | 489.0  |
| 122.5° | 534.1  | 535.2  | 535.7  | 534.6  | 532.4  | 530.3  | 528.1  | 525.9  | 528.1  | 530.3  | 532.4  |
| 125°   | 577.8  | 578.5  | 578.8  | 577.8  | 575.9  | 573.9  | 572.0  | 570.0  | 572.0  | 573.9  | 575.9  |
| 127.5° | 622.6  | 623.5  | 623.9  | 622.7  | 620.3  | 617.9  | 615.5  | 613.1  | 615.5  | 617.9  | 620.3  |
| 130°   | 665.3  | 665.8  | 666.0  | 664.6  | 661.7  | 658.9  | 656.0  | 653.2  | 656.0  | 658.9  | 661.7  |
| 132.5° | 708.4  | 708.2  | 708.1  | 707.0  | 704.8  | 702.7  | 700.5  | 698.3  | 700.5  | 702.7  | 704.8  |
| 135°   | 748.9  | 748.4  | 748.2  | 747.0  | 744.6  | 742.3  | 739.9  | 737.5  | 739.9  | 742.3  | 744.6  |
| 137.5° | 790.0  | 789.6  | 789.4  | 788.4  | 786.5  | 784.5  | 782.6  | 780.6  | 782.6  | 784.5  | 786.5  |
| 140°   | 829.2  | 828.1  | 827.6  | 826.6  | 824.7  | 822.7  | 820.8  | 818.8  | 820.8  | 822.7  | 824.7  |
| 142.5° | 867.7  | 867.0  | 866.7  | 865.7  | 863.8  | 861.8  | 859.9  | 857.9  | 859.9  | 861.8  | 863.8  |
| 145°   | 904.0  | 902.7  | 902.0  | 901.2  | 899.7  | 898.2  | 896.6  | 895.1  | 896.6  | 898.2  | 899.7  |
| 147.5° | 938.6  | 937.7  | 937.3  | 936.3  | 934.3  | 932.4  | 930.4  | 928.4  | 930.4  | 932.4  | 934.3  |
| 150°   | 969.9  | 969.0  | 968.6  | 967.9  | 966.6  | 965.3  | 964.0  | 962.7  | 964.0  | 965.3  | 966.6  |
| 152.5° | 1000.6 | 999.5  | 999.0  | 998.3  | 997.0  | 995.7  | 994.4  | 993.1  | 994.4  | 995.7  | 997.0  |
| 155°   | 1027.4 | 1026.7 | 1026.4 | 1026.1 | 1025.4 | 1024.7 | 1024.1 | 1023.4 | 1024.1 | 1024.7 | 1025.4 |
| 157.5° | 1052.5 | 1052.0 | 1051.8 | 1051.6 | 1051.2 | 1050.7 | 1050.3 | 1049.9 | 1050.3 | 1050.7 | 1051.2 |
| 160°   | 1075.7 | 1075.5 | 1075.4 | 1075.2 | 1074.7 | 1074.3 | 1073.8 | 1073.4 | 1073.8 | 1074.3 | 1074.7 |
| 162.5° | 1095.2 | 1095.0 | 1094.9 | 1094.9 | 1094.9 | 1094.9 | 1094.9 | 1094.9 | 1094.9 | 1094.9 | 1094.9 |
| 165°   | 1112.6 | 1112.6 | 1112.6 | 1112.7 | 1112.9 | 1113.1 | 1113.3 | 1113.5 | 1113.3 | 1113.1 | 1112.9 |
| 167.5° | 1127.3 | 1127.3 | 1127.3 | 1127.6 | 1128.3 | 1128.9 | 1129.6 | 1130.2 | 1129.6 | 1128.9 | 1128.3 |
| 170°   | 1139.7 | 1139.9 | 1140.0 | 1140.3 | 1141.0 | 1141.6 | 1142.3 | 1142.9 | 1142.3 | 1141.6 | 1141.0 |
| 172.5° | 1148.5 | 1148.7 | 1148.8 | 1149.1 | 1149.8 | 1150.4 | 1151.1 | 1151.7 | 1151.1 | 1150.4 | 1149.8 |
| 175°   | 1155.0 | 1155.5 | 1155.7 | 1156.0 | 1156.7 | 1157.3 | 1158.0 | 1158.6 | 1158.0 | 1157.3 | 1156.7 |
| 177.5° | 1158.9 | 1159.4 | 1159.6 | 1159.9 | 1160.6 | 1161.2 | 1161.9 | 1162.5 | 1161.9 | 1161.2 | 1160.6 |
| 180°   | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 |

TEST NUMBER: P1010365

CATALOG NUMBER: S122RDIP-B865D925UB27-4F0-XX-W2A-A1

**CANDELA DISTRIBUTION (continued):**

|        | 200°   | 202.5° | 205°   | 210°   | 215°   | 220°   | 225°   | 230°   | 235°   | 240°   | 245°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 |
| 2.5°   | 1860.9 | 1862.2 | 1866.1 | 1854.3 | 1836.0 | 1828.2 | 1804.7 | 1800.7 | 1796.8 | 1796.8 | 1800.7 |
| 5°     | 1819.0 | 1813.8 | 1815.1 | 1792.9 | 1766.7 | 1751.0 | 1718.3 | 1723.6 | 1706.6 | 1696.1 | 1698.7 |
| 7.5°   | 1773.3 | 1758.9 | 1757.6 | 1728.8 | 1696.1 | 1667.3 | 1633.3 | 1625.5 | 1609.8 | 1591.5 | 1583.6 |
| 10°    | 1715.7 | 1705.3 | 1685.7 | 1653.0 | 1611.1 | 1587.6 | 1541.8 | 1514.3 | 1510.4 | 1483.0 | 1472.5 |
| 12.5°  | 1656.9 | 1638.6 | 1619.0 | 1573.2 | 1526.1 | 1488.2 | 1454.2 | 1424.1 | 1403.2 | 1379.6 | 1364.0 |
| 15°    | 1588.9 | 1566.6 | 1544.4 | 1496.0 | 1441.1 | 1403.2 | 1352.2 | 1307.7 | 1246.3 | 1197.9 | 1170.4 |
| 17.5°  | 1514.3 | 1489.5 | 1459.4 | 1405.8 | 1352.2 | 1299.9 | 1205.7 | 1153.4 | 1110.3 | 1081.5 | 1064.5 |
| 20°    | 1437.2 | 1409.7 | 1379.6 | 1326.0 | 1233.2 | 1141.6 | 1089.3 | 1048.8 | 1022.6 | 993.9  | 972.9  |
| 22.5°  | 1356.1 | 1327.3 | 1294.6 | 1210.9 | 1112.9 | 1048.8 | 1008.3 | 970.3  | 932.4  | 916.7  | 906.3  |
| 25°    | 1280.3 | 1254.1 | 1212.3 | 1098.5 | 1021.3 | 962.5  | 916.7  | 891.9  | 872.2  | 851.3  | 831.7  |
| 27.5°  | 1201.8 | 1153.4 | 1094.6 | 999.1  | 950.7  | 890.6  | 857.9  | 839.6  | 805.6  | 791.2  | 782.0  |
| 30°    | 1107.6 | 1054.0 | 997.8  | 929.8  | 873.6  | 831.7  | 801.6  | 771.6  | 751.9  | 737.6  | 721.9  |
| 32.5°  | 1012.2 | 961.2  | 925.9  | 855.2  | 813.4  | 770.2  | 741.5  | 723.2  | 694.4  | 685.2  | 678.7  |
| 35°    | 929.8  | 886.6  | 855.2  | 797.7  | 758.5  | 719.2  | 698.3  | 670.9  | 652.6  | 635.6  | 625.1  |
| 37.5°  | 848.7  | 825.2  | 792.5  | 744.1  | 702.2  | 670.9  | 642.1  | 632.9  | 608.1  | 598.9  | 588.5  |
| 40°    | 792.5  | 757.2  | 729.7  | 687.9  | 652.6  | 618.6  | 600.2  | 579.3  | 562.3  | 547.9  | 544.0  |
| 42.5°  | 724.5  | 698.3  | 682.6  | 636.9  | 600.2  | 580.6  | 558.4  | 534.9  | 521.8  | 510.0  | 495.6  |
| 45°    | 673.5  | 649.9  | 627.7  | 591.1  | 558.4  | 533.5  | 513.9  | 498.2  | 476.0  | 470.8  | 448.5  |
| 47.5°  | 619.9  | 596.3  | 579.3  | 542.7  | 512.6  | 489.1  | 474.7  | 453.8  | 435.5  | 423.7  | 413.2  |
| 50°    | 566.2  | 546.6  | 530.9  | 499.5  | 473.4  | 448.5  | 428.9  | 408.0  | 400.2  | 380.5  | 374.0  |
| 52.5°  | 515.2  | 502.2  | 485.2  | 455.1  | 428.9  | 408.0  | 387.1  | 370.1  | 358.3  | 347.9  | 340.0  |
| 55°    | 472.1  | 451.2  | 443.3  | 410.6  | 388.4  | 366.2  | 347.9  | 337.4  | 323.0  | 316.5  | 309.9  |
| 57.5°  | 423.7  | 411.9  | 398.9  | 374.0  | 349.2  | 328.2  | 315.2  | 299.5  | 291.6  | 283.8  | 278.5  |
| 60°    | 381.9  | 364.9  | 354.4  | 333.5  | 311.2  | 291.6  | 279.9  | 268.1  | 257.6  | 251.1  | 240.6  |
| 62.5°  | 333.5  | 320.4  | 313.9  | 291.6  | 273.3  | 255.0  | 244.5  | 232.8  | 224.9  | 213.2  | 200.1  |
| 65°    | 291.6  | 281.2  | 273.3  | 255.0  | 238.0  | 221.0  | 210.5  | 196.2  | 185.7  | 179.2  | 177.8  |
| 67.5°  | 255.0  | 247.2  | 235.4  | 218.4  | 201.4  | 188.3  | 176.5  | 164.8  | 163.5  | 160.8  | 160.8  |
| 70°    | 214.5  | 206.6  | 200.1  | 181.8  | 167.4  | 153.0  | 150.4  | 146.5  | 142.5  | 141.2  | 138.6  |
| 72.5°  | 179.2  | 172.6  | 164.8  | 149.1  | 134.7  | 130.8  | 128.2  | 125.5  | 121.6  | 120.3  | 119.0  |
| 75°    | 145.2  | 136.0  | 130.8  | 116.4  | 112.5  | 109.8  | 107.2  | 103.3  | 100.7  | 99.4   | 96.8   |
| 77.5°  | 111.2  | 102.0  | 102.0  | 94.2   | 91.5   | 87.6   | 85.0   | 82.4   | 81.1   | 78.5   | 78.5   |
| 80°    | 78.5   | 78.5   | 75.8   | 71.9   | 68.0   | 66.7   | 62.8   | 61.5   | 60.2   | 61.5   | 58.8   |
| 82.5°  | 57.5   | 52.3   | 52.3   | 49.7   | 47.1   | 45.8   | 43.2   | 43.2   | 41.8   | 41.8   | 41.8   |
| 85°    | 32.7   | 32.7   | 31.4   | 28.8   | 27.5   | 27.5   | 26.2   | 26.2   | 24.8   | 24.8   | 23.5   |
| 87.5°  | 13.1   | 11.8   | 13.1   | 11.8   | 11.8   | 10.5   | 10.5   | 10.5   | 9.2    | 10.5   | 9.2    |
| 90°    | 11.4   | 12.7   | 15.1   | 19.9   | 24.7   | 29.5   | 34.3   | 33.9   | 33.4   | 33.0   | 32.5   |
| 92.5°  | 28.5   | 29.4   | 29.5   | 29.7   | 30.0   | 30.2   | 30.4   | 30.6   | 30.8   | 31.0   | 31.2   |
| 95°    | 59.6   | 60.7   | 60.9   | 61.4   | 61.8   | 62.3   | 62.7   | 62.7   | 62.7   | 62.7   | 62.7   |
| 97.5°  | 93.0   | 94.0   | 94.4   | 95.3   | 96.2   | 97.0   | 97.9   | 97.9   | 97.9   | 97.9   | 97.9   |
| 100°   | 131.3  | 132.2  | 132.5  | 133.2  | 133.9  | 134.5  | 135.2  | 135.2  | 135.2  | 135.2  | 135.2  |
| 102.5° | 170.7  | 171.4  | 171.8  | 172.7  | 173.6  | 174.4  | 175.3  | 175.5  | 175.7  | 176.0  | 176.2  |
| 105°   | 213.2  | 213.5  | 213.7  | 214.2  | 214.6  | 215.1  | 215.5  | 215.9  | 216.3  | 216.8  | 217.2  |
| 107.5° | 259.1  | 259.5  | 259.5  | 259.5  | 259.5  | 259.5  | 259.5  | 259.7  | 259.9  | 260.2  | 260.4  |
| 110°   | 303.9  | 304.6  | 304.6  | 304.6  | 304.6  | 304.6  | 304.6  | 304.6  | 304.6  | 304.6  | 304.6  |

TEST NUMBER: P1010365

CATALOG NUMBER: S122RDIP-B865D925UB27-4F0-XX-W2A-A1

**CANDELA DISTRIBUTION (continued):**

|        | 200°   | 202.5° | 205°   | 210°   | 215°   | 220°   | 225°   | 230°   | 235°   | 240°   | 245°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 112.5° | 350.9  | 351.6  | 351.5  | 351.3  | 351.0  | 350.8  | 350.6  | 350.0  | 349.3  | 348.7  | 348.0  |
| 115°   | 396.9  | 397.6  | 397.4  | 397.0  | 396.5  | 396.1  | 395.7  | 395.5  | 395.3  | 395.0  | 394.8  |
| 117.5° | 444.7  | 445.6  | 445.1  | 444.0  | 442.9  | 441.8  | 440.7  | 440.1  | 439.4  | 438.8  | 438.1  |
| 120°   | 490.7  | 491.6  | 490.7  | 489.0  | 487.3  | 485.5  | 483.8  | 483.8  | 483.8  | 483.8  | 483.8  |
| 122.5° | 534.6  | 535.7  | 535.2  | 534.1  | 533.0  | 531.9  | 530.8  | 530.2  | 529.5  | 528.9  | 528.2  |
| 125°   | 577.8  | 578.8  | 578.5  | 577.8  | 577.2  | 576.5  | 575.9  | 575.2  | 574.6  | 573.9  | 573.2  |
| 127.5° | 622.7  | 623.9  | 623.5  | 622.6  | 621.7  | 620.8  | 619.9  | 619.0  | 618.2  | 617.3  | 616.4  |
| 130°   | 664.6  | 666.0  | 665.8  | 665.3  | 664.9  | 664.4  | 664.0  | 663.6  | 663.2  | 662.7  | 662.3  |
| 132.5° | 707.0  | 708.1  | 708.2  | 708.4  | 708.7  | 708.9  | 709.1  | 708.0  | 706.9  | 705.8  | 704.7  |
| 135°   | 747.0  | 748.2  | 748.4  | 748.9  | 749.3  | 749.8  | 750.2  | 750.0  | 749.8  | 749.5  | 749.3  |
| 137.5° | 788.4  | 789.4  | 789.6  | 790.0  | 790.5  | 790.9  | 791.3  | 791.1  | 790.9  | 790.7  | 790.5  |
| 140°   | 826.6  | 827.6  | 828.1  | 829.2  | 830.3  | 831.4  | 832.5  | 832.5  | 832.5  | 832.5  | 832.5  |
| 142.5° | 865.7  | 866.7  | 867.0  | 867.7  | 868.4  | 869.0  | 869.7  | 869.9  | 870.1  | 870.4  | 870.6  |
| 145°   | 901.2  | 902.0  | 902.7  | 904.0  | 905.3  | 906.6  | 907.9  | 908.1  | 908.3  | 908.6  | 908.8  |
| 147.5° | 936.3  | 937.3  | 937.7  | 938.6  | 939.5  | 940.3  | 941.2  | 941.6  | 942.0  | 942.5  | 942.9  |
| 150°   | 967.9  | 968.6  | 969.0  | 969.9  | 970.8  | 971.6  | 972.5  | 973.2  | 973.8  | 974.5  | 975.2  |
| 152.5° | 998.3  | 999.0  | 999.5  | 1000.6 | 1001.7 | 1002.8 | 1003.9 | 1004.8 | 1005.6 | 1006.5 | 1007.4 |
| 155°   | 1026.1 | 1026.4 | 1026.7 | 1027.4 | 1028.0 | 1028.7 | 1029.3 | 1030.4 | 1031.5 | 1032.6 | 1033.7 |
| 157.5° | 1051.6 | 1051.8 | 1052.0 | 1052.5 | 1052.9 | 1053.4 | 1053.8 | 1055.3 | 1056.9 | 1058.4 | 1059.9 |
| 160°   | 1075.2 | 1075.4 | 1075.5 | 1075.7 | 1075.9 | 1076.1 | 1076.3 | 1077.6 | 1078.9 | 1080.2 | 1081.5 |
| 162.5° | 1094.9 | 1094.9 | 1095.0 | 1095.2 | 1095.5 | 1095.7 | 1095.9 | 1097.4 | 1099.0 | 1100.5 | 1102.0 |
| 165°   | 1112.7 | 1112.6 | 1112.6 | 1112.6 | 1112.6 | 1112.6 | 1112.6 | 1114.1 | 1115.6 | 1117.1 | 1118.6 |
| 167.5° | 1127.6 | 1127.3 | 1127.3 | 1127.3 | 1127.3 | 1127.3 | 1127.3 | 1128.8 | 1130.3 | 1131.8 | 1133.3 |
| 170°   | 1140.3 | 1140.0 | 1139.9 | 1139.7 | 1139.4 | 1139.2 | 1139.0 | 1140.5 | 1142.1 | 1143.6 | 1145.1 |
| 172.5° | 1149.1 | 1148.8 | 1148.7 | 1148.5 | 1148.2 | 1148.0 | 1147.8 | 1149.3 | 1150.9 | 1152.4 | 1153.9 |
| 175°   | 1156.0 | 1155.7 | 1155.5 | 1155.0 | 1154.6 | 1154.1 | 1153.7 | 1155.2 | 1156.8 | 1158.3 | 1159.8 |
| 177.5° | 1159.9 | 1159.6 | 1159.4 | 1158.9 | 1158.5 | 1158.0 | 1157.6 | 1158.9 | 1160.2 | 1161.5 | 1162.8 |
| 180°   | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 |



TEST NUMBER: P1010365

CATALOG NUMBER: S122RDIP-B865D925UB27-4F0-XX-W2A-A1

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250°   | 255°   | 260°   | 265°   | 270°   | 275°   | 280°   | 285°   | 290°   | 292.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 |
| 2.5°   | 1800.7 | 1798.1 | 1790.3 | 1792.9 | 1789.0 | 1789.0 | 1786.3 | 1786.3 | 1786.3 | 1792.9 | 1789.0 |
| 5°     | 1702.7 | 1693.5 | 1684.3 | 1680.4 | 1676.5 | 1672.6 | 1672.6 | 1671.3 | 1683.0 | 1680.4 | 1690.9 |
| 7.5°   | 1581.0 | 1578.4 | 1560.1 | 1560.1 | 1553.6 | 1551.0 | 1557.5 | 1558.8 | 1560.1 | 1562.7 | 1569.3 |
| 10°    | 1472.5 | 1466.0 | 1439.8 | 1442.4 | 1438.5 | 1433.3 | 1437.2 | 1434.6 | 1443.7 | 1446.3 | 1443.7 |
| 12.5°  | 1344.3 | 1332.6 | 1303.8 | 1289.4 | 1273.7 | 1261.9 | 1276.3 | 1265.9 | 1302.5 | 1313.0 | 1341.7 |
| 15°    | 1174.3 | 1152.1 | 1132.5 | 1132.5 | 1118.1 | 1107.6 | 1114.2 | 1125.9 | 1133.8 | 1145.6 | 1150.8 |
| 17.5°  | 1060.6 | 1051.4 | 1035.7 | 1026.6 | 1022.6 | 1018.7 | 1018.7 | 1023.9 | 1040.9 | 1039.6 | 1050.1 |
| 20°    | 963.8  | 958.6  | 950.7  | 938.9  | 935.0  | 932.4  | 932.4  | 932.4  | 944.2  | 954.6  | 961.2  |
| 22.5°  | 897.1  | 893.2  | 887.9  | 872.2  | 864.4  | 861.8  | 868.3  | 872.2  | 881.4  | 889.2  | 895.8  |
| 25°    | 830.4  | 821.2  | 812.1  | 806.9  | 802.9  | 802.9  | 805.6  | 806.9  | 810.8  | 814.7  | 822.6  |
| 27.5°  | 775.5  | 768.9  | 755.9  | 741.5  | 741.5  | 737.6  | 740.2  | 742.8  | 751.9  | 765.0  | 771.6  |
| 30°    | 714.0  | 712.7  | 707.5  | 702.2  | 697.0  | 694.4  | 699.6  | 703.6  | 704.9  | 711.4  | 711.4  |
| 32.5°  | 669.6  | 660.4  | 651.2  | 646.0  | 643.4  | 642.1  | 643.4  | 648.6  | 648.6  | 656.5  | 665.6  |
| 35°    | 625.1  | 619.9  | 610.7  | 601.6  | 598.9  | 592.4  | 597.6  | 602.9  | 612.0  | 615.9  | 619.9  |
| 37.5°  | 576.7  | 570.2  | 566.2  | 563.6  | 558.4  | 559.7  | 555.8  | 563.6  | 571.5  | 570.2  | 572.8  |
| 40°    | 540.1  | 528.3  | 516.5  | 515.2  | 513.9  | 512.6  | 512.6  | 513.9  | 519.2  | 524.4  | 532.2  |
| 42.5°  | 493.0  | 489.1  | 478.6  | 468.2  | 465.5  | 462.9  | 460.3  | 465.5  | 476.0  | 485.2  | 489.1  |
| 45°    | 444.6  | 439.4  | 436.8  | 428.9  | 423.7  | 422.4  | 419.8  | 426.3  | 435.5  | 439.4  | 442.0  |
| 47.5°  | 400.2  | 398.9  | 391.0  | 392.3  | 388.4  | 389.7  | 388.4  | 392.3  | 392.3  | 396.2  | 398.9  |
| 50°    | 370.1  | 366.2  | 362.2  | 359.6  | 355.7  | 355.7  | 354.4  | 355.7  | 360.9  | 366.2  | 364.9  |
| 52.5°  | 340.0  | 333.5  | 332.2  | 330.9  | 328.2  | 330.9  | 326.9  | 328.2  | 333.5  | 336.1  | 334.8  |
| 55°    | 304.7  | 303.4  | 300.8  | 298.2  | 296.9  | 295.5  | 295.5  | 295.5  | 300.8  | 304.7  | 306.0  |
| 57.5°  | 277.2  | 270.7  | 265.5  | 265.5  | 260.2  | 258.9  | 261.5  | 262.9  | 266.8  | 269.4  | 272.0  |
| 60°    | 239.3  | 236.7  | 228.9  | 224.9  | 217.1  | 215.8  | 215.8  | 221.0  | 227.5  | 236.7  | 239.3  |
| 62.5°  | 198.8  | 194.9  | 193.5  | 193.5  | 193.5  | 193.5  | 193.5  | 193.5  | 193.5  | 194.9  | 194.9  |
| 65°    | 176.5  | 177.8  | 176.5  | 175.2  | 176.5  | 176.5  | 175.2  | 175.2  | 175.2  | 176.5  | 177.8  |
| 67.5°  | 158.2  | 156.9  | 158.2  | 156.9  | 155.6  | 155.6  | 154.3  | 155.6  | 156.9  | 158.2  | 158.2  |
| 70°    | 137.3  | 137.3  | 136.0  | 137.3  | 136.0  | 134.7  | 133.4  | 133.4  | 136.0  | 137.3  | 137.3  |
| 72.5°  | 117.7  | 117.7  | 116.4  | 116.4  | 113.8  | 113.8  | 115.1  | 113.8  | 113.8  | 117.7  | 117.7  |
| 75°    | 98.1   | 96.8   | 95.5   | 95.5   | 94.2   | 94.2   | 94.2   | 92.8   | 95.5   | 95.5   | 96.8   |
| 77.5°  | 77.2   | 77.2   | 77.2   | 75.8   | 75.8   | 74.5   | 74.5   | 75.8   | 75.8   | 75.8   | 77.2   |
| 80°    | 58.8   | 58.8   | 58.8   | 57.5   | 56.2   | 56.2   | 56.2   | 56.2   | 56.2   | 57.5   | 56.2   |
| 82.5°  | 40.5   | 40.5   | 40.5   | 40.5   | 40.5   | 39.2   | 39.2   | 39.2   | 40.5   | 40.5   | 39.2   |
| 85°    | 24.8   | 23.5   | 24.8   | 24.8   | 23.5   | 24.8   | 23.5   | 23.5   | 22.2   | 22.2   | 23.5   |
| 87.5°  | 10.5   | 9.2    | 7.8    | 7.8    | 9.2    | 7.8    | 7.8    | 7.8    | 9.2    | 7.8    | 7.8    |
| 90°    | 32.3   | 32.4   | 32.6   | 32.9   | 33.1   | 33.3   | 33.1   | 32.9   | 32.6   | 32.4   | 32.3   |
| 92.5°  | 31.3   | 31.3   | 31.3   | 31.3   | 31.3   | 31.3   | 31.3   | 31.3   | 31.3   | 31.3   | 31.3   |
| 95°    | 62.7   | 62.5   | 62.0   | 61.6   | 61.1   | 60.7   | 61.1   | 61.6   | 62.0   | 62.5   | 62.7   |
| 97.5°  | 97.9   | 97.9   | 97.9   | 97.9   | 97.9   | 97.9   | 97.9   | 97.9   | 97.9   | 97.9   | 97.9   |
| 100°   | 135.2  | 135.1  | 134.9  | 134.6  | 134.4  | 134.2  | 134.4  | 134.6  | 134.9  | 135.1  | 135.2  |
| 102.5° | 176.3  | 176.2  | 176.0  | 175.7  | 175.5  | 175.3  | 175.5  | 175.7  | 176.0  | 176.2  | 176.3  |
| 105°   | 217.4  | 217.4  | 217.4  | 217.4  | 217.4  | 217.4  | 217.4  | 217.4  | 217.4  | 217.4  | 217.4  |
| 107.5° | 260.5  | 260.0  | 258.9  | 257.8  | 256.7  | 255.6  | 256.7  | 257.8  | 258.9  | 260.0  | 260.5  |
| 110°   | 304.6  | 304.3  | 303.6  | 302.9  | 302.3  | 301.6  | 302.3  | 302.9  | 303.6  | 304.3  | 304.6  |



TEST NUMBER: P1010365

CATALOG NUMBER: S122RDIP-B865D925UB27-4F0-XX-W2A-A1

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250°   | 255°   | 260°   | 265°   | 270°   | 275°   | 280°   | 285°   | 290°   | 292.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 112.5° | 347.7  | 347.5  | 347.0  | 346.6  | 346.1  | 345.7  | 346.1  | 346.6  | 347.0  | 347.5  | 347.7  |
| 115°   | 394.7  | 394.4  | 393.7  | 393.0  | 392.4  | 391.7  | 392.4  | 393.0  | 393.7  | 394.4  | 394.7  |
| 117.5° | 437.8  | 437.5  | 436.8  | 436.1  | 435.5  | 434.8  | 435.5  | 436.1  | 436.8  | 437.5  | 437.8  |
| 120°   | 483.8  | 483.5  | 482.8  | 482.2  | 481.5  | 480.9  | 481.5  | 482.2  | 482.8  | 483.5  | 483.8  |
| 122.5° | 527.9  | 527.7  | 527.2  | 526.8  | 526.3  | 525.9  | 526.3  | 526.8  | 527.2  | 527.7  | 527.9  |
| 125°   | 572.9  | 572.8  | 572.6  | 572.4  | 572.2  | 572.0  | 572.2  | 572.4  | 572.6  | 572.8  | 572.9  |
| 127.5° | 616.0  | 615.7  | 615.0  | 614.4  | 613.7  | 613.1  | 613.7  | 614.4  | 615.0  | 615.7  | 616.0  |
| 130°   | 662.1  | 661.7  | 660.8  | 659.9  | 659.0  | 658.1  | 659.0  | 659.9  | 660.8  | 661.7  | 662.1  |
| 132.5° | 704.2  | 703.9  | 703.2  | 702.5  | 701.9  | 701.2  | 701.9  | 702.5  | 703.2  | 703.9  | 704.2  |
| 135°   | 749.2  | 748.9  | 748.2  | 747.6  | 746.9  | 746.3  | 746.9  | 747.6  | 748.2  | 748.9  | 749.2  |
| 137.5° | 790.4  | 790.0  | 789.1  | 788.2  | 787.3  | 786.4  | 787.3  | 788.2  | 789.1  | 790.0  | 790.4  |
| 140°   | 832.5  | 832.1  | 831.2  | 830.3  | 829.4  | 828.5  | 829.4  | 830.3  | 831.2  | 832.1  | 832.5  |
| 142.5° | 870.7  | 870.3  | 869.4  | 868.5  | 867.6  | 866.7  | 867.6  | 868.5  | 869.4  | 870.3  | 870.7  |
| 145°   | 908.9  | 908.5  | 907.6  | 906.7  | 905.8  | 904.9  | 905.8  | 906.7  | 907.6  | 908.5  | 908.9  |
| 147.5° | 943.1  | 942.7  | 941.8  | 940.9  | 940.1  | 939.2  | 940.1  | 940.9  | 941.8  | 942.7  | 943.1  |
| 150°   | 975.5  | 975.2  | 974.5  | 973.8  | 973.2  | 972.5  | 973.2  | 973.8  | 974.5  | 975.2  | 975.5  |
| 152.5° | 1007.8 | 1007.4 | 1006.5 | 1005.6 | 1004.8 | 1003.9 | 1004.8 | 1005.6 | 1006.5 | 1007.4 | 1007.8 |
| 155°   | 1034.2 | 1033.9 | 1033.2 | 1032.6 | 1031.9 | 1031.3 | 1031.9 | 1032.6 | 1033.2 | 1033.9 | 1034.2 |
| 157.5° | 1060.7 | 1060.2 | 1059.1 | 1058.0 | 1056.9 | 1055.8 | 1056.9 | 1058.0 | 1059.1 | 1060.2 | 1060.7 |
| 160°   | 1082.2 | 1081.8 | 1080.9 | 1080.0 | 1079.2 | 1078.3 | 1079.2 | 1080.0 | 1080.9 | 1081.8 | 1082.2 |
| 162.5° | 1102.8 | 1102.3 | 1101.2 | 1100.1 | 1099.0 | 1097.9 | 1099.0 | 1100.1 | 1101.2 | 1102.3 | 1102.8 |
| 165°   | 1119.4 | 1118.9 | 1117.8 | 1116.7 | 1115.6 | 1114.5 | 1115.6 | 1116.7 | 1117.8 | 1118.9 | 1119.4 |
| 167.5° | 1134.1 | 1133.6 | 1132.5 | 1131.4 | 1130.3 | 1129.2 | 1130.3 | 1131.4 | 1132.5 | 1133.6 | 1134.1 |
| 170°   | 1145.9 | 1145.2 | 1143.9 | 1142.6 | 1141.3 | 1140.0 | 1141.3 | 1142.6 | 1143.9 | 1145.2 | 1145.9 |
| 172.5° | 1154.7 | 1154.0 | 1152.7 | 1151.4 | 1150.1 | 1148.8 | 1150.1 | 1151.4 | 1152.7 | 1154.0 | 1154.7 |
| 175°   | 1160.6 | 1159.9 | 1158.6 | 1157.3 | 1156.0 | 1154.7 | 1156.0 | 1157.3 | 1158.6 | 1159.9 | 1160.6 |
| 177.5° | 1163.5 | 1162.8 | 1161.5 | 1160.2 | 1158.9 | 1157.6 | 1158.9 | 1160.2 | 1161.5 | 1162.8 | 1163.5 |
| 180°   | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 |

TEST NUMBER: P1010365

CATALOG NUMBER: S122RDIP-B865D925UB27-4F0-XX-W2A-A1

**CANDELA DISTRIBUTION (continued):**

|        | 295°   | 300°   | 305°   | 310°   | 315°   | 320°   | 325°   | 330°   | 335°   | 337.5° | 340°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 | 1881.8 |
| 2.5°   | 1792.9 | 1799.4 | 1796.8 | 1782.4 | 1796.8 | 1800.7 | 1808.6 | 1816.4 | 1821.7 | 1829.5 | 1836.0 |
| 5°     | 1680.4 | 1693.5 | 1701.3 | 1693.5 | 1719.7 | 1723.6 | 1741.9 | 1752.3 | 1768.0 | 1781.1 | 1791.6 |
| 7.5°   | 1574.5 | 1585.0 | 1600.6 | 1603.3 | 1619.0 | 1637.3 | 1663.4 | 1689.6 | 1714.4 | 1727.5 | 1739.3 |
| 10°    | 1460.7 | 1479.0 | 1502.6 | 1497.3 | 1520.9 | 1549.6 | 1577.1 | 1619.0 | 1639.9 | 1663.4 | 1684.3 |
| 12.5°  | 1347.0 | 1358.7 | 1390.1 | 1400.6 | 1434.6 | 1456.8 | 1494.7 | 1520.9 | 1573.2 | 1600.6 | 1619.0 |
| 15°    | 1148.2 | 1196.6 | 1235.8 | 1282.9 | 1327.3 | 1369.2 | 1403.2 | 1450.3 | 1496.0 | 1517.0 | 1547.0 |
| 17.5°  | 1057.9 | 1080.2 | 1103.7 | 1127.3 | 1184.8 | 1259.3 | 1319.5 | 1370.5 | 1409.7 | 1437.2 | 1472.5 |
| 20°    | 963.8  | 986.0  | 1012.2 | 1034.4 | 1069.7 | 1123.3 | 1197.9 | 1285.5 | 1332.6 | 1361.3 | 1395.3 |
| 22.5°  | 897.1  | 918.0  | 935.0  | 954.6  | 982.1  | 1021.3 | 1077.6 | 1186.1 | 1248.9 | 1284.2 | 1314.3 |
| 25°    | 825.2  | 851.3  | 869.6  | 884.0  | 906.3  | 949.4  | 995.2  | 1056.6 | 1169.1 | 1196.6 | 1238.4 |
| 27.5°  | 775.5  | 783.3  | 804.2  | 826.5  | 848.7  | 872.2  | 919.3  | 971.6  | 1047.5 | 1107.6 | 1158.6 |
| 30°    | 716.6  | 736.2  | 755.9  | 765.0  | 784.6  | 818.6  | 847.4  | 903.6  | 962.5  | 1009.6 | 1071.0 |
| 32.5°  | 672.2  | 683.9  | 697.0  | 719.2  | 737.6  | 761.1  | 789.9  | 836.9  | 886.6  | 916.7  | 963.8  |
| 35°    | 622.5  | 630.3  | 657.8  | 666.9  | 685.2  | 708.8  | 737.6  | 774.2  | 827.8  | 851.3  | 885.3  |
| 37.5°  | 575.4  | 593.7  | 601.6  | 622.5  | 639.5  | 663.0  | 683.9  | 725.8  | 761.1  | 788.6  | 819.9  |
| 40°    | 538.8  | 546.6  | 561.0  | 579.3  | 593.7  | 612.0  | 638.2  | 668.2  | 706.2  | 728.4  | 755.9  |
| 42.5°  | 494.3  | 500.9  | 519.2  | 529.6  | 553.2  | 570.2  | 585.9  | 622.5  | 656.5  | 673.5  | 700.9  |
| 45°    | 445.9  | 461.6  | 473.4  | 494.3  | 507.4  | 528.3  | 547.9  | 574.1  | 605.5  | 625.1  | 640.8  |
| 47.5°  | 404.1  | 419.8  | 431.5  | 451.2  | 472.1  | 481.2  | 502.2  | 529.6  | 558.4  | 574.1  | 596.3  |
| 50°    | 370.1  | 375.3  | 397.5  | 406.7  | 428.9  | 447.2  | 461.6  | 485.2  | 516.5  | 525.7  | 544.0  |
| 52.5°  | 337.4  | 341.3  | 355.7  | 367.5  | 387.1  | 402.8  | 421.1  | 443.3  | 469.5  | 483.9  | 498.2  |
| 55°    | 308.6  | 311.2  | 317.8  | 330.9  | 343.9  | 363.5  | 380.5  | 401.5  | 423.7  | 439.4  | 452.5  |
| 57.5°  | 275.9  | 281.2  | 286.4  | 294.2  | 307.3  | 325.6  | 343.9  | 363.5  | 381.9  | 392.3  | 409.3  |
| 60°    | 238.0  | 245.9  | 255.0  | 264.2  | 273.3  | 286.4  | 307.3  | 325.6  | 342.6  | 351.8  | 364.9  |
| 62.5°  | 197.5  | 213.2  | 221.0  | 231.5  | 239.3  | 251.1  | 266.8  | 287.7  | 299.5  | 311.2  | 321.7  |
| 65°    | 177.8  | 179.2  | 180.5  | 190.9  | 205.3  | 217.1  | 231.5  | 247.2  | 265.5  | 273.3  | 281.2  |
| 67.5°  | 158.2  | 159.5  | 162.2  | 163.5  | 168.7  | 181.8  | 197.5  | 214.5  | 228.9  | 234.1  | 241.9  |
| 70°    | 138.6  | 138.6  | 143.8  | 145.2  | 146.5  | 147.8  | 160.8  | 177.8  | 190.9  | 197.5  | 206.6  |
| 72.5°  | 117.7  | 119.0  | 121.6  | 122.9  | 125.5  | 128.2  | 132.1  | 141.2  | 156.9  | 163.5  | 173.9  |
| 75°    | 96.8   | 98.1   | 99.4   | 100.7  | 104.6  | 105.9  | 109.8  | 115.1  | 121.6  | 129.5  | 136.0  |
| 77.5°  | 77.2   | 77.2   | 78.5   | 81.1   | 83.7   | 85.0   | 88.9   | 91.5   | 94.2   | 98.1   | 103.3  |
| 80°    | 57.5   | 58.8   | 58.8   | 61.5   | 61.5   | 62.8   | 64.1   | 68.0   | 70.6   | 73.2   | 75.8   |
| 82.5°  | 39.2   | 41.8   | 41.8   | 41.8   | 43.2   | 44.5   | 45.8   | 45.8   | 48.4   | 49.7   | 53.6   |
| 85°    | 23.5   | 24.8   | 24.8   | 24.8   | 23.5   | 26.2   | 26.2   | 27.5   | 27.5   | 27.5   | 28.8   |
| 87.5°  | 9.2    | 7.8    | 9.2    | 9.2    | 9.2    | 10.5   | 9.2    | 9.2    | 10.5   | 11.8   | 11.8   |
| 90°    | 32.5   | 33.0   | 33.4   | 33.9   | 34.3   | 29.5   | 24.7   | 19.9   | 15.1   | 12.7   | 11.4   |
| 92.5°  | 31.2   | 31.0   | 30.8   | 30.6   | 30.4   | 30.2   | 30.0   | 29.7   | 29.5   | 29.4   | 28.5   |
| 95°    | 62.7   | 62.7   | 62.7   | 62.7   | 62.7   | 62.3   | 61.8   | 61.4   | 60.9   | 60.7   | 59.6   |
| 97.5°  | 97.9   | 97.9   | 97.9   | 97.9   | 97.9   | 97.0   | 96.2   | 95.3   | 94.4   | 94.0   | 93.0   |
| 100°   | 135.2  | 135.2  | 135.2  | 135.2  | 135.2  | 134.5  | 133.9  | 133.2  | 132.5  | 132.2  | 131.3  |
| 102.5° | 176.2  | 176.0  | 175.7  | 175.5  | 175.3  | 174.4  | 173.6  | 172.7  | 171.8  | 171.4  | 170.7  |
| 105°   | 217.2  | 216.8  | 216.3  | 215.9  | 215.5  | 215.1  | 214.6  | 214.2  | 213.7  | 213.5  | 213.2  |
| 107.5° | 260.4  | 260.2  | 259.9  | 259.7  | 259.5  | 259.5  | 259.5  | 259.5  | 259.5  | 259.5  | 259.1  |
| 110°   | 304.6  | 304.6  | 304.6  | 304.6  | 304.6  | 304.6  | 304.6  | 304.6  | 304.6  | 304.6  | 303.9  |

TEST NUMBER: P1010365

CATALOG NUMBER: S122RDIP-B865D925UB27-4F0-XX-W2A-A1

**CANDELA DISTRIBUTION (continued):**

|        | 295°   | 300°   | 305°   | 310°   | 315°   | 320°   | 325°   | 330°   | 335°   | 337.5° | 340°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 112.5° | 348.0  | 348.7  | 349.3  | 350.0  | 350.6  | 350.8  | 351.0  | 351.3  | 351.5  | 351.6  | 350.9  |
| 115°   | 394.8  | 395.0  | 395.3  | 395.5  | 395.7  | 396.1  | 396.5  | 397.0  | 397.4  | 397.6  | 396.9  |
| 117.5° | 438.1  | 438.8  | 439.4  | 440.1  | 440.7  | 441.8  | 442.9  | 444.0  | 445.1  | 445.6  | 444.7  |
| 120°   | 483.8  | 483.8  | 483.8  | 483.8  | 483.8  | 485.5  | 487.3  | 489.0  | 490.7  | 491.6  | 490.7  |
| 122.5° | 528.2  | 528.9  | 529.5  | 530.2  | 530.8  | 531.9  | 533.0  | 534.1  | 535.2  | 535.7  | 534.6  |
| 125°   | 573.2  | 573.9  | 574.6  | 575.2  | 575.9  | 576.5  | 577.2  | 577.8  | 578.5  | 578.8  | 577.8  |
| 127.5° | 616.4  | 617.3  | 618.2  | 619.0  | 619.9  | 620.8  | 621.7  | 622.6  | 623.5  | 623.9  | 622.7  |
| 130°   | 662.3  | 662.7  | 663.2  | 663.6  | 664.0  | 664.4  | 664.9  | 665.3  | 665.8  | 666.0  | 664.6  |
| 132.5° | 704.7  | 705.8  | 706.9  | 708.0  | 709.1  | 708.9  | 708.7  | 708.4  | 708.2  | 708.1  | 707.0  |
| 135°   | 749.3  | 749.5  | 749.8  | 750.0  | 750.2  | 749.8  | 749.3  | 748.9  | 748.4  | 748.2  | 747.0  |
| 137.5° | 790.5  | 790.7  | 790.9  | 791.1  | 791.3  | 790.9  | 790.5  | 790.0  | 789.6  | 789.4  | 788.4  |
| 140°   | 832.5  | 832.5  | 832.5  | 832.5  | 832.5  | 831.4  | 830.3  | 829.2  | 828.1  | 827.6  | 826.6  |
| 142.5° | 870.6  | 870.4  | 870.1  | 869.9  | 869.7  | 869.0  | 868.4  | 867.7  | 867.0  | 866.7  | 865.7  |
| 145°   | 908.8  | 908.6  | 908.3  | 908.1  | 907.9  | 906.6  | 905.3  | 904.0  | 902.7  | 902.0  | 901.2  |
| 147.5° | 942.9  | 942.5  | 942.0  | 941.6  | 941.2  | 940.3  | 939.5  | 938.6  | 937.7  | 937.3  | 936.3  |
| 150°   | 975.2  | 974.5  | 973.8  | 973.2  | 972.5  | 971.6  | 970.8  | 969.9  | 969.0  | 968.6  | 967.9  |
| 152.5° | 1007.4 | 1006.5 | 1005.6 | 1004.8 | 1003.9 | 1002.8 | 1001.7 | 1000.6 | 999.5  | 999.0  | 998.3  |
| 155°   | 1033.7 | 1032.6 | 1031.5 | 1030.4 | 1029.3 | 1028.7 | 1028.0 | 1027.4 | 1026.7 | 1026.4 | 1026.1 |
| 157.5° | 1059.9 | 1058.4 | 1056.9 | 1055.3 | 1053.8 | 1053.4 | 1052.9 | 1052.5 | 1052.0 | 1051.8 | 1051.6 |
| 160°   | 1081.5 | 1080.2 | 1078.9 | 1077.6 | 1076.3 | 1076.1 | 1075.9 | 1075.7 | 1075.5 | 1075.4 | 1075.2 |
| 162.5° | 1102.0 | 1100.5 | 1099.0 | 1097.4 | 1095.9 | 1095.7 | 1095.5 | 1095.2 | 1095.0 | 1094.9 | 1094.9 |
| 165°   | 1118.6 | 1117.1 | 1115.6 | 1114.1 | 1112.6 | 1112.6 | 1112.6 | 1112.6 | 1112.6 | 1112.6 | 1112.7 |
| 167.5° | 1133.3 | 1131.8 | 1130.3 | 1128.8 | 1127.3 | 1127.3 | 1127.3 | 1127.3 | 1127.3 | 1127.3 | 1127.6 |
| 170°   | 1145.1 | 1143.6 | 1142.1 | 1140.5 | 1139.0 | 1139.2 | 1139.4 | 1139.7 | 1139.9 | 1140.0 | 1140.3 |
| 172.5° | 1153.9 | 1152.4 | 1150.9 | 1149.3 | 1147.8 | 1148.0 | 1148.2 | 1148.5 | 1148.7 | 1148.8 | 1149.1 |
| 175°   | 1159.8 | 1158.3 | 1156.8 | 1155.2 | 1153.7 | 1154.1 | 1154.6 | 1155.0 | 1155.5 | 1155.7 | 1156.0 |
| 177.5° | 1162.8 | 1161.5 | 1160.2 | 1158.9 | 1157.6 | 1158.0 | 1158.5 | 1158.9 | 1159.4 | 1159.6 | 1159.9 |
| 180°   | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 | 1160.6 |

TEST NUMBER: P1010365

CATALOG NUMBER: S122RDIP-B865D925UB27-4F0-XX-W2A-A1

**CANDELA DISTRIBUTION (continued):**

|        | 345°   | 350°   | 355°   | 360°   |
|--------|--------|--------|--------|--------|
| 0°     | 1881.8 | 1881.8 | 1881.8 | 1881.8 |
| 2.5°   | 1847.8 | 1843.9 | 1867.4 | 1893.6 |
| 5°     | 1809.9 | 1816.4 | 1846.5 | 1883.1 |
| 7.5°   | 1770.7 | 1785.0 | 1820.3 | 1868.7 |
| 10°    | 1715.7 | 1741.9 | 1795.5 | 1845.2 |
| 12.5°  | 1662.1 | 1697.4 | 1748.4 | 1807.3 |
| 15°    | 1602.0 | 1641.2 | 1704.0 | 1774.6 |
| 17.5°  | 1535.3 | 1579.7 | 1653.0 | 1730.1 |
| 20°    | 1464.6 | 1523.5 | 1600.6 | 1684.3 |
| 22.5°  | 1386.2 | 1456.8 | 1536.6 | 1629.4 |
| 25°    | 1310.3 | 1387.5 | 1467.3 | 1574.5 |
| 27.5°  | 1235.8 | 1311.6 | 1400.6 | 1509.1 |
| 30°    | 1161.3 | 1230.6 | 1326.0 | 1442.4 |
| 32.5°  | 1081.5 | 1153.4 | 1254.1 | 1373.1 |
| 35°    | 1008.3 | 1080.2 | 1174.3 | 1292.0 |
| 37.5°  | 929.8  | 1006.9 | 1097.2 | 1218.8 |
| 40°    | 838.2  | 928.5  | 1016.1 | 1132.5 |
| 42.5°  | 762.4  | 857.9  | 942.9  | 1052.7 |
| 45°    | 702.2  | 792.5  | 863.1  | 970.3  |
| 47.5°  | 646.0  | 719.2  | 791.2  | 890.6  |
| 50°    | 592.4  | 648.6  | 723.2  | 812.1  |
| 52.5°  | 537.5  | 585.9  | 649.9  | 733.6  |
| 55°    | 487.8  | 533.5  | 591.1  | 655.2  |
| 57.5°  | 442.0  | 474.7  | 532.2  | 589.8  |
| 60°    | 391.0  | 425.0  | 469.5  | 517.9  |
| 62.5°  | 347.9  | 374.0  | 415.9  | 456.4  |
| 65°    | 302.1  | 326.9  | 358.3  | 396.2  |
| 67.5°  | 260.2  | 282.5  | 307.3  | 337.4  |
| 70°    | 222.3  | 239.3  | 257.6  | 283.8  |
| 72.5°  | 181.8  | 200.1  | 217.1  | 238.0  |
| 75°    | 149.1  | 156.9  | 171.3  | 185.7  |
| 77.5°  | 115.1  | 125.5  | 133.4  | 145.2  |
| 80°    | 82.4   | 91.5   | 94.2   | 103.3  |
| 82.5°  | 54.9   | 60.2   | 65.4   | 68.0   |
| 85°    | 31.4   | 34.0   | 39.2   | 40.5   |
| 87.5°  | 11.8   | 13.1   | 15.7   | 18.3   |
| 90°    | 8.8    | 6.2    | 3.6    | 1.0    |
| 92.5°  | 26.8   | 25.0   | 23.3   | 21.5   |
| 95°    | 57.4   | 55.3   | 53.1   | 50.9   |
| 97.5°  | 91.1   | 89.1   | 87.2   | 85.2   |
| 100°   | 129.6  | 127.9  | 126.1  | 124.4  |
| 102.5° | 169.4  | 168.1  | 166.8  | 165.5  |
| 105°   | 212.5  | 211.9  | 211.2  | 210.6  |
| 107.5° | 258.2  | 257.3  | 256.5  | 255.6  |
| 110°   | 302.6  | 301.3  | 300.0  | 298.7  |



TEST NUMBER: P1010365

CATALOG NUMBER: S122RDIP-B865D925UB27-4F0-XX-W2A-A1

**CANDELA DISTRIBUTION (continued):**

|        | 345°   | 350°   | 355°   | 360°   |
|--------|--------|--------|--------|--------|
| 112.5° | 349.6  | 348.3  | 347.0  | 345.7  |
| 115°   | 395.6  | 394.3  | 393.0  | 391.7  |
| 117.5° | 443.0  | 441.3  | 439.5  | 437.8  |
| 120°   | 489.0  | 487.3  | 485.5  | 483.8  |
| 122.5° | 532.4  | 530.3  | 528.1  | 525.9  |
| 125°   | 575.9  | 573.9  | 572.0  | 570.0  |
| 127.5° | 620.3  | 617.9  | 615.5  | 613.1  |
| 130°   | 661.7  | 658.9  | 656.0  | 653.2  |
| 132.5° | 704.8  | 702.7  | 700.5  | 698.3  |
| 135°   | 744.6  | 742.3  | 739.9  | 737.5  |
| 137.5° | 786.5  | 784.5  | 782.6  | 780.6  |
| 140°   | 824.7  | 822.7  | 820.8  | 818.8  |
| 142.5° | 863.8  | 861.8  | 859.9  | 857.9  |
| 145°   | 899.7  | 898.2  | 896.6  | 895.1  |
| 147.5° | 934.3  | 932.4  | 930.4  | 928.4  |
| 150°   | 966.6  | 965.3  | 964.0  | 962.7  |
| 152.5° | 997.0  | 995.7  | 994.4  | 993.1  |
| 155°   | 1025.4 | 1024.7 | 1024.1 | 1023.4 |
| 157.5° | 1051.2 | 1050.7 | 1050.3 | 1049.9 |
| 160°   | 1074.7 | 1074.3 | 1073.8 | 1073.4 |
| 162.5° | 1094.9 | 1094.9 | 1094.9 | 1094.9 |
| 165°   | 1112.9 | 1113.1 | 1113.3 | 1113.5 |
| 167.5° | 1128.3 | 1128.9 | 1129.6 | 1130.2 |
| 170°   | 1141.0 | 1141.6 | 1142.3 | 1142.9 |
| 172.5° | 1149.8 | 1150.4 | 1151.1 | 1151.7 |
| 175°   | 1156.7 | 1157.3 | 1158.0 | 1158.6 |
| 177.5° | 1160.6 | 1161.2 | 1161.9 | 1162.5 |
| 180°   | 1160.6 | 1160.6 | 1160.6 | 1160.6 |

(END OF REPORT)