

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009411

Luminaire Tested: S122DIP-B675D925UB35-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009411
REPORT IS A COMBINATION OF REPORTS P984697 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D925UB35-4F0-XX-W2A-F
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6408.0 lumens
Efficiency: N/A
Efficacy: 99.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009411

CATALOG NUMBER: S122DIP-B675D925UB35-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1009411

CATALOG NUMBER: S122DIP-B675D925UB35-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	44	43	42
2	88	80	74	69	80	73	68	64	61	57	54	49	47	44	38	37	35
3	80	70	63	57	73	65	58	53	54	49	45	43	40	37	34	32	30
4	73	62	55	49	66	57	50	45	48	43	38	39	35	32	30	28	26
5	67	55	47	42	61	51	44	39	43	37	33	35	31	28	27	25	22
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20
7	57	45	37	31	52	41	34	29	35	29	25	28	24	21	23	20	18
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16967	16967	16967
5°	16995	16172	16058
10°	16856	15435	15129
15°	16609	14694	14152
20°	16276	13886	13227
25°	15944	13042	12304
30°	15524	12249	11334
35°	15131	11412	10383
40°	14643	10587	9482
45°	14159	9769	8599
50°	13628	8936	7684
55°	13073	8044	6817
60°	12447	7080	5915
65°	11760	6100	4967
70°	10892	5029	4010
75°	9683	3875	3097
80°	8231	2635	1993
85°	5975	1226	849

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14159 cd/sqm

TEST NUMBER: P1009411

CATALOG NUMBER: S122DIP-B675D925UB35-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.9	1.6
10°-20°	283.8	4.4
20°-30°	417.1	6.5
30°-40°	484.5	7.6
40°-50°	483.9	7.6
50°-60°	421.9	6.6
60°-70°	311.9	4.9
70°-80°	176.5	2.8
80°-90°	48.8	0.8
90°-100°	41.4	0.6
100°-110°	154.2	2.4
110°-120°	409.1	6.4
120°-130°	678.5	10.6
130°-140°	720.7	11.2
140°-150°	669.9	10.5
150°-160°	538.5	8.4
160°-170°	347.0	5.4
170°-180°	119.4	1.9
0°-30°	801.8	12.5
0°-40°	1286.3	20.1
0°-60°	2192.1	34.2
0°-90°	2729.2	42.6
90°-120°	604.7	9.4
90°-150°	2673.8	41.7
90°-180°	3679.0	57.4
0°-180°	6408.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1072	1072	1072	1072	1072	
5°	1072	1068	1056	1065	1063	102
15°	1020	1014	1001	1005	1000	287
25°	924	915	898	900	898	425
35°	797	786	770	764	759	497
45°	648	641	626	614	610	500
55°	491	484	472	460	454	439
65°	331	325	314	305	300	327
75°	173	171	166	160	162	185
85°	42	41	40	37	36	47
90°	1	11	18	23	24	6
95°	59	29	35	40	39	70
105°	276	303	55	65	69	295
115°	522	538	560	140	74	514
125°	738	750	767	774	776	658
135°	913	928	936	945	943	706
145°	1060	1059	1074	1080	1076	663
155°	1167	1159	1170	1175	1168	538
165°	1229	1224	1227	1233	1227	347
175°	1258	1251	1253	1259	1250	120
180°	1255	1255	1255	1255	1255	

TEST NUMBER: P1009411

CATALOG NUMBER: S122DIP-B675D925UB35-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1071.9	1071.9	1071.9	1071.9	1071.9
2.5°	1078.1	1072.9	1061.6	1071.9	1069.8
5°	1071.9	1067.7	1056.4	1064.7	1062.6
7.5°	1064.7	1058.5	1047.1	1055.4	1053.3
10°	1053.3	1046.1	1033.7	1042.0	1038.9
12.5°	1037.9	1031.7	1019.3	1024.5	1022.4
15°	1020.3	1014.2	1000.8	1004.9	999.7
17.5°	998.7	992.5	979.1	984.3	979.1
20°	975.0	968.8	954.4	957.5	953.3
22.5°	951.3	942.0	928.6	928.6	926.5
25°	923.5	915.2	897.7	899.7	897.7
27.5°	892.5	885.3	871.9	868.8	863.7
30°	861.6	853.4	837.9	834.8	830.7
32.5°	828.6	822.5	806.0	799.8	795.7
35°	796.7	786.4	769.9	763.7	758.6
37.5°	760.6	751.3	734.8	727.6	722.5
40°	723.5	715.3	698.8	689.5	685.4
42.5°	687.4	679.2	662.7	652.4	646.2
45°	648.3	641.1	625.6	614.3	610.1
47.5°	610.1	602.9	586.4	575.1	568.9
50°	569.9	564.8	550.4	535.9	530.8
52.5°	530.8	523.6	510.2	498.8	491.6
55°	490.6	484.4	472.0	459.7	454.5
57.5°	450.4	445.2	431.8	419.5	415.3
60°	410.2	406.1	391.6	380.3	377.2
62.5°	371.0	363.8	353.5	343.2	339.1
65°	330.8	324.7	314.3	305.1	299.9
67.5°	289.6	284.5	275.2	268.0	263.8
70°	251.5	247.4	238.1	230.9	226.7
72.5°	212.3	208.2	203.0	195.8	192.7
75°	173.1	171.1	165.9	159.7	161.8
77.5°	138.1	134.0	131.9	128.8	125.7
80°	103.1	102.0	100.0	96.9	94.8
82.5°	70.1	70.1	69.1	64.9	64.9
85°	42.3	41.2	40.2	37.1	36.1
87.5°	18.6	16.5	14.4	11.3	10.3
90°	0.9	10.9	18.2	22.7	24.5
92.5°	22.7	19.1	21.8	23.6	24.5
95°	59.0	29.1	35.4	40.0	39.0
97.5°	106.2	31.8	46.3	49.0	49.9
100°	160.7	36.3	51.8	59.0	60.8
102.5°	220.6	218.8	53.6	63.6	66.3
105°	276.0	303.3	55.4	65.4	69.0
107.5°	340.5	363.2	57.2	67.2	70.8
110°	402.2	421.3	158.9	68.1	71.7

TEST NUMBER: P1009411

CATALOG NUMBER: S122DIP-B675D925UB35-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	460.4	476.7	461.3	69.9	72.6
115°	522.1	537.5	560.2	139.8	74.5
117.5°	575.7	593.8	609.3	479.4	241.5
120°	635.6	649.2	665.6	676.5	553.9
122.5°	686.4	701.0	719.1	724.6	725.5
125°	738.2	750.0	767.3	773.6	776.3
127.5°	785.4	798.1	811.8	820.8	821.7
130°	829.9	844.4	854.4	864.4	863.5
132.5°	875.3	887.1	897.1	905.3	904.4
135°	913.4	928.0	936.1	945.2	943.4
137.5°	953.4	964.3	973.4	982.5	979.7
140°	992.4	999.7	1009.7	1017.9	1013.3
142.5°	1025.1	1031.5	1043.3	1050.6	1046.0
145°	1059.6	1058.7	1074.2	1080.5	1076.0
147.5°	1089.6	1086.9	1102.3	1106.9	1103.2
150°	1118.7	1112.3	1126.8	1132.3	1127.7
152.5°	1143.2	1135.9	1149.5	1155.0	1148.6
155°	1166.8	1158.6	1169.5	1175.0	1167.7
157.5°	1185.8	1178.6	1186.8	1193.1	1185.8
160°	1202.2	1196.7	1202.2	1207.6	1201.3
162.5°	1216.7	1211.3	1215.8	1222.2	1214.0
165°	1229.4	1224.0	1226.7	1233.1	1226.7
167.5°	1239.4	1234.0	1236.7	1243.1	1234.9
170°	1247.6	1242.1	1244.0	1250.3	1242.1
172.5°	1253.0	1247.6	1249.4	1255.8	1247.6
175°	1257.6	1251.2	1253.0	1259.4	1250.3
177.5°	1259.4	1253.0	1253.9	1260.3	1252.1
180°	1254.9	1254.9	1254.9	1254.9	1254.9

(END OF REPORT)