

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010393

Luminaire Tested: S122RDIP-B865D925UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010393
REPORT IS A COMBINATION OF REPORTS P988818 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B865D925UB50-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6330.0 lumens
Efficiency: N/A
Efficacy: 84.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010393

CATALOG NUMBER: S122RDIP-B865D925UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1010393

CATALOG NUMBER: S122RDIP-B865D925UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46	46	46
1	97	93	89	86	89	86	82	80	72	69	67	59	57	56	47	46	45	39	39	39
2	89	82	76	71	81	75	70	66	63	60	56	52	49	47	42	40	38	34	34	34
3	81	72	65	60	74	67	61	56	56	52	48	46	43	40	37	35	33	29	29	29
4	75	64	57	51	68	59	53	48	50	45	41	42	38	35	34	31	29	25	25	25
5	69	57	50	44	63	53	46	41	45	40	36	37	34	31	30	28	26	22	22	22
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20	20	20
7	59	47	39	34	54	43	37	32	37	32	28	31	27	24	25	23	20	18	18	18
8	54	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	18	16	16	16
9	51	39	32	27	47	36	30	25	31	26	22	26	22	19	22	19	17	14	14	14
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15	13	13	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22182	22182	22182
5°	22218	21103	20947
10°	21999	20016	19354
15°	21696	18731	17540
20°	21297	17270	15642
25°	20886	15770	13905
30°	20337	14311	12008
35°	19797	12840	10380
40°	19249	11394	8702
45°	18612	9901	7239
50°	17954	8462	5894
55°	17267	7025	4679
60°	16471	5617	3539
65°	15553	4283	2877
70°	14443	3107	2289
75°	13051	2371	1748
80°	11034	1605	1173
85°	7698	735	567

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18612 cd/sqm

TEST NUMBER: P1010393

CATALOG NUMBER: S122RDIP-B865D925UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.3	2.1
10°-20°	360.5	5.7
20°-30°	506.2	8.0
30°-40°	551.8	8.7
40°-50°	507.1	8.0
50°-60°	398.3	6.3
60°-70°	259.2	4.1
70°-80°	133.5	2.1
80°-90°	37.2	0.6
90°-100°	200.3	3.2
100°-110°	677.1	10.7
110°-120°	711.8	11.2
120°-130°	585.3	9.2
130°-140°	470.3	7.4
140°-150°	355.3	5.6
150°-160°	249.8	3.9
160°-170°	147.1	2.3
170°-180°	47.8	0.8
0°-30°	998.1	15.8
0°-40°	1549.8	24.5
0°-60°	2455.2	38.8
0°-90°	2885.2	45.6
90°-120°	1589.2	25.1
90°-150°	3000.1	47.4
90°-180°	3445.0	54.4
0°-180°	6330.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1401	1401	1401	1401	1401	
5°	1401	1395	1378	1390	1386	133
15°	1333	1319	1276	1252	1239	376
25°	1210	1169	1086	1034	1014	556
35°	1042	978	866	786	758	652
45°	852	767	634	544	514	658
55°	648	549	412	336	312	579
65°	438	335	221	178	174	434
75°	233	145	102	93	91	247
85°	54	28	24	24	24	63
90°	1	13	32	31	31	5
95°	33	82	372	141	108	34
105°	116	175	704	1258	1071	123
115°	204	258	589	1216	1409	203
125°	285	337	566	985	1143	253
135°	334	399	560	828	947	258
145°	382	439	557	691	756	240
155°	434	469	541	611	636	200
165°	473	487	518	549	558	133
175°	493	494	498	504	503	47
180°	494	494	494	494	494	

TEST NUMBER: P1010393

CATALOG NUMBER: S122RDIP-B865D925UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1401.3	1401.3	1401.3	1401.3	1401.3
2.5°	1407.7	1401.3	1387.4	1400.1	1397.5
5°	1401.3	1395.0	1378.5	1389.9	1386.1
7.5°	1389.9	1382.3	1364.5	1369.6	1363.3
10°	1374.7	1365.8	1340.5	1336.6	1329.0
12.5°	1355.7	1344.3	1310.0	1302.4	1288.5
15°	1332.8	1318.9	1275.8	1251.7	1239.0
17.5°	1306.2	1285.9	1232.7	1204.8	1184.5
20°	1275.8	1250.4	1187.0	1155.3	1127.4
22.5°	1242.8	1213.6	1140.1	1097.0	1077.9
25°	1209.8	1169.2	1085.5	1033.6	1014.5
27.5°	1170.5	1127.4	1034.8	975.2	946.1
30°	1128.7	1080.5	979.0	914.3	880.1
32.5°	1088.1	1029.8	925.8	849.7	818.0
35°	1042.4	977.8	866.2	786.3	758.4
37.5°	998.0	928.3	810.4	722.9	691.2
40°	951.1	875.0	752.0	662.0	629.0
42.5°	902.9	821.8	693.7	599.8	568.1
45°	852.2	767.2	634.1	544.0	513.6
47.5°	804.0	714.0	577.0	487.0	459.1
50°	750.8	660.7	521.2	433.7	407.1
52.5°	698.8	603.6	468.0	384.3	360.2
55°	648.0	549.1	412.2	336.1	312.0
57.5°	596.0	494.6	362.7	291.7	271.4
60°	542.8	441.3	310.7	246.0	225.7
62.5°	490.8	389.3	266.3	205.4	195.3
65°	437.5	334.8	220.7	177.5	173.7
67.5°	386.8	284.1	177.5	156.0	152.2
70°	333.5	234.6	147.1	134.4	129.4
72.5°	282.8	189.0	123.0	112.9	110.3
75°	233.3	144.6	101.5	92.6	91.3
77.5°	183.9	102.7	79.9	74.8	72.3
80°	138.2	73.6	60.9	55.8	55.8
82.5°	96.4	49.5	41.8	39.3	39.3
85°	54.5	27.9	24.1	24.1	24.1
87.5°	20.3	10.1	10.1	8.9	8.9
90°	1.0	12.8	32.3	30.9	31.4
92.5°	14.3	45.2	146.3	67.5	58.0
95°	33.3	81.7	372.5	140.6	108.3
97.5°	49.4	107.8	607.2	282.2	181.5
100°	73.2	132.1	750.6	562.0	340.2
102.5°	95.0	153.9	755.4	950.2	663.2
105°	115.9	174.8	704.1	1258.5	1070.8
107.5°	138.7	195.7	656.6	1370.1	1345.4
110°	161.5	217.1	624.3	1352.0	1457.6

TEST NUMBER: P1010393

CATALOG NUMBER: S122RDIP-B865D925UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	182.4	237.6	603.4	1290.8	1455.7
115°	204.3	258.0	589.1	1215.8	1409.1
117.5°	227.1	278.4	581.5	1144.0	1338.8
120°	248.0	298.4	574.8	1079.8	1271.3
122.5°	267.9	318.8	571.0	1030.0	1201.0
125°	285.0	337.3	566.3	984.8	1143.0
127.5°	299.3	354.9	563.4	946.4	1088.9
130°	311.7	370.6	561.5	907.4	1044.2
132.5°	323.1	385.8	560.6	867.0	997.7
135°	334.5	399.1	559.6	827.6	947.3
137.5°	344.9	410.4	559.6	787.6	898.9
140°	357.3	421.0	558.7	752.5	848.5
142.5°	369.6	429.5	558.7	718.8	798.1
145°	382.0	439.0	556.8	691.2	756.3
147.5°	395.3	446.6	553.9	667.0	719.3
150°	408.6	454.2	551.1	646.2	687.0
152.5°	421.9	461.8	546.3	628.6	659.4
155°	434.2	468.9	540.6	611.4	635.7
157.5°	444.7	474.6	534.9	595.3	614.8
160°	455.1	480.3	529.2	579.2	594.8
162.5°	465.6	484.6	524.5	563.9	575.8
165°	473.2	487.4	517.8	549.2	557.7
167.5°	479.8	490.3	512.1	535.9	540.6
170°	486.5	491.7	507.4	523.6	525.4
172.5°	490.3	493.2	501.7	512.6	513.1
175°	493.1	493.6	497.9	504.0	502.6
177.5°	495.0	494.1	494.1	497.9	495.0
180°	494.1	494.1	494.1	494.1	494.1

(END OF REPORT)