

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009418

Luminaire Tested: S122DIP-B675D925UB40-4F0-XX-W2A-D1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009418
REPORT IS A COMBINATION OF REPORTS P984704 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B675D925UB40-4F0-XX-W2A-D1
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5944.9 lumens
Efficiency: N/A
Efficacy: 92.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009418

CATALOG NUMBER: S122DIP-B675D925UB40-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1009418

CATALOG NUMBER: S122DIP-B675D925UB40-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47
1	94	90	85	81	86	82	78	75	66	64	61	53	51	49	40	38	37
2	85	78	71	65	77	71	65	60	57	53	50	45	42	40	34	32	31
3	78	68	60	54	70	62	55	50	50	45	41	40	36	33	30	28	25
4	71	60	51	45	64	54	47	42	44	39	35	35	31	28	27	24	22
5	65	53	45	38	59	48	41	35	39	34	30	31	27	24	24	21	19
6	60	47	39	33	54	43	36	31	35	30	26	28	24	21	21	18	16
7	55	42	34	29	50	39	32	27	32	26	22	26	21	18	20	17	14
8	51	38	31	25	46	35	28	23	29	24	20	23	19	16	18	15	13
9	47	35	27	22	43	32	25	21	27	21	18	21	17	14	16	14	11
10	44	32	25	20	40	29	23	18	24	19	16	20	16	13	15	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11147	11147	11147
5°	11197	10672	10612
10°	11122	10301	10152
15°	10965	9919	9680
20°	10767	9518	9232
25°	10573	9134	8827
30°	10297	8743	8425
35°	10020	8366	8130
40°	9729	8041	7836
45°	9450	7745	7580
50°	9152	7473	7328
55°	8839	7184	7072
60°	8454	6883	6801
65°	8055	6537	6491
70°	7600	6165	6156
75°	7021	5793	5842
80°	6108	5405	5514
85°	5184	5040	5232

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9450 cd/sqm

TEST NUMBER: P1009418

CATALOG NUMBER: S122DIP-B675D925UB40-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.8	1.1
10°-20°	191.5	3.2
20°-30°	290.1	4.9
30°-40°	353.3	5.9
40°-50°	380.1	6.4
50°-60°	369.1	6.2
60°-70°	322.4	5.4
70°-80°	248.1	4.2
80°-90°	169.5	2.9
90°-100°	186.6	3.1
100°-110°	312.6	5.3
110°-120°	447.0	7.5
120°-130°	546.0	9.2
130°-140°	591.2	9.9
140°-150°	569.3	9.6
150°-160°	475.7	8.0
160°-170°	315.5	5.3
170°-180°	110.3	1.9
0°-30°	548.3	9.2
0°-40°	901.6	15.2
0°-60°	1650.8	27.8
0°-90°	2390.8	40.2
90°-120°	946.3	15.9
90°-150°	2652.8	44.6
90°-180°	3554.0	59.8
0°-180°	5944.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	704	704	704	704	704	
5°	706	703	697	703	702	67
15°	674	676	676	685	684	190
25°	612	620	629	641	644	282
35°	528	545	564	587	594	330
45°	433	460	496	528	538	334
55°	332	368	422	458	472	297
65°	227	277	337	379	392	225
75°	126	183	248	292	305	133
85°	37	100	165	208	222	39
90°	11	82	169	208	221	10
95°	59	117	180	219	229	63
105°	216	249	304	342	353	229
115°	397	414	458	488	496	392
125°	574	583	612	637	645	513
135°	741	752	764	784	789	573
145°	898	905	911	918	919	561
155°	1027	1030	1032	1037	1034	473
165°	1117	1116	1116	1123	1118	315
175°	1162	1159	1157	1164	1158	110
180°	1164	1164	1164	1164	1164	

TEST NUMBER: P1009418

CATALOG NUMBER: S122DIP-B675D925UB40-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	704.2	704.2	704.2	704.2	704.2
2.5°	709.3	706.2	699.1	704.2	702.2
5°	706.2	703.2	697.1	703.2	702.2
7.5°	701.1	699.1	694.0	701.1	700.1
10°	695.0	693.0	689.9	698.1	697.1
12.5°	684.8	685.8	683.8	692.0	690.9
15°	673.6	675.6	675.6	684.8	683.8
17.5°	659.3	663.4	666.4	675.6	675.6
20°	645.0	650.1	654.2	665.4	665.4
22.5°	629.7	635.8	641.9	653.2	655.2
25°	612.4	619.5	628.7	640.9	644.0
27.5°	591.9	603.2	613.4	628.7	630.7
30°	571.5	584.8	598.1	614.4	617.5
32.5°	549.1	564.4	580.7	600.1	606.2
35°	527.6	545.0	564.4	586.8	594.0
37.5°	504.2	523.6	548.1	572.5	579.7
40°	480.7	503.1	530.7	557.2	566.4
42.5°	458.2	480.7	513.4	543.0	552.1
45°	432.7	460.3	496.0	527.6	537.8
47.5°	408.2	437.8	478.7	511.3	522.5
50°	382.7	414.4	460.3	495.0	506.2
52.5°	358.2	391.9	440.9	476.6	488.9
55°	331.7	368.4	421.5	458.2	471.5
57.5°	306.2	347.0	400.1	439.9	453.1
60°	278.6	322.5	380.7	419.5	433.7
62.5°	254.1	300.1	358.2	400.1	413.3
65°	226.6	276.6	336.8	378.6	391.9
67.5°	202.1	254.1	315.4	357.2	371.5
70°	175.5	228.6	291.9	335.8	348.0
72.5°	151.0	206.2	270.5	313.3	328.6
75°	125.5	182.7	248.0	291.9	305.2
77.5°	101.0	160.2	226.6	270.5	284.7
80°	76.5	138.8	205.1	248.0	262.3
82.5°	56.1	117.4	184.7	227.6	240.9
85°	36.7	100.0	165.3	208.2	222.5
87.5°	22.5	83.7	149.0	190.8	204.1
90°	11.2	82.2	169.1	207.9	221.2
92.5°	30.8	92.8	156.0	196.7	209.0
95°	59.3	117.0	180.3	219.0	229.3
97.5°	92.6	145.3	208.4	246.2	258.4
100°	131.9	177.5	237.7	275.4	285.6
102.5°	172.1	211.7	270.7	308.5	318.7
105°	216.3	248.9	303.9	341.6	352.8
107.5°	261.5	289.9	340.9	376.6	383.0
110°	303.7	330.0	380.0	412.7	421.0

TEST NUMBER: P1009418

CATALOG NUMBER: S122DIP-B675D925UB40-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	350.9	373.1	419.1	448.7	458.0
115°	397.1	414.1	458.1	487.8	496.1
117.5°	442.2	458.2	496.2	523.8	531.1
120°	488.4	500.3	533.3	561.8	570.2
122.5°	530.6	541.5	574.3	598.9	606.1
125°	573.7	582.6	612.3	637.0	645.1
127.5°	617.0	626.8	650.5	672.0	678.3
130°	657.3	669.0	688.6	711.0	715.3
132.5°	702.4	711.3	727.5	746.1	751.4
135°	740.7	751.5	763.7	784.2	789.4
137.5°	784.0	792.8	799.9	818.3	821.6
140°	822.3	830.1	837.0	853.4	855.6
142.5°	861.6	869.4	872.4	885.5	886.7
145°	897.9	904.8	910.7	917.8	918.9
147.5°	931.3	940.1	944.1	947.0	946.2
150°	965.7	971.6	975.5	978.5	975.5
152.5°	996.1	1002.0	1006.9	1010.9	1006.9
155°	1026.6	1029.5	1032.5	1037.4	1034.5
157.5°	1053.1	1055.1	1057.0	1063.9	1059.0
160°	1076.7	1078.7	1079.6	1085.5	1081.6
162.5°	1098.3	1098.3	1099.3	1106.2	1101.3
165°	1117.0	1116.0	1116.0	1122.9	1118.0
167.5°	1133.7	1130.7	1130.7	1137.6	1132.7
170°	1146.4	1143.5	1142.5	1149.4	1143.5
172.5°	1155.3	1152.3	1151.4	1158.2	1152.3
175°	1162.2	1159.2	1157.3	1164.1	1158.2
177.5°	1166.1	1163.1	1161.2	1167.1	1161.2
180°	1164.1	1164.1	1164.1	1164.1	1164.1

(END OF REPORT)