

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007324

Luminaire Tested: S122IP-B1080UB2750-4F0-XX-W2A-1_3500K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007324
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122IP-B1080UB2750-4F0-XX-W2A-1_3500K
Description: Define 2 Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3866.0 lumens
Efficiency: N/A
Efficacy: 110.5 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 35
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007324

CATALOG NUMBER: S122IP-B1080UB2750-4F0-XX-W2A-1_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1007324

CATALOG NUMBER: S122IP-B1080UB2750-4F0-XX-W2A-1_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007324

CATALOG NUMBER: S122IP-B1080UB2750-4F0-XX-W2A-1_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	3.9	0.1
90°-100°	85.5	2.2
100°-110°	271.7	7.0
110°-120°	464.8	12.0
120°-130°	611.3	15.8
130°-140°	686.2	17.7
140°-150°	672.9	17.4
150°-160°	564.5	14.6
160°-170°	374.4	9.7
170°-180°	130.8	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	3.9	0.1
90°-120°	822.0	21.3
90°-150°	2792.4	72.2
90°-180°	3862.0	99.9
0°-180°	3866.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	15	41	38	40	4
95°	61	72	75	75	72	68
105°	251	254	256	259	259	265
115°	466	473	471	470	466	461
125°	678	689	685	682	681	606
135°	878	891	893	892	888	678
145°	1066	1074	1081	1082	1077	666
155°	1218	1222	1225	1231	1228	561
165°	1325	1324	1324	1332	1327	374
175°	1379	1376	1373	1381	1374	131
180°	1381	1381	1381	1381	1381	

TEST NUMBER: P1007324

CATALOG NUMBER: S122IP-B1080UB2750-4F0-XX-W2A-1_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.2	15.2	40.8	38.5	39.6
92.5°	25.6	35.0	36.1	37.3	37.3
95°	60.6	72.3	74.6	74.6	72.3
97.5°	101.4	111.9	116.6	116.6	116.6
100°	148.0	157.4	160.9	160.9	159.7
102.5°	197.0	204.0	208.7	209.8	208.7
105°	250.6	254.1	256.5	258.8	258.8
107.5°	304.3	308.9	308.9	310.1	304.3
110°	355.5	362.5	362.5	362.5	359.0

TEST NUMBER: P1007324

CATALOG NUMBER: S122IP-B1080UB2750-4F0-XX-W2A-1_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	411.5	418.5	417.3	413.8	411.5
115°	466.3	473.3	471.0	469.8	466.3
117.5°	521.1	530.4	524.6	521.1	517.6
120°	575.9	585.2	575.9	575.9	572.4
122.5°	626.0	637.6	631.8	628.3	626.0
125°	678.4	688.9	685.4	681.9	680.8
127.5°	729.7	742.6	737.9	733.2	729.7
130°	777.5	792.7	790.4	788.0	783.4
132.5°	831.2	842.8	844.0	838.2	834.7
135°	877.8	890.6	892.9	891.8	888.3
137.5°	929.1	939.6	941.9	940.7	936.1
140°	974.5	985.0	990.9	990.9	986.2
142.5°	1021.2	1031.7	1035.2	1036.3	1031.7
145°	1065.5	1073.6	1080.6	1081.8	1077.1
147.5°	1105.1	1115.6	1120.3	1122.6	1117.9
150°	1145.9	1152.9	1157.6	1161.1	1157.6
152.5°	1182.0	1189.0	1194.9	1199.5	1194.9
155°	1218.2	1221.7	1225.2	1231.0	1227.5
157.5°	1249.7	1252.0	1254.3	1262.5	1256.6
160°	1277.6	1280.0	1281.1	1288.1	1283.5
162.5°	1303.3	1303.3	1304.4	1312.6	1306.8
165°	1325.4	1324.3	1324.3	1332.4	1326.6
167.5°	1345.2	1341.7	1341.7	1349.9	1344.1
170°	1360.4	1356.9	1355.7	1363.9	1356.9
172.5°	1370.9	1367.4	1366.2	1374.4	1367.4
175°	1379.0	1375.5	1373.2	1381.4	1374.4
177.5°	1383.7	1380.2	1377.9	1384.9	1377.9
180°	1381.4	1381.4	1381.4	1381.4	1381.4

(END OF REPORT)