

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009436

Luminaire Tested: S122DIP-B865D1080UB27-4F0-XX-W2A-D1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009436
REPORT IS A COMBINATION OF REPORTS P984722 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D1080UB27-4F0-XX-W2A-D1
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7260.0 lumens
Efficiency: N/A
Efficacy: 88.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009436

CATALOG NUMBER: S122DIP-B865D1080UB27-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1009436

CATALOG NUMBER: S122DIP-B865D1080UB27-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49
1	95	90	86	82	86	82	78	75	67	65	62	54	52	50	41	40	39
2	86	78	71	66	78	71	65	60	58	54	50	46	43	41	36	33	32
3	78	68	60	54	71	62	55	50	51	46	42	41	37	34	31	29	26
4	71	60	52	45	64	55	47	42	45	40	35	36	32	29	28	25	22
5	65	53	45	38	59	49	41	36	40	34	30	32	28	25	25	22	19
6	60	47	39	33	54	43	36	31	36	30	26	29	25	21	22	19	17
7	55	43	35	29	50	39	32	27	32	27	23	26	22	19	20	17	15
8	51	39	31	25	46	35	28	24	29	24	20	24	20	17	19	15	13
9	48	35	28	22	43	32	26	21	27	22	18	22	18	15	17	14	12
10	44	32	25	20	40	30	23	19	25	20	16	20	16	13	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14283	14283	14283
5°	14349	13674	13596
10°	14252	13200	13008
15°	14050	12710	12404
20°	13797	12196	11829
25°	13546	11704	11310
30°	13195	11202	10795
35°	12840	10720	10417
40°	12465	10303	10041
45°	12110	9925	9714
50°	11727	9576	9390
55°	11325	9205	9062
60°	10833	8819	8716
65°	10320	8376	8318
70°	9740	7899	7888
75°	9001	7423	7484
80°	7832	6928	7066
85°	6653	6461	6704

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12110 cd/sqm

TEST NUMBER: P1009436

CATALOG NUMBER: S122DIP-B865D1080UB27-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.5	1.2
10°-20°	245.3	3.4
20°-30°	371.7	5.1
30°-40°	452.7	6.2
40°-50°	487.0	6.7
50°-60°	473.0	6.5
60°-70°	413.1	5.7
70°-80°	317.9	4.4
80°-90°	216.8	3.0
90°-100°	231.3	3.2
100°-110°	375.5	5.2
110°-120°	529.8	7.3
120°-130°	643.0	8.9
130°-140°	694.1	9.6
140°-150°	667.2	9.2
150°-160°	557.3	7.7
160°-170°	369.6	5.1
170°-180°	129.2	1.8
0°-30°	702.6	9.7
0°-40°	1155.3	15.9
0°-60°	2115.3	29.1
0°-90°	3063.0	42.2
90°-120°	1136.5	15.7
90°-150°	3140.8	43.3
90°-180°	4197.0	57.8
0°-180°	7260.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	902	902	902	902	902	
5°	905	901	893	901	900	86
15°	863	866	866	878	876	243
25°	785	794	806	821	825	361
35°	676	698	723	752	761	423
45°	554	590	636	676	689	428
55°	425	472	540	587	604	380
65°	290	354	432	485	502	288
75°	161	234	318	374	391	170
85°	47	128	212	267	285	50
90°	14	104	213	263	280	13
95°	70	143	224	274	287	75
105°	254	295	366	414	428	269
115°	466	487	544	582	592	460
125°	672	683	721	753	764	601
135°	868	881	896	922	929	671
145°	1052	1060	1067	1076	1078	658
155°	1203	1206	1210	1215	1212	554
165°	1309	1308	1308	1316	1310	369
175°	1362	1358	1356	1364	1357	129
180°	1364	1364	1364	1364	1364	

TEST NUMBER: P1009436

CATALOG NUMBER: S122DIP-B865D1080UB27-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	902.3	902.3	902.3	902.3	902.3
2.5°	908.9	905.0	895.8	902.3	899.7
5°	905.0	901.0	893.2	901.0	899.7
7.5°	898.4	895.8	889.3	898.4	897.1
10°	890.6	888.0	884.0	894.5	893.2
12.5°	877.5	878.8	876.2	886.6	885.3
15°	863.1	865.7	865.7	877.5	876.2
17.5°	844.8	850.0	854.0	865.7	865.7
20°	826.5	833.0	838.3	852.6	852.6
22.5°	806.9	814.7	822.6	836.9	839.6
25°	784.6	793.8	805.6	821.3	825.2
27.5°	758.5	772.9	785.9	805.6	808.2
30°	732.3	749.3	766.3	787.3	791.2
32.5°	703.6	723.2	744.1	768.9	776.8
35°	676.1	698.3	723.2	751.9	761.1
37.5°	646.0	670.9	702.3	733.6	742.8
40°	615.9	644.7	680.0	714.0	725.8
42.5°	587.2	615.9	657.8	695.7	707.5
45°	554.5	589.8	635.6	676.1	689.2
47.5°	523.1	561.0	613.3	655.2	669.6
50°	490.4	530.9	589.8	634.3	648.6
52.5°	459.0	502.2	564.9	610.7	626.4
55°	425.0	472.1	540.1	587.2	604.2
57.5°	392.3	444.6	512.6	563.6	580.6
60°	357.0	413.2	487.8	537.5	555.8
62.5°	325.6	384.5	459.0	512.6	529.6
65°	290.3	354.4	431.6	485.2	502.2
67.5°	258.9	325.6	404.1	457.7	476.0
70°	224.9	292.9	374.0	430.2	445.9
72.5°	193.5	264.2	346.5	401.5	421.1
75°	160.9	234.1	317.8	374.0	391.0
77.5°	129.5	205.3	290.3	346.5	364.9
80°	98.1	177.9	262.9	317.8	336.1
82.5°	71.9	150.4	236.7	291.6	308.6
85°	47.1	128.2	211.9	266.8	285.1
87.5°	28.8	107.2	190.9	244.5	261.5
90°	14.3	103.9	212.9	262.9	279.7
92.5°	37.1	115.6	196.6	248.7	264.3
95°	70.3	143.3	224.1	273.8	287.2
97.5°	109.3	175.9	256.3	304.7	320.4
100°	155.4	212.9	289.6	338.0	351.2
102.5°	202.3	252.4	327.6	375.9	389.1
105°	254.0	295.4	365.7	413.7	428.1
107.5°	306.9	342.9	408.3	454.0	462.6
110°	356.2	389.3	453.4	495.2	506.2

TEST NUMBER: P1009436

CATALOG NUMBER: S122DIP-B865D1080UB27-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	411.5	439.4	498.3	536.8	548.8
115°	465.6	486.9	543.5	581.5	592.5
117.5°	518.4	538.1	587.2	623.0	632.6
120°	572.5	587.0	630.1	666.7	677.6
122.5°	622.0	634.8	677.4	709.3	718.8
125°	672.4	682.8	721.3	753.1	763.7
127.5°	723.1	734.5	765.1	793.2	801.6
130°	770.3	783.9	809.1	838.2	844.0
132.5°	823.2	833.4	854.2	878.5	885.6
135°	868.0	880.6	896.0	922.3	929.3
137.5°	918.6	929.0	937.8	961.5	966.0
140°	963.5	972.5	980.9	1001.8	1005.1
142.5°	1009.5	1018.6	1022.0	1038.9	1040.8
145°	1052.0	1060.0	1066.9	1075.9	1077.9
147.5°	1091.1	1101.5	1106.1	1109.7	1109.0
150°	1131.4	1138.3	1142.9	1146.3	1142.9
152.5°	1167.1	1174.0	1179.7	1184.3	1179.7
155°	1202.7	1206.2	1209.6	1215.4	1211.9
157.5°	1233.8	1236.1	1238.4	1246.5	1240.7
160°	1261.4	1263.7	1264.9	1271.8	1267.2
162.5°	1286.8	1286.8	1287.9	1296.0	1290.2
165°	1308.6	1307.5	1307.5	1315.5	1309.8
167.5°	1328.2	1324.7	1324.7	1332.8	1327.0
170°	1343.2	1339.7	1338.5	1346.6	1339.7
172.5°	1353.5	1350.1	1348.9	1357.0	1350.1
175°	1361.6	1358.1	1355.8	1363.9	1357.0
177.5°	1366.2	1362.7	1360.4	1367.3	1360.4
180°	1363.9	1363.9	1363.9	1363.9	1363.9

(END OF REPORT)