

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009448

Luminaire Tested: S122DIP-B865D1080UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009448
REPORT IS A COMBINATION OF REPORTS P984749 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D1080UB30-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7340.0 lumens
Efficiency: N/A
Efficacy: 89.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009448

CATALOG NUMBER: S122DIP-B865D1080UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1009448

CATALOG NUMBER: S122DIP-B865D1080UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54
1	97	93	89	86	89	86	82	79	72	69	67	59	58	56	48	47	46
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	42	40	38
3	81	71	64	58	74	66	59	54	56	51	47	46	43	40	37	35	33
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	30	28
5	68	56	48	42	62	52	45	40	44	39	34	37	33	29	30	27	25
6	62	50	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	25	22	19
8	54	41	34	28	49	38	31	27	33	27	23	28	23	20	23	20	17
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	16
10	47	35	27	23	43	32	26	21	28	23	19	24	19	16	20	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21715	21715	21715
5°	21750	20698	20551
10°	21572	19755	19363
15°	21257	18804	18112
20°	20830	17770	16928
25°	20403	16691	15747
30°	19868	15677	14505
35°	19364	14605	13287
40°	18739	13549	12135
45°	18121	12501	11007
50°	17443	11436	9834
55°	16728	10296	8724
60°	15931	9062	7571
65°	15052	7808	6357
70°	13936	6435	5134
75°	12396	4961	3964
80°	10531	3370	2550
85°	7642	1567	1086

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18121 cd/sqm

TEST NUMBER: P1009448

CATALOG NUMBER: S122DIP-B865D1080UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.1	1.8
10°-20°	363.3	4.9
20°-30°	533.8	7.3
30°-40°	620.0	8.4
40°-50°	619.2	8.4
50°-60°	540.0	7.4
60°-70°	399.1	5.4
70°-80°	225.8	3.1
80°-90°	63.5	0.9
90°-100°	85.1	1.2
100°-110°	270.5	3.7
110°-120°	462.9	6.3
120°-130°	608.8	8.3
130°-140°	683.4	9.3
140°-150°	670.1	9.1
150°-160°	562.1	7.7
160°-170°	372.8	5.1
170°-180°	130.3	1.8
0°-30°	1026.2	14.0
0°-40°	1646.2	22.4
0°-60°	2805.4	38.2
0°-90°	3493.9	47.6
90°-120°	818.5	11.2
90°-150°	2780.8	37.9
90°-180°	3846.0	52.4
0°-180°	7340.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1372	1372	1372	1372	1372	
5°	1372	1366	1352	1362	1360	130
15°	1306	1298	1281	1286	1279	368
25°	1182	1171	1149	1152	1149	544
35°	1020	1006	985	977	971	637
45°	830	820	801	786	781	640
55°	628	620	604	588	582	561
65°	423	416	402	390	384	419
75°	222	219	212	204	207	236
85°	54	53	51	48	46	60
90°	1	15	41	38	40	7
95°	60	72	74	74	72	67
105°	250	253	255	258	258	264
115°	464	471	469	468	464	459
125°	676	686	683	679	678	604
135°	874	887	889	888	885	675
145°	1061	1069	1076	1077	1073	663
155°	1213	1217	1220	1226	1222	558
165°	1320	1319	1319	1327	1321	372
175°	1373	1370	1368	1376	1369	130
180°	1376	1376	1376	1376	1376	

TEST NUMBER: P1009448

CATALOG NUMBER: S122DIP-B865D1080UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1371.8	1371.8	1371.8	1371.8	1371.8
2.5°	1379.7	1373.1	1358.6	1371.8	1369.1
5°	1371.8	1366.5	1352.0	1362.5	1359.9
7.5°	1362.5	1354.6	1340.1	1350.7	1348.0
10°	1348.0	1338.8	1323.0	1333.5	1329.6
12.5°	1328.2	1320.3	1304.5	1311.1	1308.5
15°	1305.8	1297.9	1280.8	1286.0	1279.4
17.5°	1278.1	1270.2	1253.1	1259.7	1253.1
20°	1247.8	1239.9	1221.4	1225.4	1220.1
22.5°	1217.4	1205.6	1188.4	1188.4	1185.8
25°	1181.8	1171.3	1148.9	1151.5	1148.9
27.5°	1142.3	1133.0	1115.9	1111.9	1105.3
30°	1102.7	1092.1	1072.4	1068.4	1063.1
32.5°	1060.5	1052.6	1031.5	1023.6	1018.3
35°	1019.6	1006.4	985.3	977.4	970.8
37.5°	973.4	961.6	940.5	931.2	924.6
40°	925.9	915.4	894.3	882.4	877.1
42.5°	879.8	869.2	848.1	834.9	827.0
45°	829.7	820.4	800.6	786.1	780.9
47.5°	780.9	771.6	750.5	736.0	728.1
50°	729.4	722.8	704.4	685.9	679.3
52.5°	679.3	670.1	652.9	638.4	629.2
55°	627.8	619.9	604.1	588.3	581.7
57.5°	576.4	569.8	552.7	536.8	531.6
60°	525.0	519.7	501.2	486.7	482.8
62.5°	474.8	465.6	452.4	439.2	434.0
65°	423.4	415.5	402.3	390.4	383.8
67.5°	370.6	364.0	352.2	342.9	337.7
70°	321.8	316.6	304.7	295.5	290.2
72.5°	271.7	266.4	259.8	250.6	246.7
75°	221.6	219.0	212.4	204.4	207.1
77.5°	176.7	171.5	168.8	164.9	160.9
80°	131.9	130.6	127.9	124.0	121.3
82.5°	89.7	89.7	88.4	83.1	83.1
85°	54.1	52.8	51.4	47.5	46.2
87.5°	23.7	21.1	18.5	14.5	13.2
90°	1.2	15.1	40.6	38.3	39.5
92.5°	25.5	34.8	36.0	37.1	37.1
95°	60.4	72.0	74.3	74.3	72.0
97.5°	101.0	111.4	116.1	116.1	116.1
100°	147.4	156.7	160.2	160.2	159.0
102.5°	196.2	203.2	207.8	209.0	207.8
105°	249.6	253.1	255.4	257.7	257.7
107.5°	303.0	307.6	307.6	308.8	303.0
110°	354.1	361.0	361.0	361.0	357.6

TEST NUMBER: P1009448

CATALOG NUMBER: S122DIP-B865D1080UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	409.8	416.8	415.6	412.1	409.8
115°	464.4	471.3	469.0	467.8	464.4
117.5°	518.9	528.2	522.4	518.9	515.4
120°	573.5	582.8	573.5	573.5	570.0
122.5°	623.4	635.0	629.2	625.7	623.4
125°	675.6	686.1	682.6	679.1	678.0
127.5°	726.7	739.5	734.8	730.2	726.7
130°	774.3	789.4	787.1	784.8	780.1
132.5°	827.7	839.3	840.5	834.7	831.2
135°	874.2	886.9	889.2	888.1	884.6
137.5°	925.2	935.7	938.0	936.8	932.2
140°	970.5	981.0	986.8	986.8	982.1
142.5°	1016.9	1027.4	1030.9	1032.0	1027.4
145°	1061.1	1069.2	1076.1	1077.3	1072.7
147.5°	1100.5	1111.0	1115.6	1117.9	1113.3
150°	1141.2	1148.1	1152.8	1156.3	1152.8
152.5°	1177.1	1184.1	1189.9	1194.6	1189.9
155°	1213.1	1216.6	1220.1	1225.9	1222.4
157.5°	1244.5	1246.8	1249.1	1257.2	1251.4
160°	1272.3	1274.7	1275.8	1282.8	1278.1
162.5°	1297.9	1297.9	1299.0	1307.2	1301.4
165°	1319.9	1318.8	1318.8	1326.9	1321.1
167.5°	1339.7	1336.2	1336.2	1344.3	1338.5
170°	1354.8	1351.3	1350.1	1358.2	1351.3
172.5°	1365.2	1361.7	1360.6	1368.7	1361.7
175°	1373.3	1369.9	1367.5	1375.7	1368.7
177.5°	1378.0	1374.5	1372.2	1379.1	1372.2
180°	1375.7	1375.7	1375.7	1375.7	1375.7

(END OF REPORT)