

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009456

Luminaire Tested: S122DIP-B865D1080UB35-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009456
REPORT IS A COMBINATION OF REPORTS P984757 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D1080UB35-4F0-XX-W2A-F
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7830.0 lumens
Efficiency: N/A
Efficacy: 95.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009456

CATALOG NUMBER: S122DIP-B865D1080UB35-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1009456

CATALOG NUMBER: S122DIP-B865D1080UB35-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	97	92	88	85	88	85	81	78	70	68	66	57	56	54	45	44	43
2	88	81	75	69	80	74	69	64	62	58	55	50	48	45	40	38	37
3	80	71	64	58	73	65	59	54	54	50	46	45	41	38	35	33	31
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	28	26	23
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	21
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16
9	49	37	30	25	45	35	28	23	29	24	21	25	21	18	20	17	15
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21808	21808	21808
5°	21844	20787	20638
10°	21665	19840	19446
15°	21348	18885	18190
20°	20918	17847	17001
25°	20491	16763	15814
30°	19953	15744	14568
35°	19447	14668	13344
40°	18820	13607	12187
45°	18197	12556	11053
50°	17517	11485	9876
55°	16800	10340	8762
60°	15998	9101	7602
65°	15116	7841	6385
70°	13997	6463	5155
75°	12447	4982	3981
80°	10578	3386	2563
85°	7670	1576	1091

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18197 cd/sqm

TEST NUMBER: P1009456

CATALOG NUMBER: S122DIP-B865D1080UB35-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.7	1.7
10°-20°	364.8	4.7
20°-30°	536.1	6.8
30°-40°	622.7	8.0
40°-50°	621.9	7.9
50°-60°	542.3	6.9
60°-70°	400.8	5.1
70°-80°	226.8	2.9
80°-90°	62.5	0.8
90°-100°	48.6	0.6
100°-110°	181.2	2.3
110°-120°	480.7	6.1
120°-130°	797.2	10.2
130°-140°	846.8	10.8
140°-150°	787.0	10.1
150°-160°	632.7	8.1
160°-170°	407.7	5.2
170°-180°	140.3	1.8
0°-30°	1030.6	13.2
0°-40°	1653.3	21.1
0°-60°	2817.5	36.0
0°-90°	3507.6	44.8
90°-120°	710.5	9.1
90°-150°	3141.6	40.1
90°-180°	4322.0	55.2
0°-180°	7830.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1378	1378	1378	1378	1378	
5°	1378	1372	1358	1368	1366	131
15°	1311	1304	1286	1292	1285	369
25°	1187	1176	1154	1156	1154	546
35°	1024	1011	990	982	975	639
45°	833	824	804	790	784	643
55°	630	623	607	591	584	564
65°	425	417	404	392	386	420
75°	222	220	213	205	208	237
85°	54	53	52	48	46	61
90°	1	13	21	27	29	7
95°	69	34	42	47	46	82
105°	324	356	65	77	81	347
115°	613	632	658	164	88	604
125°	867	881	902	909	912	774
135°	1073	1090	1100	1111	1108	829
145°	1245	1244	1262	1270	1264	779
155°	1371	1361	1374	1380	1372	632
165°	1444	1438	1441	1449	1441	408
175°	1478	1470	1472	1480	1469	141
180°	1474	1474	1474	1474	1474	

TEST NUMBER: P1009456

CATALOG NUMBER: S122DIP-B865D1080UB35-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1377.7	1377.7	1377.7	1377.7	1377.7
2.5°	1385.6	1379.0	1364.4	1377.7	1375.0
5°	1377.7	1372.4	1357.8	1368.4	1365.7
7.5°	1368.4	1360.4	1345.9	1356.5	1353.8
10°	1353.8	1344.5	1328.7	1339.2	1335.3
12.5°	1334.0	1326.0	1310.1	1316.7	1314.1
15°	1311.4	1303.5	1286.3	1291.6	1284.9
17.5°	1283.6	1275.7	1258.4	1265.1	1258.4
20°	1253.1	1245.2	1226.7	1230.6	1225.3
22.5°	1222.7	1210.8	1193.5	1193.5	1190.9
25°	1186.9	1176.3	1153.8	1156.4	1153.8
27.5°	1147.2	1137.9	1120.7	1116.7	1110.1
30°	1107.4	1096.8	1077.0	1073.0	1067.7
32.5°	1065.0	1057.1	1035.9	1028.0	1022.7
35°	1024.0	1010.7	989.5	981.6	975.0
37.5°	977.6	965.7	944.5	935.2	928.6
40°	929.9	919.3	898.1	886.2	880.9
42.5°	883.6	873.0	851.8	838.5	830.6
45°	833.2	823.9	804.1	789.5	784.2
47.5°	784.2	774.9	753.7	739.2	731.2
50°	732.5	725.9	707.4	688.8	682.2
52.5°	682.2	672.9	655.7	641.1	631.9
55°	630.5	622.6	606.7	590.8	584.2
57.5°	578.9	572.3	555.0	539.1	533.8
60°	527.2	521.9	503.4	488.8	484.8
62.5°	476.9	467.6	454.4	441.1	435.8
65°	425.2	417.3	404.0	392.1	385.5
67.5°	372.2	365.6	353.7	344.4	339.1
70°	323.2	317.9	306.0	296.7	291.4
72.5°	272.9	267.6	261.0	251.7	247.7
75°	222.5	219.9	213.3	205.3	208.0
77.5°	177.5	172.2	169.6	165.6	161.6
80°	132.5	131.1	128.5	124.5	121.9
82.5°	90.1	90.1	88.8	83.5	83.5
85°	54.3	53.0	51.7	47.7	46.4
87.5°	23.8	21.2	18.5	14.6	13.2
90°	1.1	12.8	21.3	26.7	28.8
92.5°	26.7	22.4	25.6	27.7	28.8
95°	69.3	34.1	41.6	46.9	45.9
97.5°	124.8	37.3	54.4	57.6	58.7
100°	188.8	42.7	60.8	69.3	71.5
102.5°	259.2	257.1	62.9	74.7	77.9
105°	324.3	356.3	65.1	76.8	81.1
107.5°	400.1	426.7	67.2	78.9	83.2
110°	472.6	495.0	186.7	80.0	84.3

TEST NUMBER: P1009456

CATALOG NUMBER: S122DIP-B865D1080UB35-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	540.9	560.1	542.0	82.1	85.3
115°	613.4	631.6	658.2	164.3	87.5
117.5°	676.4	697.7	715.9	563.3	283.8
120°	746.8	762.8	782.0	794.8	650.8
122.5°	806.5	823.6	844.9	851.4	852.4
125°	867.4	881.2	901.5	909.0	912.2
127.5°	922.8	937.8	953.8	964.4	965.5
130°	975.1	992.2	1003.9	1015.6	1014.6
132.5°	1028.4	1042.3	1054.1	1063.7	1062.6
135°	1073.3	1090.3	1099.9	1110.6	1108.5
137.5°	1120.2	1133.0	1143.7	1154.3	1151.1
140°	1166.1	1174.6	1186.3	1195.9	1190.6
142.5°	1204.5	1211.9	1225.8	1234.4	1229.0
145°	1245.0	1244.0	1262.1	1269.6	1264.2
147.5°	1280.2	1277.0	1295.2	1300.5	1296.2
150°	1314.4	1306.9	1324.0	1330.4	1325.0
152.5°	1343.2	1334.6	1350.6	1357.0	1349.6
155°	1370.9	1361.3	1374.1	1380.5	1372.0
157.5°	1393.3	1384.8	1394.4	1401.8	1393.3
160°	1412.5	1406.1	1412.5	1418.9	1411.4
162.5°	1429.6	1423.2	1428.5	1436.0	1426.4
165°	1444.5	1438.1	1441.3	1448.8	1441.3
167.5°	1456.3	1449.9	1453.1	1460.5	1450.9
170°	1465.9	1459.5	1461.6	1469.1	1459.5
172.5°	1472.3	1465.9	1468.0	1475.5	1465.9
175°	1477.6	1470.1	1472.3	1479.7	1469.1
177.5°	1479.7	1472.3	1473.3	1480.8	1471.2
180°	1474.4	1474.4	1474.4	1474.4	1474.4

(END OF REPORT)