

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007356

Luminaire Tested: S122IP-B330UB2750-4F0-XX-W2A-1_5000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007356
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122IP-B330UB2750-4F0-XX-W2A-1_5000K
Description: Define 2 Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1133.0 lumens
Efficiency: N/A
Efficacy: 121.8 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 9.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007356

CATALOG NUMBER: S122IP-B330UB2750-4F0-XX-W2A-1_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1007356

CATALOG NUMBER: S122IP-B330UB2750-4F0-XX-W2A-1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007356

CATALOG NUMBER: S122IP-B330UB2750-4F0-XX-W2A-1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.2	0.1
90°-100°	25.0	2.2
100°-110°	79.6	7.0
110°-120°	136.2	12.0
120°-130°	179.2	15.8
130°-140°	201.1	17.7
140°-150°	197.2	17.4
150°-160°	165.4	14.6
160°-170°	109.7	9.7
170°-180°	38.3	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.2	0.1
90°-120°	240.9	21.3
90°-150°	818.4	72.2
90°-180°	1132.0	99.9
0°-180°	1133.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	4	12	11	12	1
95°	18	21	22	22	21	20
105°	74	74	75	76	76	78
115°	137	139	138	138	137	135
125°	199	202	201	200	200	178
135°	257	261	262	261	260	199
145°	312	315	317	317	316	195
155°	357	358	359	361	360	164
165°	388	388	388	390	389	110
175°	404	403	402	405	403	38
180°	405	405	405	405	405	

TEST NUMBER: P1007356

CATALOG NUMBER: S122IP-B330UB2750-4F0-XX-W2A-1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.3	4.4	12.0	11.3	11.6
92.5°	7.5	10.2	10.6	10.9	10.9
95°	17.8	21.2	21.9	21.9	21.2
97.5°	29.7	32.8	34.2	34.2	34.2
100°	43.4	46.1	47.1	47.1	46.8
102.5°	57.7	59.8	61.2	61.5	61.2
105°	73.5	74.5	75.2	75.8	75.8
107.5°	89.2	90.5	90.5	90.9	89.2
110°	104.2	106.2	106.2	106.2	105.2



TEST NUMBER: P1007356

CATALOG NUMBER: S122IP-B330UB2750-4F0-XX-W2A-1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	120.6	122.6	122.3	121.3	120.6
115°	136.7	138.7	138.0	137.7	136.7
117.5°	152.7	155.4	153.7	152.7	151.7
120°	168.8	171.5	168.8	168.8	167.7
122.5°	183.5	186.9	185.2	184.1	183.5
125°	198.8	201.9	200.9	199.9	199.5
127.5°	213.9	217.6	216.3	214.9	213.9
130°	227.9	232.3	231.6	230.9	229.6
132.5°	243.6	247.0	247.3	245.6	244.6
135°	257.3	261.0	261.7	261.4	260.3
137.5°	272.3	275.4	276.0	275.7	274.3
140°	285.6	288.7	290.4	290.4	289.0
142.5°	299.3	302.3	303.4	303.7	302.3
145°	312.3	314.6	316.7	317.0	315.7
147.5°	323.9	326.9	328.3	329.0	327.6
150°	335.8	337.9	339.2	340.3	339.2
152.5°	346.4	348.5	350.2	351.5	350.2
155°	357.0	358.0	359.1	360.8	359.7
157.5°	366.2	366.9	367.6	370.0	368.3
160°	374.4	375.1	375.5	377.5	376.1
162.5°	381.9	381.9	382.3	384.7	383.0
165°	388.4	388.1	388.1	390.5	388.8
167.5°	394.2	393.2	393.2	395.6	393.9
170°	398.7	397.7	397.3	399.7	397.7
172.5°	401.8	400.7	400.4	402.8	400.7
175°	404.2	403.1	402.4	404.8	402.8
177.5°	405.5	404.5	403.8	405.9	403.8
180°	404.8	404.8	404.8	404.8	404.8

(END OF REPORT)