

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009457

Luminaire Tested: S122DIP-B865D1080UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009457
REPORT IS A COMBINATION OF REPORTS P984758 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D1080UB35-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7371.0 lumens
Efficiency: N/A
Efficacy: 90.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009457

CATALOG NUMBER: S122DIP-B865D1080UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1009457

CATALOG NUMBER: S122DIP-B865D1080UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54
1	97	93	89	86	89	86	82	79	72	69	67	59	58	56	48	47	46
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	42	40	38
3	81	71	64	58	74	66	59	54	56	51	47	46	43	40	37	35	33
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	30	28
5	68	56	48	42	62	52	45	40	44	39	34	37	33	29	30	27	25
6	62	50	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	25	22	19
8	54	41	34	28	49	38	31	27	33	27	23	28	23	20	23	20	17
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	16
10	47	35	27	23	43	32	26	21	28	23	19	24	19	16	20	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21808	21808	21808
5°	21844	20787	20638
10°	21665	19840	19446
15°	21348	18885	18190
20°	20918	17847	17001
25°	20491	16763	15814
30°	19953	15744	14568
35°	19447	14668	13344
40°	18820	13607	12187
45°	18197	12556	11053
50°	17517	11485	9876
55°	16800	10340	8762
60°	15998	9101	7602
65°	15116	7841	6385
70°	13997	6463	5155
75°	12447	4982	3981
80°	10578	3386	2563
85°	7670	1576	1091

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18197 cd/sqm

TEST NUMBER: P1009457

CATALOG NUMBER: S122DIP-B865D1080UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.7	1.8
10°-20°	364.8	4.9
20°-30°	536.1	7.3
30°-40°	622.7	8.4
40°-50°	621.9	8.4
50°-60°	542.3	7.4
60°-70°	400.8	5.4
70°-80°	226.8	3.1
80°-90°	63.8	0.9
90°-100°	85.5	1.2
100°-110°	271.7	3.7
110°-120°	464.8	6.3
120°-130°	611.3	8.3
130°-140°	686.2	9.3
140°-150°	672.9	9.1
150°-160°	564.5	7.7
160°-170°	374.4	5.1
170°-180°	130.8	1.8
0°-30°	1030.6	14.0
0°-40°	1653.3	22.4
0°-60°	2817.5	38.2
0°-90°	3508.9	47.6
90°-120°	822.0	11.2
90°-150°	2792.4	37.9
90°-180°	3862.0	52.4
0°-180°	7371.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1378	1378	1378	1378	1378	
5°	1378	1372	1358	1368	1366	131
15°	1311	1304	1286	1292	1285	369
25°	1187	1176	1154	1156	1154	546
35°	1024	1011	990	982	975	639
45°	833	824	804	790	784	643
55°	630	623	607	591	584	564
65°	425	417	404	392	386	420
75°	222	220	213	205	208	237
85°	54	53	52	48	46	61
90°	1	15	41	38	40	7
95°	61	72	75	75	72	68
105°	251	254	256	259	259	265
115°	466	473	471	470	466	461
125°	678	689	685	682	681	606
135°	878	891	893	892	888	678
145°	1066	1074	1081	1082	1077	666
155°	1218	1222	1225	1231	1228	561
165°	1325	1324	1324	1332	1327	374
175°	1379	1376	1373	1381	1374	131
180°	1381	1381	1381	1381	1381	

TEST NUMBER: P1009457

CATALOG NUMBER: S122DIP-B865D1080UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1377.7	1377.7	1377.7	1377.7	1377.7
2.5°	1385.6	1379.0	1364.4	1377.7	1375.0
5°	1377.7	1372.4	1357.8	1368.4	1365.7
7.5°	1368.4	1360.4	1345.9	1356.5	1353.8
10°	1353.8	1344.5	1328.7	1339.2	1335.3
12.5°	1334.0	1326.0	1310.1	1316.7	1314.1
15°	1311.4	1303.5	1286.3	1291.6	1284.9
17.5°	1283.6	1275.7	1258.4	1265.1	1258.4
20°	1253.1	1245.2	1226.7	1230.6	1225.3
22.5°	1222.7	1210.8	1193.5	1193.5	1190.9
25°	1186.9	1176.3	1153.8	1156.4	1153.8
27.5°	1147.2	1137.9	1120.7	1116.7	1110.1
30°	1107.4	1096.8	1077.0	1073.0	1067.7
32.5°	1065.0	1057.1	1035.9	1028.0	1022.7
35°	1024.0	1010.7	989.5	981.6	975.0
37.5°	977.6	965.7	944.5	935.2	928.6
40°	929.9	919.3	898.1	886.2	880.9
42.5°	883.6	873.0	851.8	838.5	830.6
45°	833.2	823.9	804.1	789.5	784.2
47.5°	784.2	774.9	753.7	739.2	731.2
50°	732.5	725.9	707.4	688.8	682.2
52.5°	682.2	672.9	655.7	641.1	631.9
55°	630.5	622.6	606.7	590.8	584.2
57.5°	578.9	572.3	555.0	539.1	533.8
60°	527.2	521.9	503.4	488.8	484.8
62.5°	476.9	467.6	454.4	441.1	435.8
65°	425.2	417.3	404.0	392.1	385.5
67.5°	372.2	365.6	353.7	344.4	339.1
70°	323.2	317.9	306.0	296.7	291.4
72.5°	272.9	267.6	261.0	251.7	247.7
75°	222.5	219.9	213.3	205.3	208.0
77.5°	177.5	172.2	169.6	165.6	161.6
80°	132.5	131.1	128.5	124.5	121.9
82.5°	90.1	90.1	88.8	83.5	83.5
85°	54.3	53.0	51.7	47.7	46.4
87.5°	23.8	21.2	18.5	14.6	13.2
90°	1.2	15.2	40.8	38.5	39.6
92.5°	25.6	35.0	36.1	37.3	37.3
95°	60.6	72.3	74.6	74.6	72.3
97.5°	101.4	111.9	116.6	116.6	116.6
100°	148.0	157.4	160.9	160.9	159.7
102.5°	197.0	204.0	208.7	209.8	208.7
105°	250.6	254.1	256.5	258.8	258.8
107.5°	304.3	308.9	308.9	310.1	304.3
110°	355.5	362.5	362.5	362.5	359.0

TEST NUMBER: P1009457

CATALOG NUMBER: S122DIP-B865D1080UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	411.5	418.5	417.3	413.8	411.5
115°	466.3	473.3	471.0	469.8	466.3
117.5°	521.1	530.4	524.6	521.1	517.6
120°	575.9	585.2	575.9	575.9	572.4
122.5°	626.0	637.6	631.8	628.3	626.0
125°	678.4	688.9	685.4	681.9	680.8
127.5°	729.7	742.6	737.9	733.2	729.7
130°	777.5	792.7	790.4	788.0	783.4
132.5°	831.2	842.8	844.0	838.2	834.7
135°	877.8	890.6	892.9	891.8	888.3
137.5°	929.1	939.6	941.9	940.7	936.1
140°	974.5	985.0	990.9	990.9	986.2
142.5°	1021.2	1031.7	1035.2	1036.3	1031.7
145°	1065.5	1073.6	1080.6	1081.8	1077.1
147.5°	1105.1	1115.6	1120.3	1122.6	1117.9
150°	1145.9	1152.9	1157.6	1161.1	1157.6
152.5°	1182.0	1189.0	1194.9	1199.5	1194.9
155°	1218.2	1221.7	1225.2	1231.0	1227.5
157.5°	1249.7	1252.0	1254.3	1262.5	1256.6
160°	1277.6	1280.0	1281.1	1288.1	1283.5
162.5°	1303.3	1303.3	1304.4	1312.6	1306.8
165°	1325.4	1324.3	1324.3	1332.4	1326.6
167.5°	1345.2	1341.7	1341.7	1349.9	1344.1
170°	1360.4	1356.9	1355.7	1363.9	1356.9
172.5°	1370.9	1367.4	1366.2	1374.4	1367.4
175°	1379.0	1375.5	1373.2	1381.4	1374.4
177.5°	1383.7	1380.2	1377.9	1384.9	1377.9
180°	1381.4	1381.4	1381.4	1381.4	1381.4

(END OF REPORT)