

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007382

Luminaire Tested: S122IP-B530UB2750-4F0-XX-W2A-1_2700K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007382
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122IP-B530UB2750-4F0-XX-W2A-1_2700K
Description: Define 2 Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1879.0 lumens
Efficiency: N/A
Efficacy: 122.0 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 15.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007382

CATALOG NUMBER: S122IP-B530UB2750-4F0-XX-W2A-1_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1007382

CATALOG NUMBER: S122IP-B530UB2750-4F0-XX-W2A-1_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007382

CATALOG NUMBER: S122IP-B530UB2750-4F0-XX-W2A-1_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.9	0.1
90°-100°	41.5	2.2
100°-110°	132.0	7.0
110°-120°	225.9	12.0
120°-130°	297.1	15.8
130°-140°	333.5	17.7
140°-150°	327.1	17.4
150°-160°	274.3	14.6
160°-170°	182.0	9.7
170°-180°	63.6	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.9	0.1
90°-120°	399.5	21.3
90°-150°	1357.2	72.2
90°-180°	1877.0	99.9
0°-180°	1879.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	7	20	19	19	2
95°	30	35	36	36	35	33
105°	122	124	125	126	126	129
115°	227	230	229	228	227	224
125°	330	335	333	331	331	295
135°	427	433	434	433	432	330
145°	518	522	525	526	524	324
155°	592	594	596	598	597	273
165°	644	644	644	648	645	182
175°	670	669	667	671	668	64
180°	671	671	671	671	671	

TEST NUMBER: P1007382

CATALOG NUMBER: S122IP-B530UB2750-4F0-XX-W2A-1_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.6	7.4	19.8	18.7	19.3
92.5°	12.5	17.0	17.6	18.1	18.1
95°	29.5	35.1	36.3	36.3	35.1
97.5°	49.3	54.4	56.7	56.7	56.7
100°	72.0	76.5	78.2	78.2	77.6
102.5°	95.8	99.2	101.4	102.0	101.4
105°	121.8	123.5	124.6	125.8	125.8
107.5°	147.9	150.1	150.1	150.7	147.9
110°	172.8	176.2	176.2	176.2	174.5

TEST NUMBER: P1007382

CATALOG NUMBER: S122IP-B530UB2750-4F0-XX-W2A-1_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	200.0	203.4	202.8	201.1	200.0
115°	226.6	230.0	228.9	228.3	226.6
117.5°	253.3	257.8	255.0	253.3	251.6
120°	279.9	284.4	279.9	279.9	278.2
122.5°	304.3	309.9	307.1	305.4	304.3
125°	329.7	334.8	333.1	331.4	330.9
127.5°	354.7	360.9	358.6	356.4	354.7
130°	377.9	385.3	384.1	383.0	380.7
132.5°	404.0	409.6	410.2	407.4	405.7
135°	426.6	432.9	434.0	433.4	431.7
137.5°	451.6	456.7	457.8	457.2	455.0
140°	473.7	478.8	481.6	481.6	479.3
142.5°	496.3	501.4	503.1	503.7	501.4
145°	517.9	521.8	525.2	525.8	523.5
147.5°	537.1	542.2	544.5	545.6	543.3
150°	556.9	560.3	562.6	564.3	562.6
152.5°	574.5	577.9	580.7	583.0	580.7
155°	592.1	593.8	595.5	598.3	596.6
157.5°	607.4	608.5	609.6	613.6	610.8
160°	621.0	622.1	622.7	626.1	623.8
162.5°	633.4	633.4	634.0	638.0	635.1
165°	644.2	643.6	643.6	647.6	644.8
167.5°	653.8	652.1	652.1	656.1	653.3
170°	661.2	659.5	658.9	662.9	659.5
172.5°	666.3	664.6	664.0	668.0	664.6
175°	670.3	668.6	667.4	671.4	668.0
177.5°	672.5	670.8	669.7	673.1	669.7
180°	671.4	671.4	671.4	671.4	671.4

(END OF REPORT)