

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009473

Luminaire Tested: S122DIP-B865D1080UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009473
REPORT IS A COMBINATION OF REPORTS P984777 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D1080UB50-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7406.6 lumens
Efficiency: N/A
Efficacy: 90.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009473

CATALOG NUMBER: S122DIP-B865D1080UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1009473

CATALOG NUMBER: S122DIP-B865D1080UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45	45	45
1	97	92	89	85	89	85	82	79	71	68	66	58	56	55	46	45	44	38	38	38
2	88	81	75	69	80	74	69	64	62	58	55	51	48	46	40	38	37	32	32	32
3	80	71	64	58	73	65	59	54	55	50	46	45	41	39	36	33	31	27	27	27
4	73	63	55	49	67	58	51	46	49	43	39	40	36	33	32	29	27	23	23	23
5	67	56	48	42	62	52	44	39	43	38	34	36	32	29	29	26	24	20	20	20
6	62	50	42	36	57	46	39	34	39	34	29	32	28	25	26	23	21	18	18	18
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16	16	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17	14	14	14
9	50	37	30	25	45	35	28	24	30	24	21	25	21	18	20	17	15	13	13	13
10	46	34	27	22	42	32	25	21	27	22	19	23	19	16	19	16	14	12	12	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20880	20880	20880
5°	20914	19903	19762
10°	20745	18996	18619
15°	20441	18082	17417
20°	20030	17088	16278
25°	19621	16049	15141
30°	19106	15074	13949
35°	18619	14045	12776
40°	18021	13030	11670
45°	17424	12022	10584
50°	16773	10997	9456
55°	16086	9900	8388
60°	15318	8714	7279
65°	14472	7509	6113
70°	13404	6188	4936
75°	11921	4770	3811
80°	10123	3241	2453
85°	7345	1509	1044

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17424 cd/sqm

TEST NUMBER: P1009473

CATALOG NUMBER: S122DIP-B865D1080UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.1	1.7
10°-20°	349.3	4.7
20°-30°	513.3	6.9
30°-40°	596.2	8.0
40°-50°	595.5	8.0
50°-60°	519.2	7.0
60°-70°	383.8	5.2
70°-80°	217.2	2.9
80°-90°	61.0	0.8
90°-100°	235.3	3.2
100°-110°	795.5	10.7
110°-120°	836.1	11.3
120°-130°	687.6	9.3
130°-140°	552.5	7.5
140°-150°	417.4	5.6
150°-160°	293.4	4.0
160°-170°	172.8	2.3
170°-180°	56.2	0.8
0°-30°	986.8	13.3
0°-40°	1583.0	21.4
0°-60°	2697.7	36.4
0°-90°	3359.7	45.4
90°-120°	1866.9	25.2
90°-150°	3524.5	47.6
90°-180°	4047.0	54.6
0°-180°	7406.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1319	1319	1319	1319	1319	
5°	1319	1314	1300	1310	1308	125
15°	1256	1248	1232	1237	1230	354
25°	1136	1126	1105	1107	1105	523
35°	980	968	948	940	934	612
45°	798	789	770	756	751	616
55°	604	596	581	566	559	540
65°	407	400	387	375	369	403
75°	213	210	204	197	199	227
85°	52	51	50	46	44	58
90°	1	15	38	36	37	6
95°	39	96	438	165	127	40
105°	136	205	827	1478	1258	145
115°	240	303	692	1428	1655	238
125°	335	396	665	1157	1343	298
135°	393	469	658	972	1113	304
145°	449	516	654	812	888	282
155°	510	551	635	718	747	235
165°	556	573	608	645	655	157
175°	579	580	585	592	590	55
180°	580	580	580	580	580	

TEST NUMBER: P1009473

CATALOG NUMBER: S122DIP-B865D1080UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1319.1	1319.1	1319.1	1319.1	1319.1
2.5°	1326.7	1320.4	1306.4	1319.1	1316.6
5°	1319.1	1314.0	1300.1	1310.2	1307.7
7.5°	1310.2	1302.6	1288.7	1298.8	1296.3
10°	1296.3	1287.4	1272.2	1282.3	1278.5
12.5°	1277.2	1269.6	1254.4	1260.8	1258.2
15°	1255.7	1248.1	1231.6	1236.7	1230.3
17.5°	1229.0	1221.4	1204.9	1211.3	1204.9
20°	1199.9	1192.3	1174.5	1178.3	1173.2
22.5°	1170.7	1159.3	1142.8	1142.8	1140.3
25°	1136.5	1126.3	1104.7	1107.3	1104.7
27.5°	1098.4	1089.5	1073.0	1069.2	1062.9
30°	1060.4	1050.2	1031.2	1027.4	1022.3
32.5°	1019.8	1012.2	991.9	984.3	979.2
35°	980.4	967.8	947.5	939.9	933.5
37.5°	936.1	924.6	904.3	895.5	889.1
40°	890.4	880.2	860.0	848.5	843.5
42.5°	846.0	835.9	815.6	802.9	795.3
45°	797.8	788.9	769.9	755.9	750.9
47.5°	750.9	742.0	721.7	707.7	700.1
50°	701.4	695.1	677.3	659.5	653.2
52.5°	653.2	644.3	627.8	613.9	605.0
55°	603.7	596.1	580.9	565.7	559.3
57.5°	554.3	547.9	531.4	516.2	511.2
60°	504.8	499.7	482.0	468.0	464.2
62.5°	456.6	447.7	435.0	422.4	417.3
65°	407.1	399.5	386.9	375.4	369.1
67.5°	356.4	350.1	338.7	329.8	324.7
70°	309.5	304.4	293.0	284.1	279.0
72.5°	261.3	256.2	249.9	241.0	237.2
75°	213.1	210.5	204.2	196.6	199.1
77.5°	170.0	164.9	162.4	158.5	154.7
80°	126.8	125.6	123.0	119.2	116.7
82.5°	86.2	86.2	85.0	79.9	79.9
85°	52.0	50.7	49.5	45.7	44.4
87.5°	22.8	20.3	17.8	14.0	12.7
90°	1.1	15.0	38.0	36.2	36.8
92.5°	16.7	53.0	171.9	79.2	68.1
95°	39.1	96.0	437.6	165.2	127.3
97.5°	58.0	126.7	713.3	331.5	213.2
100°	86.0	155.2	881.8	660.2	399.6
102.5°	111.6	180.8	887.4	1116.2	779.1
105°	136.2	205.4	827.1	1478.5	1258.0
107.5°	163.0	230.0	771.3	1609.6	1580.6
110°	189.8	255.0	733.4	1588.4	1712.3

TEST NUMBER: P1009473

CATALOG NUMBER: S122DIP-B865D1080UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	214.3	279.0	708.8	1516.4	1710.1
115°	240.0	303.0	692.1	1428.2	1655.4
117.5°	266.8	327.0	683.1	1344.0	1572.8
120°	291.3	350.5	675.3	1268.6	1493.5
122.5°	314.8	374.5	670.9	1210.1	1410.9
125°	334.9	396.2	665.3	1157.0	1342.8
127.5°	351.6	416.9	661.9	1111.8	1279.2
130°	366.1	435.4	659.7	1066.1	1226.8
132.5°	379.5	453.2	658.6	1018.6	1172.1
135°	392.9	468.8	657.5	972.2	1112.9
137.5°	405.2	482.2	657.5	925.4	1056.0
140°	419.7	494.5	656.4	884.0	996.8
142.5°	434.2	504.6	656.4	844.4	937.7
145°	448.7	515.7	654.1	812.1	888.5
147.5°	464.4	524.6	650.8	783.6	845.0
150°	480.0	533.6	647.4	759.0	807.0
152.5°	495.6	542.5	641.8	738.4	774.7
155°	510.1	550.8	635.1	718.3	746.8
157.5°	522.4	557.6	628.4	699.3	722.2
160°	534.7	564.2	621.8	680.3	698.8
162.5°	547.0	569.3	616.2	662.5	676.4
165°	555.9	572.6	608.4	645.2	655.2
167.5°	563.7	576.0	601.7	629.6	635.1
170°	571.5	577.6	596.1	615.0	617.3
172.5°	576.0	579.4	589.4	602.2	602.8
175°	579.3	579.9	584.9	592.2	590.5
177.5°	581.6	580.5	580.5	584.9	581.6
180°	580.5	580.5	580.5	580.5	580.5

(END OF REPORT)