

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009481

Luminaire Tested: S122DIP-B865D330UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009481
REPORT IS A COMBINATION OF REPORTS P984785 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D330UB27-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4629.0 lumens
Efficiency: N/A
Efficacy: 82.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009481

CATALOG NUMBER: S122DIP-B865D330UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1009481

CATALOG NUMBER: S122DIP-B865D330UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	97	97	97	88	88	88	79	79	79
1	103	99	95	91	98	94	91	87	85	83	80	77	75	73	70	68	67
2	94	86	80	75	89	82	77	72	75	70	66	68	64	61	61	59	56
3	86	76	68	62	81	73	66	60	66	60	56	60	56	52	54	51	48
4	79	67	59	53	75	64	57	51	59	53	48	54	49	44	49	45	41
5	72	60	52	45	69	58	50	44	53	46	41	48	43	39	44	40	36
6	67	54	46	40	63	52	44	39	48	41	36	44	38	34	40	35	32
7	62	49	41	35	59	47	39	34	43	37	32	40	34	30	36	32	28
8	58	45	37	31	55	43	35	30	40	33	29	36	31	27	34	29	25
9	54	41	33	28	51	39	32	27	36	30	26	34	28	24	31	26	23
10	50	38	30	25	48	36	29	25	34	28	23	31	26	22	29	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21528	21528	21528
5°	21563	20520	20374
10°	21386	19585	19195
15°	21074	18642	17956
20°	20651	17617	16783
25°	20229	16547	15611
30°	19697	15541	14381
35°	19197	14479	13172
40°	18579	13433	12031
45°	17963	12395	10911
50°	17292	11337	9750
55°	16587	10207	8649
60°	15794	8984	7505
65°	14924	7740	6302
70°	13819	6380	5090
75°	12290	4917	3930
80°	10443	3341	2529
85°	7571	1555	1077

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17963 cd/sqm

TEST NUMBER: P1009481

CATALOG NUMBER: S122DIP-B865D330UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.0	2.8
10°-20°	360.1	7.8
20°-30°	529.2	11.4
30°-40°	614.7	13.3
40°-50°	613.9	13.3
50°-60°	535.3	11.6
60°-70°	395.7	8.5
70°-80°	223.9	4.8
80°-90°	60.3	1.3
90°-100°	25.8	0.6
100°-110°	82.1	1.8
110°-120°	140.6	3.0
120°-130°	184.8	4.0
130°-140°	207.5	4.5
140°-150°	203.5	4.4
150°-160°	170.7	3.7
160°-170°	113.2	2.4
170°-180°	39.6	0.9
0°-30°	1017.4	22.0
0°-40°	1632.1	35.3
0°-60°	2781.3	60.1
0°-90°	3461.2	74.8
90°-120°	248.5	5.4
90°-150°	844.4	18.2
90°-180°	1168.0	25.2
0°-180°	4629.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1360	1360	1360	1360	1360	
5°	1360	1355	1340	1351	1348	129
15°	1295	1287	1270	1275	1268	365
25°	1172	1161	1139	1142	1139	539
35°	1011	998	977	969	962	631
45°	822	813	794	779	774	635
55°	622	615	599	583	577	557
65°	420	412	399	387	380	415
75°	220	217	210	203	205	234
85°	54	52	51	47	46	60
90°	0	5	12	12	12	4
95°	18	22	23	23	22	20
105°	76	77	78	78	78	80
115°	141	143	142	142	141	139
125°	205	208	207	206	206	183
135°	265	269	270	270	269	205
145°	322	325	327	327	326	201
155°	368	369	370	372	371	170
165°	401	400	400	403	401	113
175°	417	416	415	418	416	40
180°	418	418	418	418	418	

TEST NUMBER: P1009481

CATALOG NUMBER: S122DIP-B865D330UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1360.0	1360.0	1360.0	1360.0	1360.0
2.5°	1367.8	1361.3	1346.9	1360.0	1357.4
5°	1360.0	1354.7	1340.4	1350.8	1348.2
7.5°	1350.8	1343.0	1328.6	1339.1	1336.4
10°	1336.4	1327.3	1311.6	1322.1	1318.1
12.5°	1316.8	1309.0	1293.3	1299.8	1297.2
15°	1294.6	1286.7	1269.7	1275.0	1268.4
17.5°	1267.1	1259.3	1242.3	1248.8	1242.3
20°	1237.1	1229.2	1210.9	1214.8	1209.6
22.5°	1207.0	1195.2	1178.2	1178.2	1175.6
25°	1171.7	1161.2	1139.0	1141.6	1139.0
27.5°	1132.4	1123.3	1106.3	1102.4	1095.8
30°	1093.2	1082.8	1063.1	1059.2	1054.0
32.5°	1051.4	1043.5	1022.6	1014.8	1009.5
35°	1010.8	997.8	976.8	969.0	962.4
37.5°	965.1	953.3	932.4	923.2	916.7
40°	918.0	907.5	886.6	874.8	869.6
42.5°	872.2	861.8	840.8	827.8	819.9
45°	822.5	813.4	793.8	779.4	774.1
47.5°	774.1	765.0	744.1	729.7	721.8
50°	723.1	716.6	698.3	680.0	673.5
52.5°	673.5	664.3	647.3	632.9	623.8
55°	622.5	614.6	598.9	583.2	576.7
57.5°	571.5	564.9	547.9	532.2	527.0
60°	520.5	515.2	496.9	482.5	478.6
62.5°	470.8	461.6	448.5	435.5	430.2
65°	419.8	411.9	398.8	387.1	380.5
67.5°	367.5	360.9	349.1	340.0	334.8
70°	319.1	313.8	302.1	292.9	287.7
72.5°	269.4	264.1	257.6	248.5	244.5
75°	219.7	217.1	210.5	202.7	205.3
77.5°	175.2	170.0	167.4	163.5	159.5
80°	130.8	129.5	126.8	122.9	120.3
82.5°	88.9	88.9	87.6	82.4	82.4
85°	53.6	52.3	51.0	47.1	45.8
87.5°	23.5	20.9	18.3	14.4	13.1
90°	0.4	4.6	12.3	11.6	12.0
92.5°	7.8	10.6	10.9	11.3	11.3
95°	18.3	21.9	22.6	22.6	21.9
97.5°	30.7	33.8	35.2	35.2	35.2
100°	44.8	47.6	48.6	48.6	48.3
102.5°	59.6	61.7	63.1	63.4	63.1
105°	75.8	76.8	77.5	78.3	78.3
107.5°	92.0	93.4	93.4	93.8	92.0
110°	107.5	109.6	109.6	109.6	108.6

TEST NUMBER: P1009481

CATALOG NUMBER: S122DIP-B865D330UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	124.4	126.5	126.2	125.1	124.4
115°	141.0	143.1	142.4	142.1	141.0
117.5°	157.6	160.4	158.6	157.6	156.5
120°	174.1	176.9	174.1	174.1	173.1
122.5°	189.3	192.8	191.0	190.0	189.3
125°	205.1	208.3	207.3	206.2	205.9
127.5°	220.7	224.5	223.1	221.7	220.7
130°	235.1	239.7	239.0	238.3	236.9
132.5°	251.3	254.9	255.2	253.4	252.4
135°	265.4	269.3	270.0	269.7	268.6
137.5°	280.9	284.1	284.8	284.5	283.0
140°	294.7	297.9	299.6	299.6	298.2
142.5°	308.8	312.0	313.0	313.4	312.0
145°	322.2	324.6	326.8	327.1	325.7
147.5°	334.2	337.3	338.7	339.4	338.0
150°	346.5	348.6	350.0	351.1	350.0
152.5°	357.4	359.5	361.3	362.7	361.3
155°	368.4	369.4	370.5	372.2	371.2
157.5°	377.9	378.6	379.3	381.7	380.0
160°	386.3	387.0	387.4	389.5	388.1
162.5°	394.1	394.1	394.4	396.9	395.1
165°	400.8	400.4	400.4	402.9	401.1
167.5°	406.8	405.7	405.7	408.2	406.4
170°	411.4	410.3	409.9	412.4	410.3
172.5°	414.5	413.5	413.1	415.6	413.5
175°	417.0	415.9	415.2	417.7	415.6
177.5°	418.4	417.3	416.6	418.8	416.6
180°	417.7	417.7	417.7	417.7	417.7

(END OF REPORT)