

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009482

Luminaire Tested: S122DIP-B865D330UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009482
REPORT IS A COMBINATION OF REPORTS P984786 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D330UB27-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4738.5 lumens
Efficiency: N/A
Efficacy: 84.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009482

CATALOG NUMBER: S122DIP-B865D330UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1009482

CATALOG NUMBER: S122DIP-B865D330UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77
1	103	98	94	91	98	94	90	87	84	82	79	76	74	72	68	67	65
2	94	86	80	74	89	82	76	71	74	70	66	67	63	60	60	57	55
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	53	50	47
4	78	67	59	53	74	64	57	51	58	52	47	53	48	44	48	44	40
5	72	60	52	45	68	57	50	44	52	46	41	47	42	38	43	39	35
6	67	54	46	39	63	52	44	38	47	41	36	43	38	33	39	35	31
7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	36	31	28
8	57	45	36	31	54	43	35	30	39	33	28	36	31	27	33	28	25
9	54	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	23
10	50	38	30	25	48	36	29	24	33	27	23	31	25	22	28	24	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21528	21528	21528
5°	21563	20520	20374
10°	21386	19585	19195
15°	21074	18642	17956
20°	20651	17617	16783
25°	20229	16547	15611
30°	19697	15541	14381
35°	19197	14479	13172
40°	18579	13433	12031
45°	17963	12395	10911
50°	17292	11337	9750
55°	16587	10207	8649
60°	15794	8984	7505
65°	14924	7740	6302
70°	13819	6380	5090
75°	12290	4917	3930
80°	10443	3341	2529
85°	7571	1555	1077

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17963 cd/sqm

TEST NUMBER: P1009482

CATALOG NUMBER: S122DIP-B865D330UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.0	2.7
10°-20°	360.1	7.6
20°-30°	529.2	11.2
30°-40°	614.7	13.0
40°-50°	613.9	13.0
50°-60°	535.3	11.3
60°-70°	395.7	8.4
70°-80°	223.9	4.7
80°-90°	60.3	1.3
90°-100°	74.3	1.6
100°-110°	251.1	5.3
110°-120°	263.9	5.6
120°-130°	217.0	4.6
130°-140°	174.4	3.7
140°-150°	131.7	2.8
150°-160°	92.6	2.0
160°-170°	54.5	1.2
170°-180°	17.7	0.4
0°-30°	1017.4	21.5
0°-40°	1632.1	34.4
0°-60°	2781.3	58.7
0°-90°	3461.2	73.0
90°-120°	589.2	12.4
90°-150°	1112.4	23.5
90°-180°	1277.0	26.9
0°-180°	4738.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1360	1360	1360	1360	1360	
5°	1360	1355	1340	1351	1348	129
15°	1295	1287	1270	1275	1268	365
25°	1172	1161	1139	1142	1139	539
35°	1011	998	977	969	962	631
45°	822	813	794	779	774	635
55°	622	615	599	583	577	557
65°	420	412	399	387	380	415
75°	220	217	210	203	205	234
85°	54	52	51	47	46	60
90°	0	5	12	11	12	4
95°	12	30	138	52	40	13
105°	43	65	261	467	397	46
115°	76	96	218	451	522	75
125°	106	125	210	365	424	94
135°	124	148	208	307	351	96
145°	142	163	206	256	280	89
155°	161	174	200	227	236	74
165°	176	181	192	204	207	49
175°	183	183	185	187	186	17
180°	183	183	183	183	183	

TEST NUMBER: P1009482

CATALOG NUMBER: S122DIP-B865D330UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1360.0	1360.0	1360.0	1360.0	1360.0
2.5°	1367.8	1361.3	1346.9	1360.0	1357.4
5°	1360.0	1354.7	1340.4	1350.8	1348.2
7.5°	1350.8	1343.0	1328.6	1339.1	1336.4
10°	1336.4	1327.3	1311.6	1322.1	1318.1
12.5°	1316.8	1309.0	1293.3	1299.8	1297.2
15°	1294.6	1286.7	1269.7	1275.0	1268.4
17.5°	1267.1	1259.3	1242.3	1248.8	1242.3
20°	1237.1	1229.2	1210.9	1214.8	1209.6
22.5°	1207.0	1195.2	1178.2	1178.2	1175.6
25°	1171.7	1161.2	1139.0	1141.6	1139.0
27.5°	1132.4	1123.3	1106.3	1102.4	1095.8
30°	1093.2	1082.8	1063.1	1059.2	1054.0
32.5°	1051.4	1043.5	1022.6	1014.8	1009.5
35°	1010.8	997.8	976.8	969.0	962.4
37.5°	965.1	953.3	932.4	923.2	916.7
40°	918.0	907.5	886.6	874.8	869.6
42.5°	872.2	861.8	840.8	827.8	819.9
45°	822.5	813.4	793.8	779.4	774.1
47.5°	774.1	765.0	744.1	729.7	721.8
50°	723.1	716.6	698.3	680.0	673.5
52.5°	673.5	664.3	647.3	632.9	623.8
55°	622.5	614.6	598.9	583.2	576.7
57.5°	571.5	564.9	547.9	532.2	527.0
60°	520.5	515.2	496.9	482.5	478.6
62.5°	470.8	461.6	448.5	435.5	430.2
65°	419.8	411.9	398.8	387.1	380.5
67.5°	367.5	360.9	349.1	340.0	334.8
70°	319.1	313.8	302.1	292.9	287.7
72.5°	269.4	264.1	257.6	248.5	244.5
75°	219.7	217.1	210.5	202.7	205.3
77.5°	175.2	170.0	167.4	163.5	159.5
80°	130.8	129.5	126.8	122.9	120.3
82.5°	88.9	88.9	87.6	82.4	82.4
85°	53.6	52.3	51.0	47.1	45.8
87.5°	23.5	20.9	18.3	14.4	13.1
90°	0.4	4.8	12.0	11.4	11.6
92.5°	5.3	16.8	54.3	25.0	21.5
95°	12.3	30.3	138.1	52.2	40.2
97.5°	18.3	40.0	225.1	104.6	67.3
100°	27.1	49.0	278.3	208.4	126.1
102.5°	35.2	57.0	280.1	352.3	245.9
105°	43.0	64.8	261.1	466.6	397.1
107.5°	51.4	72.6	243.4	508.0	498.9
110°	59.9	80.5	231.5	501.4	540.4



TEST NUMBER: P1009482

CATALOG NUMBER: S122DIP-B865D330UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	67.6	88.1	223.7	478.6	539.7
115°	75.7	95.6	218.4	450.8	522.5
117.5°	84.2	103.2	215.6	424.2	496.4
120°	92.0	110.6	213.1	400.4	471.4
122.5°	99.4	118.2	211.7	381.9	445.3
125°	105.7	125.0	210.0	365.2	423.8
127.5°	111.0	131.6	208.9	350.9	403.7
130°	115.6	137.4	208.2	336.5	387.2
132.5°	119.8	143.0	207.9	321.4	369.9
135°	124.0	148.0	207.5	306.8	351.3
137.5°	127.9	152.2	207.5	292.1	333.3
140°	132.5	156.1	207.2	279.0	314.6
142.5°	137.0	159.2	207.2	266.5	295.9
145°	141.6	162.8	206.5	256.3	280.4
147.5°	146.6	165.6	205.4	247.3	266.7
150°	151.5	168.4	204.3	239.6	254.7
152.5°	156.4	171.2	202.6	233.0	244.5
155°	161.0	173.8	200.5	226.8	235.7
157.5°	164.9	176.0	198.4	220.7	227.9
160°	168.8	178.1	196.2	214.8	220.5
162.5°	172.6	179.7	194.5	209.1	213.5
165°	175.5	180.8	192.0	203.6	206.8
167.5°	177.9	181.8	189.9	198.7	200.5
170°	180.4	182.3	188.1	194.2	194.8
172.5°	181.8	182.8	186.0	190.0	190.2
175°	182.8	183.0	184.6	186.9	186.4
177.5°	183.6	183.2	183.2	184.6	183.6
180°	183.2	183.2	183.2	183.2	183.2

(END OF REPORT)