

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009490

Luminaire Tested: S122DIP-B865D330UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009490
REPORT IS A COMBINATION OF REPORTS P984809 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D330UB30-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4669.0 lumens
Efficiency: N/A
Efficacy: 83.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009490

CATALOG NUMBER: S122DIP-B865D330UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1009490

CATALOG NUMBER: S122DIP-B865D330UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	97	97	97	88	88	88	79	79	79
1	103	99	95	91	98	94	91	87	85	83	80	77	75	73	70	68	67
2	94	86	80	75	89	82	77	72	75	70	66	68	64	61	61	59	56
3	86	76	68	62	81	73	66	60	66	60	56	60	56	52	54	51	48
4	79	67	59	53	75	64	57	51	59	53	48	54	49	44	49	45	41
5	72	60	52	45	69	58	50	44	53	46	41	48	43	39	44	40	36
6	67	54	46	40	63	52	44	39	48	41	36	44	38	34	40	35	32
7	62	49	41	35	59	47	39	34	43	37	32	40	34	30	36	32	28
8	58	45	37	31	55	43	35	30	40	33	29	36	31	27	34	29	25
9	54	41	33	28	51	39	32	27	36	30	26	34	28	24	31	26	23
10	50	38	30	25	48	36	29	25	34	28	23	31	26	22	29	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21715	21715	21715
5°	21750	20698	20551
10°	21572	19755	19363
15°	21257	18804	18112
20°	20830	17770	16928
25°	20403	16691	15747
30°	19868	15677	14505
35°	19364	14605	13287
40°	18739	13549	12135
45°	18121	12501	11007
50°	17443	11436	9834
55°	16728	10296	8724
60°	15931	9062	7571
65°	15052	7808	6357
70°	13936	6435	5134
75°	12396	4961	3964
80°	10531	3370	2550
85°	7642	1567	1086

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18121 cd/sqm

TEST NUMBER: P1009490

CATALOG NUMBER: S122DIP-B865D330UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.1	2.8
10°-20°	363.3	7.8
20°-30°	533.8	11.4
30°-40°	620.0	13.3
40°-50°	619.2	13.3
50°-60°	540.0	11.6
60°-70°	399.1	8.5
70°-80°	225.8	4.8
80°-90°	60.8	1.3
90°-100°	26.1	0.6
100°-110°	82.8	1.8
110°-120°	141.8	3.0
120°-130°	186.4	4.0
130°-140°	209.3	4.5
140°-150°	205.2	4.4
150°-160°	172.1	3.7
160°-170°	114.2	2.4
170°-180°	39.9	0.9
0°-30°	1026.2	22.0
0°-40°	1646.2	35.3
0°-60°	2805.4	60.1
0°-90°	3491.2	74.8
90°-120°	250.7	5.4
90°-150°	851.6	18.2
90°-180°	1178.0	25.2
0°-180°	4669.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1372	1372	1372	1372	1372	
5°	1372	1366	1352	1362	1360	130
15°	1306	1298	1281	1286	1279	368
25°	1182	1171	1149	1152	1149	544
35°	1020	1006	985	977	971	637
45°	830	820	801	786	781	640
55°	628	620	604	588	582	561
65°	423	416	402	390	384	419
75°	222	219	212	204	207	236
85°	54	53	51	48	46	60
90°	0	5	12	12	12	4
95°	18	22	23	23	22	21
105°	76	78	78	79	79	81
115°	142	144	144	143	142	141
125°	207	210	209	208	208	185
135°	268	272	272	272	271	207
145°	325	327	330	330	328	203
155°	372	373	374	375	374	171
165°	404	404	404	406	405	114
175°	421	420	419	421	419	40
180°	421	421	421	421	421	

TEST NUMBER: P1009490

CATALOG NUMBER: S122DIP-B865D330UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1371.8	1371.8	1371.8	1371.8	1371.8
2.5°	1379.7	1373.1	1358.6	1371.8	1369.1
5°	1371.8	1366.5	1352.0	1362.5	1359.9
7.5°	1362.5	1354.6	1340.1	1350.7	1348.0
10°	1348.0	1338.8	1323.0	1333.5	1329.6
12.5°	1328.2	1320.3	1304.5	1311.1	1308.5
15°	1305.8	1297.9	1280.8	1286.0	1279.4
17.5°	1278.1	1270.2	1253.1	1259.7	1253.1
20°	1247.8	1239.9	1221.4	1225.4	1220.1
22.5°	1217.4	1205.6	1188.4	1188.4	1185.8
25°	1181.8	1171.3	1148.9	1151.5	1148.9
27.5°	1142.3	1133.0	1115.9	1111.9	1105.3
30°	1102.7	1092.1	1072.4	1068.4	1063.1
32.5°	1060.5	1052.6	1031.5	1023.6	1018.3
35°	1019.6	1006.4	985.3	977.4	970.8
37.5°	973.4	961.6	940.5	931.2	924.6
40°	925.9	915.4	894.3	882.4	877.1
42.5°	879.8	869.2	848.1	834.9	827.0
45°	829.7	820.4	800.6	786.1	780.9
47.5°	780.9	771.6	750.5	736.0	728.1
50°	729.4	722.8	704.4	685.9	679.3
52.5°	679.3	670.1	652.9	638.4	629.2
55°	627.8	619.9	604.1	588.3	581.7
57.5°	576.4	569.8	552.7	536.8	531.6
60°	525.0	519.7	501.2	486.7	482.8
62.5°	474.8	465.6	452.4	439.2	434.0
65°	423.4	415.5	402.3	390.4	383.8
67.5°	370.6	364.0	352.2	342.9	337.7
70°	321.8	316.6	304.7	295.5	290.2
72.5°	271.7	266.4	259.8	250.6	246.7
75°	221.6	219.0	212.4	204.4	207.1
77.5°	176.7	171.5	168.8	164.9	160.9
80°	131.9	130.6	127.9	124.0	121.3
82.5°	89.7	89.7	88.4	83.1	83.1
85°	54.1	52.8	51.4	47.5	46.2
87.5°	23.7	21.1	18.5	14.5	13.2
90°	0.4	4.6	12.4	11.7	12.1
92.5°	7.8	10.7	11.0	11.4	11.4
95°	18.5	22.0	22.8	22.8	22.0
97.5°	30.9	34.1	35.6	35.6	35.6
100°	45.1	48.0	49.1	49.1	48.7
102.5°	60.1	62.2	63.6	64.0	63.6
105°	76.4	77.5	78.2	78.9	78.9
107.5°	92.8	94.2	94.2	94.6	92.8
110°	108.4	110.6	110.6	110.6	109.5

TEST NUMBER: P1009490

CATALOG NUMBER: S122DIP-B865D330UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	125.5	127.6	127.3	126.2	125.5
115°	142.2	144.3	143.6	143.3	142.2
117.5°	158.9	161.8	160.0	158.9	157.8
120°	175.6	178.5	175.6	175.6	174.6
122.5°	190.9	194.5	192.7	191.6	190.9
125°	206.9	210.1	209.0	208.0	207.6
127.5°	222.5	226.5	225.0	223.6	222.5
130°	237.1	241.7	241.0	240.3	238.9
132.5°	253.5	257.0	257.4	255.6	254.5
135°	267.7	271.6	272.3	272.0	270.9
137.5°	283.3	286.5	287.2	286.9	285.5
140°	297.2	300.4	302.2	302.2	300.8
142.5°	311.4	314.6	315.7	316.0	314.6
145°	324.9	327.4	329.6	329.9	328.5
147.5°	337.0	340.2	341.6	342.4	340.9
150°	349.5	351.6	353.0	354.1	353.0
152.5°	360.5	362.6	364.4	365.8	364.4
155°	371.5	372.6	373.6	375.4	374.3
157.5°	381.1	381.8	382.5	385.0	383.2
160°	389.6	390.3	390.7	392.8	391.4
162.5°	397.5	397.5	397.8	400.3	398.5
165°	404.2	403.9	403.9	406.3	404.6
167.5°	410.3	409.2	409.2	411.7	409.9
170°	414.9	413.8	413.5	415.9	413.8
172.5°	418.1	417.0	416.7	419.1	417.0
175°	420.6	419.5	418.8	421.3	419.1
177.5°	422.0	420.9	420.2	422.3	420.2
180°	421.3	421.3	421.3	421.3	421.3

(END OF REPORT)