

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007394

Luminaire Tested: S122IP-B530UB2750-4F0-XX-W2A_3500K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007394
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122IP-B530UB2750-4F0-XX-W2A_3500K
Description: Define 2 Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2129.0 lumens
Efficiency: N/A
Efficacy: 138.2 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 15.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007394

CATALOG NUMBER: S122IP-B530UB2750-4F0-XX-W2A_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1007394

CATALOG NUMBER: S122IP-B530UB2750-4F0-XX-W2A_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007394

CATALOG NUMBER: S122IP-B530UB2750-4F0-XX-W2A_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.3	0.1
90°-100°	23.9	1.1
100°-110°	89.2	4.2
110°-120°	236.6	11.1
120°-130°	392.4	18.4
130°-140°	416.9	19.6
140°-150°	387.4	18.2
150°-160°	311.5	14.6
160°-170°	200.7	9.4
170°-180°	69.1	3.2
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.3	0.1
90°-120°	349.8	16.4
90°-150°	1546.5	72.6
90°-180°	2128.0	100.0
0°-180°	2129.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	6	10	13	14	2
95°	34	17	20	23	23	40
105°	160	175	32	38	40	171
115°	302	311	324	81	43	297
125°	427	434	444	447	449	381
135°	528	537	541	547	546	408
145°	613	612	621	625	622	383
155°	675	670	676	680	675	311
165°	711	708	710	713	710	201
175°	727	724	725	728	723	69
180°	726	726	726	726	726	

TEST NUMBER: P1007394

CATALOG NUMBER: S122IP-B530UB2750-4F0-XX-W2A_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.5	6.3	10.5	13.1	14.2
92.5°	13.1	11.0	12.6	13.7	14.2
95°	34.1	16.8	20.5	23.1	22.6
97.5°	61.4	18.4	26.8	28.4	28.9
100°	93.0	21.0	29.9	34.1	35.2
102.5°	127.6	126.6	31.0	36.8	38.3
105°	159.6	175.4	32.0	37.8	39.9
107.5°	196.9	210.1	33.1	38.9	41.0
110°	232.6	243.7	91.9	39.4	41.5

TEST NUMBER: P1007394

CATALOG NUMBER: S122IP-B530UB2750-4F0-XX-W2A_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	266.3	275.7	266.8	40.4	42.0
115°	302.0	310.9	324.0	80.9	43.1
117.5°	333.0	343.5	352.4	277.3	139.7
120°	367.6	375.5	384.9	391.2	320.4
122.5°	397.0	405.4	415.9	419.1	419.6
125°	427.0	433.8	443.8	447.4	449.0
127.5°	454.3	461.6	469.5	474.7	475.3
130°	480.0	488.4	494.2	500.0	499.4
132.5°	506.3	513.1	518.9	523.6	523.1
135°	528.3	536.7	541.4	546.7	545.6
137.5°	551.4	557.7	563.0	568.2	566.7
140°	574.0	578.2	584.0	588.7	586.1
142.5°	592.9	596.6	603.4	607.6	605.0
145°	612.9	612.3	621.3	624.9	622.3
147.5°	630.2	628.6	637.5	640.2	638.1
150°	647.0	643.3	651.7	654.9	652.3
152.5°	661.2	657.0	664.9	668.0	664.3
155°	674.8	670.1	676.4	679.6	675.4
157.5°	685.9	681.7	686.4	690.1	685.9
160°	695.3	692.2	695.3	698.5	694.8
162.5°	703.7	700.6	703.2	706.9	702.1
165°	711.1	707.9	709.5	713.2	709.5
167.5°	716.8	713.7	715.3	718.9	714.2
170°	721.6	718.4	719.5	723.2	718.4
172.5°	724.7	721.6	722.6	726.3	721.6
175°	727.4	723.7	724.7	728.4	723.2
177.5°	728.4	724.7	725.3	728.9	724.2
180°	725.8	725.8	725.8	725.8	725.8

(END OF REPORT)