

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007415

Luminaire Tested: S122IP-B725UB2750-4F0-XX-W2A-1_4000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007415
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122IP-B725UB2750-4F0-XX-W2A-1_4000K
Description: Define 2 Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2517.0 lumens
Efficiency: N/A
Efficacy: 119.3 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 21.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007415

CATALOG NUMBER: S122IP-B725UB2750-4F0-XX-W2A-1_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007415

CATALOG NUMBER: S122IP-B725UB2750-4F0-XX-W2A-1_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007415

CATALOG NUMBER: S122IP-B725UB2750-4F0-XX-W2A-1_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.6	0.1
90°-100°	55.6	2.2
100°-110°	176.9	7.0
110°-120°	302.6	12.0
120°-130°	398.0	15.8
130°-140°	446.8	17.7
140°-150°	438.1	17.4
150°-160°	367.5	14.6
160°-170°	243.7	9.7
170°-180°	85.2	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.6	0.1
90°-120°	535.2	21.3
90°-150°	1818.0	72.2
90°-180°	2514.0	99.9
0°-180°	2517.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	10	27	25	26	3
95°	40	47	49	49	47	44
105°	163	166	167	168	168	172
115°	304	308	307	306	304	300
125°	442	448	446	444	443	395
135°	572	580	581	581	578	442
145°	694	699	704	704	701	433
155°	793	795	798	802	799	365
165°	863	862	862	868	864	243
175°	898	896	894	899	895	85
180°	899	899	899	899	899	

TEST NUMBER: P1007415

CATALOG NUMBER: S122IP-B725UB2750-4F0-XX-W2A-1_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.8	9.9	26.6	25.0	25.8
92.5°	16.7	22.8	23.5	24.3	24.3
95°	39.5	47.1	48.6	48.6	47.1
97.5°	66.0	72.9	75.9	75.9	75.9
100°	96.4	102.5	104.7	104.7	104.0
102.5°	128.3	132.8	135.9	136.6	135.9
105°	163.2	165.5	167.0	168.5	168.5
107.5°	198.1	201.1	201.1	201.9	198.1
110°	231.5	236.0	236.0	236.0	233.8

TEST NUMBER: P1007415

CATALOG NUMBER: S122IP-B725UB2750-4F0-XX-W2A-1_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	267.9	272.5	271.7	269.4	267.9
115°	303.6	308.1	306.6	305.9	303.6
117.5°	339.3	345.3	341.5	339.3	337.0
120°	374.9	381.0	374.9	374.9	372.6
122.5°	407.6	415.1	411.4	409.1	407.6
125°	441.7	448.5	446.3	444.0	443.2
127.5°	475.1	483.5	480.4	477.4	475.1
130°	506.2	516.1	514.6	513.1	510.0
132.5°	541.1	548.7	549.5	545.7	543.4
135°	571.5	579.8	581.4	580.6	578.3
137.5°	604.9	611.7	613.2	612.5	609.4
140°	634.5	641.3	645.1	645.1	642.1
142.5°	664.8	671.7	674.0	674.7	671.7
145°	693.7	699.0	703.6	704.3	701.3
147.5°	719.5	726.3	729.4	730.9	727.8
150°	746.1	750.6	753.6	755.9	753.6
152.5°	769.6	774.1	777.9	781.0	777.9
155°	793.1	795.4	797.7	801.5	799.2
157.5°	813.6	815.1	816.6	821.9	818.2
160°	831.8	833.3	834.1	838.6	835.6
162.5°	848.5	848.5	849.3	854.6	850.8
165°	862.9	862.2	862.2	867.5	863.7
167.5°	875.8	873.6	873.6	878.9	875.1
170°	885.7	883.4	882.7	888.0	883.4
172.5°	892.5	890.3	889.5	894.8	890.3
175°	897.8	895.6	894.0	899.4	894.8
177.5°	900.9	898.6	897.1	901.6	897.1
180°	899.4	899.4	899.4	899.4	899.4

(END OF REPORT)