

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007416

Luminaire Tested: S122IP-B725UB2750-4F0-XX-W2A-1_5000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007416
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122IP-B725UB2750-4F0-XX-W2A-1_5000K
Description: Define 2 Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2434.0 lumens
Efficiency: N/A
Efficacy: 115.4 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 21.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007416

CATALOG NUMBER: S122IP-B725UB2750-4F0-XX-W2A-1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007416

CATALOG NUMBER: S122IP-B725UB2750-4F0-XX-W2A-1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007416

CATALOG NUMBER: S122IP-B725UB2750-4F0-XX-W2A-1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.5	0.1
90°-100°	53.8	2.2
100°-110°	171.0	7.0
110°-120°	292.7	12.0
120°-130°	384.9	15.8
130°-140°	432.0	17.7
140°-150°	423.7	17.4
150°-160°	355.4	14.6
160°-170°	235.7	9.7
170°-180°	82.4	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.5	0.1
90°-120°	517.5	21.3
90°-150°	1758.1	72.2
90°-180°	2432.0	99.9
0°-180°	2434.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	10	26	24	25	2
95°	38	46	47	47	46	43
105°	158	160	162	163	163	167
115°	294	298	296	296	294	290
125°	427	434	432	429	429	382
135°	553	561	562	562	559	427
145°	671	676	680	681	678	419
155°	767	769	771	775	773	353
165°	834	834	834	839	835	235
175°	868	866	865	870	865	82
180°	870	870	870	870	870	

TEST NUMBER: P1007416

CATALOG NUMBER: S122IP-B725UB2750-4F0-XX-W2A-1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.7	9.5	25.7	24.2	25.0
92.5°	16.1	22.0	22.8	23.5	23.5
95°	38.2	45.5	47.0	47.0	45.5
97.5°	63.9	70.5	73.4	73.4	73.4
100°	93.2	99.1	101.3	101.3	100.5
102.5°	124.0	128.4	131.4	132.1	131.4
105°	157.8	160.0	161.5	162.9	162.9
107.5°	191.6	194.5	194.5	195.2	191.6
110°	223.8	228.3	228.3	228.3	226.0

TEST NUMBER: P1007416

CATALOG NUMBER: S122IP-B725UB2750-4F0-XX-W2A-1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	259.1	263.5	262.7	260.5	259.1
115°	293.6	298.0	296.5	295.8	293.6
117.5°	328.1	333.9	330.3	328.1	325.9
120°	362.6	368.4	362.6	362.6	360.4
122.5°	394.1	401.5	397.8	395.6	394.1
125°	427.1	433.8	431.5	429.3	428.6
127.5°	459.4	467.5	464.6	461.6	459.4
130°	489.5	499.1	497.6	496.1	493.2
132.5°	523.3	530.6	531.4	527.7	525.5
135°	552.6	560.7	562.2	561.5	559.3
137.5°	584.9	591.5	593.0	592.3	589.3
140°	613.6	620.2	623.8	623.8	620.9
142.5°	642.9	649.5	651.7	652.5	649.5
145°	670.8	675.9	680.4	681.1	678.1
147.5°	695.8	702.4	705.3	706.8	703.8
150°	721.4	725.9	728.8	731.0	728.8
152.5°	744.2	748.6	752.3	755.2	752.3
155°	767.0	769.2	771.4	775.0	772.8
157.5°	786.8	788.2	789.7	794.8	791.2
160°	804.4	805.9	806.6	811.0	808.1
162.5°	820.5	820.5	821.3	826.4	822.7
165°	834.5	833.7	833.7	838.9	835.2
167.5°	847.0	844.7	844.7	849.9	846.2
170°	856.5	854.3	853.6	858.7	854.3
172.5°	863.1	860.9	860.2	865.3	860.9
175°	868.2	866.0	864.6	869.7	865.3
177.5°	871.2	869.0	867.5	871.9	867.5
180°	869.7	869.7	869.7	869.7	869.7

(END OF REPORT)