

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009516

Luminaire Tested: S122DIP-B865D330UB50-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009516
REPORT IS A COMBINATION OF REPORTS P984835 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D330UB50-4F0-XX-W2A-F
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4624.0 lumens
Efficiency: N/A
Efficacy: 82.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009516

CATALOG NUMBER: S122DIP-B865D330UB50-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1009516

CATALOG NUMBER: S122DIP-B865D330UB50-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77
1	103	98	94	91	97	93	90	87	84	82	79	76	74	72	68	66	65
2	94	86	80	74	89	82	76	71	74	69	65	67	63	60	60	57	55
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	53	50	47
4	78	67	59	53	74	64	56	51	58	52	47	53	48	44	47	44	40
5	72	60	51	45	68	57	49	44	52	46	41	47	42	38	43	39	35
6	66	54	45	39	63	52	44	38	47	41	36	43	37	33	39	34	31
7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	36	31	28
8	57	44	36	31	54	43	35	30	39	33	28	36	30	26	33	28	25
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22
10	50	38	30	25	47	36	29	24	33	27	23	31	25	22	28	24	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20880	20880	20880
5°	20914	19903	19762
10°	20745	18996	18619
15°	20441	18082	17417
20°	20030	17088	16278
25°	19621	16049	15141
30°	19106	15074	13949
35°	18619	14045	12776
40°	18021	13030	11670
45°	17424	12022	10584
50°	16773	10997	9456
55°	16086	9900	8388
60°	15318	8714	7279
65°	14472	7509	6113
70°	13404	6188	4936
75°	11921	4770	3811
80°	10123	3241	2453
85°	7345	1509	1044

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17424 cd/sqm

TEST NUMBER: P1009516

CATALOG NUMBER: S122DIP-B865D330UB50-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.1	2.7
10°-20°	349.3	7.6
20°-30°	513.3	11.1
30°-40°	596.2	12.9
40°-50°	595.5	12.9
50°-60°	519.2	11.2
60°-70°	383.8	8.3
70°-80°	217.2	4.7
80°-90°	58.1	1.3
90°-100°	14.3	0.3
100°-110°	53.1	1.1
110°-120°	140.9	3.0
120°-130°	233.7	5.1
130°-140°	248.3	5.4
140°-150°	230.7	5.0
150°-160°	185.5	4.0
160°-170°	119.5	2.6
170°-180°	41.1	0.9
0°-30°	986.8	21.3
0°-40°	1583.0	34.2
0°-60°	2697.7	58.3
0°-90°	3356.8	72.6
90°-120°	208.3	4.5
90°-150°	921.1	19.9
90°-180°	1267.0	27.4
0°-180°	4624.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1319	1319	1319	1319	1319	
5°	1319	1314	1300	1310	1308	125
15°	1256	1248	1232	1237	1230	354
25°	1136	1126	1105	1107	1105	523
35°	980	968	948	940	934	612
45°	798	789	770	756	751	616
55°	604	596	581	566	559	540
65°	407	400	387	375	369	403
75°	213	210	204	197	199	227
85°	52	51	50	46	44	58
90°	0	4	6	8	8	4
95°	20	10	12	14	13	24
105°	95	104	19	22	24	102
115°	180	185	193	48	26	177
125°	254	258	264	266	267	227
135°	315	320	322	326	325	243
145°	365	365	370	372	371	228
155°	402	399	403	405	402	185
165°	424	422	423	425	423	120
175°	433	431	432	434	431	41
180°	432	432	432	432	432	

TEST NUMBER: P1009516

CATALOG NUMBER: S122DIP-B865D330UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1319.1	1319.1	1319.1	1319.1	1319.1
2.5°	1326.7	1320.4	1306.4	1319.1	1316.6
5°	1319.1	1314.0	1300.1	1310.2	1307.7
7.5°	1310.2	1302.6	1288.7	1298.8	1296.3
10°	1296.3	1287.4	1272.2	1282.3	1278.5
12.5°	1277.2	1269.6	1254.4	1260.8	1258.2
15°	1255.7	1248.1	1231.6	1236.7	1230.3
17.5°	1229.0	1221.4	1204.9	1211.3	1204.9
20°	1199.9	1192.3	1174.5	1178.3	1173.2
22.5°	1170.7	1159.3	1142.8	1142.8	1140.3
25°	1136.5	1126.3	1104.7	1107.3	1104.7
27.5°	1098.4	1089.5	1073.0	1069.2	1062.9
30°	1060.4	1050.2	1031.2	1027.4	1022.3
32.5°	1019.8	1012.2	991.9	984.3	979.2
35°	980.4	967.8	947.5	939.9	933.5
37.5°	936.1	924.6	904.3	895.5	889.1
40°	890.4	880.2	860.0	848.5	843.5
42.5°	846.0	835.9	815.6	802.9	795.3
45°	797.8	788.9	769.9	755.9	750.9
47.5°	750.9	742.0	721.7	707.7	700.1
50°	701.4	695.1	677.3	659.5	653.2
52.5°	653.2	644.3	627.8	613.9	605.0
55°	603.7	596.1	580.9	565.7	559.3
57.5°	554.3	547.9	531.4	516.2	511.2
60°	504.8	499.7	482.0	468.0	464.2
62.5°	456.6	447.7	435.0	422.4	417.3
65°	407.1	399.5	386.9	375.4	369.1
67.5°	356.4	350.1	338.7	329.8	324.7
70°	309.5	304.4	293.0	284.1	279.0
72.5°	261.3	256.2	249.9	241.0	237.2
75°	213.1	210.5	204.2	196.6	199.1
77.5°	170.0	164.9	162.4	158.5	154.7
80°	126.8	125.6	123.0	119.2	116.7
82.5°	86.2	86.2	85.0	79.9	79.9
85°	52.0	50.7	49.5	45.7	44.4
87.5°	22.8	20.3	17.8	14.0	12.7
90°	0.3	3.8	6.3	7.8	8.4
92.5°	7.8	6.6	7.5	8.1	8.4
95°	20.3	10.0	12.2	13.8	13.4
97.5°	36.6	10.9	16.0	16.9	17.2
100°	55.4	12.5	17.8	20.3	21.0
102.5°	76.0	75.4	18.5	21.9	22.8
105°	95.1	104.5	19.1	22.5	23.8
107.5°	117.3	125.1	19.7	23.1	24.4
110°	138.6	145.1	54.7	23.5	24.7



TEST NUMBER: P1009516

CATALOG NUMBER: S122DIP-B865D330UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	158.6	164.2	158.9	24.1	25.0
115°	179.8	185.2	193.0	48.2	25.6
117.5°	198.3	204.6	209.9	165.1	83.2
120°	218.9	223.6	229.3	233.0	190.8
122.5°	236.5	241.5	247.7	249.6	249.9
125°	254.3	258.4	264.3	266.5	267.4
127.5°	270.6	274.9	279.6	282.8	283.1
130°	285.9	290.9	294.3	297.8	297.5
132.5°	301.5	305.6	309.0	311.8	311.5
135°	314.7	319.7	322.5	325.6	325.0
137.5°	328.4	332.2	335.3	338.4	337.5
140°	341.9	344.4	347.8	350.6	349.1
142.5°	353.1	355.3	359.4	361.9	360.3
145°	365.0	364.7	370.0	372.2	370.6
147.5°	375.3	374.4	379.7	381.3	380.0
150°	385.3	383.2	388.2	390.0	388.5
152.5°	393.8	391.3	396.0	397.9	395.7
155°	401.9	399.1	402.9	404.7	402.2
157.5°	408.5	406.0	408.8	411.0	408.5
160°	414.1	412.2	414.1	416.0	413.8
162.5°	419.1	417.2	418.8	421.0	418.2
165°	423.5	421.6	422.6	424.8	422.6
167.5°	426.9	425.1	426.0	428.2	425.4
170°	429.8	427.9	428.5	430.7	427.9
172.5°	431.6	429.8	430.4	432.6	429.8
175°	433.2	431.0	431.6	433.8	430.7
177.5°	433.8	431.6	431.9	434.1	431.3
180°	432.3	432.3	432.3	432.3	432.3

(END OF REPORT)