

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009517

Luminaire Tested: S122DIP-B865D330UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009517
REPORT IS A COMBINATION OF REPORTS P984836 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D330UB50-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4489.0 lumens
Efficiency: N/A
Efficacy: 80.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009517

CATALOG NUMBER: S122DIP-B865D330UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1009517

CATALOG NUMBER: S122DIP-B865D330UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	97	97	97	88	88	88	79	79	79
1	103	99	95	91	98	94	91	87	85	83	80	77	75	73	70	68	67
2	94	86	80	75	89	82	77	72	75	70	66	68	64	61	61	59	56
3	86	76	68	62	81	73	66	60	66	60	56	60	56	52	54	51	48
4	79	67	59	53	75	64	57	51	59	53	48	54	49	44	49	45	41
5	72	60	52	45	69	58	50	44	53	46	41	48	43	39	44	40	36
6	67	54	46	40	63	52	44	39	48	41	36	44	38	34	40	35	32
7	62	49	41	35	59	47	39	34	43	37	32	40	34	30	36	32	28
8	58	45	37	31	55	43	35	30	40	33	29	36	31	27	34	29	25
9	54	41	33	28	51	39	32	27	36	30	26	34	28	24	31	26	23
10	50	38	30	25	48	36	29	25	34	28	23	31	26	22	29	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20880	20880	20880
5°	20914	19903	19762
10°	20745	18996	18619
15°	20441	18082	17417
20°	20030	17088	16278
25°	19621	16049	15141
30°	19106	15074	13949
35°	18619	14045	12776
40°	18021	13030	11670
45°	17424	12022	10584
50°	16773	10997	9456
55°	16086	9900	8388
60°	15318	8714	7279
65°	14472	7509	6113
70°	13404	6188	4936
75°	11921	4770	3811
80°	10123	3241	2453
85°	7345	1509	1044

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17424 cd/sqm

TEST NUMBER: P1009517

CATALOG NUMBER: S122DIP-B865D330UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.1	2.8
10°-20°	349.3	7.8
20°-30°	513.3	11.4
30°-40°	596.2	13.3
40°-50°	595.5	13.3
50°-60°	519.2	11.6
60°-70°	383.8	8.6
70°-80°	217.2	4.8
80°-90°	58.5	1.3
90°-100°	25.0	0.6
100°-110°	79.6	1.8
110°-120°	136.2	3.0
120°-130°	179.2	4.0
130°-140°	201.1	4.5
140°-150°	197.2	4.4
150°-160°	165.4	3.7
160°-170°	109.7	2.4
170°-180°	38.3	0.9
0°-30°	986.8	22.0
0°-40°	1583.0	35.3
0°-60°	2697.7	60.1
0°-90°	3357.1	74.8
90°-120°	240.9	5.4
90°-150°	818.4	18.2
90°-180°	1132.0	25.2
0°-180°	4489.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1319	1319	1319	1319	1319	
5°	1319	1314	1300	1310	1308	125
15°	1256	1248	1232	1237	1230	354
25°	1136	1126	1105	1107	1105	523
35°	980	968	948	940	934	612
45°	798	789	770	756	751	616
55°	604	596	581	566	559	540
65°	407	400	387	375	369	403
75°	213	210	204	197	199	227
85°	52	51	50	46	44	58
90°	0	4	12	11	12	4
95°	18	21	22	22	21	20
105°	74	74	75	76	76	78
115°	137	139	138	138	137	135
125°	199	202	201	200	200	178
135°	257	261	262	261	260	199
145°	312	315	317	317	316	195
155°	357	358	359	361	360	164
165°	388	388	388	390	389	110
175°	404	403	402	405	403	38
180°	405	405	405	405	405	

TEST NUMBER: P1009517

CATALOG NUMBER: S122DIP-B865D330UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1319.1	1319.1	1319.1	1319.1	1319.1
2.5°	1326.7	1320.4	1306.4	1319.1	1316.6
5°	1319.1	1314.0	1300.1	1310.2	1307.7
7.5°	1310.2	1302.6	1288.7	1298.8	1296.3
10°	1296.3	1287.4	1272.2	1282.3	1278.5
12.5°	1277.2	1269.6	1254.4	1260.8	1258.2
15°	1255.7	1248.1	1231.6	1236.7	1230.3
17.5°	1229.0	1221.4	1204.9	1211.3	1204.9
20°	1199.9	1192.3	1174.5	1178.3	1173.2
22.5°	1170.7	1159.3	1142.8	1142.8	1140.3
25°	1136.5	1126.3	1104.7	1107.3	1104.7
27.5°	1098.4	1089.5	1073.0	1069.2	1062.9
30°	1060.4	1050.2	1031.2	1027.4	1022.3
32.5°	1019.8	1012.2	991.9	984.3	979.2
35°	980.4	967.8	947.5	939.9	933.5
37.5°	936.1	924.6	904.3	895.5	889.1
40°	890.4	880.2	860.0	848.5	843.5
42.5°	846.0	835.9	815.6	802.9	795.3
45°	797.8	788.9	769.9	755.9	750.9
47.5°	750.9	742.0	721.7	707.7	700.1
50°	701.4	695.1	677.3	659.5	653.2
52.5°	653.2	644.3	627.8	613.9	605.0
55°	603.7	596.1	580.9	565.7	559.3
57.5°	554.3	547.9	531.4	516.2	511.2
60°	504.8	499.7	482.0	468.0	464.2
62.5°	456.6	447.7	435.0	422.4	417.3
65°	407.1	399.5	386.9	375.4	369.1
67.5°	356.4	350.1	338.7	329.8	324.7
70°	309.5	304.4	293.0	284.1	279.0
72.5°	261.3	256.2	249.9	241.0	237.2
75°	213.1	210.5	204.2	196.6	199.1
77.5°	170.0	164.9	162.4	158.5	154.7
80°	126.8	125.6	123.0	119.2	116.7
82.5°	86.2	86.2	85.0	79.9	79.9
85°	52.0	50.7	49.5	45.7	44.4
87.5°	22.8	20.3	17.8	14.0	12.7
90°	0.3	4.4	12.0	11.3	11.6
92.5°	7.5	10.2	10.6	10.9	10.9
95°	17.8	21.2	21.9	21.9	21.2
97.5°	29.7	32.8	34.2	34.2	34.2
100°	43.4	46.1	47.1	47.1	46.8
102.5°	57.7	59.8	61.2	61.5	61.2
105°	73.5	74.5	75.2	75.8	75.8
107.5°	89.2	90.5	90.5	90.9	89.2
110°	104.2	106.2	106.2	106.2	105.2

TEST NUMBER: P1009517

CATALOG NUMBER: S122DIP-B865D330UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	120.6	122.6	122.3	121.3	120.6
115°	136.7	138.7	138.0	137.7	136.7
117.5°	152.7	155.4	153.7	152.7	151.7
120°	168.8	171.5	168.8	168.8	167.7
122.5°	183.5	186.9	185.2	184.1	183.5
125°	198.8	201.9	200.9	199.9	199.5
127.5°	213.9	217.6	216.3	214.9	213.9
130°	227.9	232.3	231.6	230.9	229.6
132.5°	243.6	247.0	247.3	245.6	244.6
135°	257.3	261.0	261.7	261.4	260.3
137.5°	272.3	275.4	276.0	275.7	274.3
140°	285.6	288.7	290.4	290.4	289.0
142.5°	299.3	302.3	303.4	303.7	302.3
145°	312.3	314.6	316.7	317.0	315.7
147.5°	323.9	326.9	328.3	329.0	327.6
150°	335.8	337.9	339.2	340.3	339.2
152.5°	346.4	348.5	350.2	351.5	350.2
155°	357.0	358.0	359.1	360.8	359.7
157.5°	366.2	366.9	367.6	370.0	368.3
160°	374.4	375.1	375.5	377.5	376.1
162.5°	381.9	381.9	382.3	384.7	383.0
165°	388.4	388.1	388.1	390.5	388.8
167.5°	394.2	393.2	393.2	395.6	393.9
170°	398.7	397.7	397.3	399.7	397.7
172.5°	401.8	400.7	400.4	402.8	400.7
175°	404.2	403.1	402.4	404.8	402.8
177.5°	405.5	404.5	403.8	405.9	403.8
180°	404.8	404.8	404.8	404.8	404.8

(END OF REPORT)