

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009525

Luminaire Tested: S122DIP-B865D530UB27-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009525
REPORT IS A COMBINATION OF REPORTS P984844 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D530UB27-4F0-XX-W2A-F
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5562.0 lumens
Efficiency: N/A
Efficacy: 89.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009525

CATALOG NUMBER: S122DIP-B865D530UB27-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1009525

CATALOG NUMBER: S122DIP-B865D530UB27-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	60	58	57
2	92	84	78	72	86	79	73	69	69	65	61	61	57	55	52	50	48
3	84	74	66	60	78	69	63	57	61	56	52	54	50	46	46	43	41
4	76	65	57	51	71	62	54	49	54	49	44	48	43	40	42	38	35
5	70	58	50	44	66	55	48	42	49	43	38	43	38	34	37	34	31
6	65	52	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27
7	60	47	39	34	56	45	37	32	40	34	29	35	30	27	31	27	24
8	56	43	35	30	52	41	34	29	37	31	26	32	28	24	29	25	22
9	52	39	32	27	49	37	30	26	34	28	24	30	25	22	26	22	20
10	49	36	29	24	46	34	28	23	31	25	21	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21528	21528	21528
5°	21563	20520	20374
10°	21386	19585	19195
15°	21074	18642	17956
20°	20651	17617	16783
25°	20229	16547	15611
30°	19697	15541	14381
35°	19197	14479	13172
40°	18579	13433	12031
45°	17963	12395	10911
50°	17292	11337	9750
55°	16587	10207	8649
60°	15794	8984	7505
65°	14924	7740	6302
70°	13819	6380	5090
75°	12290	4917	3930
80°	10443	3341	2529
85°	7571	1555	1077

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17963 cd/sqm

TEST NUMBER: P1009525

CATALOG NUMBER: S122DIP-B865D530UB27-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.0	2.3
10°-20°	360.1	6.5
20°-30°	529.2	9.5
30°-40°	614.7	11.1
40°-50°	613.9	11.0
50°-60°	535.3	9.6
60°-70°	395.7	7.1
70°-80°	223.9	4.0
80°-90°	60.3	1.1
90°-100°	23.6	0.4
100°-110°	88.1	1.6
110°-120°	233.6	4.2
120°-130°	387.5	7.0
130°-140°	411.6	7.4
140°-150°	382.5	6.9
150°-160°	307.5	5.5
160°-170°	198.2	3.6
170°-180°	68.2	1.2
0°-30°	1017.4	18.3
0°-40°	1632.1	29.3
0°-60°	2781.3	50.0
0°-90°	3461.3	62.2
90°-120°	345.3	6.2
90°-150°	1526.9	27.5
90°-180°	2101.0	37.8
0°-180°	5562.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1360	1360	1360	1360	1360	
5°	1360	1355	1340	1351	1348	129
15°	1295	1287	1270	1275	1268	365
25°	1172	1161	1139	1142	1139	539
35°	1011	998	977	969	962	631
45°	822	813	794	779	774	635
55°	622	615	599	583	577	557
65°	420	412	399	387	380	415
75°	220	217	210	203	205	234
85°	54	52	51	47	46	60
90°	0	6	10	13	14	5
95°	34	17	20	23	22	40
105°	158	173	32	37	39	168
115°	298	307	320	80	42	293
125°	422	428	438	442	443	376
135°	522	530	535	540	539	403
145°	605	605	613	617	614	378
155°	666	662	668	671	667	307
165°	702	699	700	704	700	198
175°	718	714	716	719	714	68
180°	717	717	717	717	717	

TEST NUMBER: P1009525

CATALOG NUMBER: S122DIP-B865D530UB27-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1360.0	1360.0	1360.0	1360.0	1360.0
2.5°	1367.8	1361.3	1346.9	1360.0	1357.4
5°	1360.0	1354.7	1340.4	1350.8	1348.2
7.5°	1350.8	1343.0	1328.6	1339.1	1336.4
10°	1336.4	1327.3	1311.6	1322.1	1318.1
12.5°	1316.8	1309.0	1293.3	1299.8	1297.2
15°	1294.6	1286.7	1269.7	1275.0	1268.4
17.5°	1267.1	1259.3	1242.3	1248.8	1242.3
20°	1237.1	1229.2	1210.9	1214.8	1209.6
22.5°	1207.0	1195.2	1178.2	1178.2	1175.6
25°	1171.7	1161.2	1139.0	1141.6	1139.0
27.5°	1132.4	1123.3	1106.3	1102.4	1095.8
30°	1093.2	1082.8	1063.1	1059.2	1054.0
32.5°	1051.4	1043.5	1022.6	1014.8	1009.5
35°	1010.8	997.8	976.8	969.0	962.4
37.5°	965.1	953.3	932.4	923.2	916.7
40°	918.0	907.5	886.6	874.8	869.6
42.5°	872.2	861.8	840.8	827.8	819.9
45°	822.5	813.4	793.8	779.4	774.1
47.5°	774.1	765.0	744.1	729.7	721.8
50°	723.1	716.6	698.3	680.0	673.5
52.5°	673.5	664.3	647.3	632.9	623.8
55°	622.5	614.6	598.9	583.2	576.7
57.5°	571.5	564.9	547.9	532.2	527.0
60°	520.5	515.2	496.9	482.5	478.6
62.5°	470.8	461.6	448.5	435.5	430.2
65°	419.8	411.9	398.8	387.1	380.5
67.5°	367.5	360.9	349.1	340.0	334.8
70°	319.1	313.8	302.1	292.9	287.7
72.5°	269.4	264.1	257.6	248.5	244.5
75°	219.7	217.1	210.5	202.7	205.3
77.5°	175.2	170.0	167.4	163.5	159.5
80°	130.8	129.5	126.8	122.9	120.3
82.5°	88.9	88.9	87.6	82.4	82.4
85°	53.6	52.3	51.0	47.1	45.8
87.5°	23.5	20.9	18.3	14.4	13.1
90°	0.5	6.2	10.4	13.0	14.0
92.5°	13.0	10.9	12.4	13.5	14.0
95°	33.7	16.6	20.2	22.8	22.3
97.5°	60.7	18.1	26.4	28.0	28.5
100°	91.8	20.7	29.6	33.7	34.7
102.5°	126.0	125.0	30.6	36.3	37.9
105°	157.6	173.2	31.6	37.3	39.4
107.5°	194.4	207.4	32.7	38.4	40.4
110°	229.7	240.6	90.7	38.9	41.0

TEST NUMBER: P1009525

CATALOG NUMBER: S122DIP-B865D530UB27-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	262.9	272.2	263.4	39.9	41.5
115°	298.1	307.0	319.9	79.8	42.5
117.5°	328.7	339.1	347.9	273.8	137.9
120°	363.0	370.7	380.1	386.3	316.3
122.5°	392.0	400.3	410.7	413.8	414.3
125°	421.5	428.3	438.1	441.8	443.3
127.5°	448.5	455.8	463.5	468.7	469.2
130°	473.9	482.2	487.9	493.6	493.1
132.5°	499.8	506.6	512.3	516.9	516.4
135°	521.6	529.9	534.6	539.8	538.7
137.5°	544.4	550.7	555.8	561.0	559.5
140°	566.7	570.9	576.6	581.2	578.7
142.5°	585.4	589.0	595.8	599.9	597.3
145°	605.1	604.6	613.4	617.0	614.4
147.5°	622.2	620.6	629.5	632.1	630.0
150°	638.8	635.2	643.5	646.6	644.0
152.5°	652.8	648.6	656.4	659.5	655.9
155°	666.3	661.6	667.8	670.9	666.8
157.5°	677.2	673.0	677.7	681.3	677.2
160°	686.5	683.4	686.5	689.6	686.0
162.5°	694.8	691.7	694.3	697.9	693.2
165°	702.1	698.9	700.5	704.1	700.5
167.5°	707.8	704.6	706.2	709.8	705.2
170°	712.4	709.3	710.4	714.0	709.3
172.5°	715.5	712.4	713.5	717.1	712.4
175°	718.1	714.5	715.5	719.2	714.0
177.5°	719.2	715.5	716.1	719.7	715.0
180°	716.6	716.6	716.6	716.6	716.6

(END OF REPORT)