

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007442

Luminaire Tested: S122IP-B925UB2750-4F0-XX-W2A-1_2700K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007442
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122IP-B925UB2750-4F0-XX-W2A-1_2700K
Description: Define 2 Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3248.0 lumens
Efficiency: N/A
Efficacy: 114.0 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 28.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007442

CATALOG NUMBER: S122IP-B925UB2750-4F0-XX-W2A-1_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1007442

CATALOG NUMBER: S122IP-B925UB2750-4F0-XX-W2A-1_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007442

CATALOG NUMBER: S122IP-B925UB2750-4F0-XX-W2A-1_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	3.3	0.1
90°-100°	71.8	2.2
100°-110°	228.2	7.0
110°-120°	390.5	12.0
120°-130°	513.6	15.8
130°-140°	576.5	17.7
140°-150°	565.4	17.4
150°-160°	474.2	14.6
160°-170°	314.5	9.7
170°-180°	109.9	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	3.3	0.1
90°-120°	690.5	21.3
90°-150°	2346.0	72.2
90°-180°	3245.0	99.9
0°-180°	3248.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	13	34	32	33	3
95°	51	61	63	63	61	57
105°	211	214	216	217	217	222
115°	392	398	396	395	392	388
125°	570	579	576	573	572	509
135°	738	748	750	749	746	570
145°	895	902	908	909	905	559
155°	1023	1026	1029	1034	1031	471
165°	1114	1113	1113	1119	1114	314
175°	1159	1156	1154	1161	1155	110
180°	1161	1161	1161	1161	1161	

TEST NUMBER: P1007442

CATALOG NUMBER: S122IP-B925UB2750-4F0-XX-W2A-1_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.0	12.7	34.3	32.3	33.3
92.5°	21.5	29.4	30.4	31.3	31.3
95°	50.9	60.7	62.7	62.7	60.7
97.5°	85.2	94.0	97.9	97.9	97.9
100°	124.4	132.2	135.2	135.2	134.2
102.5°	165.5	171.4	175.3	176.3	175.3
105°	210.6	213.5	215.5	217.4	217.4
107.5°	255.6	259.5	259.5	260.5	255.6
110°	298.7	304.6	304.6	304.6	301.6

TEST NUMBER: P1007442

CATALOG NUMBER: S122IP-B925UB2750-4F0-XX-W2A-1_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	345.7	351.6	350.6	347.7	345.7
115°	391.7	397.6	395.7	394.7	391.7
117.5°	437.8	445.6	440.7	437.8	434.8
120°	483.8	491.6	483.8	483.8	480.9
122.5°	525.9	535.7	530.8	527.9	525.9
125°	570.0	578.8	575.9	572.9	572.0
127.5°	613.1	623.9	619.9	616.0	613.1
130°	653.2	666.0	664.0	662.1	658.1
132.5°	698.3	708.1	709.1	704.2	701.2
135°	737.5	748.2	750.2	749.2	746.3
137.5°	780.6	789.4	791.3	790.4	786.4
140°	818.8	827.6	832.5	832.5	828.5
142.5°	857.9	866.7	869.7	870.7	866.7
145°	895.1	902.0	907.9	908.9	904.9
147.5°	928.4	937.3	941.2	943.1	939.2
150°	962.7	968.6	972.5	975.5	972.5
152.5°	993.1	999.0	1003.9	1007.8	1003.9
155°	1023.4	1026.4	1029.3	1034.2	1031.3
157.5°	1049.9	1051.8	1053.8	1060.7	1055.8
160°	1073.4	1075.4	1076.3	1082.2	1078.3
162.5°	1094.9	1094.9	1095.9	1102.8	1097.9
165°	1113.5	1112.6	1112.6	1119.4	1114.5
167.5°	1130.2	1127.3	1127.3	1134.1	1129.2
170°	1142.9	1140.0	1139.0	1145.9	1140.0
172.5°	1151.7	1148.8	1147.8	1154.7	1148.8
175°	1158.6	1155.7	1153.7	1160.6	1154.7
177.5°	1162.5	1159.6	1157.6	1163.5	1157.6
180°	1160.6	1160.6	1160.6	1160.6	1160.6

(END OF REPORT)