

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007452

Luminaire Tested: S122IP-B925UB2750-4F0-XX-W2A_2700K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007452
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122IP-B925UB2750-4F0-XX-W2A_2700K
Description: Define 2 Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3634.0 lumens
Efficiency: N/A
Efficacy: 127.5 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 28.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007452

CATALOG NUMBER: S122IP-B925UB2750-4F0-XX-W2A_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1007452

CATALOG NUMBER: S122IP-B925UB2750-4F0-XX-W2A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	8	8	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	4	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	3	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007452

CATALOG NUMBER: S122IP-B925UB2750-4F0-XX-W2A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.2	0.1
90°-100°	40.9	1.1
100°-110°	152.3	4.2
110°-120°	403.9	11.1
120°-130°	669.8	18.4
130°-140°	711.5	19.6
140°-150°	661.3	18.2
150°-160°	531.6	14.6
160°-170°	342.6	9.4
170°-180°	117.9	3.2
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.2	0.1
90°-120°	597.0	16.4
90°-150°	2639.6	72.6
90°-180°	3632.0	99.9
0°-180°	3634.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	11	18	22	24	3
95°	58	29	35	39	38	69
105°	272	299	55	64	68	291
115°	515	531	553	138	74	507
125°	729	740	758	764	766	650
135°	902	916	924	933	931	697
145°	1046	1045	1060	1067	1062	654
155°	1152	1144	1155	1160	1153	531
165°	1214	1208	1211	1217	1211	343
175°	1242	1235	1237	1243	1234	118
180°	1239	1239	1239	1239	1239	

TEST NUMBER: P1007452

CATALOG NUMBER: S122IP-B925UB2750-4F0-XX-W2A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.9	10.8	17.9	22.4	24.2
92.5°	22.4	18.8	21.5	23.3	24.2
95°	58.3	28.7	35.0	39.4	38.5
97.5°	104.9	31.4	45.7	48.4	49.3
100°	158.7	35.9	51.1	58.3	60.1
102.5°	217.8	216.0	52.9	62.7	65.4
105°	272.5	299.4	54.7	64.5	68.1
107.5°	336.2	358.6	56.5	66.3	69.9
110°	397.1	415.9	156.9	67.2	70.8

TEST NUMBER: P1007452

CATALOG NUMBER: S122IP-B925UB2750-4F0-XX-W2A_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	454.5	470.6	455.4	69.0	71.7
115°	515.4	530.7	553.1	138.0	73.5
117.5°	568.3	586.2	601.5	473.3	238.4
120°	627.5	640.9	657.1	667.8	546.8
122.5°	677.7	692.0	710.0	715.3	716.2
125°	728.8	740.4	757.5	763.7	766.4
127.5°	775.4	787.9	801.4	810.4	811.2
130°	819.3	833.7	843.5	853.4	852.5
132.5°	864.1	875.8	885.6	893.7	892.8
135°	901.8	916.1	924.2	933.2	931.4
137.5°	941.2	952.0	960.9	969.9	967.2
140°	979.8	986.9	996.8	1004.9	1000.4
142.5°	1012.0	1018.3	1030.0	1037.1	1032.7
145°	1046.1	1045.2	1060.4	1066.7	1062.2
147.5°	1075.7	1073.0	1088.2	1092.7	1089.1
150°	1104.4	1098.1	1112.4	1117.8	1113.3
152.5°	1128.6	1121.4	1134.8	1140.2	1134.0
155°	1151.9	1143.8	1154.6	1159.9	1152.8
157.5°	1170.7	1163.5	1171.6	1177.9	1170.7
160°	1186.8	1181.5	1186.8	1192.2	1185.9
162.5°	1201.2	1195.8	1200.3	1206.6	1198.5
165°	1213.7	1208.4	1211.0	1217.3	1211.0
167.5°	1223.6	1218.2	1220.9	1227.2	1219.1
170°	1231.7	1226.3	1228.1	1234.3	1226.3
172.5°	1237.0	1231.7	1233.5	1239.7	1231.7
175°	1241.5	1235.2	1237.0	1243.3	1234.3
177.5°	1243.3	1237.0	1237.9	1244.2	1236.1
180°	1238.8	1238.8	1238.8	1238.8	1238.8

(END OF REPORT)