

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007337

Luminaire Tested: S122IP-B1080UB30-4F0-XX-W2A-1

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007337
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122IP-B1080UB30-4F0-XX-W2A-1
Description: Define 2 Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3850.0 lumens
Efficiency: N/A
Efficacy: 110.0 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 35
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007337

CATALOG NUMBER: S122IP-B1080UB30-4F0-XX-W2A-1

Luminous Intensity Polar Plot



TEST NUMBER: P1007337

CATALOG NUMBER: S122IP-B1080UB30-4F0-XX-W2A-1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	8	8	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	4	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	3	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007337

CATALOG NUMBER: S122IP-B1080UB30-4F0-XX-W2A-1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	3.9	0.1
90°-100°	85.1	2.2
100°-110°	270.5	7.0
110°-120°	462.9	12.0
120°-130°	608.8	15.8
130°-140°	683.4	17.7
140°-150°	670.1	17.4
150°-160°	562.1	14.6
160°-170°	372.8	9.7
170°-180°	130.3	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	3.9	0.1
90°-120°	818.5	21.3
90°-150°	2780.8	72.2
90°-180°	3846.0	99.9
0°-180°	3850.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	15	41	38	40	4
95°	60	72	74	74	72	67
105°	250	253	255	258	258	264
115°	464	471	469	468	464	459
125°	676	686	683	679	678	604
135°	874	887	889	888	885	675
145°	1061	1069	1076	1077	1073	663
155°	1213	1217	1220	1226	1222	558
165°	1320	1319	1319	1327	1321	372
175°	1373	1370	1368	1376	1369	130
180°	1376	1376	1376	1376	1376	

TEST NUMBER: P1007337

CATALOG NUMBER: S122IP-B1080UB30-4F0-XX-W2A-1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.2	15.1	40.6	38.3	39.5
92.5°	25.5	34.8	36.0	37.1	37.1
95°	60.4	72.0	74.3	74.3	72.0
97.5°	101.0	111.4	116.1	116.1	116.1
100°	147.4	156.7	160.2	160.2	159.0
102.5°	196.2	203.2	207.8	209.0	207.8
105°	249.6	253.1	255.4	257.7	257.7
107.5°	303.0	307.6	307.6	308.8	303.0
110°	354.1	361.0	361.0	361.0	357.6

TEST NUMBER: P1007337

CATALOG NUMBER: S122IP-B1080UB30-4F0-XX-W2A-1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	409.8	416.8	415.6	412.1	409.8
115°	464.4	471.3	469.0	467.8	464.4
117.5°	518.9	528.2	522.4	518.9	515.4
120°	573.5	582.8	573.5	573.5	570.0
122.5°	623.4	635.0	629.2	625.7	623.4
125°	675.6	686.1	682.6	679.1	678.0
127.5°	726.7	739.5	734.8	730.2	726.7
130°	774.3	789.4	787.1	784.8	780.1
132.5°	827.7	839.3	840.5	834.7	831.2
135°	874.2	886.9	889.2	888.1	884.6
137.5°	925.2	935.7	938.0	936.8	932.2
140°	970.5	981.0	986.8	986.8	982.1
142.5°	1016.9	1027.4	1030.9	1032.0	1027.4
145°	1061.1	1069.2	1076.1	1077.3	1072.7
147.5°	1100.5	1111.0	1115.6	1117.9	1113.3
150°	1141.2	1148.1	1152.8	1156.3	1152.8
152.5°	1177.1	1184.1	1189.9	1194.6	1189.9
155°	1213.1	1216.6	1220.1	1225.9	1222.4
157.5°	1244.5	1246.8	1249.1	1257.2	1251.4
160°	1272.3	1274.7	1275.8	1282.8	1278.1
162.5°	1297.9	1297.9	1299.0	1307.2	1301.4
165°	1319.9	1318.8	1318.8	1326.9	1321.1
167.5°	1339.7	1336.2	1336.2	1344.3	1338.5
170°	1354.8	1351.3	1350.1	1358.2	1351.3
172.5°	1365.2	1361.7	1360.6	1368.7	1361.7
175°	1373.3	1369.9	1367.5	1375.7	1368.7
177.5°	1378.0	1374.5	1372.2	1379.1	1372.2
180°	1375.7	1375.7	1375.7	1375.7	1375.7

(END OF REPORT)