

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009617

Luminaire Tested: S122DIP-B865D925UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009617
REPORT IS A COMBINATION OF REPORTS P984966 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D925UB27-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7015.1 lumens
Efficiency: N/A
Efficacy: 93.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009617

CATALOG NUMBER: S122DIP-B865D925UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1009617

CATALOG NUMBER: S122DIP-B865D925UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	89	86	90	86	83	80	73	70	68	60	59	57	49	48	47
2	89	81	75	70	82	75	70	65	64	60	56	53	50	48	43	41	39
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	36	34
4	74	63	55	49	68	59	52	46	50	45	40	42	38	35	34	31	29
5	68	56	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25
6	63	51	43	37	58	47	40	35	40	35	30	34	30	26	28	25	22
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	22	20
8	54	42	34	28	50	39	32	27	33	28	24	28	24	21	23	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	18	16
10	47	35	28	23	43	32	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21528	21528	21528
5°	21563	20520	20374
10°	21386	19585	19195
15°	21074	18642	17956
20°	20651	17617	16783
25°	20229	16547	15611
30°	19697	15541	14381
35°	19197	14479	13172
40°	18579	13433	12031
45°	17963	12395	10911
50°	17292	11337	9750
55°	16587	10207	8649
60°	15794	8984	7505
65°	14924	7740	6302
70°	13819	6380	5090
75°	12290	4917	3930
80°	10443	3341	2529
85°	7571	1555	1077

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17963 cd/sqm

TEST NUMBER: P1009617

CATALOG NUMBER: S122DIP-B865D925UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.0	1.8
10°-20°	360.1	5.1
20°-30°	529.2	7.5
30°-40°	614.7	8.8
40°-50°	613.9	8.8
50°-60°	535.3	7.6
60°-70°	395.7	5.6
70°-80°	223.9	3.2
80°-90°	62.3	0.9
90°-100°	206.5	2.9
100°-110°	698.2	10.0
110°-120°	733.9	10.5
120°-130°	603.5	8.6
130°-140°	484.9	6.9
140°-150°	366.3	5.2
150°-160°	257.5	3.7
160°-170°	151.6	2.2
170°-180°	49.3	0.7
0°-30°	1017.4	14.5
0°-40°	1632.1	23.3
0°-60°	2781.3	39.6
0°-90°	3463.3	49.4
90°-120°	1638.5	23.4
90°-150°	3093.3	44.1
90°-180°	3552.0	50.6
0°-180°	7015.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1360	1360	1360	1360	1360	
5°	1360	1355	1340	1351	1348	129
15°	1295	1287	1270	1275	1268	365
25°	1172	1161	1139	1142	1139	539
35°	1011	998	977	969	962	631
45°	822	813	794	779	774	635
55°	622	615	599	583	577	557
65°	420	412	399	387	380	415
75°	220	217	210	203	205	234
85°	54	52	51	47	46	60
90°	1	13	33	32	32	6
95°	34	84	384	145	112	35
105°	120	180	726	1298	1104	127
115°	211	266	607	1254	1453	209
125°	294	348	584	1015	1179	261
135°	345	412	577	853	977	266
145°	394	453	574	713	780	247
155°	448	483	557	630	655	206
165°	488	503	534	566	575	138
175°	508	509	513	520	518	48
180°	509	509	509	509	509	

TEST NUMBER: P1009617

CATALOG NUMBER: S122DIP-B865D925UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1360.0	1360.0	1360.0	1360.0	1360.0
2.5°	1367.8	1361.3	1346.9	1360.0	1357.4
5°	1360.0	1354.7	1340.4	1350.8	1348.2
7.5°	1350.8	1343.0	1328.6	1339.1	1336.4
10°	1336.4	1327.3	1311.6	1322.1	1318.1
12.5°	1316.8	1309.0	1293.3	1299.8	1297.2
15°	1294.6	1286.7	1269.7	1275.0	1268.4
17.5°	1267.1	1259.3	1242.3	1248.8	1242.3
20°	1237.1	1229.2	1210.9	1214.8	1209.6
22.5°	1207.0	1195.2	1178.2	1178.2	1175.6
25°	1171.7	1161.2	1139.0	1141.6	1139.0
27.5°	1132.4	1123.3	1106.3	1102.4	1095.8
30°	1093.2	1082.8	1063.1	1059.2	1054.0
32.5°	1051.4	1043.5	1022.6	1014.8	1009.5
35°	1010.8	997.8	976.8	969.0	962.4
37.5°	965.1	953.3	932.4	923.2	916.7
40°	918.0	907.5	886.6	874.8	869.6
42.5°	872.2	861.8	840.8	827.8	819.9
45°	822.5	813.4	793.8	779.4	774.1
47.5°	774.1	765.0	744.1	729.7	721.8
50°	723.1	716.6	698.3	680.0	673.5
52.5°	673.5	664.3	647.3	632.9	623.8
55°	622.5	614.6	598.9	583.2	576.7
57.5°	571.5	564.9	547.9	532.2	527.0
60°	520.5	515.2	496.9	482.5	478.6
62.5°	470.8	461.6	448.5	435.5	430.2
65°	419.8	411.9	398.8	387.1	380.5
67.5°	367.5	360.9	349.1	340.0	334.8
70°	319.1	313.8	302.1	292.9	287.7
72.5°	269.4	264.1	257.6	248.5	244.5
75°	219.7	217.1	210.5	202.7	205.3
77.5°	175.2	170.0	167.4	163.5	159.5
80°	130.8	129.5	126.8	122.9	120.3
82.5°	88.9	88.9	87.6	82.4	82.4
85°	53.6	52.3	51.0	47.1	45.8
87.5°	23.5	20.9	18.3	14.4	13.1
90°	1.0	13.2	33.3	31.8	32.3
92.5°	14.7	46.5	150.9	69.6	59.8
95°	34.3	84.2	384.0	145.0	111.7
97.5°	50.9	111.2	626.0	291.0	187.1
100°	75.4	136.2	774.0	579.5	350.7
102.5°	98.0	158.7	778.8	979.7	683.8
105°	119.5	180.2	725.9	1297.6	1104.1
107.5°	143.0	201.8	677.0	1412.7	1387.2
110°	166.5	223.9	643.7	1394.1	1502.8

TEST NUMBER: P1009617

CATALOG NUMBER: S122DIP-B865D925UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	188.1	244.9	622.1	1330.9	1500.9
115°	210.6	266.0	607.4	1253.6	1452.9
117.5°	234.1	287.0	599.6	1179.5	1380.4
120°	255.7	307.6	592.7	1113.4	1310.8
122.5°	276.3	328.7	588.8	1062.0	1238.3
125°	293.9	347.8	583.9	1015.4	1178.6
127.5°	308.6	365.9	581.0	975.8	1122.7
130°	321.3	382.1	579.0	935.6	1076.7
132.5°	333.1	397.8	578.0	894.0	1028.7
135°	344.8	411.5	577.0	853.3	976.7
137.5°	355.6	423.2	577.0	812.2	926.8
140°	368.4	434.0	576.1	776.0	874.9
142.5°	381.1	442.8	576.1	741.2	822.9
145°	393.8	452.6	574.1	712.7	779.8
147.5°	407.5	460.4	571.2	687.8	741.6
150°	421.3	468.3	568.2	666.2	708.3
152.5°	435.0	476.2	563.3	648.0	679.9
155°	447.7	483.4	557.4	630.4	655.4
157.5°	458.5	489.4	551.6	613.8	633.9
160°	469.3	495.2	545.7	597.1	613.3
162.5°	480.0	499.6	540.8	581.4	593.7
165°	487.9	502.6	533.9	566.2	575.1
167.5°	494.7	505.6	528.1	552.6	557.4
170°	501.6	507.0	523.2	539.8	541.8
172.5°	505.5	508.4	517.3	528.6	529.0
175°	508.5	509.0	513.4	519.7	518.3
177.5°	510.4	509.4	509.4	513.4	510.4
180°	509.4	509.4	509.4	509.4	509.4

(END OF REPORT)