

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010395

Luminaire Tested: S123DIP-B1000D1025UB2750-4F0-XX-W2A-A_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010395
REPORT IS A COMBINATION OF REPORTS P989029 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D1025UB2750-4F0-XX-W2A-A_3000K
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8271.0 lumens
Efficiency: N/A
Efficacy: 109.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010395

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010395

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57
1	98	94	90	87	91	87	84	81	74	72	69	62	60	59	51	50	49
2	90	82	76	71	83	76	71	67	65	61	58	55	52	50	45	43	41
3	82	73	65	60	75	67	61	56	58	53	49	49	45	42	40	38	36
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31
5	69	58	49	44	64	54	46	41	46	41	36	39	35	32	33	29	27
6	64	52	44	38	59	48	41	36	42	36	32	35	31	28	30	26	24
7	59	47	39	33	54	44	36	31	38	32	28	32	28	25	27	24	21
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	25	21	19
9	51	39	31	26	47	36	29	25	32	26	22	27	23	20	23	20	17
10	47	35	28	24	44	33	27	22	29	24	20	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15029	15029	15029	15029
5°	15039	17316	15082	12923
10°	14943	20955	14958	11285
15°	14737	24851	14856	10158
20°	14559	28611	14590	9348
25°	14294	29332	14326	8925
30°	14106	24234	14106	8647
35°	13872	16208	13786	8402
40°	13592	11700	13425	8027
45°	13241	9267	12860	7561
50°	12386	7870	11945	7103
55°	11448	6916	10982	6593
60°	10497	6022	9937	6056
65°	9452	5156	8995	5341
70°	8366	4281	7810	4503
75°	7155	3228	6691	3475
80°	5657	2154	5217	2283
85°	3900	989	3122	900

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 24237 cd/sqm

TEST NUMBER: P1010395

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.3	1.7
10°-20°	441.0	5.3
20°-30°	742.1	9.0
30°-40°	838.6	10.1
40°-50°	751.1	9.1
50°-60°	606.3	7.3
60°-70°	422.5	5.1
70°-80°	221.8	2.7
80°-90°	55.8	0.7
90°-100°	46.9	0.6
100°-110°	226.7	2.7
110°-120°	555.6	6.7
120°-130°	705.4	8.5
130°-140°	753.5	9.1
140°-150°	704.6	8.5
150°-160°	568.4	6.9
160°-170°	366.8	4.4
170°-180°	126.4	1.5
0°-30°	1320.4	16.0
0°-40°	2159.1	26.1
0°-60°	3516.5	42.5
0°-90°	4216.7	51.0
90°-120°	829.3	10.0
90°-150°	2992.8	36.2
90°-180°	4054.0	49.0
0°-180°	8271.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1396	1396	1396	1396	1396	
5°	1395	1659	1399	1238	1395	132
15°	1331	2469	1342	1009	1331	376
25°	1218	2930	1220	892	1218	562
35°	1074	1579	1068	818	1074	672
45°	892	852	866	695	892	682
55°	632	579	606	552	632	566
65°	391	376	372	390	391	389
75°	188	194	176	208	188	202
85°	41	45	32	41	41	47
90°	1	30	1	30	1	6
95°	60	38	60	38	60	72
105°	294	44	294	44	294	312
115°	552	581	552	581	552	545
125°	779	794	779	794	779	696
135°	969	979	969	979	969	746
145°	1118	1129	1118	1129	1118	700
155°	1232	1230	1232	1230	1232	568
165°	1299	1296	1299	1296	1299	367
175°	1330	1325	1330	1325	1330	127
180°	1330	1330	1330	1330	1330	

TEST NUMBER: P1010395

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2
2.5°	1400.3	1411.1	1416.5	1424.6	1432.7	1444.9	1449.0	1455.7	1453.0	1458.4	1461.2
5°	1394.9	1413.8	1430.0	1450.3	1469.3	1482.8	1496.3	1518.0	1534.2	1536.9	1549.1
7.5°	1385.4	1412.4	1440.9	1469.3	1505.8	1527.4	1551.8	1581.6	1605.9	1645.2	1660.0
10°	1373.2	1411.1	1451.7	1490.9	1541.0	1574.8	1604.6	1654.6	1704.7	1745.3	1783.2
12.5°	1354.3	1401.6	1454.4	1512.6	1577.5	1616.7	1657.3	1723.6	1799.4	1861.6	1902.2
15°	1331.3	1390.8	1458.4	1520.7	1592.4	1665.4	1708.7	1783.2	1891.4	1949.6	2053.7
17.5°	1312.3	1373.2	1440.9	1538.3	1635.7	1708.7	1739.9	1876.5	1950.9	2048.3	2166.0
20°	1282.6	1359.7	1446.3	1543.7	1669.5	1714.2	1777.7	1915.7	2007.7	2134.9	2279.7
22.5°	1251.5	1334.0	1438.2	1539.6	1680.3	1727.7	1814.3	1923.9	2070.0	2195.8	2355.4
25°	1217.6	1306.9	1412.4	1532.9	1670.9	1739.9	1821.0	1956.3	2114.6	2272.9	2420.4
27.5°	1183.8	1281.2	1390.8	1511.2	1645.2	1726.3	1807.5	1948.2	2151.1	2323.0	2511.0
30°	1151.3	1248.7	1358.3	1481.4	1622.2	1700.6	1777.7	1953.6	2179.6	2373.0	2562.4
32.5°	1116.2	1216.3	1331.3	1434.1	1576.2	1660.0	1746.6	1953.6	2197.1	2402.8	2576.0
35°	1074.2	1177.0	1275.8	1378.6	1519.3	1612.7	1710.1	1940.1	2213.4	2412.3	2519.1
37.5°	1033.6	1124.3	1209.5	1309.6	1457.1	1557.2	1669.5	1923.9	2205.3	2371.7	2401.4
40°	987.6	1078.3	1147.3	1240.6	1396.2	1512.6	1626.2	1902.2	2170.1	2275.6	2189.0
42.5°	943.0	1014.7	1074.2	1164.9	1334.0	1447.6	1570.7	1863.0	2101.1	2122.7	1927.9
45°	891.6	943.0	995.7	1098.6	1266.3	1382.7	1519.3	1806.1	1990.1	1927.9	1681.7
47.5°	825.3	871.3	929.5	1024.2	1194.6	1315.0	1444.9	1733.1	1829.1	1699.3	1430.0
50°	761.7	800.9	855.0	947.0	1118.9	1236.6	1374.6	1618.1	1665.4	1461.2	1232.5
52.5°	698.1	727.9	780.6	872.6	1044.5	1158.1	1283.9	1500.4	1473.3	1254.2	1051.2
55°	631.8	657.5	707.6	798.2	957.9	1066.1	1186.5	1355.6	1285.3	1076.9	914.6
57.5°	566.9	593.9	645.3	721.1	871.3	976.8	1072.9	1205.5	1099.9	933.5	790.1
60°	508.7	531.7	570.9	645.3	782.0	867.2	955.2	1045.8	957.9	796.9	687.3
62.5°	447.8	469.5	506.0	573.6	691.3	767.1	837.5	911.9	814.5	696.8	599.3
65°	391.0	408.6	442.4	504.6	600.7	662.9	719.8	771.2	692.7	584.5	511.4
67.5°	339.6	354.5	382.9	438.3	519.5	564.2	610.2	653.5	587.2	500.6	438.3
70°	284.1	296.3	322.0	362.6	427.5	473.5	507.3	539.8	480.3	411.3	369.3
72.5°	235.4	247.6	263.8	305.8	350.4	378.8	415.3	432.9	399.1	342.3	300.3
75°	188.1	197.5	212.4	239.5	281.4	300.3	323.3	336.9	305.8	267.9	242.2
77.5°	147.5	151.5	162.4	181.3	209.7	231.3	248.9	257.1	235.4	211.1	189.4
80°	104.2	109.6	117.7	133.9	155.6	162.4	173.2	182.6	169.1	147.5	133.9
82.5°	69.0	75.8	79.8	86.6	100.1	108.2	110.9	119.1	106.9	98.8	93.4
85°	40.6	43.3	44.6	48.7	55.5	59.5	63.6	64.9	62.2	60.9	55.5
87.5°	20.3	20.3	20.3	23.0	24.4	27.1	28.4	28.4	28.4	27.1	25.7
90°	1.0	3.2	5.4	7.6	9.8	10.9	12.3	15.2	18.0	20.9	23.7
92.5°	22.7	21.4	20.1	18.8	17.5	16.8	17.8	19.8	21.7	23.7	25.7
95°	60.3	51.3	42.3	33.3	24.3	19.8	21.0	23.4	25.8	28.2	30.6
97.5°	109.7	103.5	97.4	91.2	85.1	82.0	76.4	65.2	54.0	42.8	31.6
100°	167.0	171.4	175.8	180.1	184.5	186.7	169.6	135.3	101.1	66.8	32.6
102.5°	232.2	235.0	237.9	240.7	243.6	245.0	225.9	187.7	149.5	111.3	73.1
105°	294.4	296.8	299.2	301.7	304.1	305.3	295.4	275.7	255.9	236.2	216.4
107.5°	360.6	362.6	364.6	366.5	368.5	369.5	371.1	374.4	377.7	381.0	384.3
110°	426.8	428.6	430.3	432.1	433.8	434.7	435.9	438.3	440.8	443.2	445.6

TEST NUMBER: P1010395

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	490.1	491.6	493.2	494.7	496.2	497.0	498.2	500.6	503.1	505.5	507.9
115°	552.3	553.6	554.9	556.2	557.5	558.2	559.2	561.2	563.1	565.1	567.1
117.5°	613.6	615.1	616.7	618.2	619.7	620.5	621.0	622.1	623.2	624.3	625.4
120°	669.9	671.9	673.9	675.8	677.8	678.8	679.1	679.8	680.5	681.1	681.8
122.5°	727.2	728.7	730.3	731.8	733.3	734.1	734.5	735.4	736.3	737.2	738.1
125°	778.6	780.4	782.1	783.9	785.6	786.5	786.9	787.8	788.7	789.5	790.4
127.5°	830.0	831.8	833.5	835.3	837.0	837.9	838.4	839.5	840.6	841.7	842.8
130°	877.4	879.2	880.9	882.7	884.4	885.3	885.7	886.6	887.5	888.3	889.2
132.5°	922.8	924.6	926.3	928.1	929.8	930.7	931.0	931.7	932.4	933.0	933.7
135°	969.3	970.6	971.9	973.2	974.5	975.2	975.6	976.5	977.4	978.3	979.2
137.5°	1008.8	1010.6	1012.3	1014.1	1015.8	1016.7	1016.9	1017.4	1017.8	1018.3	1018.7
140°	1048.3	1049.6	1050.9	1052.2	1053.5	1054.2	1054.5	1055.2	1055.9	1056.5	1057.2
142.5°	1084.9	1086.2	1087.5	1088.8	1090.1	1090.8	1091.1	1091.8	1092.5	1093.1	1093.8
145°	1118.5	1120.0	1121.6	1123.1	1124.6	1125.4	1125.6	1126.1	1126.5	1127.0	1127.4
147.5°	1151.1	1152.2	1153.3	1154.4	1155.5	1156.0	1156.2	1156.7	1157.1	1157.6	1158.0
150°	1180.7	1181.4	1182.0	1182.7	1183.4	1183.7	1183.9	1184.4	1184.8	1185.3	1185.7
152.5°	1207.4	1207.6	1207.8	1208.1	1208.3	1208.4	1208.5	1208.7	1209.0	1209.2	1209.4
155°	1232.1	1231.7	1231.2	1230.8	1230.3	1230.1	1230.2	1230.4	1230.7	1230.9	1231.1
157.5°	1251.9	1251.9	1251.9	1251.9	1251.9	1251.9	1251.8	1251.6	1251.3	1251.1	1250.9
160°	1269.6	1269.4	1269.2	1269.0	1268.8	1268.7	1268.6	1268.4	1268.1	1267.9	1267.7
162.5°	1286.4	1285.8	1285.1	1284.5	1283.8	1283.5	1283.4	1283.2	1282.9	1282.7	1282.5
165°	1299.3	1298.6	1298.0	1297.3	1296.6	1296.3	1296.2	1296.0	1295.7	1295.5	1295.3
167.5°	1310.1	1309.2	1308.4	1307.5	1306.6	1306.2	1306.2	1306.2	1306.2	1306.2	1306.2
170°	1319.0	1318.1	1317.3	1316.4	1315.5	1315.1	1315.1	1315.1	1315.1	1315.1	1315.1
172.5°	1325.0	1323.9	1322.8	1321.7	1320.6	1320.0	1320.1	1320.3	1320.6	1320.8	1321.0
175°	1329.9	1328.8	1327.7	1326.6	1325.5	1325.0	1325.1	1325.3	1325.6	1325.8	1326.0
177.5°	1331.9	1330.8	1329.7	1328.6	1327.5	1326.9	1327.0	1327.2	1327.5	1327.7	1327.9
180°	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9

TEST NUMBER: P1010395

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2
2.5°	1470.6	1473.3	1482.8	1489.6	1503.1	1501.7	1501.7	1500.4	1496.3	1503.1	1507.2
5°	1573.4	1596.4	1599.2	1628.9	1630.3	1642.4	1650.6	1643.8	1660.0	1658.7	1646.5
7.5°	1700.6	1731.7	1746.6	1775.0	1807.5	1799.4	1830.5	1835.9	1833.2	1846.7	1856.2
10°	1840.0	1894.1	1932.0	1984.7	1998.3	2006.4	2026.7	2044.3	2079.4	2052.4	2070.0
12.5°	1999.6	2038.9	2088.9	2172.8	2214.7	2241.8	2251.3	2263.4	2287.8	2272.9	2274.3
15°	2133.6	2186.3	2271.6	2375.7	2387.9	2421.7	2413.6	2486.7	2521.8	2469.1	2498.8
17.5°	2272.9	2343.3	2444.7	2535.4	2586.8	2609.8	2631.4	2701.8	2699.1	2691.0	2697.7
20°	2362.2	2477.2	2603.0	2723.4	2738.3	2755.9	2814.1	2843.8	2838.4	2861.4	2876.3
22.5°	2488.0	2609.8	2743.7	2823.5	2857.4	2877.7	2923.7	2942.6	2950.7	2956.1	2946.7
25°	2593.5	2723.4	2822.2	2892.5	2912.8	2923.7	2938.5	2944.0	2939.9	2930.4	2938.5
27.5°	2665.3	2769.4	2837.1	2869.5	2858.7	2841.1	2812.7	2793.8	2751.8	2731.5	2755.9
30°	2695.0	2741.0	2761.3	2707.2	2653.1	2609.8	2555.7	2455.6	2377.1	2400.1	2369.0
32.5°	2647.7	2617.9	2520.5	2381.1	2339.2	2268.8	2116.0	1998.3	2002.3	1940.1	1965.8
35°	2508.3	2373.0	2189.0	1978.0	1922.5	1884.6	1716.9	1691.2	1637.0	1578.9	1595.1
37.5°	2262.1	2064.6	1841.3	1685.7	1603.2	1520.7	1426.0	1369.2	1336.7	1312.3	1331.3
40°	1961.7	1720.9	1536.9	1397.6	1327.2	1274.5	1209.5	1152.7	1116.2	1112.1	1118.9
42.5°	1666.8	1463.9	1294.7	1162.2	1139.2	1076.9	1035.0	990.3	979.5	961.9	971.4
45°	1411.1	1246.0	1106.7	998.5	971.4	955.2	903.8	875.3	863.2	852.3	868.6
47.5°	1225.7	1052.6	951.1	886.2	859.1	832.0	803.6	784.7	775.2	776.6	775.2
50°	1047.2	920.0	830.7	780.6	764.4	745.5	722.5	710.3	706.2	694.0	703.5
52.5°	901.0	809.0	746.8	699.5	687.3	673.8	654.8	648.0	638.6	635.9	635.9
55°	783.3	711.6	661.6	630.5	615.6	604.8	593.9	585.8	579.1	579.1	579.1
57.5°	691.3	629.1	592.6	565.5	560.1	549.3	537.1	537.1	527.6	526.3	530.3
60°	612.9	557.4	529.0	506.0	497.9	495.2	483.0	483.0	480.3	473.5	478.9
62.5°	533.1	492.5	468.1	450.5	442.4	442.4	432.9	426.2	426.2	427.5	424.8
65°	460.0	430.2	408.6	395.1	391.0	385.6	384.2	378.8	374.8	376.1	374.8
67.5°	395.1	372.1	357.2	346.3	339.6	336.9	332.8	332.8	330.1	331.5	324.7
70°	336.9	313.9	301.7	290.9	288.2	288.2	282.8	284.1	281.4	285.5	282.8
72.5°	277.3	259.8	250.3	246.2	243.5	242.2	239.5	236.8	235.4	238.1	236.8
75°	224.6	209.7	202.9	200.2	197.5	197.5	196.2	194.8	193.5	193.5	193.5
77.5°	174.5	165.1	156.9	159.6	155.6	156.9	152.9	152.9	154.2	152.9	152.9
80°	128.5	121.8	121.8	119.1	113.6	116.4	116.4	112.3	110.9	113.6	109.6
82.5°	85.2	83.9	81.2	79.8	77.1	78.5	77.1	75.8	74.4	77.1	74.4
85°	50.1	50.1	48.7	46.0	48.7	47.4	46.0	46.0	44.6	44.6	44.6
87.5°	25.7	23.0	23.0	21.6	23.0	20.3	21.6	20.3	18.9	20.3	18.9
90°	24.6	25.5	26.4	27.3	27.7	27.9	28.3	28.8	29.2	29.6	29.2
92.5°	27.2	28.8	30.3	31.8	32.6	32.7	32.9	33.2	33.4	33.6	33.4
95°	32.1	33.7	35.2	36.7	37.5	37.5	37.5	37.5	37.5	37.5	37.5
97.5°	33.4	35.1	36.9	38.6	39.5	39.6	39.8	40.1	40.3	40.5	40.3
100°	34.4	36.1	37.9	39.6	40.5	40.6	40.8	41.1	41.3	41.5	41.3
102.5°	65.9	58.6	51.4	44.1	40.5	40.7	41.2	41.6	42.1	42.5	42.1
105°	177.5	138.7	99.8	60.9	41.5	41.7	42.2	42.6	43.1	43.5	43.1
107.5°	350.5	316.7	282.9	249.1	232.2	217.8	189.1	160.3	131.6	102.8	131.6
110°	438.4	431.1	423.9	416.6	413.0	397.3	365.9	334.5	303.1	271.7	303.1

TEST NUMBER: P1010395

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	509.9	511.8	513.8	515.7	516.7	516.5	516.1	515.6	515.2	514.8	515.2
115°	569.3	571.5	573.7	575.9	577.0	577.4	578.3	579.2	580.1	581.0	580.1
117.5°	627.2	628.9	630.7	632.4	633.3	633.4	633.6	633.9	634.1	634.3	634.1
120°	683.6	685.3	687.1	688.8	689.7	689.7	689.7	689.7	689.7	689.7	689.7
122.5°	739.2	740.3	741.4	742.5	743.0	743.1	743.3	743.6	743.8	744.0	743.8
125°	790.8	791.3	791.7	792.2	792.4	792.6	793.1	793.5	794.0	794.4	794.0
127.5°	843.5	844.1	844.8	845.5	845.8	845.6	845.1	844.7	844.2	843.8	844.2
130°	890.1	891.0	891.9	892.8	893.2	893.0	892.5	892.1	891.6	891.2	891.6
132.5°	934.6	935.5	936.4	937.3	937.7	937.4	936.7	936.0	935.4	934.7	935.4
135°	979.8	980.5	981.1	981.8	982.1	981.8	981.1	980.5	979.8	979.2	979.8
137.5°	1019.8	1020.9	1022.0	1023.1	1023.6	1023.4	1022.9	1022.5	1022.0	1021.6	1022.0
140°	1058.1	1059.0	1059.9	1060.8	1061.2	1061.0	1060.5	1060.1	1059.6	1059.2	1059.6
142.5°	1094.4	1095.1	1095.7	1096.4	1096.7	1096.4	1095.7	1095.1	1094.4	1093.8	1094.4
145°	1127.8	1128.2	1128.7	1129.1	1129.3	1129.3	1129.3	1129.3	1129.3	1129.3	1129.3
147.5°	1158.4	1158.9	1159.3	1159.8	1160.0	1159.4	1158.3	1157.2	1156.1	1155.0	1156.1
150°	1186.1	1186.5	1187.0	1187.4	1187.6	1187.3	1186.6	1186.0	1185.3	1184.7	1185.3
152.5°	1210.3	1211.1	1212.0	1212.9	1213.3	1212.8	1211.7	1210.6	1209.5	1208.4	1209.5
155°	1232.2	1233.3	1234.4	1235.5	1236.0	1235.3	1234.0	1232.7	1231.4	1230.1	1231.4
157.5°	1252.2	1253.5	1254.8	1256.1	1256.8	1255.9	1254.2	1252.4	1250.7	1248.9	1250.7
160°	1269.0	1270.3	1271.6	1272.9	1273.6	1272.8	1271.3	1269.8	1268.2	1266.7	1268.2
162.5°	1284.0	1285.6	1287.1	1288.6	1289.4	1288.7	1287.4	1286.1	1284.8	1283.5	1284.8
165°	1297.1	1298.8	1300.6	1302.3	1303.2	1302.4	1300.9	1299.4	1297.8	1296.3	1297.8
167.5°	1308.0	1309.7	1311.5	1313.2	1314.1	1313.2	1311.5	1309.7	1308.0	1306.2	1308.0
170°	1316.9	1318.6	1320.4	1322.1	1323.0	1322.1	1320.4	1318.6	1316.9	1315.1	1316.9
172.5°	1322.8	1324.5	1326.3	1328.0	1328.9	1327.9	1325.9	1324.0	1322.0	1320.0	1322.0
175°	1327.5	1329.1	1330.6	1332.1	1332.9	1332.0	1330.3	1328.5	1326.8	1325.0	1326.8
177.5°	1329.7	1331.4	1333.2	1334.9	1335.8	1334.7	1332.5	1330.4	1328.2	1326.0	1328.2
180°	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9

TEST NUMBER: P1010395

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2
2.5°	1496.3	1500.4	1489.6	1486.9	1486.9	1492.3	1488.2	1451.7	1458.4	1450.3	1447.6
5°	1661.4	1653.3	1642.4	1637.0	1630.3	1611.3	1610.0	1568.0	1559.9	1532.9	1520.7
7.5°	1842.7	1835.9	1803.4	1799.4	1796.7	1779.1	1734.4	1689.8	1657.3	1626.2	1596.4
10°	2049.7	2029.4	2014.5	1984.7	1969.9	1945.5	1887.3	1845.4	1789.9	1742.6	1680.3
12.5°	2298.6	2275.6	2225.6	2203.9	2185.0	2117.3	2059.1	2011.8	1903.6	1871.1	1794.0
15°	2481.3	2432.6	2427.1	2379.8	2377.1	2302.7	2191.7	2140.3	2056.4	1937.4	1857.6
17.5°	2678.8	2635.5	2601.7	2544.8	2536.7	2466.4	2385.2	2259.4	2167.4	2053.7	1952.3
20°	2823.5	2800.5	2742.4	2719.4	2672.0	2612.5	2528.6	2373.0	2260.7	2147.1	2022.6
22.5°	2938.5	2915.5	2869.5	2838.4	2811.4	2734.3	2634.1	2501.6	2347.3	2198.5	2070.0
25°	2937.2	2930.4	2911.5	2896.6	2876.3	2819.5	2735.6	2608.4	2436.6	2272.9	2094.3
27.5°	2770.8	2789.7	2822.2	2838.4	2834.4	2826.3	2778.9	2672.0	2517.8	2323.0	2122.7
30°	2424.4	2493.4	2554.3	2635.5	2659.8	2719.4	2746.4	2685.5	2562.4	2381.1	2159.3
32.5°	2010.4	2110.6	2243.1	2287.8	2364.9	2479.9	2608.4	2631.4	2554.3	2415.0	2182.3
35°	1649.2	1731.7	1834.6	1904.9	1973.9	2160.6	2323.0	2463.7	2489.4	2397.4	2176.9
37.5°	1365.1	1423.3	1513.9	1573.4	1637.0	1796.7	2024.0	2206.6	2335.1	2337.8	2162.0
40°	1159.5	1185.2	1263.6	1306.9	1367.8	1505.8	1708.7	1946.9	2134.9	2221.5	2122.7
42.5°	982.2	1016.0	1081.0	1113.5	1152.7	1273.1	1407.0	1633.0	1865.7	2051.0	2049.7
45°	876.7	901.0	930.8	957.9	1002.5	1074.2	1227.1	1396.2	1619.4	1829.1	1911.7
47.5°	783.3	806.3	836.1	844.2	874.0	941.6	1035.0	1182.5	1390.8	1599.2	1754.7
50°	704.9	723.8	744.1	759.0	772.5	828.0	898.3	1022.8	1189.2	1390.8	1584.3
52.5°	644.0	657.5	675.1	683.2	695.4	736.0	790.1	882.1	1018.7	1202.7	1390.8
55°	587.2	596.6	607.5	621.0	626.4	656.2	698.1	776.6	878.0	1043.1	1221.7
57.5°	534.4	538.5	545.2	553.3	560.1	585.8	622.3	675.1	764.4	891.6	1060.7
60°	474.9	485.7	489.8	497.9	501.9	522.2	550.6	595.3	664.3	773.9	901.0
62.5°	424.8	431.6	438.3	442.4	451.9	458.6	481.6	522.2	579.1	660.2	775.2
65°	380.2	382.9	386.9	391.0	393.7	401.8	423.5	450.5	493.8	565.5	654.8
67.5°	328.8	331.5	336.9	338.2	340.9	351.8	363.9	386.9	423.5	477.6	550.6
70°	278.7	282.8	285.5	288.2	292.2	296.3	309.8	328.8	357.2	395.1	451.9
72.5°	235.4	239.5	239.5	242.2	240.8	246.2	259.8	273.3	292.2	323.3	373.4
75°	192.1	192.1	194.8	196.2	197.5	202.9	208.3	219.2	234.1	258.4	289.5
77.5°	151.5	150.2	152.9	152.9	152.9	156.9	162.4	167.8	177.2	194.8	219.2
80°	110.9	110.9	113.6	115.0	112.3	113.6	116.4	121.8	128.5	140.7	154.2
82.5°	73.1	78.5	77.1	78.5	77.1	79.8	81.2	82.5	85.2	90.6	100.1
85°	44.6	44.6	44.6	46.0	44.6	46.0	46.0	46.0	47.4	50.1	54.1
87.5°	18.9	18.9	18.9	20.3	18.9	18.9	20.3	18.9	20.3	20.3	21.6
90°	28.8	28.3	27.9	27.7	27.3	26.4	25.5	24.6	23.7	20.9	18.0
92.5°	33.2	32.9	32.7	32.6	31.8	30.3	28.8	27.2	25.7	23.7	21.7
95°	37.5	37.5	37.5	37.5	36.7	35.2	33.7	32.1	30.6	28.2	25.8
97.5°	40.1	39.8	39.6	39.5	38.6	36.9	35.1	33.4	31.6	42.8	54.0
100°	41.1	40.8	40.6	40.5	39.6	37.9	36.1	34.4	32.6	66.8	101.1
102.5°	41.6	41.2	40.7	40.5	44.1	51.4	58.6	65.9	73.1	111.3	149.5
105°	42.6	42.2	41.7	41.5	60.9	99.8	138.7	177.5	216.4	236.2	255.9
107.5°	160.3	189.1	217.8	232.2	249.1	282.9	316.7	350.5	384.3	381.0	377.7
110°	334.5	365.9	397.3	413.0	416.6	423.9	431.1	438.4	445.6	443.2	440.8

TEST NUMBER: P1010395

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	515.6	516.1	516.5	516.7	515.7	513.8	511.8	509.9	507.9	505.5	503.1
115°	579.2	578.3	577.4	577.0	575.9	573.7	571.5	569.3	567.1	565.1	563.1
117.5°	633.9	633.6	633.4	633.3	632.4	630.7	628.9	627.2	625.4	624.3	623.2
120°	689.7	689.7	689.7	689.7	688.8	687.1	685.3	683.6	681.8	681.1	680.5
122.5°	743.6	743.3	743.1	743.0	742.5	741.4	740.3	739.2	738.1	737.2	736.3
125°	793.5	793.1	792.6	792.4	792.2	791.7	791.3	790.8	790.4	789.5	788.7
127.5°	844.7	845.1	845.6	845.8	845.5	844.8	844.1	843.5	842.8	841.7	840.6
130°	892.1	892.5	893.0	893.2	892.8	891.9	891.0	890.1	889.2	888.3	887.5
132.5°	936.0	936.7	937.4	937.7	937.3	936.4	935.5	934.6	933.7	933.0	932.4
135°	980.5	981.1	981.8	982.1	981.8	981.1	980.5	979.8	979.2	978.3	977.4
137.5°	1022.5	1022.9	1023.4	1023.6	1023.1	1022.0	1020.9	1019.8	1018.7	1018.3	1017.8
140°	1060.1	1060.5	1061.0	1061.2	1060.8	1059.9	1059.0	1058.1	1057.2	1056.5	1055.9
142.5°	1095.1	1095.7	1096.4	1096.7	1096.4	1095.7	1095.1	1094.4	1093.8	1093.1	1092.5
145°	1129.3	1129.3	1129.3	1129.3	1129.1	1128.7	1128.2	1127.8	1127.4	1127.0	1126.5
147.5°	1157.2	1158.3	1159.4	1160.0	1159.8	1159.3	1158.9	1158.4	1158.0	1157.6	1157.1
150°	1186.0	1186.6	1187.3	1187.6	1187.4	1187.0	1186.5	1186.1	1185.7	1185.3	1184.8
152.5°	1210.6	1211.7	1212.8	1213.3	1212.9	1212.0	1211.1	1210.3	1209.4	1209.2	1209.0
155°	1232.7	1234.0	1235.3	1236.0	1235.5	1234.4	1233.3	1232.2	1231.1	1230.9	1230.7
157.5°	1252.4	1254.2	1255.9	1256.8	1256.1	1254.8	1253.5	1252.2	1250.9	1251.1	1251.3
160°	1269.8	1271.3	1272.8	1273.6	1272.9	1271.6	1270.3	1269.0	1267.7	1267.9	1268.1
162.5°	1286.1	1287.4	1288.7	1289.4	1288.6	1287.1	1285.6	1284.0	1282.5	1282.7	1282.9
165°	1299.4	1300.9	1302.4	1303.2	1302.3	1300.6	1298.8	1297.1	1295.3	1295.5	1295.7
167.5°	1309.7	1311.5	1313.2	1314.1	1313.2	1311.5	1309.7	1308.0	1306.2	1306.2	1306.2
170°	1318.6	1320.4	1322.1	1323.0	1322.1	1320.4	1318.6	1316.9	1315.1	1315.1	1315.1
172.5°	1324.0	1325.9	1327.9	1328.9	1328.0	1326.3	1324.5	1322.8	1321.0	1320.8	1320.6
175°	1328.5	1330.3	1332.0	1332.9	1332.1	1330.6	1329.1	1327.5	1326.0	1325.8	1325.6
177.5°	1330.4	1332.5	1334.7	1335.8	1334.9	1333.2	1331.4	1329.7	1327.9	1327.7	1327.5
180°	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9

TEST NUMBER: P1010395

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2
2.5°	1434.1	1430.0	1430.0	1427.3	1419.2	1404.3	1403.0	1405.7	1397.6	1389.5	1377.3
5°	1504.4	1478.7	1470.6	1462.5	1446.3	1419.2	1408.4	1398.9	1384.0	1366.5	1347.5
7.5°	1564.0	1527.4	1516.6	1501.7	1469.3	1431.4	1407.0	1386.7	1366.5	1342.1	1319.1
10°	1638.4	1585.6	1559.9	1538.3	1493.6	1440.9	1404.3	1374.6	1342.1	1312.3	1282.6
12.5°	1722.3	1637.0	1628.9	1576.2	1524.7	1446.3	1401.6	1358.3	1315.0	1278.5	1247.4
15°	1792.6	1699.3	1665.4	1630.3	1531.5	1434.1	1390.8	1342.1	1292.0	1252.8	1206.8
17.5°	1837.3	1760.2	1688.4	1641.1	1538.3	1451.7	1367.8	1312.3	1259.6	1205.5	1167.6
20°	1891.4	1779.1	1716.9	1653.3	1551.8	1438.2	1354.3	1285.3	1220.3	1171.6	1125.6
22.5°	1945.5	1794.0	1742.6	1673.6	1554.5	1424.6	1329.9	1260.9	1186.5	1137.8	1087.7
25°	1940.1	1815.6	1730.4	1672.2	1527.4	1412.4	1301.5	1220.3	1151.3	1089.1	1039.0
27.5°	1944.1	1791.3	1704.7	1637.0	1508.5	1394.9	1271.7	1186.5	1114.8	1049.9	997.1
30°	1945.5	1754.7	1679.0	1597.8	1473.3	1352.9	1237.9	1151.3	1075.6	1005.2	957.9
32.5°	1941.4	1725.0	1630.3	1557.2	1417.9	1312.3	1198.7	1106.7	1029.6	964.6	920.0
35°	1932.0	1689.8	1580.2	1488.2	1361.0	1254.2	1162.2	1067.5	984.9	925.4	874.0
37.5°	1906.3	1651.9	1527.4	1436.8	1294.7	1186.5	1105.3	1026.9	947.0	876.7	833.4
40°	1887.3	1600.5	1474.7	1375.9	1223.0	1117.5	1049.9	975.5	897.0	833.4	791.5
42.5°	1844.0	1551.8	1420.6	1302.9	1152.7	1044.5	980.9	921.3	853.7	791.5	753.6
45°	1773.7	1499.0	1354.3	1235.2	1075.6	972.8	914.6	865.9	806.3	746.8	708.9
47.5°	1674.9	1423.3	1283.9	1164.9	999.8	895.6	837.5	800.9	753.6	703.5	671.0
50°	1568.0	1340.7	1212.2	1094.5	926.8	825.3	768.5	734.6	703.5	657.5	626.4
52.5°	1428.7	1252.8	1129.7	1017.4	848.3	750.9	700.8	676.5	644.0	611.5	584.5
55°	1293.4	1139.2	1037.7	930.8	771.2	680.5	631.8	606.1	587.2	560.1	538.5
57.5°	1136.5	1033.6	940.3	842.9	699.5	616.9	570.9	539.8	527.6	515.5	495.2
60°	991.7	913.2	837.5	756.3	625.0	550.6	506.0	481.6	469.5	461.3	447.8
62.5°	859.1	798.2	733.3	668.3	549.3	481.6	447.8	423.5	412.6	411.3	399.1
65°	731.9	688.6	635.9	572.3	478.9	419.4	386.9	372.1	359.9	359.9	350.4
67.5°	604.8	575.0	533.1	488.4	415.3	359.9	330.1	316.6	309.8	309.8	303.1
70°	503.3	483.0	445.1	405.9	342.3	300.3	277.3	265.2	261.1	262.5	257.1
72.5°	408.6	386.9	355.8	327.4	280.1	248.9	232.7	219.2	212.4	213.8	212.4
75°	316.6	305.8	278.7	257.1	219.2	197.5	182.6	175.9	170.5	171.8	169.1
77.5°	238.1	221.9	207.0	192.1	169.1	151.5	139.4	132.6	128.5	128.5	128.5
80°	162.4	159.6	147.5	139.4	120.4	106.9	97.4	96.1	92.0	92.0	92.0
82.5°	105.5	98.8	92.0	86.6	75.8	67.6	63.6	60.9	59.5	58.2	60.9
85°	58.2	54.1	51.4	46.0	41.9	37.9	33.8	32.5	31.1	32.5	31.1
87.5°	23.0	18.9	18.9	17.6	16.2	14.9	14.9	12.2	12.2	10.8	10.8
90°	15.2	12.3	10.9	9.8	7.6	5.4	3.2	1.0	3.2	5.4	7.6
92.5°	19.8	17.8	16.8	17.5	18.8	20.1	21.4	22.7	21.4	20.1	18.8
95°	23.4	21.0	19.8	24.3	33.3	42.3	51.3	60.3	51.3	42.3	33.3
97.5°	65.2	76.4	82.0	85.1	91.2	97.4	103.5	109.7	103.5	97.4	91.2
100°	135.3	169.6	186.7	184.5	180.1	175.8	171.4	167.0	171.4	175.8	180.1
102.5°	187.7	225.9	245.0	243.6	240.7	237.9	235.0	232.2	235.0	237.9	240.7
105°	275.7	295.4	305.3	304.1	301.7	299.2	296.8	294.4	296.8	299.2	301.7
107.5°	374.4	371.1	369.5	368.5	366.5	364.6	362.6	360.6	362.6	364.6	366.5
110°	438.3	435.9	434.7	433.8	432.1	430.3	428.6	426.8	428.6	430.3	432.1

TEST NUMBER: P1010395

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	500.6	498.2	497.0	496.2	494.7	493.2	491.6	490.1	491.6	493.2	494.7
115°	561.2	559.2	558.2	557.5	556.2	554.9	553.6	552.3	553.6	554.9	556.2
117.5°	622.1	621.0	620.5	619.7	618.2	616.7	615.1	613.6	615.1	616.7	618.2
120°	679.8	679.1	678.8	677.8	675.8	673.9	671.9	669.9	671.9	673.9	675.8
122.5°	735.4	734.5	734.1	733.3	731.8	730.3	728.7	727.2	728.7	730.3	731.8
125°	787.8	786.9	786.5	785.6	783.9	782.1	780.4	778.6	780.4	782.1	783.9
127.5°	839.5	838.4	837.9	837.0	835.3	833.5	831.8	830.0	831.8	833.5	835.3
130°	886.6	885.7	885.3	884.4	882.7	880.9	879.2	877.4	879.2	880.9	882.7
132.5°	931.7	931.0	930.7	929.8	928.1	926.3	924.6	922.8	924.6	926.3	928.1
135°	976.5	975.6	975.2	974.5	973.2	971.9	970.6	969.3	970.6	971.9	973.2
137.5°	1017.4	1016.9	1016.7	1015.8	1014.1	1012.3	1010.6	1008.8	1010.6	1012.3	1014.1
140°	1055.2	1054.5	1054.2	1053.5	1052.2	1050.9	1049.6	1048.3	1049.6	1050.9	1052.2
142.5°	1091.8	1091.1	1090.8	1090.1	1088.8	1087.5	1086.2	1084.9	1086.2	1087.5	1088.8
145°	1126.1	1125.6	1125.4	1124.6	1123.1	1121.6	1120.0	1118.5	1120.0	1121.6	1123.1
147.5°	1156.7	1156.2	1156.0	1155.5	1154.4	1153.3	1152.2	1151.1	1152.2	1153.3	1154.4
150°	1184.4	1183.9	1183.7	1183.4	1182.7	1182.0	1181.4	1180.7	1181.4	1182.0	1182.7
152.5°	1208.7	1208.5	1208.4	1208.3	1208.1	1207.8	1207.6	1207.4	1207.6	1207.8	1208.1
155°	1230.4	1230.2	1230.1	1230.3	1230.8	1231.2	1231.7	1232.1	1231.7	1231.2	1230.8
157.5°	1251.6	1251.8	1251.9	1251.9	1251.9	1251.9	1251.9	1251.9	1251.9	1251.9	1251.9
160°	1268.4	1268.6	1268.7	1268.8	1269.0	1269.2	1269.4	1269.6	1269.4	1269.2	1269.0
162.5°	1283.2	1283.4	1283.5	1283.8	1284.5	1285.1	1285.8	1286.4	1285.8	1285.1	1284.5
165°	1296.0	1296.2	1296.3	1296.6	1297.3	1298.0	1298.6	1299.3	1298.6	1298.0	1297.3
167.5°	1306.2	1306.2	1306.2	1306.6	1307.5	1308.4	1309.2	1310.1	1309.2	1308.4	1307.5
170°	1315.1	1315.1	1315.1	1315.5	1316.4	1317.3	1318.1	1319.0	1318.1	1317.3	1316.4
172.5°	1320.3	1320.1	1320.0	1320.6	1321.7	1322.8	1323.9	1325.0	1323.9	1322.8	1321.7
175°	1325.3	1325.1	1325.0	1325.5	1326.6	1327.7	1328.8	1329.9	1328.8	1327.7	1326.6
177.5°	1327.2	1327.0	1326.9	1327.5	1328.6	1329.7	1330.8	1331.9	1330.8	1329.7	1328.6
180°	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9

TEST NUMBER: P1010395

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2
2.5°	1374.6	1373.2	1375.9	1367.8	1354.3	1347.5	1328.6	1324.5	1323.2	1324.5	1325.9
5°	1336.7	1335.3	1331.3	1317.7	1301.5	1289.3	1266.3	1265.0	1256.9	1248.7	1252.8
7.5°	1300.2	1294.7	1286.6	1269.0	1247.4	1233.9	1214.9	1201.4	1190.6	1183.8	1178.4
10°	1263.6	1255.5	1247.4	1224.4	1197.3	1177.0	1154.0	1143.2	1131.0	1125.6	1120.2
12.5°	1216.3	1208.2	1193.3	1166.2	1150.0	1124.3	1101.3	1090.5	1083.7	1072.9	1066.1
15°	1178.4	1162.2	1154.0	1125.6	1091.8	1089.1	1047.2	1044.5	1030.9	1030.9	1020.1
17.5°	1135.1	1122.9	1108.0	1079.6	1055.3	1030.9	1009.3	1001.2	989.0	986.3	980.9
20°	1093.2	1076.9	1071.5	1043.1	1017.4	987.6	964.6	956.5	951.1	945.7	949.8
22.5°	1049.9	1036.3	1022.8	997.1	978.2	948.4	934.9	926.8	918.6	915.9	917.3
25°	1007.9	995.7	982.2	956.5	936.2	911.9	899.7	895.6	891.6	891.6	890.2
27.5°	967.3	955.2	943.0	920.0	899.7	882.1	872.6	868.6	864.5	867.2	869.9
30°	925.4	914.6	903.8	883.5	867.2	851.0	845.6	842.9	841.5	848.3	848.3
32.5°	887.5	878.0	869.9	851.0	834.8	821.2	817.2	818.5	819.9	823.9	826.6
35°	848.3	841.5	833.4	817.2	803.6	791.5	792.8	792.8	795.5	802.3	807.7
37.5°	813.1	803.6	796.9	783.3	772.5	761.7	765.8	769.8	772.5	780.6	783.3
40°	771.2	767.1	761.7	748.2	738.7	737.3	738.7	741.4	746.8	750.9	754.9
42.5°	737.3	731.9	725.2	714.3	706.2	707.6	708.9	711.6	714.3	721.1	725.2
45°	699.5	695.4	690.0	680.5	673.8	675.1	676.5	676.5	679.2	687.3	690.0
47.5°	657.5	658.9	652.1	642.6	638.6	638.6	638.6	641.3	648.0	650.8	652.1
50°	616.9	614.2	612.9	603.4	600.7	599.3	600.7	602.0	611.5	610.2	614.2
52.5°	573.6	573.6	572.3	566.9	562.8	562.8	560.1	566.9	569.6	572.3	576.3
55°	531.7	527.6	526.3	523.6	518.2	516.8	519.5	527.6	530.3	533.1	537.1
57.5°	485.7	485.7	483.0	478.9	478.9	478.9	478.9	484.3	488.4	491.1	499.2
60°	443.8	438.3	434.3	434.3	434.3	432.9	441.1	441.1	449.2	450.5	453.2
62.5°	393.7	391.0	388.3	389.6	388.3	391.0	393.7	399.1	400.5	404.5	408.6
65°	346.3	346.3	343.6	351.8	346.3	346.3	353.1	353.1	355.8	359.9	365.3
67.5°	300.3	301.7	299.0	299.0	301.7	303.1	304.4	309.8	311.2	316.6	323.3
70°	253.0	255.7	257.1	254.3	257.1	259.8	262.5	263.8	269.2	271.9	276.0
72.5°	211.1	213.8	209.7	211.1	212.4	215.1	216.5	219.2	221.9	230.0	232.7
75°	169.1	167.8	166.4	171.8	169.1	174.5	175.9	175.9	178.6	185.4	188.1
77.5°	129.9	129.9	131.2	128.5	132.6	131.2	132.6	136.6	140.7	140.7	151.5
80°	90.6	93.4	93.4	93.4	94.7	96.1	93.4	100.1	101.5	101.5	105.5
82.5°	58.2	59.5	58.2	60.9	60.9	63.6	62.2	63.6	66.3	69.0	70.4
85°	31.1	31.1	33.8	33.8	32.5	33.8	32.5	33.8	36.5	36.5	37.9
87.5°	10.8	10.8	10.8	10.8	12.2	10.8	12.2	12.2	10.8	10.8	14.9
90°	9.8	10.9	12.3	15.2	18.0	20.9	23.7	24.6	25.5	26.4	27.3
92.5°	17.5	16.8	17.8	19.8	21.7	23.7	25.7	27.2	28.8	30.3	31.8
95°	24.3	19.8	21.0	23.4	25.8	28.2	30.6	32.1	33.7	35.2	36.7
97.5°	85.1	82.0	76.4	65.2	54.0	42.8	31.6	33.4	35.1	36.9	38.6
100°	184.5	186.7	169.6	135.3	101.1	66.8	32.6	34.4	36.1	37.9	39.6
102.5°	243.6	245.0	225.9	187.7	149.5	111.3	73.1	65.9	58.6	51.4	44.1
105°	304.1	305.3	295.4	275.7	255.9	236.2	216.4	177.5	138.7	99.8	60.9
107.5°	368.5	369.5	371.1	374.4	377.7	381.0	384.3	350.5	316.7	282.9	249.1
110°	433.8	434.7	435.9	438.3	440.8	443.2	445.6	438.4	431.1	423.9	416.6

TEST NUMBER: P1010395

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	496.2	497.0	498.2	500.6	503.1	505.5	507.9	509.9	511.8	513.8	515.7
115°	557.5	558.2	559.2	561.2	563.1	565.1	567.1	569.3	571.5	573.7	575.9
117.5°	619.7	620.5	621.0	622.1	623.2	624.3	625.4	627.2	628.9	630.7	632.4
120°	677.8	678.8	679.1	679.8	680.5	681.1	681.8	683.6	685.3	687.1	688.8
122.5°	733.3	734.1	734.5	735.4	736.3	737.2	738.1	739.2	740.3	741.4	742.5
125°	785.6	786.5	786.9	787.8	788.7	789.5	790.4	790.8	791.3	791.7	792.2
127.5°	837.0	837.9	838.4	839.5	840.6	841.7	842.8	843.5	844.1	844.8	845.5
130°	884.4	885.3	885.7	886.6	887.5	888.3	889.2	890.1	891.0	891.9	892.8
132.5°	929.8	930.7	931.0	931.7	932.4	933.0	933.7	934.6	935.5	936.4	937.3
135°	974.5	975.2	975.6	976.5	977.4	978.3	979.2	979.8	980.5	981.1	981.8
137.5°	1015.8	1016.7	1016.9	1017.4	1017.8	1018.3	1018.7	1019.8	1020.9	1022.0	1023.1
140°	1053.5	1054.2	1054.5	1055.2	1055.9	1056.5	1057.2	1058.1	1059.0	1059.9	1060.8
142.5°	1090.1	1090.8	1091.1	1091.8	1092.5	1093.1	1093.8	1094.4	1095.1	1095.7	1096.4
145°	1124.6	1125.4	1125.6	1126.1	1126.5	1127.0	1127.4	1127.8	1128.2	1128.7	1129.1
147.5°	1155.5	1156.0	1156.2	1156.7	1157.1	1157.6	1158.0	1158.4	1158.9	1159.3	1159.8
150°	1183.4	1183.7	1183.9	1184.4	1184.8	1185.3	1185.7	1186.1	1186.5	1187.0	1187.4
152.5°	1208.3	1208.4	1208.5	1208.7	1209.0	1209.2	1209.4	1210.3	1211.1	1212.0	1212.9
155°	1230.3	1230.1	1230.2	1230.4	1230.7	1230.9	1231.1	1232.2	1233.3	1234.4	1235.5
157.5°	1251.9	1251.9	1251.8	1251.6	1251.3	1251.1	1250.9	1252.2	1253.5	1254.8	1256.1
160°	1268.8	1268.7	1268.6	1268.4	1268.1	1267.9	1267.7	1269.0	1270.3	1271.6	1272.9
162.5°	1283.8	1283.5	1283.4	1283.2	1282.9	1282.7	1282.5	1284.0	1285.6	1287.1	1288.6
165°	1296.6	1296.3	1296.2	1296.0	1295.7	1295.5	1295.3	1297.1	1298.8	1300.6	1302.3
167.5°	1306.6	1306.2	1306.2	1306.2	1306.2	1306.2	1306.2	1308.0	1309.7	1311.5	1313.2
170°	1315.5	1315.1	1315.1	1315.1	1315.1	1315.1	1315.1	1316.9	1318.6	1320.4	1322.1
172.5°	1320.6	1320.0	1320.1	1320.3	1320.6	1320.8	1321.0	1322.8	1324.5	1326.3	1328.0
175°	1325.5	1325.0	1325.1	1325.3	1325.6	1325.8	1326.0	1327.5	1329.1	1330.6	1332.1
177.5°	1327.5	1326.9	1327.0	1327.2	1327.5	1327.7	1327.9	1329.7	1331.4	1333.2	1334.9
180°	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9

TEST NUMBER: P1010395

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2
2.5°	1324.5	1325.9	1320.5	1316.4	1327.2	1320.5	1320.5	1321.8	1319.1	1323.2	1321.8
5°	1250.1	1251.5	1242.0	1244.7	1239.3	1237.9	1236.6	1244.7	1243.3	1242.0	1244.7
7.5°	1177.0	1177.0	1173.0	1170.3	1170.3	1166.2	1171.6	1170.3	1173.0	1173.0	1177.0
10°	1116.2	1118.9	1112.1	1105.3	1104.0	1105.3	1105.3	1106.7	1108.0	1117.5	1116.2
12.5°	1066.1	1062.0	1060.7	1056.6	1049.9	1047.2	1044.5	1059.3	1055.3	1055.3	1055.3
15°	1010.6	1020.1	1018.7	1006.6	1003.9	1009.3	1006.6	1006.6	1020.1	1018.7	1017.4
17.5°	980.9	978.2	975.5	968.7	970.0	968.7	970.0	970.0	978.2	978.2	978.2
20°	947.0	941.6	941.6	938.9	938.9	934.9	940.3	941.6	947.0	947.0	948.4
22.5°	917.3	913.2	913.2	911.9	914.6	909.2	914.6	915.9	915.9	920.0	920.0
25°	891.6	888.9	888.9	891.6	891.6	891.6	891.6	897.0	892.9	894.3	892.9
27.5°	868.6	869.9	871.3	872.6	871.3	872.6	874.0	876.7	878.0	876.7	874.0
30°	846.9	851.0	852.3	852.3	855.0	856.4	857.8	857.8	859.1	855.0	857.8
32.5°	830.7	830.7	833.4	834.8	837.5	838.8	838.8	841.5	840.2	836.1	837.5
35°	807.7	807.7	813.1	815.8	819.9	818.5	819.9	819.9	821.2	818.5	814.5
37.5°	784.7	787.4	787.4	792.8	794.2	795.5	794.2	796.9	795.5	792.8	791.5
40°	757.6	756.3	757.6	761.7	763.0	763.0	763.0	765.8	765.8	765.8	764.4
42.5°	723.8	727.9	726.5	730.6	729.2	729.2	731.9	734.6	736.0	731.9	733.3
45°	691.3	691.3	694.0	694.0	695.4	695.4	700.8	698.1	700.8	698.1	699.5
47.5°	656.2	657.5	657.5	658.9	661.6	664.3	661.6	662.9	662.9	664.3	661.6
50°	616.9	616.9	619.6	623.7	629.1	626.4	625.0	630.5	626.4	626.4	623.7
52.5°	576.3	580.4	581.8	585.8	589.9	591.2	592.6	589.9	591.2	587.2	588.5
55°	537.1	538.5	543.9	547.9	552.0	552.0	550.6	552.0	553.3	547.9	547.9
57.5°	497.9	501.9	507.3	507.3	512.8	512.8	511.4	511.4	512.8	508.7	507.3
60°	455.9	460.0	466.8	466.8	474.9	476.2	473.5	470.8	470.8	466.8	468.1
62.5°	411.3	415.3	419.4	426.2	431.6	428.9	434.3	428.9	430.2	422.1	422.1
65°	372.1	373.4	380.2	386.9	386.9	389.6	386.9	388.3	384.2	384.2	378.8
67.5°	326.1	326.1	332.8	339.6	346.3	346.3	346.3	342.3	342.3	338.2	338.2
70°	285.5	284.1	290.9	294.9	299.0	300.3	297.6	296.3	293.6	289.5	288.2
72.5°	235.4	238.1	244.9	247.6	254.3	253.0	259.8	251.6	251.6	244.9	243.5
75°	190.8	193.5	200.2	204.3	208.3	208.3	212.4	208.3	202.9	200.2	198.9
77.5°	151.5	150.2	155.6	162.4	163.7	162.4	165.1	163.7	158.3	158.3	155.6
80°	108.2	112.3	117.7	116.4	121.8	120.4	120.4	117.7	117.7	113.6	116.4
82.5°	71.7	75.8	77.1	75.8	77.1	79.8	81.2	79.8	79.8	77.1	78.5
85°	37.9	37.9	40.6	41.9	40.6	40.6	41.9	46.0	43.3	40.6	43.3
87.5°	12.2	10.8	10.8	12.2	10.8	10.8	12.2	12.2	13.5	13.5	13.5
90°	27.7	27.9	28.3	28.8	29.2	29.6	29.2	28.8	28.3	27.9	27.7
92.5°	32.6	32.7	32.9	33.2	33.4	33.6	33.4	33.2	32.9	32.7	32.6
95°	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5
97.5°	39.5	39.6	39.8	40.1	40.3	40.5	40.3	40.1	39.8	39.6	39.5
100°	40.5	40.6	40.8	41.1	41.3	41.5	41.3	41.1	40.8	40.6	40.5
102.5°	40.5	40.7	41.2	41.6	42.1	42.5	42.1	41.6	41.2	40.7	40.5
105°	41.5	41.7	42.2	42.6	43.1	43.5	43.1	42.6	42.2	41.7	41.5
107.5°	232.2	217.8	189.1	160.3	131.6	102.8	131.6	160.3	189.1	217.8	232.2
110°	413.0	397.3	365.9	334.5	303.1	271.7	303.1	334.5	365.9	397.3	413.0

TEST NUMBER: P1010395

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	516.7	516.5	516.1	515.6	515.2	514.8	515.2	515.6	516.1	516.5	516.7
115°	577.0	577.4	578.3	579.2	580.1	581.0	580.1	579.2	578.3	577.4	577.0
117.5°	633.3	633.4	633.6	633.9	634.1	634.3	634.1	633.9	633.6	633.4	633.3
120°	689.7	689.7	689.7	689.7	689.7	689.7	689.7	689.7	689.7	689.7	689.7
122.5°	743.0	743.1	743.3	743.6	743.8	744.0	743.8	743.6	743.3	743.1	743.0
125°	792.4	792.6	793.1	793.5	794.0	794.4	794.0	793.5	793.1	792.6	792.4
127.5°	845.8	845.6	845.1	844.7	844.2	843.8	844.2	844.7	845.1	845.6	845.8
130°	893.2	893.0	892.5	892.1	891.6	891.2	891.6	892.1	892.5	893.0	893.2
132.5°	937.7	937.4	936.7	936.0	935.4	934.7	935.4	936.0	936.7	937.4	937.7
135°	982.1	981.8	981.1	980.5	979.8	979.2	979.8	980.5	981.1	981.8	982.1
137.5°	1023.6	1023.4	1022.9	1022.5	1022.0	1021.6	1022.0	1022.5	1022.9	1023.4	1023.6
140°	1061.2	1061.0	1060.5	1060.1	1059.6	1059.2	1059.6	1060.1	1060.5	1061.0	1061.2
142.5°	1096.7	1096.4	1095.7	1095.1	1094.4	1093.8	1094.4	1095.1	1095.7	1096.4	1096.7
145°	1129.3	1129.3	1129.3	1129.3	1129.3	1129.3	1129.3	1129.3	1129.3	1129.3	1129.3
147.5°	1160.0	1159.4	1158.3	1157.2	1156.1	1155.0	1156.1	1157.2	1158.3	1159.4	1160.0
150°	1187.6	1187.3	1186.6	1186.0	1185.3	1184.7	1185.3	1186.0	1186.6	1187.3	1187.6
152.5°	1213.3	1212.8	1211.7	1210.6	1209.5	1208.4	1209.5	1210.6	1211.7	1212.8	1213.3
155°	1236.0	1235.3	1234.0	1232.7	1231.4	1230.1	1231.4	1232.7	1234.0	1235.3	1236.0
157.5°	1256.8	1255.9	1254.2	1252.4	1250.7	1248.9	1250.7	1252.4	1254.2	1255.9	1256.8
160°	1273.6	1272.8	1271.3	1269.8	1268.2	1266.7	1268.2	1269.8	1271.3	1272.8	1273.6
162.5°	1289.4	1288.7	1287.4	1286.1	1284.8	1283.5	1284.8	1286.1	1287.4	1288.7	1289.4
165°	1303.2	1302.4	1300.9	1299.4	1297.8	1296.3	1297.8	1299.4	1300.9	1302.4	1303.2
167.5°	1314.1	1313.2	1311.5	1309.7	1308.0	1306.2	1308.0	1309.7	1311.5	1313.2	1314.1
170°	1323.0	1322.1	1320.4	1318.6	1316.9	1315.1	1316.9	1318.6	1320.4	1322.1	1323.0
172.5°	1328.9	1327.9	1325.9	1324.0	1322.0	1320.0	1322.0	1324.0	1325.9	1327.9	1328.9
175°	1332.9	1332.0	1330.3	1328.5	1326.8	1325.0	1326.8	1328.5	1330.3	1332.0	1332.9
177.5°	1335.8	1334.7	1332.5	1330.4	1328.2	1326.0	1328.2	1330.4	1332.5	1334.7	1335.8
180°	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9

TEST NUMBER: P1010395

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2
2.5°	1325.9	1328.6	1329.9	1324.5	1320.5	1327.2	1336.7	1343.5	1348.9	1355.6	1359.7
5°	1247.4	1256.9	1256.9	1259.6	1263.6	1270.4	1288.0	1300.2	1311.0	1319.1	1325.9
7.5°	1181.1	1187.9	1191.9	1198.7	1205.5	1214.9	1235.2	1252.8	1269.0	1278.5	1289.3
10°	1121.6	1127.0	1133.7	1137.8	1150.0	1163.5	1189.2	1204.1	1223.0	1237.9	1251.5
12.5°	1064.7	1083.7	1087.7	1086.4	1097.2	1112.1	1137.8	1160.8	1181.1	1196.0	1210.9
15°	1024.2	1030.9	1039.0	1037.7	1060.7	1064.7	1086.4	1113.5	1140.5	1150.0	1163.5
17.5°	979.5	990.3	998.5	1002.5	1009.3	1024.2	1044.5	1064.7	1099.9	1101.3	1136.5
20°	944.3	955.2	960.6	966.0	970.0	987.6	1005.2	1028.2	1056.6	1071.5	1090.5
22.5°	921.3	926.8	930.8	934.9	940.3	949.8	971.4	997.1	1016.0	1032.3	1044.5
25°	894.3	899.7	905.1	907.8	911.9	917.3	933.5	953.8	980.9	991.7	1003.9
27.5°	875.3	875.3	878.0	878.0	883.5	888.9	901.0	920.0	941.6	955.2	971.4
30°	855.0	853.7	855.0	853.7	852.3	860.5	871.3	887.5	902.4	918.6	929.5
32.5°	834.8	833.4	833.4	834.8	829.3	833.4	838.8	853.7	869.9	878.0	890.2
35°	813.1	810.4	810.4	810.4	807.7	805.0	810.4	823.9	834.8	845.6	855.0
37.5°	791.5	787.4	787.4	784.7	782.0	777.9	777.9	788.8	803.6	807.7	819.9
40°	761.7	761.7	759.0	757.6	754.9	752.2	748.2	757.6	771.2	775.2	784.7
42.5°	731.9	727.9	726.5	726.5	726.5	722.5	719.8	726.5	734.6	741.4	746.8
45°	698.1	695.4	696.8	695.4	692.7	691.3	690.0	692.7	702.2	704.9	711.6
47.5°	661.6	660.2	660.2	658.9	657.5	658.9	653.5	660.2	662.9	665.6	671.0
50°	623.7	622.3	621.0	619.6	619.6	621.0	619.6	619.6	625.0	627.8	633.2
52.5°	585.8	581.8	581.8	580.4	580.4	577.7	580.4	581.8	584.5	587.2	589.9
55°	545.2	545.2	541.2	541.2	538.5	538.5	539.8	538.5	543.9	546.6	546.6
57.5°	506.0	500.6	501.9	499.2	496.5	495.2	495.2	497.9	500.6	500.6	503.3
60°	464.1	458.6	457.3	451.9	454.6	450.5	451.9	451.9	457.3	454.6	457.3
62.5°	422.1	415.3	411.3	408.6	408.6	409.9	407.2	405.9	408.6	411.3	416.7
65°	377.5	373.4	369.3	365.3	365.3	363.9	366.6	362.6	361.2	362.6	365.3
67.5°	331.5	327.4	323.3	319.3	320.6	316.6	313.9	317.9	315.2	316.6	319.3
70°	286.8	284.1	276.0	273.3	271.9	273.3	271.9	269.2	273.3	271.9	273.3
72.5°	242.2	239.5	235.4	228.6	228.6	227.3	225.9	225.9	224.6	224.6	224.6
75°	198.9	193.5	189.4	188.1	185.4	184.0	182.6	179.9	181.3	182.6	179.9
77.5°	154.2	147.5	146.1	146.1	142.1	142.1	143.4	142.1	140.7	140.7	140.7
80°	113.6	108.2	108.2	105.5	102.8	102.8	102.8	102.8	101.5	100.1	101.5
82.5°	73.1	71.7	70.4	70.4	73.1	67.6	70.4	69.0	67.6	67.6	66.3
85°	40.6	41.9	40.6	41.9	39.2	40.6	40.6	40.6	39.2	40.6	37.9
87.5°	14.9	14.9	14.9	16.2	16.2	16.2	16.2	16.2	17.6	16.2	16.2
90°	27.3	26.4	25.5	24.6	23.7	20.9	18.0	15.2	12.3	10.9	9.8
92.5°	31.8	30.3	28.8	27.2	25.7	23.7	21.7	19.8	17.8	16.8	17.5
95°	36.7	35.2	33.7	32.1	30.6	28.2	25.8	23.4	21.0	19.8	24.3
97.5°	38.6	36.9	35.1	33.4	31.6	42.8	54.0	65.2	76.4	82.0	85.1
100°	39.6	37.9	36.1	34.4	32.6	66.8	101.1	135.3	169.6	186.7	184.5
102.5°	44.1	51.4	58.6	65.9	73.1	111.3	149.5	187.7	225.9	245.0	243.6
105°	60.9	99.8	138.7	177.5	216.4	236.2	255.9	275.7	295.4	305.3	304.1
107.5°	249.1	282.9	316.7	350.5	384.3	381.0	377.7	374.4	371.1	369.5	368.5
110°	416.6	423.9	431.1	438.4	445.6	443.2	440.8	438.3	435.9	434.7	433.8

TEST NUMBER: P1010395

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	515.7	513.8	511.8	509.9	507.9	505.5	503.1	500.6	498.2	497.0	496.2
115°	575.9	573.7	571.5	569.3	567.1	565.1	563.1	561.2	559.2	558.2	557.5
117.5°	632.4	630.7	628.9	627.2	625.4	624.3	623.2	622.1	621.0	620.5	619.7
120°	688.8	687.1	685.3	683.6	681.8	681.1	680.5	679.8	679.1	678.8	677.8
122.5°	742.5	741.4	740.3	739.2	738.1	737.2	736.3	735.4	734.5	734.1	733.3
125°	792.2	791.7	791.3	790.8	790.4	789.5	788.7	787.8	786.9	786.5	785.6
127.5°	845.5	844.8	844.1	843.5	842.8	841.7	840.6	839.5	838.4	837.9	837.0
130°	892.8	891.9	891.0	890.1	889.2	888.3	887.5	886.6	885.7	885.3	884.4
132.5°	937.3	936.4	935.5	934.6	933.7	933.0	932.4	931.7	931.0	930.7	929.8
135°	981.8	981.1	980.5	979.8	979.2	978.3	977.4	976.5	975.6	975.2	974.5
137.5°	1023.1	1022.0	1020.9	1019.8	1018.7	1018.3	1017.8	1017.4	1016.9	1016.7	1015.8
140°	1060.8	1059.9	1059.0	1058.1	1057.2	1056.5	1055.9	1055.2	1054.5	1054.2	1053.5
142.5°	1096.4	1095.7	1095.1	1094.4	1093.8	1093.1	1092.5	1091.8	1091.1	1090.8	1090.1
145°	1129.1	1128.7	1128.2	1127.8	1127.4	1127.0	1126.5	1126.1	1125.6	1125.4	1124.6
147.5°	1159.8	1159.3	1158.9	1158.4	1158.0	1157.6	1157.1	1156.7	1156.2	1156.0	1155.5
150°	1187.4	1187.0	1186.5	1186.1	1185.7	1185.3	1184.8	1184.4	1183.9	1183.7	1183.4
152.5°	1212.9	1212.0	1211.1	1210.3	1209.4	1209.2	1209.0	1208.7	1208.5	1208.4	1208.3
155°	1235.5	1234.4	1233.3	1232.2	1231.1	1230.9	1230.7	1230.4	1230.2	1230.1	1230.3
157.5°	1256.1	1254.8	1253.5	1252.2	1250.9	1251.1	1251.3	1251.6	1251.8	1251.9	1251.9
160°	1272.9	1271.6	1270.3	1269.0	1267.7	1267.9	1268.1	1268.4	1268.6	1268.7	1268.8
162.5°	1288.6	1287.1	1285.6	1284.0	1282.5	1282.7	1282.9	1283.2	1283.4	1283.5	1283.8
165°	1302.3	1300.6	1298.8	1297.1	1295.3	1295.5	1295.7	1296.0	1296.2	1296.3	1296.6
167.5°	1313.2	1311.5	1309.7	1308.0	1306.2	1306.2	1306.2	1306.2	1306.2	1306.2	1306.6
170°	1322.1	1320.4	1318.6	1316.9	1315.1	1315.1	1315.1	1315.1	1315.1	1315.1	1315.5
172.5°	1328.0	1326.3	1324.5	1322.8	1321.0	1320.8	1320.6	1320.3	1320.1	1320.0	1320.6
175°	1332.1	1330.6	1329.1	1327.5	1326.0	1325.8	1325.6	1325.3	1325.1	1325.0	1325.5
177.5°	1334.9	1333.2	1331.4	1329.7	1327.9	1327.7	1327.5	1327.2	1327.0	1326.9	1327.5
180°	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9

TEST NUMBER: P1010395

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1396.2	1396.2	1396.2	1396.2
2.5°	1366.5	1370.5	1384.0	1400.3
5°	1339.4	1350.2	1369.2	1394.9
7.5°	1309.6	1325.9	1352.9	1385.4
10°	1275.8	1298.8	1332.6	1373.2
12.5°	1239.3	1269.0	1312.3	1354.3
15°	1216.3	1246.0	1285.3	1331.3
17.5°	1171.6	1206.8	1247.4	1312.3
20°	1125.6	1164.9	1217.6	1282.6
22.5°	1090.5	1132.4	1182.5	1251.5
25°	1048.5	1091.8	1145.9	1217.6
27.5°	1003.9	1047.2	1108.0	1183.8
30°	970.0	1012.0	1070.2	1151.3
32.5°	929.5	970.0	1030.9	1116.2
35°	883.5	929.5	987.6	1074.2
37.5°	848.3	890.2	951.1	1033.6
40°	810.4	846.9	906.5	987.6
42.5°	769.8	810.4	861.8	943.0
45°	731.9	761.7	814.5	891.6
47.5°	691.3	725.2	765.8	825.3
50°	648.0	676.5	721.1	761.7
52.5°	606.1	629.1	667.0	698.1
55°	561.5	584.5	612.9	631.8
57.5°	519.5	535.8	554.7	566.9
60°	468.1	484.3	496.5	508.7
62.5°	422.1	434.3	441.1	447.8
65°	374.8	381.5	385.6	391.0
67.5°	323.3	330.1	331.5	339.6
70°	276.0	277.3	280.1	284.1
72.5°	231.3	234.1	232.7	235.4
75°	185.4	188.1	185.4	188.1
77.5°	140.7	143.4	143.4	147.5
80°	101.5	102.8	104.2	104.2
82.5°	66.3	70.4	67.6	69.0
85°	37.9	39.2	39.2	40.6
87.5°	17.6	18.9	17.6	20.3
90°	7.6	5.4	3.2	1.0
92.5°	18.8	20.1	21.4	22.7
95°	33.3	42.3	51.3	60.3
97.5°	91.2	97.4	103.5	109.7
100°	180.1	175.8	171.4	167.0
102.5°	240.7	237.9	235.0	232.2
105°	301.7	299.2	296.8	294.4
107.5°	366.5	364.6	362.6	360.6
110°	432.1	430.3	428.6	426.8

TEST NUMBER: P1010395

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	494.7	493.2	491.6	490.1
115°	556.2	554.9	553.6	552.3
117.5°	618.2	616.7	615.1	613.6
120°	675.8	673.9	671.9	669.9
122.5°	731.8	730.3	728.7	727.2
125°	783.9	782.1	780.4	778.6
127.5°	835.3	833.5	831.8	830.0
130°	882.7	880.9	879.2	877.4
132.5°	928.1	926.3	924.6	922.8
135°	973.2	971.9	970.6	969.3
137.5°	1014.1	1012.3	1010.6	1008.8
140°	1052.2	1050.9	1049.6	1048.3
142.5°	1088.8	1087.5	1086.2	1084.9
145°	1123.1	1121.6	1120.0	1118.5
147.5°	1154.4	1153.3	1152.2	1151.1
150°	1182.7	1182.0	1181.4	1180.7
152.5°	1208.1	1207.8	1207.6	1207.4
155°	1230.8	1231.2	1231.7	1232.1
157.5°	1251.9	1251.9	1251.9	1251.9
160°	1269.0	1269.2	1269.4	1269.6
162.5°	1284.5	1285.1	1285.8	1286.4
165°	1297.3	1298.0	1298.6	1299.3
167.5°	1307.5	1308.4	1309.2	1310.1
170°	1316.4	1317.3	1318.1	1319.0
172.5°	1321.7	1322.8	1323.9	1325.0
175°	1326.6	1327.7	1328.8	1329.9
177.5°	1328.6	1329.7	1330.8	1331.9
180°	1329.9	1329.9	1329.9	1329.9

(END OF REPORT)