

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010400

Luminaire Tested: S123DIP-B1000D1025UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010400
REPORT IS A COMBINATION OF REPORTS P989034 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D1025UB2750-4F0-XX-W2A-D_3000K
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8231.0 lumens
Efficiency: N/A
Efficacy: 109.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010400

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010400

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53			46
1	96	91	87	83	88	84	80	77	70	67	65	57	55	53	45	44	43			37
2	87	79	73	67	79	73	67	62	61	56	53	50	46	44	39	37	35			30
3	79	69	62	55	72	64	57	52	53	48	44	43	40	37	34	32	30			25
4	72	61	53	47	66	56	49	43	47	42	37	39	34	31	31	28	25			21
5	66	54	46	40	60	50	43	37	42	36	32	34	30	27	27	24	22			18
6	61	49	40	34	56	45	37	32	38	32	28	31	27	23	25	22	19			16
7	56	44	36	30	51	40	33	28	34	28	24	28	24	21	23	19	17			14
8	52	40	32	26	48	37	30	25	31	25	21	26	21	18	21	17	15			13
9	49	36	29	23	44	33	27	22	28	23	19	24	19	16	19	16	14			11
10	45	33	26	21	41	31	24	20	26	21	17	22	18	15	18	15	12			10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13369	13369	13369
5°	13405	12976	12966
10°	13279	12625	12529
15°	13104	12237	12065
20°	12854	11804	11566
25°	12548	11317	11051
30°	12233	10876	10532
35°	11881	10413	10110
40°	11544	9989	9664
45°	11171	9580	9297
50°	10802	9175	8898
55°	10393	8758	8531
60°	9993	8332	8156
65°	9582	7879	7716
70°	8964	7369	7261
75°	8182	6788	6793
80°	7269	6203	6260
85°	6368	5725	5878

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11171 cd/sqm

TEST NUMBER: P1010400

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.8	1.4
10°-20°	335.9	4.1
20°-30°	502.3	6.1
30°-40°	599.7	7.3
40°-50°	627.4	7.6
50°-60°	588.8	7.2
60°-70°	491.8	6.0
70°-80°	351.7	4.3
80°-90°	211.9	2.6
90°-100°	178.4	2.2
100°-110°	323.4	3.9
110°-120°	620.2	7.5
120°-130°	742.2	9.0
130°-140°	770.1	9.4
140°-150°	708.1	8.6
150°-160°	568.4	6.9
160°-170°	366.8	4.5
170°-180°	126.4	1.5
0°-30°	955.9	11.6
0°-40°	1555.6	18.9
0°-60°	2771.8	33.7
0°-90°	3827.2	46.5
90°-120°	1122.0	13.6
90°-150°	3342.3	40.6
90°-180°	4404.0	53.5
0°-180°	8231.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1242	1242	1242	1242	1242	
5°	1243	1241	1232	1243	1242	118
15°	1184	1188	1186	1200	1199	333
25°	1069	1082	1086	1104	1104	493
35°	920	942	959	980	985	575
45°	752	785	818	844	855	580
55°	574	618	667	704	714	514
65°	396	449	509	549	563	392
75°	215	279	346	391	407	230
85°	66	134	206	252	265	68
90°	19	95	177	227	242	16
95°	75	87	164	213	227	84
105°	305	349	318	181	195	323
115°	559	581	639	681	696	553
125°	783	791	834	864	876	700
135°	972	977	995	1023	1027	748
145°	1120	1125	1127	1140	1146	701
155°	1232	1230	1231	1236	1230	568
165°	1299	1296	1295	1303	1296	367
175°	1330	1325	1326	1333	1325	127
180°	1330	1330	1330	1330	1330	

TEST NUMBER: P1010400

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1242.0	1242.0	1242.0	1242.0	1242.0
2.5°	1248.7	1244.7	1233.9	1244.7	1243.3
5°	1243.3	1240.6	1232.5	1243.3	1242.0
7.5°	1233.9	1233.9	1225.7	1239.3	1237.9
10°	1220.3	1223.0	1216.3	1229.8	1227.1
12.5°	1204.1	1208.1	1204.1	1216.3	1213.6
15°	1183.8	1187.9	1186.5	1200.0	1198.7
17.5°	1159.4	1167.6	1166.2	1178.4	1175.7
20°	1132.4	1140.5	1143.2	1155.4	1156.7
22.5°	1104.0	1112.1	1116.2	1132.4	1131.0
25°	1068.8	1082.3	1086.4	1104.0	1104.0
27.5°	1035.0	1049.9	1058.0	1072.9	1074.2
30°	998.4	1016.0	1026.9	1043.1	1043.1
32.5°	957.9	978.2	993.0	1010.6	1014.7
35°	920.0	941.6	959.2	979.5	984.9
37.5°	879.4	903.7	924.0	947.0	951.1
40°	838.8	863.2	890.2	913.2	918.6
42.5°	794.2	825.3	853.7	879.4	887.5
45°	752.2	784.7	818.5	844.2	855.0
47.5°	707.6	744.1	782.0	810.4	818.5
50°	664.3	702.2	744.1	775.2	784.7
52.5°	618.3	658.9	706.2	738.7	750.9
55°	573.6	618.3	667.0	703.5	714.3
57.5°	530.3	576.3	629.1	665.6	677.8
60°	484.3	533.0	588.5	626.4	641.3
62.5°	441.0	491.1	550.6	588.5	602.0
65°	396.4	449.2	508.7	549.3	562.8
67.5°	351.8	407.2	466.8	511.4	522.2
70°	304.4	362.6	427.5	470.8	484.3
72.5°	261.1	319.3	386.9	431.6	445.1
75°	215.1	278.7	346.3	391.0	407.2
77.5°	175.9	239.5	307.1	354.5	366.6
80°	133.9	200.2	270.6	316.6	330.1
82.5°	97.4	165.1	236.8	282.8	296.3
85°	66.3	133.9	205.6	251.6	265.2
87.5°	40.6	108.2	177.2	223.2	236.8
90°	18.6	94.8	176.6	226.6	242.0
92.5°	38.9	91.2	167.8	219.3	232.5
95°	75.2	87.4	164.5	213.4	226.9
97.5°	123.2	144.2	157.4	205.9	220.4
100°	179.2	242.2	150.3	197.4	212.0
102.5°	243.0	293.7	182.7	188.0	203.5
105°	305.2	348.6	317.9	180.8	195.0
107.5°	370.1	407.4	477.7	362.1	244.9
110°	434.9	467.2	532.2	534.8	404.3

TEST NUMBER: P1010400

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	498.2	524.1	586.4	629.0	639.3
115°	559.1	581.2	638.8	681.2	696.0
117.5°	620.4	638.1	689.0	729.4	741.2
120°	675.3	691.0	738.6	777.6	787.1
122.5°	732.6	742.2	788.2	822.8	833.3
125°	782.7	790.6	833.7	864.1	875.6
127.5°	834.1	840.6	879.3	909.4	916.9
130°	881.5	888.0	919.0	948.7	954.8
132.5°	925.5	933.4	956.7	985.1	991.5
135°	972.0	976.6	995.4	1022.7	1026.6
137.5°	1011.5	1018.1	1029.5	1056.1	1060.8
140°	1049.7	1055.6	1062.6	1086.9	1091.7
142.5°	1086.3	1090.8	1093.8	1114.3	1118.2
145°	1119.9	1125.4	1127.4	1140.1	1145.5
147.5°	1151.1	1156.0	1158.0	1164.1	1164.5
150°	1180.7	1183.7	1185.7	1187.6	1187.4
152.5°	1207.4	1208.4	1209.4	1213.3	1208.4
155°	1232.1	1230.1	1231.1	1236.0	1230.1
157.5°	1251.9	1251.9	1250.9	1256.8	1248.9
160°	1269.6	1268.7	1267.7	1273.6	1266.7
162.5°	1286.4	1283.5	1282.5	1289.4	1283.5
165°	1299.3	1296.3	1295.3	1303.2	1296.3
167.5°	1310.1	1306.2	1306.2	1314.1	1306.2
170°	1319.0	1315.1	1315.1	1323.0	1315.1
172.5°	1325.0	1320.0	1321.0	1328.9	1320.0
175°	1329.9	1325.0	1326.0	1332.9	1325.0
177.5°	1331.9	1326.9	1327.9	1335.8	1326.0
180°	1329.9	1329.9	1329.9	1329.9	1329.9

(END OF REPORT)