

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010403

Luminaire Tested: S123DIP-B1000D1025UB2750-4F0-XX-W2A-D_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010403
REPORT IS A COMBINATION OF REPORTS P989037 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D1025UB2750-4F0-XX-W2A-D_5000K
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7914.0 lumens
Efficiency: N/A
Efficacy: 105.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010403

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-D_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010403

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-D_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53
1	96	91	87	83	88	84	80	77	70	67	65	57	55	53	45	44	43
2	87	79	73	67	79	73	67	62	61	56	53	50	46	44	39	37	35
3	79	69	62	55	72	64	57	52	53	48	44	43	40	37	34	32	30
4	72	61	53	47	66	56	49	43	47	42	37	39	34	31	31	28	25
5	66	54	46	40	60	50	43	37	42	36	32	34	30	27	27	24	22
6	61	49	40	34	56	45	37	32	38	32	28	31	27	23	25	22	19
7	56	44	36	30	51	40	33	28	34	28	24	28	24	21	23	19	17
8	52	40	32	26	48	37	30	25	31	25	21	26	21	18	21	17	15
9	49	36	29	23	44	33	27	22	28	23	19	24	19	16	19	16	14
10	45	33	26	21	41	31	24	20	26	21	17	22	18	15	18	15	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12853	12853	12853
5°	12888	12476	12466
10°	12768	12138	12046
15°	12598	11764	11599
20°	12358	11349	11120
25°	12064	10880	10624
30°	11761	10457	10127
35°	11423	10011	9720
40°	11100	9605	9292
45°	10740	9211	8939
50°	10386	8821	8555
55°	9993	8421	8203
60°	9609	8011	7840
65°	9213	7575	7418
70°	8620	7085	6983
75°	7867	6528	6532
80°	6993	5962	6019
85°	6119	5505	5650

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10740 cd/sqm

TEST NUMBER: P1010403

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-D_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.3	1.4
10°-20°	322.9	4.1
20°-30°	482.9	6.1
30°-40°	576.5	7.3
40°-50°	603.2	7.6
50°-60°	566.1	7.2
60°-70°	472.8	6.0
70°-80°	338.1	4.3
80°-90°	203.7	2.6
90°-100°	171.5	2.2
100°-110°	311.0	3.9
110°-120°	596.3	7.5
120°-130°	713.6	9.0
130°-140°	740.4	9.4
140°-150°	680.9	8.6
150°-160°	546.5	6.9
160°-170°	352.7	4.5
170°-180°	121.5	1.5
0°-30°	919.1	11.6
0°-40°	1495.6	18.9
0°-60°	2664.9	33.7
0°-90°	3679.6	46.5
90°-120°	1078.8	13.6
90°-150°	3213.7	40.6
90°-180°	4234.0	53.5
0°-180°	7914.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1194	1194	1194	1194	1194	
5°	1195	1193	1185	1195	1194	113
15°	1138	1142	1141	1154	1152	321
25°	1028	1041	1044	1061	1061	474
35°	884	905	922	942	947	553
45°	723	754	787	812	822	558
55°	552	594	641	676	687	494
65°	381	432	489	528	541	377
75°	207	268	333	376	392	221
85°	64	129	198	242	255	66
90°	18	91	170	218	233	15
95°	72	84	158	205	218	80
105°	294	335	306	174	188	311
115°	538	559	614	655	669	531
125°	752	760	802	831	842	673
135°	935	939	957	983	987	720
145°	1077	1082	1084	1096	1102	674
155°	1185	1183	1184	1188	1183	546
165°	1249	1246	1246	1253	1246	353
175°	1279	1274	1275	1282	1274	122
180°	1279	1279	1279	1279	1279	

TEST NUMBER: P1010403

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1194.1	1194.1	1194.1	1194.1	1194.1
2.5°	1200.6	1196.7	1186.3	1196.7	1195.4
5°	1195.4	1192.8	1185.0	1195.4	1194.1
7.5°	1186.3	1186.3	1178.5	1191.5	1190.2
10°	1173.3	1175.9	1169.4	1182.4	1179.8
12.5°	1157.6	1161.5	1157.6	1169.4	1166.8
15°	1138.1	1142.0	1140.7	1153.7	1152.4
17.5°	1114.7	1122.5	1121.2	1132.9	1130.3
20°	1088.7	1096.5	1099.1	1110.8	1112.1
22.5°	1061.4	1069.2	1073.1	1088.7	1087.4
25°	1027.6	1040.6	1044.5	1061.4	1061.4
27.5°	995.1	1009.4	1017.2	1031.5	1032.8
30°	959.9	976.8	987.3	1002.9	1002.9
32.5°	920.9	940.4	954.7	971.6	975.5
35°	884.5	905.3	922.2	941.7	946.9
37.5°	845.5	868.9	888.4	910.5	914.4
40°	806.5	829.9	855.9	878.0	883.2
42.5°	763.5	793.4	820.8	845.5	853.3
45°	723.2	754.4	786.9	811.7	822.1
47.5°	680.3	715.4	751.8	779.1	786.9
50°	638.7	675.1	715.4	745.3	754.4
52.5°	594.4	633.5	679.0	710.2	721.9
55°	551.5	594.4	641.3	676.4	686.8
57.5°	509.9	554.1	604.8	640.0	651.7
60°	465.7	512.5	565.8	602.2	616.5
62.5°	424.0	472.2	529.4	565.8	578.8
65°	381.1	431.8	489.1	528.1	541.1
67.5°	338.2	391.5	448.8	491.7	502.1
70°	292.7	348.6	411.0	452.7	465.7
72.5°	251.0	307.0	372.0	414.9	427.9
75°	206.8	267.9	333.0	375.9	391.5
77.5°	169.1	230.2	295.3	340.8	352.5
80°	128.8	192.5	260.1	304.4	317.4
82.5°	93.7	158.7	227.6	271.9	284.9
85°	63.7	128.8	197.7	241.9	254.9
87.5°	39.0	104.1	170.4	214.6	227.6
90°	17.9	91.1	169.8	217.8	232.7
92.5°	37.5	87.7	161.3	210.9	223.5
95°	72.3	84.0	158.3	205.2	218.2
97.5°	118.5	138.7	151.4	198.0	212.0
100°	172.3	232.9	144.6	189.9	203.8
102.5°	233.7	282.4	175.7	180.8	195.7
105°	293.5	335.2	305.7	173.9	187.5
107.5°	355.9	391.7	459.4	348.2	235.4
110°	418.2	449.2	511.7	514.2	388.8

TEST NUMBER: P1010403

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	479.0	503.9	563.7	604.9	614.7
115°	537.6	558.9	614.2	655.0	669.2
117.5°	596.5	613.5	662.5	701.4	712.7
120°	649.3	664.4	710.1	747.6	756.8
122.5°	704.4	713.7	757.8	791.1	801.2
125°	752.5	760.1	801.6	830.8	841.8
127.5°	801.9	808.2	845.5	874.3	881.5
130°	847.5	853.8	883.6	912.1	918.0
132.5°	890.0	897.6	919.9	947.1	953.4
135°	934.6	939.0	957.1	983.4	987.0
137.5°	972.6	978.9	989.9	1015.5	1020.1
140°	1009.3	1015.0	1021.8	1045.1	1049.7
142.5°	1044.5	1048.9	1051.7	1071.5	1075.1
145°	1076.8	1082.1	1084.0	1096.3	1101.5
147.5°	1106.8	1111.6	1113.5	1119.3	1119.7
150°	1135.3	1138.2	1140.1	1142.0	1141.7
152.5°	1161.0	1161.9	1162.9	1166.7	1161.9
155°	1184.7	1182.8	1183.8	1188.5	1182.8
157.5°	1203.7	1203.7	1202.8	1208.5	1200.9
160°	1220.8	1219.9	1218.9	1224.6	1218.0
162.5°	1237.0	1234.1	1233.2	1239.8	1234.1
165°	1249.3	1246.5	1245.5	1253.1	1246.5
167.5°	1259.8	1256.0	1256.0	1263.6	1256.0
170°	1268.3	1264.5	1264.5	1272.1	1264.5
172.5°	1274.0	1269.3	1270.2	1277.8	1269.3
175°	1278.8	1274.0	1275.0	1281.6	1274.0
177.5°	1280.7	1275.9	1276.9	1284.5	1275.0
180°	1278.8	1278.8	1278.8	1278.8	1278.8

(END OF REPORT)