

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009653

Luminaire Tested: S122DIP-B865D925UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009653
REPORT IS A COMBINATION OF REPORTS P985017 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D925UB50-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6803.9 lumens
Efficiency: N/A
Efficacy: 90.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009653

CATALOG NUMBER: S122DIP-B865D925UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1009653

CATALOG NUMBER: S122DIP-B865D925UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	89	86	90	86	83	80	73	70	68	60	59	57	49	48	47
2	89	81	75	70	82	75	70	65	64	60	56	53	50	48	43	41	39
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	36	34
4	74	63	55	49	68	59	52	46	50	45	40	42	38	35	34	31	29
5	68	56	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25
6	63	51	43	37	58	47	40	35	40	35	30	34	30	26	28	25	22
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	22	20
8	54	42	34	28	50	39	32	27	33	28	24	28	24	21	23	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	18	16
10	47	35	28	23	43	32	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20880	20880	20880
5°	20914	19903	19762
10°	20745	18996	18619
15°	20441	18082	17417
20°	20030	17088	16278
25°	19621	16049	15141
30°	19106	15074	13949
35°	18619	14045	12776
40°	18021	13030	11670
45°	17424	12022	10584
50°	16773	10997	9456
55°	16086	9900	8388
60°	15318	8714	7279
65°	14472	7509	6113
70°	13404	6188	4936
75°	11921	4770	3811
80°	10123	3241	2453
85°	7345	1509	1044

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17424 cd/sqm

TEST NUMBER: P1009653

CATALOG NUMBER: S122DIP-B865D925UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.1	1.8
10°-20°	349.3	5.1
20°-30°	513.3	7.5
30°-40°	596.2	8.8
40°-50°	595.5	8.8
50°-60°	519.2	7.6
60°-70°	383.8	5.6
70°-80°	217.2	3.2
80°-90°	60.5	0.9
90°-100°	200.3	2.9
100°-110°	677.1	10.0
110°-120°	711.8	10.5
120°-130°	585.3	8.6
130°-140°	470.3	6.9
140°-150°	355.3	5.2
150°-160°	249.8	3.7
160°-170°	147.1	2.2
170°-180°	47.8	0.7
0°-30°	986.8	14.5
0°-40°	1583.0	23.3
0°-60°	2697.7	39.6
0°-90°	3359.2	49.4
90°-120°	1589.2	23.4
90°-150°	3000.1	44.1
90°-180°	3445.0	50.6
0°-180°	6803.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1319	1319	1319	1319	1319	
5°	1319	1314	1300	1310	1308	125
15°	1256	1248	1232	1237	1230	354
25°	1136	1126	1105	1107	1105	523
35°	980	968	948	940	934	612
45°	798	789	770	756	751	616
55°	604	596	581	566	559	540
65°	407	400	387	375	369	403
75°	213	210	204	197	199	227
85°	52	51	50	46	44	58
90°	1	13	32	31	31	5
95°	33	82	372	141	108	34
105°	116	175	704	1258	1071	123
115°	204	258	589	1216	1409	203
125°	285	337	566	985	1143	253
135°	334	399	560	828	947	258
145°	382	439	557	691	756	240
155°	434	469	541	611	636	200
165°	473	487	518	549	558	133
175°	493	494	498	504	503	47
180°	494	494	494	494	494	

TEST NUMBER: P1009653

CATALOG NUMBER: S122DIP-B865D925UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1319.1	1319.1	1319.1	1319.1	1319.1
2.5°	1326.7	1320.4	1306.4	1319.1	1316.6
5°	1319.1	1314.0	1300.1	1310.2	1307.7
7.5°	1310.2	1302.6	1288.7	1298.8	1296.3
10°	1296.3	1287.4	1272.2	1282.3	1278.5
12.5°	1277.2	1269.6	1254.4	1260.8	1258.2
15°	1255.7	1248.1	1231.6	1236.7	1230.3
17.5°	1229.0	1221.4	1204.9	1211.3	1204.9
20°	1199.9	1192.3	1174.5	1178.3	1173.2
22.5°	1170.7	1159.3	1142.8	1142.8	1140.3
25°	1136.5	1126.3	1104.7	1107.3	1104.7
27.5°	1098.4	1089.5	1073.0	1069.2	1062.9
30°	1060.4	1050.2	1031.2	1027.4	1022.3
32.5°	1019.8	1012.2	991.9	984.3	979.2
35°	980.4	967.8	947.5	939.9	933.5
37.5°	936.1	924.6	904.3	895.5	889.1
40°	890.4	880.2	860.0	848.5	843.5
42.5°	846.0	835.9	815.6	802.9	795.3
45°	797.8	788.9	769.9	755.9	750.9
47.5°	750.9	742.0	721.7	707.7	700.1
50°	701.4	695.1	677.3	659.5	653.2
52.5°	653.2	644.3	627.8	613.9	605.0
55°	603.7	596.1	580.9	565.7	559.3
57.5°	554.3	547.9	531.4	516.2	511.2
60°	504.8	499.7	482.0	468.0	464.2
62.5°	456.6	447.7	435.0	422.4	417.3
65°	407.1	399.5	386.9	375.4	369.1
67.5°	356.4	350.1	338.7	329.8	324.7
70°	309.5	304.4	293.0	284.1	279.0
72.5°	261.3	256.2	249.9	241.0	237.2
75°	213.1	210.5	204.2	196.6	199.1
77.5°	170.0	164.9	162.4	158.5	154.7
80°	126.8	125.6	123.0	119.2	116.7
82.5°	86.2	86.2	85.0	79.9	79.9
85°	52.0	50.7	49.5	45.7	44.4
87.5°	22.8	20.3	17.8	14.0	12.7
90°	1.0	12.8	32.3	30.9	31.4
92.5°	14.3	45.2	146.3	67.5	58.0
95°	33.3	81.7	372.5	140.6	108.3
97.5°	49.4	107.8	607.2	282.2	181.5
100°	73.2	132.1	750.6	562.0	340.2
102.5°	95.0	153.9	755.4	950.2	663.2
105°	115.9	174.8	704.1	1258.5	1070.8
107.5°	138.7	195.7	656.6	1370.1	1345.4
110°	161.5	217.1	624.3	1352.0	1457.6

TEST NUMBER: P1009653

CATALOG NUMBER: S122DIP-B865D925UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	182.4	237.6	603.4	1290.8	1455.7
115°	204.3	258.0	589.1	1215.8	1409.1
117.5°	227.1	278.4	581.5	1144.0	1338.8
120°	248.0	298.4	574.8	1079.8	1271.3
122.5°	267.9	318.8	571.0	1030.0	1201.0
125°	285.0	337.3	566.3	984.8	1143.0
127.5°	299.3	354.9	563.4	946.4	1088.9
130°	311.7	370.6	561.5	907.4	1044.2
132.5°	323.1	385.8	560.6	867.0	997.7
135°	334.5	399.1	559.6	827.6	947.3
137.5°	344.9	410.4	559.6	787.6	898.9
140°	357.3	421.0	558.7	752.5	848.5
142.5°	369.6	429.5	558.7	718.8	798.1
145°	382.0	439.0	556.8	691.2	756.3
147.5°	395.3	446.6	553.9	667.0	719.3
150°	408.6	454.2	551.1	646.2	687.0
152.5°	421.9	461.8	546.3	628.6	659.4
155°	434.2	468.9	540.6	611.4	635.7
157.5°	444.7	474.6	534.9	595.3	614.8
160°	455.1	480.3	529.2	579.2	594.8
162.5°	465.6	484.6	524.5	563.9	575.8
165°	473.2	487.4	517.8	549.2	557.7
167.5°	479.8	490.3	512.1	535.9	540.6
170°	486.5	491.7	507.4	523.6	525.4
172.5°	490.3	493.2	501.7	512.6	513.1
175°	493.1	493.6	497.9	504.0	502.6
177.5°	495.0	494.1	494.1	497.9	495.0
180°	494.1	494.1	494.1	494.1	494.1

(END OF REPORT)