

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009659

Luminaire Tested: S122RDIP-B1005D1080UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009659
REPORT IS A COMBINATION OF REPORTS P987823 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B1005D1080UB27-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7636.8 lumens
Efficiency: N/A
Efficacy: 79.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009659

CATALOG NUMBER: S122RDIP-B1005D1080UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1009659

CATALOG NUMBER: S122RDIP-B1005D1080UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45		
1	97	93	89	86	89	86	82	80	71	69	67	58	57	56	46	46	45	39		
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	41	40	38	33		
3	81	72	65	60	74	67	61	56	56	52	48	46	43	40	37	35	33	29		
4	75	64	57	51	68	59	53	48	50	45	41	41	38	35	33	31	29	25		
5	69	57	50	44	63	53	46	41	45	40	36	37	34	31	30	28	25	22		
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20		
7	59	47	39	34	54	43	36	32	37	32	28	31	27	24	25	22	20	18		
8	54	42	35	30	50	39	33	28	34	29	25	28	24	21	23	20	18	16		
9	51	39	32	27	47	36	30	25	31	26	22	26	22	19	22	19	17	14		
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15	13		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	26631	26631	26631
5°	26675	25336	25148
10°	26411	24030	23237
15°	26047	22487	21058
20°	25567	20734	18779
25°	25077	18934	16694
30°	24414	17182	14417
35°	23768	15415	12462
40°	23111	13678	10448
45°	22344	11888	8691
50°	21553	10159	7075
55°	20731	8433	5617
60°	19773	6744	4250
65°	18674	5141	3455
70°	17340	3730	2747
75°	15669	2845	2098
80°	13253	1926	1409
85°	9252	881	680

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22344 cd/sqm

TEST NUMBER: P1009659

CATALOG NUMBER: S122RDIP-B1005D1080UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.7	2.1
10°-20°	432.8	5.7
20°-30°	607.7	8.0
30°-40°	662.4	8.7
40°-50°	608.8	8.0
50°-60°	478.1	6.3
60°-70°	311.2	4.1
70°-80°	160.2	2.1
80°-90°	44.7	0.6
90°-100°	242.6	3.2
100°-110°	820.3	10.7
110°-120°	862.2	11.3
120°-130°	709.0	9.3
130°-140°	569.7	7.5
140°-150°	430.4	5.6
150°-160°	302.6	4.0
160°-170°	178.2	2.3
170°-180°	58.0	0.8
0°-30°	1198.2	15.7
0°-40°	1860.7	24.4
0°-60°	2947.6	38.6
0°-90°	3463.8	45.4
90°-120°	1925.1	25.2
90°-150°	3634.3	47.6
90°-180°	4173.0	54.6
0°-180°	7636.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1682	1682	1682	1682	1682	
5°	1682	1675	1655	1669	1664	160
15°	1600	1583	1532	1503	1488	451
25°	1452	1404	1303	1241	1218	668
35°	1252	1174	1040	944	910	783
45°	1023	921	761	653	617	790
55°	778	659	495	404	374	695
65°	525	402	265	213	209	521
75°	280	174	122	111	110	296
85°	66	34	29	29	29	75
90°	1	16	39	37	38	6
95°	40	99	451	170	131	42
105°	140	212	853	1524	1297	149
115°	248	312	714	1473	1707	245
125°	345	409	686	1193	1385	307
135°	405	483	678	1003	1148	313
145°	463	532	674	837	916	290
155°	526	568	655	741	770	242
165°	573	590	627	665	676	162
175°	597	598	603	611	609	57
180°	598	598	598	598	598	

TEST NUMBER: P1009659

CATALOG NUMBER: S122RDIP-B1005D1080UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1682.4	1682.4	1682.4	1682.4	1682.4
2.5°	1690.0	1682.4	1665.6	1680.8	1677.8
5°	1682.4	1674.8	1655.0	1668.7	1664.1
7.5°	1668.7	1659.5	1638.2	1644.3	1636.7
10°	1650.4	1639.7	1609.3	1604.7	1595.6
12.5°	1627.6	1613.9	1572.7	1563.6	1546.9
15°	1600.1	1583.4	1531.6	1502.7	1487.5
17.5°	1568.2	1543.8	1479.9	1446.4	1422.0
20°	1531.6	1501.2	1425.1	1387.0	1353.5
22.5°	1492.1	1457.0	1368.7	1317.0	1294.1
25°	1452.5	1403.7	1303.3	1240.8	1218.0
27.5°	1405.3	1353.5	1242.4	1170.8	1135.8
30°	1355.0	1297.2	1175.4	1097.7	1056.6
32.5°	1306.3	1236.3	1111.4	1020.1	982.0
35°	1251.5	1173.8	1039.9	944.0	910.5
37.5°	1198.2	1114.5	972.9	867.8	829.8
40°	1141.9	1050.5	902.8	794.7	755.2
42.5°	1084.0	986.6	832.8	720.1	682.1
45°	1023.1	921.1	761.3	653.2	616.6
47.5°	965.3	857.2	692.7	584.6	551.1
50°	901.3	793.2	625.7	520.7	488.7
52.5°	838.9	724.7	561.8	461.3	432.4
55°	778.0	659.2	494.8	403.5	374.5
57.5°	715.6	593.8	435.4	350.2	325.8
60°	651.6	529.8	373.0	295.4	271.0
62.5°	589.2	467.4	319.7	246.6	234.5
65°	525.3	401.9	264.9	213.2	208.6
67.5°	464.4	341.0	213.2	187.3	182.7
70°	400.4	281.7	176.6	161.4	155.3
72.5°	339.5	226.9	147.7	135.5	132.5
75°	280.1	173.6	121.8	111.1	109.6
77.5°	220.8	123.3	95.9	89.8	86.8
80°	166.0	88.3	73.1	67.0	67.0
82.5°	115.7	59.4	50.2	47.2	47.2
85°	65.5	33.5	28.9	28.9	28.9
87.5°	24.4	12.2	12.2	10.7	10.7
90°	1.2	15.6	39.1	37.4	38.0
92.5°	17.3	54.6	177.3	81.7	70.2
95°	40.3	99.0	451.2	170.4	131.2
97.5°	59.9	130.6	735.5	341.8	219.8
100°	88.6	160.0	909.3	680.8	412.1
102.5°	115.1	186.4	915.1	1151.0	803.4
105°	140.4	211.8	852.9	1524.5	1297.2
107.5°	168.0	237.1	795.3	1659.8	1629.8
110°	195.7	263.0	756.2	1637.9	1765.7

TEST NUMBER: P1009659

CATALOG NUMBER: S122RDIP-B1005D1080UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	221.0	287.8	730.9	1563.6	1763.4
115°	247.5	312.5	713.6	1472.7	1707.0
117.5°	275.1	337.2	704.4	1385.8	1621.8
120°	300.4	361.4	696.4	1308.2	1540.1
122.5°	324.6	386.2	691.8	1247.7	1454.9
125°	345.3	408.6	686.0	1193.1	1384.7
127.5°	362.6	429.9	682.6	1146.4	1319.1
130°	377.5	448.9	680.2	1099.2	1265.0
132.5°	391.3	467.3	679.1	1050.3	1208.6
135°	405.2	483.4	677.9	1002.6	1147.6
137.5°	417.8	497.2	677.9	954.2	1088.9
140°	432.8	509.9	676.8	911.6	1027.9
142.5°	447.7	520.2	676.8	870.8	966.9
145°	462.7	531.8	674.5	837.4	916.2
147.5°	478.8	541.0	671.0	808.0	871.3
150°	494.9	550.2	667.6	782.6	832.2
152.5°	511.0	559.4	661.8	761.4	798.8
155°	526.0	568.0	654.9	740.6	770.0
157.5°	538.7	574.9	648.0	721.1	744.7
160°	551.3	581.8	641.1	701.6	720.5
162.5°	564.0	587.0	635.4	683.1	697.5
165°	573.2	590.4	627.3	665.3	675.6
167.5°	581.3	593.9	620.4	649.2	654.9
170°	589.3	595.6	614.6	634.2	636.5
172.5°	593.9	597.4	607.7	621.0	621.5
175°	597.4	598.0	603.1	610.6	608.9
177.5°	599.7	598.5	598.5	603.1	599.7
180°	598.5	598.5	598.5	598.5	598.5

(END OF REPORT)