

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010405

Luminaire Tested: S123DIP-B1000D1025UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010405
REPORT IS A COMBINATION OF REPORTS P989039 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D1025UB2750-4F0-XX-W2A-F_3000K
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8152.0 lumens
Efficiency: N/A
Efficacy: 108.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010405

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010405

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	49	47
2	89	82	75	70	82	75	70	66	64	60	57	53	51	48	44	42	40
3	81	72	64	58	75	66	60	55	56	52	48	47	44	41	39	36	34
4	74	63	55	49	68	59	52	46	50	45	41	42	38	35	35	32	29
5	68	56	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25
6	63	51	43	37	58	47	40	35	40	35	30	34	30	26	28	25	22
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	22	20
8	54	41	34	28	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	32	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16937	16937	16937
5°	16979	16352	16328
10°	16828	15798	15636
15°	16593	15222	14883
20°	16326	14585	14137
25°	15978	13910	13339
30°	15598	13212	12499
35°	15200	12498	11666
40°	14784	11751	10845
45°	14325	11021	9988
50°	13859	10209	9129
55°	13262	9362	8257
60°	12647	8428	7329
65°	12067	7417	6363
70°	11235	6297	5234
75°	10035	4987	4062
80°	8665	3505	2873
85°	6762	1882	1438

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14325 cd/sqm

TEST NUMBER: P1010405

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.3	1.8
10°-20°	418.8	5.1
20°-30°	618.6	7.6
30°-40°	722.5	8.9
40°-50°	726.3	8.9
50°-60°	638.0	7.8
60°-70°	475.2	5.8
70°-80°	270.4	3.3
80°-90°	79.5	1.0
90°-100°	46.9	0.6
100°-110°	226.7	2.8
110°-120°	555.6	6.8
120°-130°	705.4	8.7
130°-140°	753.5	9.2
140°-150°	704.6	8.6
150°-160°	568.4	7.0
160°-170°	366.8	4.5
170°-180°	126.4	1.6
0°-30°	1185.8	14.5
0°-40°	1908.2	23.4
0°-60°	3272.5	40.1
0°-90°	4097.6	50.3
90°-120°	829.3	10.2
90°-150°	2992.8	36.7
90°-180°	4054.0	49.7
0°-180°	8152.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1574	1574	1574	1574	1574	
5°	1575	1568	1553	1567	1564	149
15°	1499	1494	1476	1487	1479	423
25°	1361	1353	1335	1337	1333	627
35°	1177	1169	1151	1143	1136	736
45°	965	959	942	925	919	745
55°	732	731	713	698	691	656
65°	499	492	479	468	464	493
75°	264	258	254	248	244	282
85°	70	68	68	65	65	75
90°	1	11	24	28	30	8
95°	60	20	31	38	38	72
105°	294	305	216	42	44	312
115°	552	558	567	577	581	545
125°	779	786	790	792	794	696
135°	969	975	979	982	979	746
145°	1118	1125	1127	1129	1129	700
155°	1232	1230	1231	1236	1230	568
165°	1299	1296	1295	1303	1296	367
175°	1330	1325	1326	1333	1325	127
180°	1330	1330	1330	1330	1330	

TEST NUMBER: P1010405

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1573.5	1573.5	1573.5	1573.5	1573.5
2.5°	1580.2	1574.8	1559.9	1573.5	1572.1
5°	1574.8	1568.0	1553.2	1566.7	1564.0
7.5°	1562.6	1555.9	1541.0	1553.2	1551.8
10°	1546.4	1539.6	1522.0	1534.2	1531.5
12.5°	1524.7	1519.3	1503.1	1511.2	1509.9
15°	1499.0	1493.6	1476.0	1486.9	1478.7
17.5°	1470.6	1463.9	1446.3	1454.4	1451.7
20°	1438.2	1430.0	1412.5	1417.9	1413.8
22.5°	1401.6	1393.5	1375.9	1380.0	1374.6
25°	1361.0	1352.9	1335.3	1336.7	1332.6
27.5°	1319.1	1311.0	1292.0	1293.4	1289.3
30°	1273.1	1266.3	1247.4	1247.4	1237.9
32.5°	1227.1	1217.6	1204.1	1194.6	1190.6
35°	1177.0	1168.9	1151.3	1143.2	1136.5
37.5°	1127.0	1116.2	1098.6	1089.1	1085.0
40°	1074.2	1066.1	1047.2	1036.3	1030.9
42.5°	1021.5	1012.0	993.0	982.2	976.8
45°	964.6	959.2	941.6	925.4	918.6
47.5°	909.2	901.0	884.8	868.6	863.2
50°	852.3	845.6	828.0	813.1	805.0
52.5°	792.8	788.8	769.8	757.6	749.5
55°	731.9	730.6	713.0	698.1	691.3
57.5°	675.1	669.7	656.2	642.6	634.5
60°	612.9	611.5	595.3	583.1	576.3
62.5°	557.4	553.3	537.1	524.9	520.9
65°	499.2	492.5	478.9	468.1	464.1
67.5°	437.0	431.6	420.8	411.3	405.9
70°	381.5	373.4	365.3	355.8	349.1
72.5°	323.3	317.9	308.5	300.3	297.6
75°	263.8	258.4	254.4	247.6	243.5
77.5°	211.1	208.4	202.9	197.5	197.5
80°	159.6	155.6	152.9	151.5	151.5
82.5°	109.6	109.6	109.6	106.9	105.5
85°	70.4	67.6	67.6	64.9	64.9
87.5°	35.2	31.1	29.8	28.4	28.4
90°	1.0	10.9	23.7	27.7	29.6
92.5°	22.7	16.8	25.7	32.6	33.6
95°	60.3	19.8	30.6	37.5	37.5
97.5°	109.7	82.0	31.6	39.5	40.5
100°	167.0	186.7	32.6	40.5	41.5
102.5°	232.2	245.0	73.1	40.5	42.5
105°	294.4	305.3	216.4	41.5	43.5
107.5°	360.6	369.5	384.3	232.2	102.8
110°	426.8	434.7	445.6	413.0	271.7



TEST NUMBER: P1010405

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	490.1	497.0	507.9	516.7	514.8
115°	552.3	558.2	567.1	577.0	581.0
117.5°	613.6	620.5	625.4	633.3	634.3
120°	669.9	678.8	681.8	689.7	689.7
122.5°	727.2	734.1	738.1	743.0	744.0
125°	778.6	786.5	790.4	792.4	794.4
127.5°	830.0	837.9	842.8	845.8	843.8
130°	877.4	885.3	889.2	893.2	891.2
132.5°	922.8	930.7	933.7	937.7	934.7
135°	969.3	975.2	979.2	982.1	979.2
137.5°	1008.8	1016.7	1018.7	1023.6	1021.6
140°	1048.3	1054.2	1057.2	1061.2	1059.2
142.5°	1084.9	1090.8	1093.8	1096.7	1093.8
145°	1118.5	1125.4	1127.4	1129.3	1129.3
147.5°	1151.1	1156.0	1158.0	1160.0	1155.0
150°	1180.7	1183.7	1185.7	1187.6	1184.7
152.5°	1207.4	1208.4	1209.4	1213.3	1208.4
155°	1232.1	1230.1	1231.1	1236.0	1230.1
157.5°	1251.9	1251.9	1250.9	1256.8	1248.9
160°	1269.6	1268.7	1267.7	1273.6	1266.7
162.5°	1286.4	1283.5	1282.5	1289.4	1283.5
165°	1299.3	1296.3	1295.3	1303.2	1296.3
167.5°	1310.1	1306.2	1306.2	1314.1	1306.2
170°	1319.0	1315.1	1315.1	1323.0	1315.1
172.5°	1325.0	1320.0	1321.0	1328.9	1320.0
175°	1329.9	1325.0	1326.0	1332.9	1325.0
177.5°	1331.9	1326.9	1327.9	1335.8	1326.0
180°	1329.9	1329.9	1329.9	1329.9	1329.9

(END OF REPORT)