

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010407

Luminaire Tested: S123DIP-B1000D1025UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010407
REPORT IS A COMBINATION OF REPORTS P989041 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D1025UB2750-4F0-XX-W2A-F_4000K
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8106.0 lumens
Efficiency: N/A
Efficacy: 107.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010407

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010407

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	49	47
2	89	82	75	70	82	75	70	66	64	60	57	53	51	48	44	42	40
3	81	72	64	58	75	66	60	55	56	52	48	47	44	41	39	36	34
4	74	63	55	49	68	59	52	46	50	45	41	42	38	35	35	32	29
5	68	56	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25
6	63	51	43	37	58	47	40	35	40	35	30	34	30	26	28	25	22
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	22	20
8	54	41	34	28	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	32	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16841	16841	16841
5°	16884	16260	16236
10°	16733	15710	15549
15°	16500	15138	14799
20°	16234	14502	14058
25°	15889	13832	13264
30°	15511	13138	12430
35°	15115	12429	11601
40°	14701	11685	10784
45°	14245	10959	9933
50°	13783	10151	9078
55°	13187	9310	8211
60°	12575	8380	7288
65°	12000	7375	6326
70°	11173	6261	5204
75°	9978	4958	4041
80°	8616	3484	2858
85°	6724	1874	1432

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14245 cd/sqm

TEST NUMBER: P1010407

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.5	1.8
10°-20°	416.5	5.1
20°-30°	615.1	7.6
30°-40°	718.4	8.9
40°-50°	722.2	8.9
50°-60°	634.4	7.8
60°-70°	472.5	5.8
70°-80°	268.9	3.3
80°-90°	79.1	1.0
90°-100°	46.6	0.6
100°-110°	225.5	2.8
110°-120°	552.5	6.8
120°-130°	701.4	8.7
130°-140°	749.3	9.2
140°-150°	700.6	8.6
150°-160°	565.1	7.0
160°-170°	364.7	4.5
170°-180°	125.7	1.6
0°-30°	1179.1	14.5
0°-40°	1897.5	23.4
0°-60°	3254.2	40.1
0°-90°	4074.6	50.3
90°-120°	824.6	10.2
90°-150°	2975.8	36.7
90°-180°	4031.0	49.7
0°-180°	8106.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1565	1565	1565	1565	1565	
5°	1566	1559	1544	1558	1555	149
15°	1491	1485	1468	1478	1470	420
25°	1353	1345	1328	1329	1325	623
35°	1170	1162	1145	1137	1130	732
45°	959	954	936	920	914	741
55°	728	726	709	694	688	652
65°	496	490	476	466	461	490
75°	262	257	253	246	242	280
85°	70	67	67	65	65	75
90°	1	11	24	28	30	8
95°	60	20	30	37	37	72
105°	293	304	215	41	43	310
115°	549	555	564	574	578	542
125°	774	782	786	788	790	692
135°	964	970	974	977	974	742
145°	1112	1119	1121	1123	1123	696
155°	1225	1223	1224	1229	1223	564
165°	1292	1289	1288	1296	1289	365
175°	1322	1318	1318	1325	1318	126
180°	1322	1322	1322	1322	1322	

TEST NUMBER: P1010407

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1564.6	1564.6	1564.6	1564.6	1564.6
2.5°	1571.3	1566.0	1551.2	1564.6	1563.3
5°	1566.0	1559.2	1544.4	1557.9	1555.2
7.5°	1553.9	1547.1	1532.3	1544.4	1543.1
10°	1537.7	1531.0	1513.5	1525.6	1522.9
12.5°	1516.2	1510.8	1494.7	1502.7	1501.4
15°	1490.6	1485.2	1467.8	1478.5	1470.4
17.5°	1462.4	1455.6	1438.2	1446.2	1443.5
20°	1430.1	1422.0	1404.5	1409.9	1405.9
22.5°	1393.8	1385.7	1368.2	1372.2	1366.9
25°	1353.4	1345.3	1327.8	1329.2	1325.1
27.5°	1311.7	1303.6	1284.8	1286.1	1282.1
30°	1266.0	1259.2	1240.4	1240.4	1231.0
32.5°	1220.2	1210.8	1197.3	1187.9	1183.9
35°	1170.4	1162.4	1144.9	1136.8	1130.1
37.5°	1120.7	1109.9	1092.4	1083.0	1079.0
40°	1068.2	1060.1	1041.3	1030.5	1025.1
42.5°	1015.7	1006.3	987.5	976.7	971.3
45°	959.2	953.8	936.3	920.2	913.5
47.5°	904.1	896.0	879.8	863.7	858.3
50°	847.6	840.8	823.3	808.5	800.5
52.5°	788.4	784.3	765.5	753.4	745.3
55°	727.8	726.5	709.0	694.2	687.5
57.5°	671.3	665.9	652.5	639.0	631.0
60°	609.4	608.1	591.9	579.8	573.1
62.5°	554.3	550.2	534.1	522.0	518.0
65°	496.4	489.7	476.2	465.5	461.4
67.5°	434.5	429.2	418.4	409.0	403.6
70°	379.4	371.3	363.2	353.8	347.1
72.5°	321.5	316.2	306.7	298.7	296.0
75°	262.3	257.0	252.9	246.2	242.2
77.5°	209.9	207.2	201.8	196.4	196.4
80°	158.7	154.7	152.0	150.7	150.7
82.5°	109.0	109.0	109.0	106.3	104.9
85°	70.0	67.3	67.3	64.6	64.6
87.5°	35.0	30.9	29.6	28.3	28.3
90°	1.0	10.8	23.6	27.5	29.5
92.5°	22.6	16.7	25.5	32.4	33.4
95°	59.9	19.6	30.5	37.3	37.3
97.5°	109.1	81.5	31.4	39.3	40.3
100°	166.0	185.7	32.4	40.3	41.3
102.5°	230.9	243.6	72.7	40.3	42.2
105°	292.8	303.6	215.2	41.3	43.2
107.5°	358.6	367.4	382.2	230.9	102.2
110°	424.4	432.3	443.1	410.7	270.2



TEST NUMBER: P1010407

CATALOG NUMBER: S123DIP-B1000D1025UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	487.3	494.2	505.0	513.8	511.9
115°	549.2	555.1	563.9	573.7	577.7
117.5°	610.1	617.0	621.9	629.7	630.7
120°	666.1	674.9	677.9	685.7	685.7
122.5°	723.1	730.0	733.9	738.8	739.8
125°	774.2	782.0	786.0	787.9	789.9
127.5°	825.3	833.1	838.0	841.0	839.0
130°	872.4	880.3	884.2	888.1	886.2
132.5°	917.6	925.5	928.4	932.3	929.4
135°	963.8	969.7	973.6	976.6	973.6
137.5°	1003.1	1010.9	1012.9	1017.8	1015.8
140°	1042.4	1048.3	1051.2	1055.1	1053.2
142.5°	1078.7	1084.6	1087.6	1090.5	1087.6
145°	1112.1	1119.0	1121.0	1122.9	1122.9
147.5°	1144.5	1149.5	1151.4	1153.4	1148.5
150°	1174.0	1177.0	1178.9	1180.9	1178.0
152.5°	1200.5	1201.5	1202.5	1206.4	1201.5
155°	1225.1	1223.1	1224.1	1229.0	1223.1
157.5°	1244.8	1244.8	1243.8	1249.7	1241.8
160°	1262.4	1261.5	1260.5	1266.4	1259.5
162.5°	1279.1	1276.2	1275.2	1282.1	1276.2
165°	1291.9	1289.0	1288.0	1295.8	1289.0
167.5°	1302.7	1298.8	1298.8	1306.7	1298.8
170°	1311.6	1307.6	1307.6	1315.5	1307.6
172.5°	1317.5	1312.5	1313.5	1321.4	1312.5
175°	1322.4	1317.5	1318.4	1325.3	1317.5
177.5°	1324.3	1319.4	1320.4	1328.3	1318.4
180°	1322.4	1322.4	1322.4	1322.4	1322.4

(END OF REPORT)