

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009690

Luminaire Tested: S122RDIP-B1005D330UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009690
REPORT IS A COMBINATION OF REPORTS P987876 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B1005D330UB30-4F0-XX-W2A-A4
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5107.0 lumens
Efficiency: N/A
Efficacy: 72.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009690

CATALOG NUMBER: S122RDIP-B1005D330UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot





TEST NUMBER: P1009690

CATALOG NUMBER: S122RDIP-B1005D330UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	113	113	113	113	107	107	107	107	97	97	97	88	88	88	79	79	79	75						
1	104	100	97	94	99	96	93	90	87	85	82	79	77	75	72	70	69	65						
2	96	89	83	79	91	85	80	76	78	74	70	71	68	65	65	62	60	57						
3	89	80	73	67	84	76	70	65	70	65	61	64	60	57	58	55	53	50						
4	82	72	64	58	78	69	62	56	63	57	53	58	53	50	53	49	47	44						
5	76	65	57	51	72	62	55	50	57	51	47	53	48	44	49	45	42	39						
6	70	59	51	45	67	57	49	44	52	46	42	48	43	40	45	41	37	35						
7	66	54	46	41	63	52	45	40	48	42	38	45	39	36	41	37	34	32						
8	61	49	42	37	59	48	41	36	44	38	34	41	36	32	38	34	31	29						
9	58	46	38	33	55	44	37	33	41	35	31	38	33	30	36	31	28	26						
10	54	42	35	30	52	41	34	30	38	32	29	36	31	27	33	29	26	24						

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	34981	34981	34981	34981
5°	35062	37156	35184	29683
10°	34677	39272	34923	24512
15°	33925	39285	34499	18415
20°	33019	32472	33737	15193
25°	31922	20291	32611	12923
30°	30521	12992	31351	11127
35°	28816	9984	29748	9522
40°	26916	8392	28068	8329
45°	24887	7143	25926	6991
50°	22806	6070	23870	6047
55°	20502	5275	21607	5206
60°	18453	4022	19433	3974
65°	16541	3028	17526	3433
70°	14434	2418	15565	2799
75°	12201	1853	13314	2117
80°	9684	1259	10419	1388
85°	6724	649	7374	687

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 32000 cd/sqm

TEST NUMBER: P1009690

CATALOG NUMBER: S122RDIP-B1005D330UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	209.6	4.1
10°-20°	585.1	11.5
20°-30°	753.0	14.7
30°-40°	714.4	14.0
40°-50°	612.2	12.0
50°-60°	466.2	9.1
60°-70°	294.0	5.8
70°-80°	146.7	2.9
80°-90°	38.9	0.8
90°-100°	72.0	1.4
100°-110°	253.7	5.0
110°-120°	266.4	5.2
120°-130°	219.2	4.3
130°-140°	176.1	3.4
140°-150°	133.0	2.6
150°-160°	93.5	1.8
160°-170°	55.0	1.1
170°-180°	17.9	0.4
0°-30°	1547.7	30.3
0°-40°	2262.1	44.3
0°-60°	3340.6	65.4
0°-90°	3820.2	74.8
90°-120°	592.1	11.6
90°-150°	1120.4	21.9
90°-180°	1287.0	25.2
0°-180°	5107.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2210	2210	2210	2210	2210	
5°	2211	2459	2219	1964	2211	210
15°	2084	2775	2119	1301	2084	586
25°	1849	1480	1889	943	1849	849
35°	1517	730	1566	696	1517	949
45°	1140	507	1187	496	1140	880
55°	769	352	811	347	769	693
65°	465	183	493	207	465	462
75°	218	97	238	111	218	236
85°	48	28	52	29	48	54
90°	0	12	0	12	0	4
95°	12	40	12	40	12	13
105°	43	400	43	400	43	46
115°	76	527	76	527	76	76
125°	107	428	107	428	107	95
135°	125	354	125	354	125	97
145°	143	283	143	283	143	90
155°	162	238	162	238	162	75
165°	177	209	177	209	177	50
175°	184	188	184	188	184	18
180°	185	185	185	185	185	

TEST NUMBER: P1009690

CATALOG NUMBER: S122RDIP-B1005D330UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9
2.5°	2223.7	2232.9	2237.6	2243.7	2257.5	2266.7	2280.6	2283.6	2282.1	2288.2	2271.3
5°	2211.4	2231.4	2249.8	2265.2	2289.8	2305.1	2322.0	2342.0	2346.6	2369.6	2355.8
7.5°	2194.6	2223.7	2249.8	2280.6	2317.4	2337.4	2363.5	2394.2	2408.0	2435.7	2443.3
10°	2166.9	2208.4	2252.9	2285.2	2335.8	2371.2	2395.7	2444.9	2477.1	2518.6	2512.4
12.5°	2122.4	2176.1	2236.0	2289.8	2355.8	2378.8	2424.9	2475.6	2517.1	2555.4	2589.2
15°	2084.0	2145.4	2211.4	2277.5	2352.7	2395.7	2441.8	2507.8	2552.4	2619.9	2649.1
17.5°	2031.8	2110.1	2188.4	2262.1	2351.2	2400.3	2457.2	2521.7	2587.7	2652.2	2675.2
20°	1978.0	2062.5	2146.9	2246.8	2348.1	2395.7	2454.1	2533.9	2598.4	2649.1	2649.1
22.5°	1913.5	2016.4	2113.2	2208.4	2318.9	2388.1	2447.9	2541.6	2587.7	2598.4	2557.0
25°	1849.0	1951.9	2057.9	2176.1	2302.1	2363.5	2431.1	2518.6	2533.9	2490.9	2383.4
27.5°	1772.2	1887.4	2007.2	2134.7	2266.7	2343.5	2404.9	2463.3	2434.1	2318.9	2151.6
30°	1693.9	1818.3	1953.4	2074.8	2234.5	2305.1	2357.3	2374.2	2282.1	2094.7	1878.2
32.5°	1612.5	1733.8	1876.7	2022.6	2183.8	2251.4	2285.2	2240.6	2071.7	1835.2	1571.0
35°	1517.3	1654.0	1802.9	1955.0	2114.7	2165.4	2185.3	2076.3	1859.8	1554.2	1291.5
37.5°	1431.3	1568.0	1727.7	1882.8	2037.9	2065.6	2045.6	1875.1	1600.2	1297.7	1041.2
40°	1329.9	1475.8	1632.5	1806.0	1933.5	1941.2	1892.0	1670.9	1329.9	1045.8	887.7
42.5°	1236.3	1383.7	1540.3	1716.9	1813.7	1787.6	1721.5	1431.3	1110.3	901.5	774.0
45°	1139.5	1279.3	1448.2	1604.8	1673.9	1612.5	1512.7	1204.0	932.2	775.5	677.3
47.5°	1045.8	1176.4	1343.8	1494.3	1506.5	1437.4	1319.2	1009.0	807.8	681.9	602.0
50°	953.7	1084.2	1240.9	1365.3	1353.0	1257.8	1124.2	876.9	701.8	602.0	536.0
52.5°	861.5	979.8	1131.8	1230.1	1177.9	1085.8	953.7	743.3	612.8	525.2	474.5
55°	769.4	880.0	1010.5	1091.9	1009.0	903.0	809.3	637.3	531.4	460.7	422.3
57.5°	692.6	780.1	899.9	949.1	849.3	766.3	684.9	548.3	460.7	410.0	365.5
60°	608.1	688.0	786.3	815.5	712.6	645.0	575.9	463.8	394.7	350.1	321.0
62.5°	536.0	602.0	677.3	677.3	586.6	536.0	483.8	388.5	331.7	296.4	282.6
65°	465.3	512.9	566.7	560.5	483.8	439.2	397.8	321.0	278.0	253.4	239.6
67.5°	396.2	433.1	468.4	446.9	391.6	353.2	314.8	259.5	230.4	213.5	195.0
70°	333.3	362.4	380.9	360.9	305.6	273.4	245.7	208.9	185.8	164.3	153.6
72.5°	279.5	291.8	297.9	273.4	227.3	208.9	188.9	162.8	142.8	132.1	129.0
75°	218.1	228.8	224.2	205.8	167.4	153.6	138.2	119.8	115.2	109.0	106.0
77.5°	170.5	170.5	162.8	145.9	119.8	109.0	102.9	93.7	89.1	87.5	84.5
80°	121.3	119.8	115.2	96.8	81.4	75.3	75.3	69.1	67.6	64.5	64.5
82.5°	79.9	79.9	73.7	58.4	53.8	52.2	50.7	47.6	47.6	46.1	46.1
85°	47.6	44.5	36.9	32.3	30.7	30.7	29.2	27.6	29.2	27.6	27.6
87.5°	21.5	16.9	12.3	12.3	12.3	12.3	12.3	12.3	12.3	12.3	12.3
90°	0.4	1.4	2.8	3.6	4.3	4.8	5.3	7.1	9.6	11.7	12.1
92.5°	5.3	7.5	10.3	12.1	14.9	16.8	18.8	28.4	41.9	54.0	54.7
95°	12.4	13.9	17.4	20.6	26.3	30.6	34.8	51.2	82.1	123.3	139.3
97.5°	18.5	20.6	24.5	29.1	35.5	40.3	45.1	66.1	109.1	175.5	227.1
100°	27.4	28.4	31.6	37.3	44.4	49.4	54.4	73.2	116.6	193.3	280.7
102.5°	35.5	36.2	39.4	45.1	52.6	57.6	62.5	79.6	116.9	186.6	282.5
105°	43.4	44.8	47.3	52.6	60.4	65.4	70.4	87.1	118.7	177.3	263.3
107.5°	51.9	52.9	55.4	60.4	68.2	73.2	78.2	94.5	122.6	172.3	245.5
110°	60.4	61.8	64.0	68.6	76.0	81.2	86.3	102.0	127.6	170.9	233.5

TEST NUMBER: P1009690

CATALOG NUMBER: S122RDIP-B1005D330UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	68.2	69.6	72.1	76.4	83.5	88.8	94.2	109.1	132.9	171.3	225.6
115°	76.4	78.2	80.3	84.6	91.7	96.5	101.3	116.6	138.2	172.7	220.3
117.5°	84.9	86.3	88.5	92.4	99.1	104.1	109.1	123.3	143.9	174.8	217.5
120°	92.7	94.2	96.3	99.5	106.6	111.6	116.6	130.4	149.6	177.0	215.0
122.5°	100.2	101.3	103.4	107.0	114.1	119.2	124.4	137.2	154.6	179.4	213.6
125°	106.6	107.7	109.8	114.1	121.2	126.2	131.1	143.9	159.9	181.9	211.8
127.5°	111.9	113.4	116.2	120.8	127.6	132.8	137.9	150.3	164.9	184.4	210.7
130°	116.6	118.0	121.5	126.5	133.6	138.6	143.6	156.0	169.5	187.3	210.0
132.5°	120.8	122.6	126.5	131.8	139.3	144.2	149.2	161.0	174.1	190.1	209.7
135°	125.1	126.5	130.8	136.1	144.3	149.2	154.2	165.6	178.0	192.2	209.3
137.5°	129.0	130.8	135.0	140.7	148.9	153.5	158.1	169.5	181.2	194.4	209.3
140°	133.6	135.0	139.3	145.0	152.8	157.4	162.0	172.7	183.7	195.8	208.9
142.5°	138.2	139.3	143.2	148.9	156.4	160.6	164.9	175.2	185.8	196.9	208.9
145°	142.8	144.3	147.8	153.2	160.3	164.2	168.1	177.7	187.6	197.6	208.2
147.5°	147.8	148.9	152.4	157.4	163.5	167.0	170.6	179.8	188.7	197.9	207.2
150°	152.8	153.9	156.7	161.3	166.7	169.9	173.1	181.2	189.4	197.6	206.1
152.5°	157.8	158.1	161.0	164.9	169.9	172.7	175.5	182.6	189.8	196.9	204.3
155°	162.4	162.7	164.9	168.8	172.7	175.4	178.0	184.1	190.1	196.2	202.2
157.5°	166.3	166.7	168.4	172.0	175.2	177.5	179.8	185.1	190.1	194.7	200.1
160°	170.2	170.6	172.0	174.8	177.7	179.6	181.6	185.8	190.1	193.7	197.9
162.5°	174.1	173.8	175.2	177.3	179.8	181.2	182.6	186.2	189.8	192.6	196.2
165°	177.0	176.6	177.3	179.4	181.2	182.3	183.4	186.6	189.0	191.2	193.7
167.5°	179.4	179.1	179.8	181.2	182.6	183.4	184.1	186.6	188.7	189.8	191.5
170°	181.9	181.2	181.6	182.6	183.4	183.9	184.4	186.2	188.0	188.7	189.8
172.5°	183.4	183.0	182.6	183.7	184.1	184.4	184.8	185.8	186.9	187.3	187.6
175°	184.4	184.1	183.7	184.4	184.4	184.6	184.8	185.5	186.2	185.8	186.2
177.5°	185.1	184.4	184.1	184.8	184.8	184.8	184.8	185.1	185.8	185.1	184.8
180°	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8

TEST NUMBER: P1009690

CATALOG NUMBER: S122RDIP-B1005D330UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9
2.5°	2288.2	2291.3	2295.9	2317.4	2320.5	2326.6	2323.6	2323.6	2325.1	2322.0	2323.6
5°	2386.5	2391.1	2414.2	2440.3	2446.4	2440.3	2447.9	2458.7	2458.7	2458.7	2455.6
7.5°	2478.7	2495.6	2521.7	2560.1	2567.7	2575.4	2589.2	2580.0	2583.1	2596.9	2592.3
10°	2567.7	2592.3	2621.5	2653.7	2670.6	2681.4	2687.5	2701.3	2733.6	2696.7	2710.6
12.5°	2652.2	2687.5	2718.2	2753.6	2765.8	2779.7	2784.3	2796.6	2796.6	2795.0	2805.8
15°	2707.5	2739.7	2767.4	2790.4	2793.5	2790.4	2787.3	2788.9	2793.5	2775.1	2785.8
17.5°	2719.8	2722.8	2732.1	2722.8	2724.4	2692.1	2673.7	2669.1	2626.1	2627.6	2663.0
20°	2659.9	2607.7	2593.8	2543.2	2512.4	2429.5	2426.4	2403.4	2312.8	2340.4	2334.3
22.5°	2495.6	2406.5	2288.2	2229.9	2200.7	2113.2	2045.6	1998.0	1965.7	1933.5	1919.7
25°	2279.0	2134.7	1967.3	1852.1	1835.2	1753.8	1629.4	1571.0	1501.9	1480.4	1517.3
27.5°	1999.5	1812.2	1623.3	1446.7	1414.4	1340.7	1277.7	1236.3	1156.4	1151.8	1154.9
30°	1620.2	1431.3	1273.1	1157.9	1078.1	1044.3	1002.8	972.1	939.9	952.2	955.2
32.5°	1331.5	1151.8	1004.4	942.9	906.1	884.6	849.3	829.3	815.5	810.9	809.3
35°	1058.1	938.3	872.3	812.4	790.9	775.5	749.4	740.2	727.9	729.5	729.5
37.5°	906.1	806.3	757.1	726.4	706.4	698.8	681.9	672.6	665.0	661.9	666.5
40°	781.7	712.6	681.9	654.2	637.3	634.3	625.0	614.3	605.1	606.6	611.2
42.5°	691.1	651.1	614.3	592.8	580.5	575.9	568.2	560.5	560.5	555.9	554.4
45°	618.9	586.6	555.9	536.0	528.3	522.1	512.9	511.4	505.3	506.8	508.3
47.5°	554.4	528.3	505.3	485.3	477.6	476.1	466.9	460.7	460.7	459.2	457.6
50°	496.0	469.9	450.0	439.2	428.5	425.4	423.9	422.3	419.3	419.3	420.8
52.5°	448.4	422.3	407.0	397.8	391.6	388.5	388.5	387.0	387.0	387.0	385.5
55°	396.2	374.7	362.4	359.4	356.3	354.8	353.2	350.1	348.6	351.7	348.6
57.5°	347.1	339.4	328.6	325.6	317.9	317.9	313.3	310.2	307.1	310.2	310.2
60°	308.7	297.9	291.8	282.6	276.4	270.3	262.6	261.1	258.0	256.5	254.9
62.5°	268.8	259.5	244.2	230.4	221.1	215.0	211.9	210.4	210.4	208.9	208.9
65°	224.2	202.7	195.0	190.4	188.9	187.4	184.3	182.8	184.3	182.8	184.3
67.5°	175.1	172.0	167.4	164.3	162.8	161.3	161.3	159.7	159.7	159.7	159.7
70°	152.0	144.4	142.8	139.8	139.8	138.2	138.2	138.2	138.2	136.7	139.8
72.5°	125.9	121.3	119.8	118.3	118.3	118.3	116.7	116.7	116.7	115.2	116.7
75°	102.9	101.4	98.3	98.3	96.8	98.3	96.8	96.8	95.2	96.8	96.8
77.5°	82.9	81.4	79.9	79.9	78.3	78.3	78.3	78.3	78.3	78.3	79.9
80°	63.0	61.4	59.9	61.4	59.9	61.4	59.9	59.9	61.4	59.9	59.9
82.5°	46.1	44.5	44.5	43.0	43.0	43.0	43.0	43.0	43.0	43.0	43.0
85°	27.6	26.1	26.1	27.6	26.1	27.6	26.1	26.1	26.1	27.6	27.6
87.5°	12.3	13.8	12.3	12.3	12.3	12.3	12.3	12.3	12.3	12.3	13.8
90°	11.7	11.4	10.7	11.4	11.6	11.7	11.7	11.7	11.7	11.7	11.7
92.5°	45.8	35.9	30.6	26.7	25.2	23.8	23.5	22.0	22.4	21.7	22.4
95°	121.9	93.1	71.4	56.5	52.6	48.7	44.1	41.2	40.2	40.5	40.2
97.5°	228.8	190.5	152.1	116.2	105.6	94.9	81.0	73.9	70.0	67.9	70.0
100°	331.9	324.4	280.4	231.7	210.2	188.7	159.2	143.9	133.6	127.2	133.6
102.5°	370.3	412.2	410.8	378.4	355.3	332.2	299.6	270.8	257.3	248.0	257.3
105°	357.8	431.7	471.9	476.5	470.6	464.8	442.8	420.7	405.4	400.5	405.4
107.5°	331.5	410.8	470.5	505.3	512.4	519.5	519.2	516.0	511.3	503.2	511.3
110°	307.0	382.0	445.6	491.1	505.6	520.2	535.5	542.3	545.5	545.1	545.5

TEST NUMBER: P1009690

CATALOG NUMBER: S122RDIP-B1005D330UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	290.0	355.7	416.1	465.5	482.8	500.0	522.7	535.2	541.9	544.4	541.9
115°	276.5	335.1	389.8	436.4	454.7	473.0	498.2	514.5	523.8	527.0	523.8
117.5°	267.2	318.0	367.1	410.4	427.8	445.2	471.2	488.6	498.2	500.7	498.2
120°	260.1	306.0	350.0	387.7	403.8	420.0	444.9	461.6	471.9	475.5	471.9
122.5°	254.1	296.4	335.8	371.0	385.2	399.4	421.1	437.4	446.3	449.2	446.3
125°	248.4	287.1	323.7	355.0	368.3	381.6	402.3	415.8	424.6	427.5	424.6
127.5°	243.1	277.9	311.6	341.5	354.0	366.4	384.5	397.3	405.1	407.2	405.1
130°	237.7	269.0	299.6	327.6	339.4	351.1	368.5	380.6	387.7	390.5	387.7
132.5°	233.5	260.5	288.2	313.4	324.2	335.1	352.1	364.2	370.6	373.1	370.6
135°	229.6	252.7	276.1	299.6	309.6	319.5	334.7	346.5	352.9	354.3	352.9
137.5°	226.7	246.3	266.5	285.7	294.6	303.5	318.0	328.3	334.0	336.2	334.0
140°	224.2	240.2	257.3	273.6	281.5	289.3	300.6	309.9	315.2	317.3	315.2
142.5°	221.7	235.2	249.1	262.6	268.8	275.0	285.7	293.9	298.5	298.5	298.5
145°	219.6	230.6	242.3	253.4	258.6	263.7	272.2	278.2	281.8	282.9	281.8
147.5°	217.5	227.1	236.7	245.5	249.4	253.4	260.8	265.8	268.3	269.0	268.3
150°	214.6	223.2	231.0	238.4	241.6	244.8	250.2	254.4	256.6	256.9	256.6
152.5°	212.1	219.2	226.4	232.4	235.0	237.7	241.6	245.2	246.6	246.6	246.6
155°	208.9	215.7	221.4	226.7	228.6	230.6	234.5	237.0	238.4	237.7	238.4
157.5°	206.1	211.4	216.4	221.0	222.6	224.2	227.1	229.2	229.9	229.9	229.9
160°	202.9	207.5	211.4	215.3	216.6	217.8	220.3	222.1	222.4	222.4	222.4
162.5°	200.1	203.6	206.8	210.0	210.9	211.8	214.3	215.3	215.7	215.3	215.7
165°	196.9	199.7	202.2	204.7	205.4	206.1	207.5	208.9	208.9	208.6	208.9
167.5°	193.7	195.8	197.9	199.7	200.4	201.1	201.8	202.5	202.5	202.2	202.5
170°	191.2	193.0	194.0	195.4	195.8	196.2	196.5	197.6	197.2	196.5	197.2
172.5°	188.7	189.8	190.5	191.5	191.7	191.9	192.2	192.6	192.2	191.9	192.2
175°	186.6	187.6	188.0	188.3	188.5	188.7	188.7	189.0	188.7	188.0	188.7
177.5°	185.1	185.8	185.8	186.2	186.2	186.2	186.2	186.2	185.8	185.1	185.8
180°	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8

TEST NUMBER: P1009690

CATALOG NUMBER: S122RDIP-B1005D330UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9
2.5°	2329.7	2318.9	2315.9	2318.9	2315.9	2317.4	2306.7	2266.7	2277.5	2260.6	2269.8
5°	2461.8	2452.6	2432.6	2429.5	2426.4	2423.4	2408.0	2372.7	2358.9	2335.8	2334.3
7.5°	2587.7	2587.7	2572.3	2561.6	2547.8	2537.0	2517.1	2464.8	2443.3	2415.7	2400.3
10°	2712.1	2672.2	2689.1	2678.3	2644.5	2638.4	2601.5	2570.8	2529.3	2501.7	2477.1
12.5°	2801.2	2788.9	2773.5	2764.3	2755.1	2735.1	2710.6	2632.2	2610.7	2555.4	2527.8
15°	2798.1	2790.4	2795.0	2795.0	2792.0	2787.3	2767.4	2710.6	2673.7	2619.9	2572.3
17.5°	2647.6	2667.6	2687.5	2701.3	2732.1	2745.9	2764.3	2730.5	2707.5	2661.4	2610.7
20°	2385.0	2434.1	2492.5	2504.8	2532.4	2613.8	2650.7	2679.8	2689.1	2673.7	2632.2
22.5°	2019.5	2060.9	2202.2	2199.2	2239.1	2335.8	2443.3	2530.9	2600.0	2638.4	2623.0
25°	1581.8	1640.2	1715.4	1772.2	1902.8	2047.1	2180.7	2320.5	2440.3	2546.2	2572.3
27.5°	1196.3	1273.1	1333.0	1408.3	1474.3	1644.8	1816.8	2034.8	2174.6	2375.8	2480.2
30°	967.5	1002.8	1062.7	1098.0	1130.3	1260.8	1455.9	1670.9	1916.6	2148.5	2328.2
32.5°	826.2	850.8	895.3	910.7	944.5	1032.0	1154.9	1351.4	1604.8	1885.9	2122.4
35°	741.8	767.9	777.1	790.9	818.5	873.8	958.3	1101.1	1329.9	1604.8	1887.4
37.5°	669.6	683.4	709.5	718.7	727.9	769.4	826.2	926.0	1078.1	1303.8	1617.1
40°	618.9	626.6	640.4	648.1	654.2	683.4	734.1	801.6	913.8	1085.8	1374.5
42.5°	565.1	574.4	583.6	592.8	600.5	623.5	654.2	718.7	794.0	924.5	1133.4
45°	512.9	519.1	529.8	536.0	546.7	565.1	592.8	637.3	704.9	787.8	956.8
47.5°	465.3	473.0	477.6	485.3	493.0	512.9	539.0	568.2	623.5	704.9	827.8
50°	422.3	431.5	437.7	439.2	445.4	463.8	485.3	517.5	552.9	615.8	723.3
52.5°	391.6	393.1	397.8	403.9	402.4	413.1	433.1	457.6	494.5	545.2	623.5
55°	356.3	360.9	364.0	365.5	365.5	374.7	385.5	408.5	437.7	479.1	545.2
57.5°	311.8	316.4	325.6	328.6	333.3	337.9	342.5	357.8	382.4	422.3	476.1
60°	265.7	268.8	278.0	284.1	287.2	299.5	305.6	317.9	331.7	360.9	411.6
62.5°	213.5	216.5	221.1	227.3	233.4	251.9	267.2	279.5	290.3	310.2	351.7
65°	185.8	187.4	190.4	192.0	193.5	201.2	215.0	231.9	251.9	267.2	291.8
67.5°	161.3	162.8	164.3	167.4	168.9	170.5	176.6	181.2	201.2	222.7	241.1
70°	138.2	141.3	142.8	142.8	144.4	147.4	150.5	156.6	162.8	173.5	196.6
72.5°	116.7	118.3	121.3	121.3	121.3	124.4	127.5	130.5	133.6	139.8	149.0
75°	96.8	99.8	99.8	99.8	101.4	101.4	104.4	107.5	110.6	115.2	118.3
77.5°	79.9	79.9	79.9	79.9	81.4	81.4	82.9	86.0	87.5	89.1	92.1
80°	59.9	61.4	61.4	61.4	63.0	63.0	63.0	66.0	67.6	67.6	70.6
82.5°	44.5	44.5	44.5	46.1	44.5	46.1	46.1	47.6	46.1	47.6	49.1
85°	27.6	27.6	27.6	29.2	29.2	29.2	29.2	29.2	29.2	29.2	30.7
87.5°	13.8	13.8	13.8	13.8	13.8	13.8	13.8	13.8	15.4	13.8	13.8
90°	11.7	11.7	11.7	11.6	11.4	10.7	11.4	11.7	12.1	11.7	9.6
92.5°	22.0	23.5	23.8	25.2	26.7	30.6	35.9	45.8	54.7	54.0	41.9
95°	41.2	44.1	48.7	52.6	56.5	71.4	93.1	121.9	139.3	123.3	82.1
97.5°	73.9	81.0	94.9	105.6	116.2	152.1	190.5	228.8	227.1	175.5	109.1
100°	143.9	159.2	188.7	210.2	231.7	280.4	324.4	331.9	280.7	193.3	116.6
102.5°	270.8	299.6	332.2	355.3	378.4	410.8	412.2	370.3	282.5	186.6	116.9
105°	420.7	442.8	464.8	470.6	476.5	471.9	431.7	357.8	263.3	177.3	118.7
107.5°	516.0	519.2	519.5	512.4	505.3	470.5	410.8	331.5	245.5	172.3	122.6
110°	542.3	535.5	520.2	505.6	491.1	445.6	382.0	307.0	233.5	170.9	127.6

TEST NUMBER: P1009690

CATALOG NUMBER: S122RDIP-B1005D330UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	535.2	522.7	500.0	482.8	465.5	416.1	355.7	290.0	225.6	171.3	132.9
115°	514.5	498.2	473.0	454.7	436.4	389.8	335.1	276.5	220.3	172.7	138.2
117.5°	488.6	471.2	445.2	427.8	410.4	367.1	318.0	267.2	217.5	174.8	143.9
120°	461.6	444.9	420.0	403.8	387.7	350.0	306.0	260.1	215.0	177.0	149.6
122.5°	437.4	421.1	399.4	385.2	371.0	335.8	296.4	254.1	213.6	179.4	154.6
125°	415.8	402.3	381.6	368.3	355.0	323.7	287.1	248.4	211.8	181.9	159.9
127.5°	397.3	384.5	366.4	354.0	341.5	311.6	277.9	243.1	210.7	184.4	164.9
130°	380.6	368.5	351.1	339.4	327.6	299.6	269.0	237.7	210.0	187.3	169.5
132.5°	364.2	352.1	335.1	324.2	313.4	288.2	260.5	233.5	209.7	190.1	174.1
135°	346.5	334.7	319.5	309.6	299.6	276.1	252.7	229.6	209.3	192.2	178.0
137.5°	328.3	318.0	303.5	294.6	285.7	266.5	246.3	226.7	209.3	194.4	181.2
140°	309.9	300.6	289.3	281.5	273.6	257.3	240.2	224.2	208.9	195.8	183.7
142.5°	293.9	285.7	275.0	268.8	262.6	249.1	235.2	221.7	208.9	196.9	185.8
145°	278.2	272.2	263.7	258.6	253.4	242.3	230.6	219.6	208.2	197.6	187.6
147.5°	265.8	260.8	253.4	249.4	245.5	236.7	227.1	217.5	207.2	197.9	188.7
150°	254.4	250.2	244.8	241.6	238.4	231.0	223.2	214.6	206.1	197.6	189.4
152.5°	245.2	241.6	237.7	235.0	232.4	226.4	219.2	212.1	204.3	196.9	189.8
155°	237.0	234.5	230.6	228.6	226.7	221.4	215.7	208.9	202.2	196.2	190.1
157.5°	229.2	227.1	224.2	222.6	221.0	216.4	211.4	206.1	200.1	194.7	190.1
160°	222.1	220.3	217.8	216.6	215.3	211.4	207.5	202.9	197.9	193.7	190.1
162.5°	215.3	214.3	211.8	210.9	210.0	206.8	203.6	200.1	196.2	192.6	189.8
165°	208.9	207.5	206.1	205.4	204.7	202.2	199.7	196.9	193.7	191.2	189.0
167.5°	202.5	201.8	201.1	200.4	199.7	197.9	195.8	193.7	191.5	189.8	188.7
170°	197.6	196.5	196.2	195.8	195.4	194.0	193.0	191.2	189.8	188.7	188.0
172.5°	192.6	192.2	191.9	191.7	191.5	190.5	189.8	188.7	187.6	187.3	186.9
175°	189.0	188.7	188.7	188.5	188.3	188.0	187.6	186.6	186.2	185.8	186.2
177.5°	186.2	186.2	186.2	186.2	186.2	185.8	185.8	185.1	184.8	185.1	185.8
180°	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8

TEST NUMBER: P1009690

CATALOG NUMBER: S122RDIP-B1005D330UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9
2.5°	2256.0	2248.3	2248.3	2243.7	2243.7	2219.1	2219.1	2226.8	2217.6	2206.8	2191.5
5°	2314.3	2297.4	2292.8	2286.7	2266.7	2236.0	2223.7	2219.1	2200.7	2177.7	2151.6
7.5°	2369.6	2342.0	2328.2	2314.3	2288.2	2245.2	2220.7	2203.8	2176.1	2140.8	2107.0
10°	2423.4	2388.1	2352.7	2335.8	2299.0	2245.2	2209.9	2182.3	2142.3	2094.7	2047.1
12.5°	2472.5	2398.8	2392.7	2358.9	2305.1	2243.7	2189.9	2150.0	2099.3	2044.1	1988.8
15°	2515.5	2440.3	2403.4	2372.7	2302.1	2225.3	2168.4	2119.3	2051.7	1988.8	1921.2
17.5°	2537.0	2455.6	2431.1	2380.4	2308.2	2208.4	2131.6	2071.7	1998.0	1922.7	1845.9
20°	2558.5	2463.3	2423.4	2388.1	2289.8	2176.1	2090.1	2021.0	1939.6	1850.6	1766.1
22.5°	2569.3	2463.3	2415.7	2366.6	2271.3	2140.8	2039.4	1958.1	1862.8	1772.2	1670.9
25°	2550.8	2454.1	2397.3	2346.6	2239.1	2097.8	1981.1	1888.9	1787.6	1684.7	1581.8
27.5°	2504.8	2432.6	2366.6	2314.3	2194.6	2042.5	1919.7	1815.2	1710.8	1595.6	1491.2
30°	2418.8	2386.5	2334.3	2275.9	2145.4	1993.4	1847.5	1740.0	1624.8	1509.6	1400.6
32.5°	2285.2	2312.8	2279.0	2228.3	2087.1	1925.8	1770.7	1661.7	1535.7	1411.3	1311.5
35°	2122.4	2220.7	2202.2	2166.9	2025.6	1853.6	1698.5	1566.4	1440.5	1314.6	1214.8
37.5°	1944.2	2093.2	2108.6	2087.1	1955.0	1779.9	1609.4	1480.4	1351.4	1224.0	1122.6
40°	1700.0	1928.9	1978.0	1987.2	1881.3	1690.8	1512.7	1386.8	1259.3	1134.9	1012.0
42.5°	1475.8	1764.5	1826.0	1864.4	1787.6	1603.3	1423.6	1283.9	1157.9	1045.8	923.0
45°	1265.4	1566.4	1666.3	1715.4	1681.6	1503.5	1317.7	1187.1	1071.9	969.0	850.8
47.5°	1048.9	1351.4	1491.2	1569.5	1569.5	1402.1	1216.3	1087.3	976.7	889.2	784.8
50°	904.5	1156.4	1300.8	1403.7	1431.3	1299.2	1124.2	998.2	893.8	798.6	718.7
52.5°	770.9	996.7	1116.5	1224.0	1303.8	1188.7	1021.3	907.6	804.7	715.6	652.7
55°	666.5	835.4	944.5	1062.7	1151.8	1076.5	921.4	810.9	721.8	648.1	594.3
57.5°	566.7	714.1	803.2	907.6	1002.8	946.0	821.6	726.4	648.1	583.6	536.0
60°	482.2	602.0	671.1	752.5	870.8	830.8	727.9	640.4	577.4	519.1	479.1
62.5°	410.0	505.3	563.6	622.0	729.5	711.0	631.2	563.6	509.9	460.7	426.9
65°	336.3	414.6	460.7	511.4	597.4	605.1	540.6	493.0	443.8	400.8	370.1
67.5°	271.8	333.3	374.7	417.7	486.8	508.3	463.8	423.9	382.4	347.1	319.4
70°	219.6	262.6	293.3	327.1	383.9	410.0	387.0	359.4	325.6	296.4	271.8
72.5°	173.5	201.2	219.6	245.7	291.8	317.9	316.4	291.8	267.2	247.3	227.3
75°	127.5	149.0	164.3	181.2	218.1	242.6	248.8	238.0	213.5	198.1	182.8
77.5°	96.8	109.0	116.7	129.0	155.1	176.6	185.8	182.8	165.9	153.6	142.8
80°	73.7	76.8	79.9	84.5	106.0	125.9	132.1	130.5	121.3	116.7	104.4
82.5°	52.2	53.8	55.3	56.8	64.5	81.4	87.5	90.6	82.9	78.3	67.6
85°	30.7	32.3	32.3	35.3	36.9	41.5	52.2	52.2	50.7	44.5	43.0
87.5°	15.4	15.4	13.8	13.8	15.4	16.9	20.0	23.0	20.0	18.4	16.9
90°	7.1	5.3	4.8	4.3	3.6	2.8	1.4	0.4	1.4	2.8	3.6
92.5°	28.4	18.8	16.8	14.9	12.1	10.3	7.5	5.3	7.5	10.3	12.1
95°	51.2	34.8	30.6	26.3	20.6	17.4	13.9	12.4	13.9	17.4	20.6
97.5°	66.1	45.1	40.3	35.5	29.1	24.5	20.6	18.5	20.6	24.5	29.1
100°	73.2	54.4	49.4	44.4	37.3	31.6	28.4	27.4	28.4	31.6	37.3
102.5°	79.6	62.5	57.6	52.6	45.1	39.4	36.2	35.5	36.2	39.4	45.1
105°	87.1	70.4	65.4	60.4	52.6	47.3	44.8	43.4	44.8	47.3	52.6
107.5°	94.5	78.2	73.2	68.2	60.4	55.4	52.9	51.9	52.9	55.4	60.4
110°	102.0	86.3	81.2	76.0	68.6	64.0	61.8	60.4	61.8	64.0	68.6

TEST NUMBER: P1009690

CATALOG NUMBER: S122RDIP-B1005D330UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	109.1	94.2	88.8	83.5	76.4	72.1	69.6	68.2	69.6	72.1	76.4
115°	116.6	101.3	96.5	91.7	84.6	80.3	78.2	76.4	78.2	80.3	84.6
117.5°	123.3	109.1	104.1	99.1	92.4	88.5	86.3	84.9	86.3	88.5	92.4
120°	130.4	116.6	111.6	106.6	99.5	96.3	94.2	92.7	94.2	96.3	99.5
122.5°	137.2	124.4	119.2	114.1	107.0	103.4	101.3	100.2	101.3	103.4	107.0
125°	143.9	131.1	126.2	121.2	114.1	109.8	107.7	106.6	107.7	109.8	114.1
127.5°	150.3	137.9	132.8	127.6	120.8	116.2	113.4	111.9	113.4	116.2	120.8
130°	156.0	143.6	138.6	133.6	126.5	121.5	118.0	116.6	118.0	121.5	126.5
132.5°	161.0	149.2	144.2	139.3	131.8	126.5	122.6	120.8	122.6	126.5	131.8
135°	165.6	154.2	149.2	144.3	136.1	130.8	126.5	125.1	126.5	130.8	136.1
137.5°	169.5	158.1	153.5	148.9	140.7	135.0	130.8	129.0	130.8	135.0	140.7
140°	172.7	162.0	157.4	152.8	145.0	139.3	135.0	133.6	135.0	139.3	145.0
142.5°	175.2	164.9	160.6	156.4	148.9	143.2	139.3	138.2	139.3	143.2	148.9
145°	177.7	168.1	164.2	160.3	153.2	147.8	144.3	142.8	144.3	147.8	153.2
147.5°	179.8	170.6	167.0	163.5	157.4	152.4	148.9	147.8	148.9	152.4	157.4
150°	181.2	173.1	169.9	166.7	161.3	156.7	153.9	152.8	153.9	156.7	161.3
152.5°	182.6	175.5	172.7	169.9	164.9	161.0	158.1	157.8	158.1	161.0	164.9
155°	184.1	178.0	175.4	172.7	168.8	164.9	162.7	162.4	162.7	164.9	168.8
157.5°	185.1	179.8	177.5	175.2	172.0	168.4	166.7	166.3	166.7	168.4	172.0
160°	185.8	181.6	179.6	177.7	174.8	172.0	170.6	170.2	170.6	172.0	174.8
162.5°	186.2	182.6	181.2	179.8	177.3	175.2	173.8	174.1	173.8	175.2	177.3
165°	186.6	183.4	182.3	181.2	179.4	177.3	176.6	177.0	176.6	177.3	179.4
167.5°	186.6	184.1	183.4	182.6	181.2	179.8	179.1	179.4	179.1	179.8	181.2
170°	186.2	184.4	183.9	183.4	182.6	181.6	181.2	181.9	181.2	181.6	182.6
172.5°	185.8	184.8	184.4	184.1	183.7	182.6	183.0	183.4	183.0	182.6	183.7
175°	185.5	184.8	184.6	184.4	184.4	183.7	184.1	184.4	184.1	183.7	184.4
177.5°	185.1	184.8	184.8	184.8	184.8	184.1	184.4	185.1	184.4	184.1	184.8
180°	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8

TEST NUMBER: P1009690

CATALOG NUMBER: S122RDIP-B1005D330UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9
2.5°	2185.3	2186.9	2191.5	2177.7	2156.2	2146.9	2119.3	2114.7	2110.1	2110.1	2114.7
5°	2136.2	2130.1	2131.6	2105.5	2074.8	2056.3	2017.9	2024.1	2004.1	1991.8	1994.9
7.5°	2082.4	2065.6	2064.0	2030.2	1991.8	1958.1	1918.1	1908.9	1890.5	1869.0	1859.8
10°	2014.9	2002.6	1979.6	1941.2	1892.0	1864.4	1810.6	1778.4	1773.8	1741.5	1729.2
12.5°	1945.8	1924.3	1901.2	1847.5	1792.2	1747.7	1707.7	1672.4	1647.8	1620.2	1601.8
15°	1865.9	1839.8	1813.7	1756.9	1692.4	1647.8	1587.9	1535.7	1463.5	1406.7	1374.5
17.5°	1778.4	1749.2	1713.9	1650.9	1587.9	1526.5	1415.9	1354.5	1303.8	1270.0	1250.1
20°	1687.8	1655.5	1620.2	1557.2	1448.2	1340.7	1279.3	1231.7	1200.9	1167.2	1142.6
22.5°	1592.5	1558.8	1520.4	1422.1	1306.9	1231.7	1184.0	1139.5	1095.0	1076.5	1064.3
25°	1503.5	1472.8	1423.6	1290.0	1199.4	1130.3	1076.5	1047.4	1024.3	999.8	976.7
27.5°	1411.3	1354.5	1285.4	1173.3	1116.5	1045.8	1007.4	985.9	946.0	929.1	918.4
30°	1300.8	1237.8	1171.8	1091.9	1025.9	976.7	941.4	906.1	883.0	866.1	847.7
32.5°	1188.7	1128.8	1087.3	1004.4	955.2	904.5	870.8	849.3	815.5	804.7	797.0
35°	1091.9	1041.2	1004.4	936.8	890.7	844.6	820.1	787.8	766.3	746.4	734.1
37.5°	996.7	969.0	930.7	873.8	824.7	787.8	754.0	743.3	714.1	703.4	691.1
40°	930.7	889.2	856.9	807.8	766.3	726.4	704.9	680.3	660.4	643.5	638.9
42.5°	850.8	820.1	801.6	747.9	704.9	681.9	655.8	628.1	612.8	598.9	582.0
45°	790.9	763.3	737.1	694.1	655.8	626.6	603.5	585.1	559.0	552.9	526.8
47.5°	727.9	700.3	680.3	637.3	602.0	574.4	557.5	532.9	511.4	497.6	485.3
50°	665.0	641.9	623.5	586.6	555.9	526.8	503.7	479.1	469.9	446.9	439.2
52.5°	605.1	589.7	569.8	534.4	503.7	479.1	454.6	434.6	420.8	408.5	399.3
55°	554.4	529.8	520.6	482.2	456.1	430.0	408.5	396.2	379.3	371.6	364.0
57.5°	497.6	483.8	468.4	439.2	410.0	385.5	370.1	351.7	342.5	333.3	327.1
60°	448.4	428.5	416.2	391.6	365.5	342.5	328.6	314.8	302.5	294.9	282.6
62.5°	391.6	376.3	368.6	342.5	321.0	299.5	287.2	273.4	264.1	250.3	235.0
65°	342.5	330.2	321.0	299.5	279.5	259.5	247.3	230.4	218.1	210.4	208.9
67.5°	299.5	290.3	276.4	256.5	236.5	221.1	207.3	193.5	192.0	188.9	188.9
70°	251.9	242.6	235.0	213.5	196.6	179.7	176.6	172.0	167.4	165.9	162.8
72.5°	210.4	202.7	193.5	175.1	158.2	153.6	150.5	147.4	142.8	141.3	139.8
75°	170.5	159.7	153.6	136.7	132.1	129.0	125.9	121.3	118.3	116.7	113.6
77.5°	130.5	119.8	119.8	110.6	107.5	102.9	99.8	96.8	95.2	92.1	92.1
80°	92.1	92.1	89.1	84.5	79.9	78.3	73.7	72.2	70.6	72.2	69.1
82.5°	67.6	61.4	61.4	58.4	55.3	53.8	50.7	50.7	49.1	49.1	49.1
85°	38.4	38.4	36.9	33.8	32.3	32.3	30.7	30.7	29.2	29.2	27.6
87.5°	15.4	13.8	15.4	13.8	13.8	12.3	12.3	12.3	10.8	12.3	10.8
90°	4.3	4.8	5.3	7.1	9.6	11.7	12.1	11.7	11.4	10.7	11.4
92.5°	14.9	16.8	18.8	28.4	41.9	54.0	54.7	45.8	35.9	30.6	26.7
95°	26.3	30.6	34.8	51.2	82.1	123.3	139.3	121.9	93.1	71.4	56.5
97.5°	35.5	40.3	45.1	66.1	109.1	175.5	227.1	228.8	190.5	152.1	116.2
100°	44.4	49.4	54.4	73.2	116.6	193.3	280.7	331.9	324.4	280.4	231.7
102.5°	52.6	57.6	62.5	79.6	116.9	186.6	282.5	370.3	412.2	410.8	378.4
105°	60.4	65.4	70.4	87.1	118.7	177.3	263.3	357.8	431.7	471.9	476.5
107.5°	68.2	73.2	78.2	94.5	122.6	172.3	245.5	331.5	410.8	470.5	505.3
110°	76.0	81.2	86.3	102.0	127.6	170.9	233.5	307.0	382.0	445.6	491.1

TEST NUMBER: P1009690

CATALOG NUMBER: S122RDIP-B1005D330UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	83.5	88.8	94.2	109.1	132.9	171.3	225.6	290.0	355.7	416.1	465.5
115°	91.7	96.5	101.3	116.6	138.2	172.7	220.3	276.5	335.1	389.8	436.4
117.5°	99.1	104.1	109.1	123.3	143.9	174.8	217.5	267.2	318.0	367.1	410.4
120°	106.6	111.6	116.6	130.4	149.6	177.0	215.0	260.1	306.0	350.0	387.7
122.5°	114.1	119.2	124.4	137.2	154.6	179.4	213.6	254.1	296.4	335.8	371.0
125°	121.2	126.2	131.1	143.9	159.9	181.9	211.8	248.4	287.1	323.7	355.0
127.5°	127.6	132.8	137.9	150.3	164.9	184.4	210.7	243.1	277.9	311.6	341.5
130°	133.6	138.6	143.6	156.0	169.5	187.3	210.0	237.7	269.0	299.6	327.6
132.5°	139.3	144.2	149.2	161.0	174.1	190.1	209.7	233.5	260.5	288.2	313.4
135°	144.3	149.2	154.2	165.6	178.0	192.2	209.3	229.6	252.7	276.1	299.6
137.5°	148.9	153.5	158.1	169.5	181.2	194.4	209.3	226.7	246.3	266.5	285.7
140°	152.8	157.4	162.0	172.7	183.7	195.8	208.9	224.2	240.2	257.3	273.6
142.5°	156.4	160.6	164.9	175.2	185.8	196.9	208.9	221.7	235.2	249.1	262.6
145°	160.3	164.2	168.1	177.7	187.6	197.6	208.2	219.6	230.6	242.3	253.4
147.5°	163.5	167.0	170.6	179.8	188.7	197.9	207.2	217.5	227.1	236.7	245.5
150°	166.7	169.9	173.1	181.2	189.4	197.6	206.1	214.6	223.2	231.0	238.4
152.5°	169.9	172.7	175.5	182.6	189.8	196.9	204.3	212.1	219.2	226.4	232.4
155°	172.7	175.4	178.0	184.1	190.1	196.2	202.2	208.9	215.7	221.4	226.7
157.5°	175.2	177.5	179.8	185.1	190.1	194.7	200.1	206.1	211.4	216.4	221.0
160°	177.7	179.6	181.6	185.8	190.1	193.7	197.9	202.9	207.5	211.4	215.3
162.5°	179.8	181.2	182.6	186.2	189.8	192.6	196.2	200.1	203.6	206.8	210.0
165°	181.2	182.3	183.4	186.6	189.0	191.2	193.7	196.9	199.7	202.2	204.7
167.5°	182.6	183.4	184.1	186.6	188.7	189.8	191.5	193.7	195.8	197.9	199.7
170°	183.4	183.9	184.4	186.2	188.0	188.7	189.8	191.2	193.0	194.0	195.4
172.5°	184.1	184.4	184.8	185.8	186.9	187.3	187.6	188.7	189.8	190.5	191.5
175°	184.4	184.6	184.8	185.5	186.2	185.8	186.2	186.6	187.6	188.0	188.3
177.5°	184.8	184.8	184.8	185.1	185.8	185.1	184.8	185.1	185.8	185.8	186.2
180°	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8

TEST NUMBER: P1009690

CATALOG NUMBER: S122RDIP-B1005D330UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9
2.5°	2114.7	2111.6	2102.4	2105.5	2100.9	2100.9	2097.8	2097.8	2097.8	2105.5	2100.9
5°	1999.5	1988.8	1978.0	1973.4	1968.8	1964.2	1964.2	1962.7	1976.5	1973.4	1985.7
7.5°	1856.7	1853.6	1832.1	1832.1	1824.4	1821.4	1829.1	1830.6	1832.1	1835.2	1842.9
10°	1729.2	1721.5	1690.8	1693.9	1689.3	1683.2	1687.8	1684.7	1695.4	1698.5	1695.4
12.5°	1578.7	1564.9	1531.1	1514.2	1495.8	1482.0	1498.9	1486.6	1529.6	1541.9	1575.7
15°	1379.1	1353.0	1329.9	1329.9	1313.0	1300.8	1308.4	1322.3	1331.5	1345.3	1351.4
17.5°	1245.5	1234.7	1216.3	1205.5	1200.9	1196.3	1196.3	1202.5	1222.4	1220.9	1233.2
20°	1131.8	1125.7	1116.5	1102.7	1098.0	1095.0	1095.0	1095.0	1108.8	1121.1	1128.8
22.5°	1053.5	1048.9	1042.8	1024.3	1015.1	1012.0	1019.7	1024.3	1035.1	1044.3	1052.0
25°	975.2	964.4	953.7	947.5	942.9	942.9	946.0	947.5	952.2	956.8	966.0
27.5°	910.7	903.0	887.7	870.8	870.8	866.1	869.2	872.3	883.0	898.4	906.1
30°	838.5	837.0	830.8	824.7	818.5	815.5	821.6	826.2	827.8	835.4	835.4
32.5°	786.3	775.5	764.8	758.6	755.6	754.0	755.6	761.7	761.7	770.9	781.7
35°	734.1	727.9	717.2	706.4	703.4	695.7	701.8	708.0	718.7	723.3	727.9
37.5°	677.3	669.6	665.0	661.9	655.8	657.3	652.7	661.9	671.1	669.6	672.6
40°	634.3	620.4	606.6	605.1	603.5	602.0	602.0	603.5	609.7	615.8	625.0
42.5°	579.0	574.4	562.1	549.8	546.7	543.6	540.6	546.7	559.0	569.8	574.4
45°	522.1	516.0	512.9	503.7	497.6	496.0	493.0	500.6	511.4	516.0	519.1
47.5°	469.9	468.4	459.2	460.7	456.1	457.6	456.1	460.7	460.7	465.3	468.4
50°	434.6	430.0	425.4	422.3	417.7	417.7	416.2	417.7	423.9	430.0	428.5
52.5°	399.3	391.6	390.1	388.5	385.5	388.5	383.9	385.5	391.6	394.7	393.1
55°	357.8	356.3	353.2	350.1	348.6	347.1	347.1	347.1	353.2	357.8	359.4
57.5°	325.6	317.9	311.8	311.8	305.6	304.1	307.1	308.7	313.3	316.4	319.4
60°	281.0	278.0	268.8	264.1	254.9	253.4	253.4	259.5	267.2	278.0	281.0
62.5°	233.4	228.8	227.3	227.3	227.3	227.3	227.3	227.3	227.3	228.8	228.8
65°	207.3	208.9	207.3	205.8	207.3	207.3	205.8	205.8	205.8	207.3	208.9
67.5°	185.8	184.3	185.8	184.3	182.8	182.8	181.2	182.8	184.3	185.8	185.8
70°	161.3	161.3	159.7	161.3	159.7	158.2	156.6	156.6	159.7	161.3	161.3
72.5°	138.2	138.2	136.7	136.7	133.6	133.6	135.1	133.6	133.6	138.2	138.2
75°	115.2	113.6	112.1	112.1	110.6	110.6	110.6	109.0	112.1	112.1	113.6
77.5°	90.6	90.6	90.6	89.1	89.1	87.5	87.5	89.1	89.1	89.1	90.6
80°	69.1	69.1	69.1	67.6	66.0	66.0	66.0	66.0	66.0	67.6	66.0
82.5°	47.6	47.6	47.6	47.6	47.6	46.1	46.1	46.1	47.6	47.6	46.1
85°	29.2	27.6	29.2	29.2	27.6	29.2	27.6	27.6	26.1	26.1	27.6
87.5°	12.3	10.8	9.2	9.2	10.8	9.2	9.2	9.2	10.8	9.2	9.2
90°	11.6	11.7	11.7	11.7	11.7	11.7	11.7	11.7	11.7	11.7	11.6
92.5°	25.2	23.8	23.5	22.0	22.4	21.7	22.4	22.0	23.5	23.8	25.2
95°	52.6	48.7	44.1	41.2	40.2	40.5	40.2	41.2	44.1	48.7	52.6
97.5°	105.6	94.9	81.0	73.9	70.0	67.9	70.0	73.9	81.0	94.9	105.6
100°	210.2	188.7	159.2	143.9	133.6	127.2	133.6	143.9	159.2	188.7	210.2
102.5°	355.3	332.2	299.6	270.8	257.3	248.0	257.3	270.8	299.6	332.2	355.3
105°	470.6	464.8	442.8	420.7	405.4	400.5	405.4	420.7	442.8	464.8	470.6
107.5°	512.4	519.5	519.2	516.0	511.3	503.2	511.3	516.0	519.2	519.5	512.4
110°	505.6	520.2	535.5	542.3	545.5	545.1	545.5	542.3	535.5	520.2	505.6

TEST NUMBER: P1009690

CATALOG NUMBER: S122RDIP-B1005D330UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	482.8	500.0	522.7	535.2	541.9	544.4	541.9	535.2	522.7	500.0	482.8
115°	454.7	473.0	498.2	514.5	523.8	527.0	523.8	514.5	498.2	473.0	454.7
117.5°	427.8	445.2	471.2	488.6	498.2	500.7	498.2	488.6	471.2	445.2	427.8
120°	403.8	420.0	444.9	461.6	471.9	475.5	471.9	461.6	444.9	420.0	403.8
122.5°	385.2	399.4	421.1	437.4	446.3	449.2	446.3	437.4	421.1	399.4	385.2
125°	368.3	381.6	402.3	415.8	424.6	427.5	424.6	415.8	402.3	381.6	368.3
127.5°	354.0	366.4	384.5	397.3	405.1	407.2	405.1	397.3	384.5	366.4	354.0
130°	339.4	351.1	368.5	380.6	387.7	390.5	387.7	380.6	368.5	351.1	339.4
132.5°	324.2	335.1	352.1	364.2	370.6	373.1	370.6	364.2	352.1	335.1	324.2
135°	309.6	319.5	334.7	346.5	352.9	354.3	352.9	346.5	334.7	319.5	309.6
137.5°	294.6	303.5	318.0	328.3	334.0	336.2	334.0	328.3	318.0	303.5	294.6
140°	281.5	289.3	300.6	309.9	315.2	317.3	315.2	309.9	300.6	289.3	281.5
142.5°	268.8	275.0	285.7	293.9	298.5	298.5	298.5	293.9	285.7	275.0	268.8
145°	258.6	263.7	272.2	278.2	281.8	282.9	281.8	278.2	272.2	263.7	258.6
147.5°	249.4	253.4	260.8	265.8	268.3	269.0	268.3	265.8	260.8	253.4	249.4
150°	241.6	244.8	250.2	254.4	256.6	256.9	256.6	254.4	250.2	244.8	241.6
152.5°	235.0	237.7	241.6	245.2	246.6	246.6	246.6	245.2	241.6	237.7	235.0
155°	228.6	230.6	234.5	237.0	238.4	237.7	238.4	237.0	234.5	230.6	228.6
157.5°	222.6	224.2	227.1	229.2	229.9	229.9	229.9	229.2	227.1	224.2	222.6
160°	216.6	217.8	220.3	222.1	222.4	222.4	222.4	222.1	220.3	217.8	216.6
162.5°	210.9	211.8	214.3	215.3	215.7	215.3	215.7	215.3	214.3	211.8	210.9
165°	205.4	206.1	207.5	208.9	208.9	208.6	208.9	208.9	207.5	206.1	205.4
167.5°	200.4	201.1	201.8	202.5	202.5	202.2	202.5	202.5	201.8	201.1	200.4
170°	195.8	196.2	196.5	197.6	197.2	196.5	197.2	197.6	196.5	196.2	195.8
172.5°	191.7	191.9	192.2	192.6	192.2	191.9	192.2	192.6	192.2	191.9	191.7
175°	188.5	188.7	188.7	189.0	188.7	188.0	188.7	189.0	188.7	188.7	188.5
177.5°	186.2	186.2	186.2	186.2	185.8	185.1	185.8	186.2	186.2	186.2	186.2
180°	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8

TEST NUMBER: P1009690

CATALOG NUMBER: S122RDIP-B1005D330UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9	2209.9
2.5°	2105.5	2113.2	2110.1	2093.2	2110.1	2114.7	2123.9	2133.1	2139.3	2148.5	2156.2
5°	1973.4	1988.8	1998.0	1988.8	2019.5	2024.1	2045.6	2057.9	2076.3	2091.7	2103.9
7.5°	1849.0	1861.3	1879.7	1882.8	1901.2	1922.7	1953.4	1984.2	2013.3	2028.7	2042.5
10°	1715.4	1736.9	1764.5	1758.4	1786.1	1819.8	1852.1	1901.2	1925.8	1953.4	1978.0
12.5°	1581.8	1595.6	1632.5	1644.8	1684.7	1710.8	1755.3	1786.1	1847.5	1879.7	1901.2
15°	1348.4	1405.2	1451.3	1506.5	1558.8	1607.9	1647.8	1703.1	1756.9	1781.4	1816.8
17.5°	1242.4	1268.5	1296.2	1323.8	1391.4	1478.9	1549.5	1609.4	1655.5	1687.8	1729.2
20°	1131.8	1157.9	1188.7	1214.8	1256.2	1319.2	1406.7	1509.6	1564.9	1598.7	1638.6
22.5°	1053.5	1078.1	1098.0	1121.1	1153.3	1199.4	1265.4	1392.9	1466.6	1508.1	1543.4
25°	969.0	999.8	1021.3	1038.2	1064.3	1114.9	1168.7	1240.9	1372.9	1405.2	1454.3
27.5°	910.7	919.9	944.5	970.6	996.7	1024.3	1079.6	1141.0	1230.1	1300.8	1360.7
30°	841.6	864.6	887.7	898.4	921.4	961.4	995.2	1061.2	1130.3	1185.6	1257.8
32.5°	789.4	803.2	818.5	844.6	866.1	893.8	927.6	982.9	1041.2	1076.5	1131.8
35°	731.0	740.2	772.5	783.2	804.7	832.4	866.1	909.2	972.1	999.8	1039.7
37.5°	675.7	697.2	706.4	731.0	751.0	778.6	803.2	852.3	893.8	926.0	962.9
40°	632.7	641.9	658.8	680.3	697.2	718.7	749.4	784.8	829.3	855.4	887.7
42.5°	580.5	588.2	609.7	622.0	649.6	669.6	688.0	731.0	770.9	790.9	823.1
45°	523.7	542.1	555.9	580.5	595.9	620.4	643.5	674.2	711.0	734.1	752.5
47.5°	474.5	493.0	506.8	529.8	554.4	565.1	589.7	622.0	655.8	674.2	700.3
50°	434.6	440.8	466.9	477.6	503.7	525.2	542.1	569.8	606.6	617.4	638.9
52.5°	396.2	400.8	417.7	431.5	454.6	473.0	494.5	520.6	551.3	568.2	585.1
55°	362.4	365.5	373.2	388.5	403.9	426.9	446.9	471.5	497.6	516.0	531.4
57.5°	324.0	330.2	336.3	345.5	360.9	382.4	403.9	426.9	448.4	460.7	480.7
60°	279.5	288.7	299.5	310.2	321.0	336.3	360.9	382.4	402.4	413.1	428.5
62.5°	231.9	250.3	259.5	271.8	281.0	294.9	313.3	337.9	351.7	365.5	377.8
65°	208.9	210.4	211.9	224.2	241.1	254.9	271.8	290.3	311.8	321.0	330.2
67.5°	185.8	187.4	190.4	192.0	198.1	213.5	231.9	251.9	268.8	274.9	284.1
70°	162.8	162.8	168.9	170.5	172.0	173.5	188.9	208.9	224.2	231.9	242.6
72.5°	138.2	139.8	142.8	144.4	147.4	150.5	155.1	165.9	184.3	192.0	204.3
75°	113.6	115.2	116.7	118.3	122.9	124.4	129.0	135.1	142.8	152.0	159.7
77.5°	90.6	90.6	92.1	95.2	98.3	99.8	104.4	107.5	110.6	115.2	121.3
80°	67.6	69.1	69.1	72.2	72.2	73.7	75.3	79.9	82.9	86.0	89.1
82.5°	46.1	49.1	49.1	49.1	50.7	52.2	53.8	53.8	56.8	58.4	63.0
85°	27.6	29.2	29.2	29.2	27.6	30.7	30.7	32.3	32.3	32.3	33.8
87.5°	10.8	9.2	10.8	10.8	10.8	12.3	10.8	10.8	12.3	13.8	13.8
90°	11.4	10.7	11.4	11.7	12.1	11.7	9.6	7.1	5.3	4.8	4.3
92.5°	26.7	30.6	35.9	45.8	54.7	54.0	41.9	28.4	18.8	16.8	14.9
95°	56.5	71.4	93.1	121.9	139.3	123.3	82.1	51.2	34.8	30.6	26.3
97.5°	116.2	152.1	190.5	228.8	227.1	175.5	109.1	66.1	45.1	40.3	35.5
100°	231.7	280.4	324.4	331.9	280.7	193.3	116.6	73.2	54.4	49.4	44.4
102.5°	378.4	410.8	412.2	370.3	282.5	186.6	116.9	79.6	62.5	57.6	52.6
105°	476.5	471.9	431.7	357.8	263.3	177.3	118.7	87.1	70.4	65.4	60.4
107.5°	505.3	470.5	410.8	331.5	245.5	172.3	122.6	94.5	78.2	73.2	68.2
110°	491.1	445.6	382.0	307.0	233.5	170.9	127.6	102.0	86.3	81.2	76.0

TEST NUMBER: P1009690

CATALOG NUMBER: S122RDIP-B1005D330UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	465.5	416.1	355.7	290.0	225.6	171.3	132.9	109.1	94.2	88.8	83.5
115°	436.4	389.8	335.1	276.5	220.3	172.7	138.2	116.6	101.3	96.5	91.7
117.5°	410.4	367.1	318.0	267.2	217.5	174.8	143.9	123.3	109.1	104.1	99.1
120°	387.7	350.0	306.0	260.1	215.0	177.0	149.6	130.4	116.6	111.6	106.6
122.5°	371.0	335.8	296.4	254.1	213.6	179.4	154.6	137.2	124.4	119.2	114.1
125°	355.0	323.7	287.1	248.4	211.8	181.9	159.9	143.9	131.1	126.2	121.2
127.5°	341.5	311.6	277.9	243.1	210.7	184.4	164.9	150.3	137.9	132.8	127.6
130°	327.6	299.6	269.0	237.7	210.0	187.3	169.5	156.0	143.6	138.6	133.6
132.5°	313.4	288.2	260.5	233.5	209.7	190.1	174.1	161.0	149.2	144.2	139.3
135°	299.6	276.1	252.7	229.6	209.3	192.2	178.0	165.6	154.2	149.2	144.3
137.5°	285.7	266.5	246.3	226.7	209.3	194.4	181.2	169.5	158.1	153.5	148.9
140°	273.6	257.3	240.2	224.2	208.9	195.8	183.7	172.7	162.0	157.4	152.8
142.5°	262.6	249.1	235.2	221.7	208.9	196.9	185.8	175.2	164.9	160.6	156.4
145°	253.4	242.3	230.6	219.6	208.2	197.6	187.6	177.7	168.1	164.2	160.3
147.5°	245.5	236.7	227.1	217.5	207.2	197.9	188.7	179.8	170.6	167.0	163.5
150°	238.4	231.0	223.2	214.6	206.1	197.6	189.4	181.2	173.1	169.9	166.7
152.5°	232.4	226.4	219.2	212.1	204.3	196.9	189.8	182.6	175.5	172.7	169.9
155°	226.7	221.4	215.7	208.9	202.2	196.2	190.1	184.1	178.0	175.4	172.7
157.5°	221.0	216.4	211.4	206.1	200.1	194.7	190.1	185.1	179.8	177.5	175.2
160°	215.3	211.4	207.5	202.9	197.9	193.7	190.1	185.8	181.6	179.6	177.7
162.5°	210.0	206.8	203.6	200.1	196.2	192.6	189.8	186.2	182.6	181.2	179.8
165°	204.7	202.2	199.7	196.9	193.7	191.2	189.0	186.6	183.4	182.3	181.2
167.5°	199.7	197.9	195.8	193.7	191.5	189.8	188.7	186.6	184.1	183.4	182.6
170°	195.4	194.0	193.0	191.2	189.8	188.7	188.0	186.2	184.4	183.9	183.4
172.5°	191.5	190.5	189.8	188.7	187.6	187.3	186.9	185.8	184.8	184.4	184.1
175°	188.3	188.0	187.6	186.6	186.2	185.8	186.2	185.5	184.8	184.6	184.4
177.5°	186.2	185.8	185.8	185.1	184.8	185.1	185.8	185.1	184.8	184.8	184.8
180°	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8	184.8

TEST NUMBER: P1009690

CATALOG NUMBER: S122RDIP-B1005D330UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	2209.9	2209.9	2209.9	2209.9
2.5°	2170.0	2165.4	2193.0	2223.7
5°	2125.4	2133.1	2168.4	2211.4
7.5°	2079.4	2096.3	2137.7	2194.6
10°	2014.9	2045.6	2108.6	2166.9
12.5°	1951.9	1993.4	2053.3	2122.4
15°	1881.3	1927.3	2001.1	2084.0
17.5°	1802.9	1855.2	1941.2	2031.8
20°	1720.0	1789.1	1879.7	1978.0
22.5°	1627.9	1710.8	1804.5	1913.5
25°	1538.8	1629.4	1723.1	1849.0
27.5°	1451.3	1540.3	1644.8	1772.2
30°	1363.7	1445.1	1557.2	1693.9
32.5°	1270.0	1354.5	1472.8	1612.5
35°	1184.0	1268.5	1379.1	1517.3
37.5°	1091.9	1182.5	1288.5	1431.3
40°	984.4	1090.4	1193.3	1329.9
42.5°	895.3	1007.4	1107.3	1236.3
45°	824.7	930.7	1013.6	1139.5
47.5°	758.6	844.6	929.1	1045.8
50°	695.7	761.7	849.3	953.7
52.5°	631.2	688.0	763.3	861.5
55°	572.8	626.6	694.1	769.4
57.5°	519.1	557.5	625.0	692.6
60°	459.2	499.1	551.3	608.1
62.5°	408.5	439.2	488.4	536.0
65°	354.8	383.9	420.8	465.3
67.5°	305.6	331.7	360.9	396.2
70°	261.1	281.0	302.5	333.3
72.5°	213.5	235.0	254.9	279.5
75°	175.1	184.3	201.2	218.1
77.5°	135.1	147.4	156.6	170.5
80°	96.8	107.5	110.6	121.3
82.5°	64.5	70.6	76.8	79.9
85°	36.9	39.9	46.1	47.6
87.5°	13.8	15.4	18.4	21.5
90°	3.6	2.8	1.4	0.4
92.5°	12.1	10.3	7.5	5.3
95°	20.6	17.4	13.9	12.4
97.5°	29.1	24.5	20.6	18.5
100°	37.3	31.6	28.4	27.4
102.5°	45.1	39.4	36.2	35.5
105°	52.6	47.3	44.8	43.4
107.5°	60.4	55.4	52.9	51.9
110°	68.6	64.0	61.8	60.4

TEST NUMBER: P1009690

CATALOG NUMBER: S122RDIP-B1005D330UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	76.4	72.1	69.6	68.2
115°	84.6	80.3	78.2	76.4
117.5°	92.4	88.5	86.3	84.9
120°	99.5	96.3	94.2	92.7
122.5°	107.0	103.4	101.3	100.2
125°	114.1	109.8	107.7	106.6
127.5°	120.8	116.2	113.4	111.9
130°	126.5	121.5	118.0	116.6
132.5°	131.8	126.5	122.6	120.8
135°	136.1	130.8	126.5	125.1
137.5°	140.7	135.0	130.8	129.0
140°	145.0	139.3	135.0	133.6
142.5°	148.9	143.2	139.3	138.2
145°	153.2	147.8	144.3	142.8
147.5°	157.4	152.4	148.9	147.8
150°	161.3	156.7	153.9	152.8
152.5°	164.9	161.0	158.1	157.8
155°	168.8	164.9	162.7	162.4
157.5°	172.0	168.4	166.7	166.3
160°	174.8	172.0	170.6	170.2
162.5°	177.3	175.2	173.8	174.1
165°	179.4	177.3	176.6	177.0
167.5°	181.2	179.8	179.1	179.4
170°	182.6	181.6	181.2	181.9
172.5°	183.7	182.6	183.0	183.4
175°	184.4	183.7	184.1	184.4
177.5°	184.8	184.1	184.4	185.1
180°	184.8	184.8	184.8	184.8

(END OF REPORT)