

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009797

Luminaire Tested: S122RDIP-B1005D925UB50-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009797
REPORT IS A COMBINATION OF REPORTS P988013 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B1005D925UB50-4F0-XX-W2A-A1
Description: Define 2 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6824.0 lumens
Efficiency: N/A
Efficacy: 76.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009797

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1009797

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60	54	54	54
1	99	95	92	89	92	89	86	83	76	74	72	65	63	62	54	53	52	47	47	47
2	91	84	79	74	85	79	74	69	68	64	61	58	55	53	49	47	45	41	41	41
3	84	75	68	63	78	70	64	59	61	56	52	52	49	46	44	42	40	36	36	36
4	77	67	60	54	72	63	56	51	55	50	46	47	43	40	40	37	35	31	31	31
5	71	60	53	47	66	57	50	45	49	44	40	43	39	35	36	33	31	28	28	28
6	66	55	47	41	61	51	44	39	45	40	35	39	35	32	34	30	28	25	25	25
7	61	50	42	37	57	47	40	35	41	36	32	36	32	28	31	28	25	23	23	23
8	57	45	38	33	53	43	36	31	38	32	29	33	29	26	29	25	23	21	21	21
9	53	42	35	30	50	39	33	28	35	30	26	31	26	23	27	23	21	19	19	19
10	50	39	32	27	47	36	30	26	32	27	24	29	24	22	25	22	19	18	18	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	33644	33644	33644	33644
5°	33722	35735	33839	28548
10°	33352	37771	33587	23575
15°	32627	37783	33181	17710
20°	31757	31232	32448	14611
25°	30701	19515	31364	12430
30°	29353	12494	30153	10701
35°	27714	9603	28613	9158
40°	25888	8071	26993	8010
45°	23934	6870	24935	6725
50°	21933	5837	22959	5815
55°	19718	5072	20781	5006
60°	17749	3869	18689	3822
65°	15908	2912	16854	3303
70°	13880	2326	14967	2691
75°	11731	1782	12805	2035
80°	9317	1211	10020	1335
85°	6470	626	7091	661

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 30776 cd/sqm

TEST NUMBER: P1009797

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	201.6	3.0
10°-20°	562.7	8.2
20°-30°	724.2	10.6
30°-40°	687.1	10.1
40°-50°	588.8	8.6
50°-60°	448.4	6.6
60°-70°	282.8	4.1
70°-80°	141.1	2.1
80°-90°	39.5	0.6
90°-100°	69.7	1.0
100°-110°	221.4	3.2
110°-120°	378.9	5.6
120°-130°	498.3	7.3
130°-140°	559.3	8.2
140°-150°	548.5	8.0
150°-160°	460.1	6.7
160°-170°	305.1	4.5
170°-180°	106.6	1.6
0°-30°	1488.5	21.8
0°-40°	2175.6	31.9
0°-60°	3212.9	47.1
0°-90°	3676.2	53.9
90°-120°	670.0	9.8
90°-150°	2276.0	33.4
90°-180°	3148.0	46.1
0°-180°	6824.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2125	2125	2125	2125	2125	
5°	2127	2365	2134	1889	2127	202
15°	2004	2669	2038	1251	2004	564
25°	1778	1424	1817	907	1778	817
35°	1459	702	1507	669	1459	913
45°	1096	487	1142	477	1096	846
55°	740	338	780	334	740	667
65°	448	176	474	199	448	444
75°	210	93	229	106	210	227
85°	46	27	50	28	46	52
90°	1	32	1	32	1	6
95°	49	59	49	59	49	55
105°	204	211	204	211	204	216
115°	380	380	380	380	380	376
125°	553	555	553	555	553	494
135°	715	724	715	724	715	553
145°	868	878	868	878	868	543
155°	993	1000	993	1000	993	457
165°	1080	1081	1080	1081	1080	305
175°	1124	1120	1124	1120	1124	107
180°	1126	1126	1126	1126	1126	

TEST NUMBER: P1009797

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4
2.5°	2138.7	2147.6	2152.0	2157.9	2171.2	2180.1	2193.4	2196.3	2194.8	2200.8	2184.5
5°	2126.9	2146.1	2163.8	2178.6	2202.2	2217.0	2233.2	2252.4	2256.9	2279.0	2265.7
7.5°	2110.7	2138.7	2163.8	2193.4	2228.8	2248.0	2273.1	2302.7	2316.0	2342.5	2349.9
10°	2084.1	2123.9	2166.8	2197.8	2246.5	2280.5	2304.1	2351.4	2382.4	2422.3	2416.4
12.5°	2041.2	2092.9	2150.5	2202.2	2265.7	2287.9	2332.2	2380.9	2420.8	2457.8	2490.2
15°	2004.3	2063.4	2126.9	2190.4	2262.8	2304.1	2348.5	2412.0	2454.8	2519.8	2547.9
17.5°	1954.1	2029.4	2104.7	2175.6	2261.3	2308.6	2363.2	2425.3	2488.8	2550.8	2573.0
20°	1902.4	1983.6	2064.9	2160.9	2258.4	2304.1	2360.3	2437.1	2499.1	2547.9	2547.9
22.5°	1840.4	1939.3	2032.4	2123.9	2230.3	2296.8	2354.4	2444.5	2488.8	2499.1	2459.2
25°	1778.3	1877.3	1979.2	2092.9	2214.0	2273.1	2338.1	2422.3	2437.1	2395.7	2292.3
27.5°	1704.5	1815.3	1930.5	2053.1	2180.1	2253.9	2313.0	2369.1	2341.1	2230.3	2069.3
30°	1629.1	1748.8	1878.8	1995.4	2149.1	2217.0	2267.2	2283.5	2194.8	2014.6	1806.4
32.5°	1550.9	1667.6	1804.9	1945.2	2100.3	2165.3	2197.8	2155.0	1992.5	1765.0	1511.0
35°	1459.3	1590.7	1734.0	1880.2	2033.9	2082.6	2101.8	1996.9	1788.7	1494.7	1242.2
37.5°	1376.6	1508.0	1661.6	1810.8	1960.0	1986.6	1967.4	1803.4	1539.1	1248.1	1001.4
40°	1279.1	1419.4	1570.1	1737.0	1859.6	1866.9	1819.7	1607.0	1279.1	1005.8	853.7
42.5°	1189.0	1330.8	1481.4	1651.3	1744.4	1719.2	1655.7	1376.6	1067.9	867.0	744.4
45°	1095.9	1230.4	1392.8	1543.5	1609.9	1550.9	1454.9	1158.0	896.5	745.9	651.4
47.5°	1005.8	1131.4	1292.4	1437.1	1449.0	1382.5	1268.8	970.4	776.9	655.8	579.0
50°	917.2	1042.8	1193.4	1313.1	1301.3	1209.7	1081.2	843.4	675.0	579.0	515.5
52.5°	828.6	942.3	1088.6	1183.1	1132.9	1044.3	917.2	714.9	589.3	505.1	456.4
55°	740.0	846.3	971.9	1050.2	970.4	868.5	778.4	613.0	511.0	443.1	406.2
57.5°	666.1	750.3	865.5	912.8	816.8	737.0	658.7	527.3	443.1	394.4	351.5
60°	584.9	661.7	756.2	784.3	685.3	620.3	553.9	446.1	379.6	336.8	308.7
62.5°	515.5	579.0	651.4	651.4	564.2	515.5	465.3	373.7	319.0	285.1	271.8
65°	447.5	493.3	545.0	539.1	465.3	422.4	382.5	308.7	267.3	243.7	230.4
67.5°	381.1	416.5	450.5	429.8	376.6	339.7	302.8	249.6	221.6	205.3	187.6
70°	320.5	348.6	366.3	347.1	293.9	262.9	236.3	200.9	178.7	158.0	147.7
72.5°	268.8	280.6	286.5	262.9	218.6	200.9	181.7	156.6	137.4	127.0	124.1
75°	209.7	220.1	215.6	197.9	161.0	147.7	132.9	115.2	110.8	104.9	101.9
77.5°	163.9	163.9	156.6	140.3	115.2	104.9	99.0	90.1	85.7	84.2	81.2
80°	116.7	115.2	110.8	93.1	78.3	72.4	72.4	66.5	65.0	62.0	62.0
82.5°	76.8	76.8	70.9	56.1	51.7	50.2	48.7	45.8	45.8	44.3	44.3
85°	45.8	42.8	35.4	31.0	29.5	29.5	28.1	26.6	28.1	26.6	26.6
87.5°	20.7	16.2	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8
90°	1.0	3.5	6.1	8.6	11.1	12.4	14.7	19.4	24.0	28.7	33.3
92.5°	20.9	22.6	24.3	26.0	27.7	28.5	28.6	28.8	29.1	29.3	29.5
95°	49.4	51.5	53.6	55.7	57.8	58.9	59.1	59.5	60.0	60.4	60.8
97.5°	82.7	84.6	86.5	88.4	90.3	91.2	91.6	92.5	93.3	94.2	95.0
100°	120.7	122.4	124.1	125.8	127.5	128.3	128.6	129.2	129.9	130.5	131.1
102.5°	160.6	161.9	163.1	164.4	165.7	166.3	166.7	167.6	168.4	169.3	170.1
105°	204.3	204.9	205.5	206.2	206.8	207.1	207.3	207.7	208.2	208.6	209.0
107.5°	248.0	248.8	249.7	250.5	251.4	251.8	251.8	251.8	251.8	251.8	251.8
110°	289.8	291.1	292.3	293.6	294.9	295.5	295.5	295.5	295.5	295.5	295.5



TEST NUMBER: P1009797

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	335.4	336.7	337.9	339.2	340.5	341.1	341.0	340.8	340.5	340.3	340.1
115°	380.0	381.3	382.6	383.9	385.2	385.8	385.6	385.2	384.7	384.3	383.9
117.5°	424.7	426.4	428.1	429.8	431.5	432.3	431.8	430.7	429.7	428.6	427.6
120°	469.4	471.1	472.8	474.5	476.2	477.0	476.2	474.5	472.8	471.1	469.4
122.5°	510.2	512.3	514.4	516.5	518.6	519.7	519.2	518.1	517.1	516.0	515.0
125°	553.0	554.9	556.8	558.7	560.6	561.5	561.2	560.6	559.9	559.3	558.7
127.5°	594.8	597.1	599.4	601.7	604.0	605.2	604.8	603.9	603.1	602.2	601.4
130°	633.7	636.5	639.2	642.0	644.7	646.1	645.9	645.5	645.0	644.6	644.2
132.5°	677.4	679.5	681.6	683.7	685.8	686.9	687.0	687.2	687.5	687.7	687.9
135°	715.4	717.7	720.1	722.4	724.7	725.9	726.1	726.5	727.0	727.4	727.8
137.5°	757.2	759.1	761.0	762.9	764.8	765.8	766.0	766.4	766.9	767.3	767.7
140°	794.3	796.2	798.1	800.0	801.9	802.9	803.4	804.5	805.5	806.6	807.6
142.5°	832.3	834.2	836.1	838.0	839.9	840.9	841.2	841.8	842.5	843.1	843.7
145°	868.4	869.9	871.4	872.9	874.4	875.1	875.7	877.0	878.3	879.5	880.8
147.5°	900.7	902.6	904.5	906.4	908.3	909.3	909.7	910.6	911.4	912.3	913.1
150°	934.0	935.3	936.5	937.8	939.1	939.7	940.1	941.0	941.8	942.7	943.5
152.5°	963.4	964.7	965.9	967.2	968.5	969.1	969.6	970.7	971.8	972.8	973.9
155°	992.9	993.5	994.1	994.8	995.4	995.7	996.0	996.7	997.3	998.0	998.6
157.5°	1018.5	1018.9	1019.3	1019.8	1020.2	1020.4	1020.6	1021.0	1021.5	1021.9	1022.3
160°	1041.3	1041.7	1042.1	1042.6	1043.0	1043.2	1043.3	1043.5	1043.8	1044.0	1044.2
162.5°	1062.2	1062.2	1062.2	1062.2	1062.2	1062.2	1062.3	1062.5	1062.8	1063.0	1063.2
165°	1080.3	1080.1	1079.9	1079.6	1079.4	1079.3	1079.3	1079.3	1079.3	1079.3	1079.3
167.5°	1096.4	1095.8	1095.2	1094.5	1093.9	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6
170°	1108.8	1108.2	1107.5	1106.9	1106.2	1105.9	1105.8	1105.6	1105.4	1105.2	1105.0
172.5°	1117.3	1116.7	1116.1	1115.4	1114.8	1114.5	1114.4	1114.2	1113.9	1113.7	1113.5
175°	1124.0	1123.4	1122.7	1122.1	1121.4	1121.1	1120.9	1120.5	1120.0	1119.6	1119.2
177.5°	1127.8	1127.2	1126.5	1125.9	1125.2	1124.9	1124.7	1124.3	1123.8	1123.4	1123.0
180°	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9

TEST NUMBER: P1009797

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4
2.5°	2200.8	2203.7	2208.1	2228.8	2231.8	2237.7	2234.7	2234.7	2236.2	2233.2	2234.7
5°	2295.3	2299.7	2321.9	2347.0	2352.9	2347.0	2354.4	2364.7	2364.7	2364.7	2361.7
7.5°	2383.9	2400.2	2425.3	2462.2	2469.6	2477.0	2490.2	2481.4	2484.3	2497.6	2493.2
10°	2469.6	2493.2	2521.3	2552.3	2568.5	2578.9	2584.8	2598.1	2629.1	2593.6	2606.9
12.5°	2550.8	2584.8	2614.3	2648.3	2660.1	2673.4	2677.8	2689.6	2689.6	2688.2	2698.5
15°	2604.0	2635.0	2661.6	2683.7	2686.7	2683.7	2680.8	2682.3	2686.7	2669.0	2679.3
17.5°	2615.8	2618.7	2627.6	2618.7	2620.2	2589.2	2571.5	2567.1	2525.7	2527.2	2561.1
20°	2558.2	2508.0	2494.7	2445.9	2416.4	2336.6	2333.7	2311.5	2224.4	2251.0	2245.1
22.5°	2400.2	2314.5	2200.8	2144.6	2116.6	2032.4	1967.4	1921.6	1890.6	1859.6	1846.3
25°	2191.9	2053.1	1892.1	1781.3	1765.0	1686.8	1567.1	1511.0	1444.5	1423.8	1459.3
27.5°	1923.1	1742.9	1561.2	1391.3	1360.3	1289.4	1228.9	1189.0	1112.2	1107.8	1110.7
30°	1558.3	1376.6	1224.4	1113.7	1036.9	1004.4	964.5	935.0	903.9	915.7	918.7
32.5°	1280.6	1107.8	966.0	906.9	871.4	850.8	816.8	797.6	784.3	779.9	778.4
35°	1017.7	902.5	838.9	781.3	760.7	745.9	720.8	711.9	700.1	701.6	701.6
37.5°	871.4	775.4	728.2	698.6	679.4	672.0	655.8	646.9	639.5	636.6	641.0
40°	751.8	685.3	655.8	629.2	613.0	610.0	601.1	590.8	581.9	583.4	587.9
42.5°	664.7	626.3	590.8	570.1	558.3	553.9	546.5	539.1	539.1	534.7	533.2
45°	595.2	564.2	534.7	515.5	508.1	502.2	493.3	491.8	485.9	487.4	488.9
47.5°	533.2	508.1	485.9	466.7	459.4	457.9	449.0	443.1	443.1	441.6	440.2
50°	477.1	452.0	432.8	422.4	412.1	409.1	407.7	406.2	403.2	403.2	404.7
52.5°	431.3	406.2	391.4	382.5	376.6	373.7	373.7	372.2	372.2	372.2	370.7
55°	381.1	360.4	348.6	345.6	342.7	341.2	339.7	336.8	335.3	338.2	335.3
57.5°	333.8	326.4	316.1	313.1	305.7	305.7	301.3	298.4	295.4	298.4	298.4
60°	296.9	286.5	280.6	271.8	265.9	260.0	252.6	251.1	248.1	246.7	245.2
62.5°	258.5	249.6	234.8	221.6	212.7	206.8	203.8	202.4	202.4	200.9	200.9
65°	215.6	195.0	187.6	183.1	181.7	180.2	177.2	175.8	177.2	175.8	177.2
67.5°	168.4	165.4	161.0	158.0	156.6	155.1	155.1	153.6	153.6	153.6	153.6
70°	146.2	138.8	137.4	134.4	134.4	132.9	132.9	132.9	132.9	131.5	134.4
72.5°	121.1	116.7	115.2	113.7	113.7	113.7	112.3	112.3	112.3	110.8	112.3
75°	99.0	97.5	94.5	94.5	93.1	94.5	93.1	93.1	91.6	93.1	93.1
77.5°	79.8	78.3	76.8	76.8	75.3	75.3	75.3	75.3	75.3	75.3	76.8
80°	60.6	59.1	57.6	59.1	57.6	59.1	57.6	57.6	59.1	57.6	57.6
82.5°	44.3	42.8	42.8	41.4	41.4	41.4	41.4	41.4	41.4	41.4	41.4
85°	26.6	25.1	25.1	26.6	25.1	26.6	25.1	25.1	25.1	26.6	26.6
87.5°	11.8	13.3	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8	13.3
90°	32.9	32.5	32.0	31.6	31.4	31.5	31.7	31.9	32.1	32.3	32.1
92.5°	29.7	29.9	30.1	30.3	30.4	30.4	30.4	30.4	30.4	30.4	30.4
95°	60.8	60.8	60.8	60.8	60.8	60.6	60.2	59.7	59.3	58.9	59.3
97.5°	95.0	95.0	95.0	95.0	95.0	95.0	95.0	95.0	95.0	95.0	95.0
100°	131.1	131.1	131.1	131.1	131.1	131.0	130.8	130.6	130.4	130.2	130.4
102.5°	170.3	170.5	170.7	170.9	171.0	170.9	170.7	170.5	170.3	170.1	170.3
105°	209.4	209.8	210.3	210.7	210.9	210.9	210.9	210.9	210.9	210.9	210.9
107.5°	252.0	252.2	252.4	252.6	252.7	252.2	251.1	250.1	249.0	248.0	249.0
110°	295.5	295.5	295.5	295.5	295.5	295.2	294.5	293.9	293.2	292.6	293.2

TEST NUMBER: P1009797

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	339.5	338.9	338.2	337.6	337.3	337.1	336.7	336.2	335.8	335.4	335.8
115°	383.7	383.5	383.2	383.0	382.9	382.6	381.9	381.3	380.6	380.0	380.6
117.5°	427.0	426.3	425.7	425.0	424.7	424.4	423.8	423.1	422.5	421.9	422.5
120°	469.4	469.4	469.4	469.4	469.4	469.1	468.4	467.8	467.1	466.5	467.1
122.5°	514.4	513.7	513.1	512.4	512.1	511.9	511.5	511.0	510.6	510.2	510.6
125°	558.1	557.4	556.8	556.1	555.8	555.7	555.5	555.3	555.1	554.9	555.1
127.5°	600.6	599.7	598.9	598.0	597.6	597.3	596.7	596.0	595.4	594.8	595.4
130°	643.8	643.4	642.9	642.5	642.3	641.9	641.0	640.2	639.3	638.5	639.3
132.5°	686.8	685.8	684.7	683.6	683.1	682.8	682.2	681.5	680.9	680.3	680.9
135°	727.6	727.4	727.1	726.9	726.8	726.5	725.9	725.2	724.6	724.0	724.6
137.5°	767.5	767.3	767.1	766.9	766.8	766.4	765.5	764.6	763.8	762.9	763.8
140°	807.6	807.6	807.6	807.6	807.6	807.2	806.3	805.5	804.6	803.8	804.6
142.5°	843.9	844.1	844.4	844.6	844.7	844.3	843.4	842.6	841.7	840.9	841.7
145°	881.0	881.2	881.4	881.6	881.7	881.3	880.4	879.6	878.7	877.9	878.7
147.5°	913.5	913.9	914.4	914.8	915.0	914.6	913.7	912.9	912.0	911.2	912.0
150°	944.1	944.7	945.4	946.0	946.3	946.0	945.4	944.7	944.1	943.5	944.1
152.5°	974.7	975.6	976.4	977.3	977.7	977.3	976.4	975.6	974.7	973.9	974.7
155°	999.6	1000.7	1001.7	1002.8	1003.3	1003.0	1002.4	1001.7	1001.1	1000.5	1001.1
157.5°	1023.8	1025.3	1026.8	1028.3	1029.0	1028.5	1027.4	1026.3	1025.3	1024.2	1025.3
160°	1045.5	1046.7	1048.0	1049.3	1049.9	1049.5	1048.6	1047.8	1046.9	1046.1	1046.9
162.5°	1064.7	1066.1	1067.6	1069.1	1069.8	1069.3	1068.2	1067.2	1066.1	1065.1	1066.1
165°	1080.8	1082.3	1083.8	1085.3	1086.0	1085.5	1084.4	1083.3	1082.3	1081.2	1082.3
167.5°	1095.1	1096.5	1098.0	1099.5	1100.2	1099.7	1098.6	1097.6	1096.5	1095.5	1096.5
170°	1106.5	1107.9	1109.4	1110.9	1111.6	1111.0	1109.7	1108.4	1107.2	1105.9	1107.2
172.5°	1115.0	1116.5	1118.0	1119.5	1120.2	1119.6	1118.3	1117.0	1115.8	1114.5	1115.8
175°	1120.7	1122.2	1123.7	1125.2	1125.9	1125.3	1124.0	1122.7	1121.5	1120.2	1121.5
177.5°	1124.3	1125.5	1126.8	1128.1	1128.7	1128.1	1126.8	1125.5	1124.3	1123.0	1124.3
180°	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9

TEST NUMBER: P1009797

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4
2.5°	2240.6	2230.3	2227.3	2230.3	2227.3	2228.8	2218.5	2180.1	2190.4	2174.2	2183.0
5°	2367.7	2358.8	2339.6	2336.6	2333.7	2330.7	2316.0	2282.0	2268.7	2246.5	2245.1
7.5°	2488.8	2488.8	2474.0	2463.7	2450.4	2440.0	2420.8	2370.6	2349.9	2323.3	2308.6
10°	2608.4	2570.0	2586.3	2575.9	2543.4	2537.5	2502.1	2472.5	2432.6	2406.1	2382.4
12.5°	2694.1	2682.3	2667.5	2658.6	2649.8	2630.6	2606.9	2531.6	2510.9	2457.8	2431.2
15°	2691.1	2683.7	2688.2	2688.2	2685.2	2680.8	2661.6	2606.9	2571.5	2519.8	2474.0
17.5°	2546.4	2565.6	2584.8	2598.1	2627.6	2640.9	2658.6	2626.1	2604.0	2559.7	2510.9
20°	2293.8	2341.1	2397.2	2409.0	2435.6	2513.9	2549.3	2577.4	2586.3	2571.5	2531.6
22.5°	1942.3	1982.2	2118.0	2115.1	2153.5	2246.5	2349.9	2434.1	2500.6	2537.5	2522.7
25°	1521.3	1577.5	1649.8	1704.5	1830.0	1968.9	2097.4	2231.8	2347.0	2448.9	2474.0
27.5°	1150.6	1224.4	1282.0	1354.4	1417.9	1581.9	1747.3	1957.0	2091.5	2284.9	2385.4
30°	930.5	964.5	1022.1	1056.1	1087.1	1212.6	1400.2	1607.0	1843.3	2066.3	2239.2
32.5°	794.6	818.3	861.1	875.9	908.4	992.6	1110.7	1299.8	1543.5	1813.8	2041.2
35°	713.4	738.5	747.4	760.7	787.2	840.4	921.7	1059.0	1279.1	1543.5	1815.3
37.5°	644.0	657.3	682.4	691.2	700.1	740.0	794.6	890.6	1036.9	1254.0	1555.3
40°	595.2	602.6	615.9	623.3	629.2	657.3	706.0	771.0	878.8	1044.3	1321.9
42.5°	543.5	552.4	561.3	570.1	577.5	599.7	629.2	691.2	763.6	889.2	1090.0
45°	493.3	499.2	509.6	515.5	525.8	543.5	570.1	613.0	678.0	757.7	920.2
47.5°	447.5	454.9	459.4	466.7	474.1	493.3	518.4	546.5	599.7	678.0	796.1
50°	406.2	415.0	420.9	422.4	428.3	446.1	466.7	497.8	531.7	592.3	695.7
52.5°	376.6	378.1	382.5	388.5	387.0	397.3	416.5	440.2	475.6	524.3	599.7
55°	342.7	347.1	350.1	351.5	351.5	360.4	370.7	392.9	420.9	460.8	524.3
57.5°	299.8	304.3	313.1	316.1	320.5	324.9	329.4	344.1	367.8	406.2	457.9
60°	255.5	258.5	267.3	273.2	276.2	288.0	293.9	305.7	319.0	347.1	395.8
62.5°	205.3	208.3	212.7	218.6	224.5	242.2	257.0	268.8	279.2	298.4	338.2
65°	178.7	180.2	183.1	184.6	186.1	193.5	206.8	223.0	242.2	257.0	280.6
67.5°	155.1	156.6	158.0	161.0	162.5	163.9	169.9	174.3	193.5	214.2	231.9
70°	132.9	135.9	137.4	137.4	138.8	141.8	144.7	150.7	156.6	166.9	189.1
72.5°	112.3	113.7	116.7	116.7	116.7	119.6	122.6	125.5	128.5	134.4	143.3
75°	93.1	96.0	96.0	96.0	97.5	97.5	100.4	103.4	106.3	110.8	113.7
77.5°	76.8	76.8	76.8	76.8	78.3	78.3	79.8	82.7	84.2	85.7	88.6
80°	57.6	59.1	59.1	59.1	60.6	60.6	60.6	63.5	65.0	65.0	67.9
82.5°	42.8	42.8	42.8	44.3	42.8	44.3	44.3	45.8	44.3	45.8	47.3
85°	26.6	26.6	26.6	28.1	28.1	28.1	28.1	28.1	28.1	28.1	29.5
87.5°	13.3	13.3	13.3	13.3	13.3	13.3	13.3	13.3	14.8	13.3	13.3
90°	31.9	31.7	31.5	31.4	31.6	32.0	32.5	32.9	33.3	28.7	24.0
92.5°	30.4	30.4	30.4	30.4	30.3	30.1	29.9	29.7	29.5	29.3	29.1
95°	59.7	60.2	60.6	60.8	60.8	60.8	60.8	60.8	60.8	60.4	60.0
97.5°	95.0	95.0	95.0	95.0	95.0	95.0	95.0	95.0	95.0	94.2	93.3
100°	130.6	130.8	131.0	131.1	131.1	131.1	131.1	131.1	131.1	130.5	129.9
102.5°	170.5	170.7	170.9	171.0	170.9	170.7	170.5	170.3	170.1	169.3	168.4
105°	210.9	210.9	210.9	210.9	210.7	210.3	209.8	209.4	209.0	208.6	208.2
107.5°	250.1	251.1	252.2	252.7	252.6	252.4	252.2	252.0	251.8	251.8	251.8
110°	293.9	294.5	295.2	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5

TEST NUMBER: P1009797

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	336.2	336.7	337.1	337.3	337.6	338.2	338.9	339.5	340.1	340.3	340.5
115°	381.3	381.9	382.6	382.9	383.0	383.2	383.5	383.7	383.9	384.3	384.7
117.5°	423.1	423.8	424.4	424.7	425.0	425.7	426.3	427.0	427.6	428.6	429.7
120°	467.8	468.4	469.1	469.4	469.4	469.4	469.4	469.4	469.4	471.1	472.8
122.5°	511.0	511.5	511.9	512.1	512.4	513.1	513.7	514.4	515.0	516.0	517.1
125°	555.3	555.5	555.7	555.8	556.1	556.8	557.4	558.1	558.7	559.3	559.9
127.5°	596.0	596.7	597.3	597.6	598.0	598.9	599.7	600.6	601.4	602.2	603.1
130°	640.2	641.0	641.9	642.3	642.5	642.9	643.4	643.8	644.2	644.6	645.0
132.5°	681.5	682.2	682.8	683.1	683.6	684.7	685.8	686.8	687.9	687.7	687.5
135°	725.2	725.9	726.5	726.8	726.9	727.1	727.4	727.6	727.8	727.4	727.0
137.5°	764.6	765.5	766.4	766.8	766.9	767.1	767.3	767.5	767.7	767.3	766.9
140°	805.5	806.3	807.2	807.6	807.6	807.6	807.6	807.6	807.6	806.6	805.5
142.5°	842.6	843.4	844.3	844.7	844.6	844.4	844.1	843.9	843.7	843.1	842.5
145°	879.6	880.4	881.3	881.7	881.6	881.4	881.2	881.0	880.8	879.5	878.3
147.5°	912.9	913.7	914.6	915.0	914.8	914.4	913.9	913.5	913.1	912.3	911.4
150°	944.7	945.4	946.0	946.3	946.0	945.4	944.7	944.1	943.5	942.7	941.8
152.5°	975.6	976.4	977.3	977.7	977.3	976.4	975.6	974.7	973.9	972.8	971.8
155°	1001.7	1002.4	1003.0	1003.3	1002.8	1001.7	1000.7	999.6	998.6	998.0	997.3
157.5°	1026.3	1027.4	1028.5	1029.0	1028.3	1026.8	1025.3	1023.8	1022.3	1021.9	1021.5
160°	1047.8	1048.6	1049.5	1049.9	1049.3	1048.0	1046.7	1045.5	1044.2	1044.0	1043.8
162.5°	1067.2	1068.2	1069.3	1069.8	1069.1	1067.6	1066.1	1064.7	1063.2	1063.0	1062.8
165°	1083.3	1084.4	1085.5	1086.0	1085.3	1083.8	1082.3	1080.8	1079.3	1079.3	1079.3
167.5°	1097.6	1098.6	1099.7	1100.2	1099.5	1098.0	1096.5	1095.1	1093.6	1093.6	1093.6
170°	1108.4	1109.7	1111.0	1111.6	1110.9	1109.4	1107.9	1106.5	1105.0	1105.2	1105.4
172.5°	1117.0	1118.3	1119.6	1120.2	1119.5	1118.0	1116.5	1115.0	1113.5	1113.7	1113.9
175°	1122.7	1124.0	1125.3	1125.9	1125.2	1123.7	1122.2	1120.7	1119.2	1119.6	1120.0
177.5°	1125.5	1126.8	1128.1	1128.7	1128.1	1126.8	1125.5	1124.3	1123.0	1123.4	1123.8
180°	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9

TEST NUMBER: P1009797

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4
2.5°	2169.7	2162.4	2162.4	2157.9	2157.9	2134.3	2134.3	2141.7	2132.8	2122.5	2107.7
5°	2225.9	2209.6	2205.2	2199.3	2180.1	2150.5	2138.7	2134.3	2116.6	2094.4	2069.3
7.5°	2279.0	2252.4	2239.2	2225.9	2200.8	2159.4	2135.8	2119.5	2092.9	2059.0	2026.5
10°	2330.7	2296.8	2262.8	2246.5	2211.1	2159.4	2125.4	2098.8	2060.4	2014.6	1968.9
12.5°	2378.0	2307.1	2301.2	2268.7	2217.0	2157.9	2106.2	2067.8	2019.1	1965.9	1912.7
15°	2419.4	2347.0	2311.5	2282.0	2214.0	2140.2	2085.5	2038.3	1973.3	1912.7	1847.7
17.5°	2440.0	2361.7	2338.1	2289.4	2220.0	2123.9	2050.1	1992.5	1921.6	1849.2	1775.4
20°	2460.7	2369.1	2330.7	2296.8	2202.2	2092.9	2010.2	1943.8	1865.5	1779.8	1698.6
22.5°	2471.0	2369.1	2323.3	2276.1	2184.5	2059.0	1961.5	1883.2	1791.6	1704.5	1607.0
25°	2453.3	2360.3	2305.6	2256.9	2153.5	2017.6	1905.4	1816.7	1719.2	1620.3	1521.3
27.5°	2409.0	2339.6	2276.1	2225.9	2110.7	1964.4	1846.3	1745.8	1645.4	1534.6	1434.2
30°	2326.3	2295.3	2245.1	2188.9	2063.4	1917.2	1776.9	1673.5	1562.7	1451.9	1347.0
32.5°	2197.8	2224.4	2191.9	2143.2	2007.3	1852.2	1703.0	1598.1	1477.0	1357.4	1261.4
35°	2041.2	2135.8	2118.0	2084.1	1948.2	1782.8	1633.6	1506.6	1385.4	1264.3	1168.3
37.5°	1869.9	2013.2	2027.9	2007.3	1880.2	1711.9	1547.9	1423.8	1299.8	1177.2	1079.7
40°	1635.1	1855.1	1902.4	1911.3	1809.3	1626.2	1454.9	1333.7	1211.2	1091.5	973.4
42.5°	1419.4	1697.1	1756.2	1793.1	1719.2	1542.0	1369.2	1234.8	1113.7	1005.8	887.7
45°	1217.1	1506.6	1602.6	1649.8	1617.3	1446.0	1267.3	1141.7	1031.0	932.0	818.3
47.5°	1008.8	1299.8	1434.2	1509.5	1509.5	1348.5	1169.8	1045.7	939.4	855.2	754.8
50°	870.0	1112.2	1251.0	1350.0	1376.6	1249.6	1081.2	960.1	859.6	768.0	691.2
52.5°	741.5	958.6	1073.8	1177.2	1254.0	1143.2	982.2	872.9	774.0	688.3	627.7
55°	641.0	803.5	908.4	1022.1	1107.8	1035.4	886.2	779.9	694.2	623.3	571.6
57.5°	545.0	686.8	772.5	872.9	964.5	909.8	790.2	698.6	623.3	561.3	515.5
60°	463.8	579.0	645.5	723.7	837.5	799.1	700.1	615.9	555.4	499.2	460.8
62.5°	394.4	485.9	542.1	598.2	701.6	683.9	607.1	542.1	490.4	443.1	410.6
65°	323.5	398.8	443.1	491.8	574.6	581.9	519.9	474.1	426.9	385.5	356.0
67.5°	261.4	320.5	360.4	401.7	468.2	488.9	446.1	407.7	367.8	333.8	307.2
70°	211.2	252.6	282.1	314.6	369.3	394.4	372.2	345.6	313.1	285.1	261.4
72.5°	166.9	193.5	211.2	236.3	280.6	305.7	304.3	280.6	257.0	237.8	218.6
75°	122.6	143.3	158.0	174.3	209.7	233.4	239.3	228.9	205.3	190.5	175.8
77.5°	93.1	104.9	112.3	124.1	149.2	169.9	178.7	175.8	159.5	147.7	137.4
80°	70.9	73.9	76.8	81.2	101.9	121.1	127.0	125.5	116.7	112.3	100.4
82.5°	50.2	51.7	53.2	54.6	62.0	78.3	84.2	87.1	79.8	75.3	65.0
85°	29.5	31.0	31.0	34.0	35.4	39.9	50.2	50.2	48.7	42.8	41.4
87.5°	14.8	14.8	13.3	13.3	14.8	16.2	19.2	22.2	19.2	17.7	16.2
90°	19.4	14.7	12.4	11.1	8.6	6.1	3.5	1.0	3.5	6.1	8.6
92.5°	28.8	28.6	28.5	27.7	26.0	24.3	22.6	20.9	22.6	24.3	26.0
95°	59.5	59.1	58.9	57.8	55.7	53.6	51.5	49.4	51.5	53.6	55.7
97.5°	92.5	91.6	91.2	90.3	88.4	86.5	84.6	82.7	84.6	86.5	88.4
100°	129.2	128.6	128.3	127.5	125.8	124.1	122.4	120.7	122.4	124.1	125.8
102.5°	167.6	166.7	166.3	165.7	164.4	163.1	161.9	160.6	161.9	163.1	164.4
105°	207.7	207.3	207.1	206.8	206.2	205.5	204.9	204.3	204.9	205.5	206.2
107.5°	251.8	251.8	251.8	251.4	250.5	249.7	248.8	248.0	248.8	249.7	250.5
110°	295.5	295.5	295.5	294.9	293.6	292.3	291.1	289.8	291.1	292.3	293.6

TEST NUMBER: P1009797

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	340.8	341.0	341.1	340.5	339.2	337.9	336.7	335.4	336.7	337.9	339.2
115°	385.2	385.6	385.8	385.2	383.9	382.6	381.3	380.0	381.3	382.6	383.9
117.5°	430.7	431.8	432.3	431.5	429.8	428.1	426.4	424.7	426.4	428.1	429.8
120°	474.5	476.2	477.0	476.2	474.5	472.8	471.1	469.4	471.1	472.8	474.5
122.5°	518.1	519.2	519.7	518.6	516.5	514.4	512.3	510.2	512.3	514.4	516.5
125°	560.6	561.2	561.5	560.6	558.7	556.8	554.9	553.0	554.9	556.8	558.7
127.5°	603.9	604.8	605.2	604.0	601.7	599.4	597.1	594.8	597.1	599.4	601.7
130°	645.5	645.9	646.1	644.7	642.0	639.2	636.5	633.7	636.5	639.2	642.0
132.5°	687.2	687.0	686.9	685.8	683.7	681.6	679.5	677.4	679.5	681.6	683.7
135°	726.5	726.1	725.9	724.7	722.4	720.1	717.7	715.4	717.7	720.1	722.4
137.5°	766.4	766.0	765.8	764.8	762.9	761.0	759.1	757.2	759.1	761.0	762.9
140°	804.5	803.4	802.9	801.9	800.0	798.1	796.2	794.3	796.2	798.1	800.0
142.5°	841.8	841.2	840.9	839.9	838.0	836.1	834.2	832.3	834.2	836.1	838.0
145°	877.0	875.7	875.1	874.4	872.9	871.4	869.9	868.4	869.9	871.4	872.9
147.5°	910.6	909.7	909.3	908.3	906.4	904.5	902.6	900.7	902.6	904.5	906.4
150°	941.0	940.1	939.7	939.1	937.8	936.5	935.3	934.0	935.3	936.5	937.8
152.5°	970.7	969.6	969.1	968.5	967.2	965.9	964.7	963.4	964.7	965.9	967.2
155°	996.7	996.0	995.7	995.4	994.8	994.1	993.5	992.9	993.5	994.1	994.8
157.5°	1021.0	1020.6	1020.4	1020.2	1019.8	1019.3	1018.9	1018.5	1018.9	1019.3	1019.8
160°	1043.5	1043.3	1043.2	1043.0	1042.6	1042.1	1041.7	1041.3	1041.7	1042.1	1042.6
162.5°	1062.5	1062.3	1062.2	1062.2	1062.2	1062.2	1062.2	1062.2	1062.2	1062.2	1062.2
165°	1079.3	1079.3	1079.3	1079.4	1079.6	1079.9	1080.1	1080.3	1080.1	1079.9	1079.6
167.5°	1093.6	1093.6	1093.6	1093.9	1094.5	1095.2	1095.8	1096.4	1095.8	1095.2	1094.5
170°	1105.6	1105.8	1105.9	1106.2	1106.9	1107.5	1108.2	1108.8	1108.2	1107.5	1106.9
172.5°	1114.2	1114.4	1114.5	1114.8	1115.4	1116.1	1116.7	1117.3	1116.7	1116.1	1115.4
175°	1120.5	1120.9	1121.1	1121.4	1122.1	1122.7	1123.4	1124.0	1123.4	1122.7	1122.1
177.5°	1124.3	1124.7	1124.9	1125.2	1125.9	1126.5	1127.2	1127.8	1127.2	1126.5	1125.9
180°	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9

TEST NUMBER: P1009797

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4
2.5°	2101.8	2103.3	2107.7	2094.4	2073.7	2064.9	2038.3	2033.9	2029.4	2029.4	2033.9
5°	2054.5	2048.6	2050.1	2025.0	1995.4	1977.7	1940.8	1946.7	1927.5	1915.7	1918.6
7.5°	2002.8	1986.6	1985.1	1952.6	1915.7	1883.2	1844.8	1835.9	1818.2	1797.5	1788.7
10°	1937.8	1926.0	1903.9	1866.9	1819.7	1793.1	1741.4	1710.4	1706.0	1674.9	1663.1
12.5°	1871.4	1850.7	1828.5	1776.9	1723.7	1680.8	1642.4	1608.5	1584.8	1558.3	1540.5
15°	1794.6	1769.5	1744.4	1689.7	1627.7	1584.8	1527.2	1477.0	1407.6	1352.9	1321.9
17.5°	1710.4	1682.3	1648.3	1587.8	1527.2	1468.2	1361.8	1302.7	1254.0	1221.5	1202.3
20°	1623.2	1592.2	1558.3	1497.7	1392.8	1289.4	1230.4	1184.6	1155.0	1122.5	1098.9
22.5°	1531.7	1499.2	1462.2	1367.7	1256.9	1184.6	1138.8	1095.9	1053.1	1035.4	1023.6
25°	1446.0	1416.5	1369.2	1240.7	1153.5	1087.1	1035.4	1007.3	985.2	961.5	939.4
27.5°	1357.4	1302.7	1236.3	1128.4	1073.8	1005.8	968.9	948.2	909.8	893.6	883.3
30°	1251.0	1190.5	1127.0	1050.2	986.6	939.4	905.4	871.4	849.3	833.0	815.3
32.5°	1143.2	1085.6	1045.7	966.0	918.7	870.0	837.5	816.8	784.3	774.0	766.6
35°	1050.2	1001.4	966.0	901.0	856.7	812.4	788.7	757.7	737.0	717.8	706.0
37.5°	958.6	932.0	895.1	840.4	793.2	757.7	725.2	714.9	686.8	676.5	664.7
40°	895.1	855.2	824.2	776.9	737.0	698.6	678.0	654.3	635.1	618.9	614.4
42.5°	818.3	788.7	771.0	719.3	678.0	655.8	630.7	604.1	589.3	576.0	559.8
45°	760.7	734.1	709.0	667.6	630.7	602.6	580.5	562.7	537.6	531.7	506.6
47.5°	700.1	673.5	654.3	613.0	579.0	552.4	536.2	512.5	491.8	478.6	466.7
50°	639.5	617.4	599.7	564.2	534.7	506.6	484.5	460.8	452.0	429.8	422.4
52.5°	581.9	567.2	548.0	514.0	484.5	460.8	437.2	418.0	404.7	392.9	384.0
55°	533.2	509.6	500.7	463.8	438.7	413.6	392.9	381.1	364.8	357.4	350.1
57.5°	478.6	465.3	450.5	422.4	394.4	370.7	356.0	338.2	329.4	320.5	314.6
60°	431.3	412.1	400.3	376.6	351.5	329.4	316.1	302.8	291.0	283.6	271.8
62.5°	376.6	361.9	354.5	329.4	308.7	288.0	276.2	262.9	254.0	240.8	226.0
65°	329.4	317.6	308.7	288.0	268.8	249.6	237.8	221.6	209.7	202.4	200.9
67.5°	288.0	279.2	265.9	246.7	227.5	212.7	199.4	186.1	184.6	181.7	181.7
70°	242.2	233.4	226.0	205.3	189.1	172.8	169.9	165.4	161.0	159.5	156.6
72.5°	202.4	195.0	186.1	168.4	152.1	147.7	144.7	141.8	137.4	135.9	134.4
75°	163.9	153.6	147.7	131.5	127.0	124.1	121.1	116.7	113.7	112.3	109.3
77.5°	125.5	115.2	115.2	106.3	103.4	99.0	96.0	93.1	91.6	88.6	88.6
80°	88.6	88.6	85.7	81.2	76.8	75.3	70.9	69.4	67.9	69.4	66.5
82.5°	65.0	59.1	59.1	56.1	53.2	51.7	48.7	48.7	47.3	47.3	47.3
85°	36.9	36.9	35.4	32.5	31.0	31.0	29.5	29.5	28.1	28.1	26.6
87.5°	14.8	13.3	14.8	13.3	13.3	11.8	11.8	11.8	10.3	11.8	10.3
90°	11.1	12.4	14.7	19.4	24.0	28.7	33.3	32.9	32.5	32.0	31.6
92.5°	27.7	28.5	28.6	28.8	29.1	29.3	29.5	29.7	29.9	30.1	30.3
95°	57.8	58.9	59.1	59.5	60.0	60.4	60.8	60.8	60.8	60.8	60.8
97.5°	90.3	91.2	91.6	92.5	93.3	94.2	95.0	95.0	95.0	95.0	95.0
100°	127.5	128.3	128.6	129.2	129.9	130.5	131.1	131.1	131.1	131.1	131.1
102.5°	165.7	166.3	166.7	167.6	168.4	169.3	170.1	170.3	170.5	170.7	170.9
105°	206.8	207.1	207.3	207.7	208.2	208.6	209.0	209.4	209.8	210.3	210.7
107.5°	251.4	251.8	251.8	251.8	251.8	251.8	251.8	252.0	252.2	252.4	252.6
110°	294.9	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5

TEST NUMBER: P1009797

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	340.5	341.1	341.0	340.8	340.5	340.3	340.1	339.5	338.9	338.2	337.6
115°	385.2	385.8	385.6	385.2	384.7	384.3	383.9	383.7	383.5	383.2	383.0
117.5°	431.5	432.3	431.8	430.7	429.7	428.6	427.6	427.0	426.3	425.7	425.0
120°	476.2	477.0	476.2	474.5	472.8	471.1	469.4	469.4	469.4	469.4	469.4
122.5°	518.6	519.7	519.2	518.1	517.1	516.0	515.0	514.4	513.7	513.1	512.4
125°	560.6	561.5	561.2	560.6	559.9	559.3	558.7	558.1	557.4	556.8	556.1
127.5°	604.0	605.2	604.8	603.9	603.1	602.2	601.4	600.6	599.7	598.9	598.0
130°	644.7	646.1	645.9	645.5	645.0	644.6	644.2	643.8	643.4	642.9	642.5
132.5°	685.8	686.9	687.0	687.2	687.5	687.7	687.9	686.8	685.8	684.7	683.6
135°	724.7	725.9	726.1	726.5	727.0	727.4	727.8	727.6	727.4	727.1	726.9
137.5°	764.8	765.8	766.0	766.4	766.9	767.3	767.7	767.5	767.3	767.1	766.9
140°	801.9	802.9	803.4	804.5	805.5	806.6	807.6	807.6	807.6	807.6	807.6
142.5°	839.9	840.9	841.2	841.8	842.5	843.1	843.7	843.9	844.1	844.4	844.6
145°	874.4	875.1	875.7	877.0	878.3	879.5	880.8	881.0	881.2	881.4	881.6
147.5°	908.3	909.3	909.7	910.6	911.4	912.3	913.1	913.5	913.9	914.4	914.8
150°	939.1	939.7	940.1	941.0	941.8	942.7	943.5	944.1	944.7	945.4	946.0
152.5°	968.5	969.1	969.6	970.7	971.8	972.8	973.9	974.7	975.6	976.4	977.3
155°	995.4	995.7	996.0	996.7	997.3	998.0	998.6	999.6	1000.7	1001.7	1002.8
157.5°	1020.2	1020.4	1020.6	1021.0	1021.5	1021.9	1022.3	1023.8	1025.3	1026.8	1028.3
160°	1043.0	1043.2	1043.3	1043.5	1043.8	1044.0	1044.2	1045.5	1046.7	1048.0	1049.3
162.5°	1062.2	1062.2	1062.3	1062.5	1062.8	1063.0	1063.2	1064.7	1066.1	1067.6	1069.1
165°	1079.4	1079.3	1079.3	1079.3	1079.3	1079.3	1079.3	1080.8	1082.3	1083.8	1085.3
167.5°	1093.9	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1095.1	1096.5	1098.0	1099.5
170°	1106.2	1105.9	1105.8	1105.6	1105.4	1105.2	1105.0	1106.5	1107.9	1109.4	1110.9
172.5°	1114.8	1114.5	1114.4	1114.2	1113.9	1113.7	1113.5	1115.0	1116.5	1118.0	1119.5
175°	1121.4	1121.1	1120.9	1120.5	1120.0	1119.6	1119.2	1120.7	1122.2	1123.7	1125.2
177.5°	1125.2	1124.9	1124.7	1124.3	1123.8	1123.4	1123.0	1124.3	1125.5	1126.8	1128.1
180°	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9

TEST NUMBER: P1009797

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4
2.5°	2033.9	2030.9	2022.0	2025.0	2020.6	2020.6	2017.6	2017.6	2017.6	2025.0	2020.6
5°	1923.1	1912.7	1902.4	1898.0	1893.5	1889.1	1889.1	1887.6	1900.9	1898.0	1909.8
7.5°	1785.7	1782.8	1762.1	1762.1	1754.7	1751.7	1759.1	1760.6	1762.1	1765.0	1772.4
10°	1663.1	1655.7	1626.2	1629.1	1624.7	1618.8	1623.2	1620.3	1630.6	1633.6	1630.6
12.5°	1518.4	1505.1	1472.6	1456.3	1438.6	1425.3	1441.6	1429.8	1471.1	1482.9	1515.4
15°	1326.4	1301.3	1279.1	1279.1	1262.8	1251.0	1258.4	1271.7	1280.6	1293.9	1299.8
17.5°	1197.9	1187.5	1169.8	1159.5	1155.0	1150.6	1150.6	1156.5	1175.7	1174.2	1186.0
20°	1088.6	1082.7	1073.8	1060.5	1056.1	1053.1	1053.1	1053.1	1066.4	1078.2	1085.6
22.5°	1013.2	1008.8	1002.9	985.2	976.3	973.4	980.7	985.2	995.5	1004.4	1011.8
25°	937.9	927.6	917.2	911.3	906.9	906.9	909.8	911.3	915.7	920.2	929.0
27.5°	875.9	868.5	853.7	837.5	837.5	833.0	836.0	838.9	849.3	864.1	871.4
30°	806.5	805.0	799.1	793.2	787.2	784.3	790.2	794.6	796.1	803.5	803.5
32.5°	756.2	745.9	735.6	729.6	726.7	725.2	726.7	732.6	732.6	741.5	751.8
35°	706.0	700.1	689.8	679.4	676.5	669.1	675.0	680.9	691.2	695.7	700.1
37.5°	651.4	644.0	639.5	636.6	630.7	632.2	627.7	636.6	645.5	644.0	646.9
40°	610.0	596.7	583.4	581.9	580.5	579.0	579.0	580.5	586.4	592.3	601.1
42.5°	556.8	552.4	540.6	528.8	525.8	522.9	519.9	525.8	537.6	548.0	552.4
45°	502.2	496.3	493.3	484.5	478.6	477.1	474.1	481.5	491.8	496.3	499.2
47.5°	452.0	450.5	441.6	443.1	438.7	440.2	438.7	443.1	443.1	447.5	450.5
50°	418.0	413.6	409.1	406.2	401.7	401.7	400.3	401.7	407.7	413.6	412.1
52.5°	384.0	376.6	375.2	373.7	370.7	373.7	369.3	370.7	376.6	379.6	378.1
55°	344.1	342.7	339.7	336.8	335.3	333.8	333.8	333.8	339.7	344.1	345.6
57.5°	313.1	305.7	299.8	299.8	293.9	292.4	295.4	296.9	301.3	304.3	307.2
60°	270.3	267.3	258.5	254.0	245.2	243.7	243.7	249.6	257.0	267.3	270.3
62.5°	224.5	220.1	218.6	218.6	218.6	218.6	218.6	218.6	218.6	220.1	220.1
65°	199.4	200.9	199.4	197.9	199.4	199.4	197.9	197.9	197.9	199.4	200.9
67.5°	178.7	177.2	178.7	177.2	175.8	175.8	174.3	175.8	177.2	178.7	178.7
70°	155.1	155.1	153.6	155.1	153.6	152.1	150.7	150.7	153.6	155.1	155.1
72.5°	132.9	132.9	131.5	131.5	128.5	128.5	130.0	128.5	128.5	132.9	132.9
75°	110.8	109.3	107.8	107.8	106.3	106.3	106.3	104.9	107.8	107.8	109.3
77.5°	87.1	87.1	87.1	85.7	85.7	84.2	84.2	85.7	85.7	85.7	87.1
80°	66.5	66.5	66.5	65.0	63.5	63.5	63.5	63.5	63.5	65.0	63.5
82.5°	45.8	45.8	45.8	45.8	45.8	44.3	44.3	44.3	45.8	45.8	44.3
85°	28.1	26.6	28.1	28.1	26.6	28.1	26.6	26.6	25.1	25.1	26.6
87.5°	11.8	10.3	8.9	8.9	10.3	8.9	8.9	8.9	10.3	8.9	8.9
90°	31.4	31.5	31.7	31.9	32.1	32.3	32.1	31.9	31.7	31.5	31.4
92.5°	30.4	30.4	30.4	30.4	30.4	30.4	30.4	30.4	30.4	30.4	30.4
95°	60.8	60.6	60.2	59.7	59.3	58.9	59.3	59.7	60.2	60.6	60.8
97.5°	95.0	95.0	95.0	95.0	95.0	95.0	95.0	95.0	95.0	95.0	95.0
100°	131.1	131.0	130.8	130.6	130.4	130.2	130.4	130.6	130.8	131.0	131.1
102.5°	171.0	170.9	170.7	170.5	170.3	170.1	170.3	170.5	170.7	170.9	171.0
105°	210.9	210.9	210.9	210.9	210.9	210.9	210.9	210.9	210.9	210.9	210.9
107.5°	252.7	252.2	251.1	250.1	249.0	248.0	249.0	250.1	251.1	252.2	252.7
110°	295.5	295.2	294.5	293.9	293.2	292.6	293.2	293.9	294.5	295.2	295.5

TEST NUMBER: P1009797

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	337.3	337.1	336.7	336.2	335.8	335.4	335.8	336.2	336.7	337.1	337.3
115°	382.9	382.6	381.9	381.3	380.6	380.0	380.6	381.3	381.9	382.6	382.9
117.5°	424.7	424.4	423.8	423.1	422.5	421.9	422.5	423.1	423.8	424.4	424.7
120°	469.4	469.1	468.4	467.8	467.1	466.5	467.1	467.8	468.4	469.1	469.4
122.5°	512.1	511.9	511.5	511.0	510.6	510.2	510.6	511.0	511.5	511.9	512.1
125°	555.8	555.7	555.5	555.3	555.1	554.9	555.1	555.3	555.5	555.7	555.8
127.5°	597.6	597.3	596.7	596.0	595.4	594.8	595.4	596.0	596.7	597.3	597.6
130°	642.3	641.9	641.0	640.2	639.3	638.5	639.3	640.2	641.0	641.9	642.3
132.5°	683.1	682.8	682.2	681.5	680.9	680.3	680.9	681.5	682.2	682.8	683.1
135°	726.8	726.5	725.9	725.2	724.6	724.0	724.6	725.2	725.9	726.5	726.8
137.5°	766.8	766.4	765.5	764.6	763.8	762.9	763.8	764.6	765.5	766.4	766.8
140°	807.6	807.2	806.3	805.5	804.6	803.8	804.6	805.5	806.3	807.2	807.6
142.5°	844.7	844.3	843.4	842.6	841.7	840.9	841.7	842.6	843.4	844.3	844.7
145°	881.7	881.3	880.4	879.6	878.7	877.9	878.7	879.6	880.4	881.3	881.7
147.5°	915.0	914.6	913.7	912.9	912.0	911.2	912.0	912.9	913.7	914.6	915.0
150°	946.3	946.0	945.4	944.7	944.1	943.5	944.1	944.7	945.4	946.0	946.3
152.5°	977.7	977.3	976.4	975.6	974.7	973.9	974.7	975.6	976.4	977.3	977.7
155°	1003.3	1003.0	1002.4	1001.7	1001.1	1000.5	1001.1	1001.7	1002.4	1003.0	1003.3
157.5°	1029.0	1028.5	1027.4	1026.3	1025.3	1024.2	1025.3	1026.3	1027.4	1028.5	1029.0
160°	1049.9	1049.5	1048.6	1047.8	1046.9	1046.1	1046.9	1047.8	1048.6	1049.5	1049.9
162.5°	1069.8	1069.3	1068.2	1067.2	1066.1	1065.1	1066.1	1067.2	1068.2	1069.3	1069.8
165°	1086.0	1085.5	1084.4	1083.3	1082.3	1081.2	1082.3	1083.3	1084.4	1085.5	1086.0
167.5°	1100.2	1099.7	1098.6	1097.6	1096.5	1095.5	1096.5	1097.6	1098.6	1099.7	1100.2
170°	1111.6	1111.0	1109.7	1108.4	1107.2	1105.9	1107.2	1108.4	1109.7	1111.0	1111.6
172.5°	1120.2	1119.6	1118.3	1117.0	1115.8	1114.5	1115.8	1117.0	1118.3	1119.6	1120.2
175°	1125.9	1125.3	1124.0	1122.7	1121.5	1120.2	1121.5	1122.7	1124.0	1125.3	1125.9
177.5°	1128.7	1128.1	1126.8	1125.5	1124.3	1123.0	1124.3	1125.5	1126.8	1128.1	1128.7
180°	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9

TEST NUMBER: P1009797

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4	2125.4
2.5°	2025.0	2032.4	2029.4	2013.2	2029.4	2033.9	2042.7	2051.6	2057.5	2066.3	2073.7
5°	1898.0	1912.7	1921.6	1912.7	1942.3	1946.7	1967.4	1979.2	1996.9	2011.7	2023.5
7.5°	1778.3	1790.1	1807.9	1810.8	1828.5	1849.2	1878.8	1908.3	1936.4	1951.1	1964.4
10°	1649.8	1670.5	1697.1	1691.2	1717.8	1750.3	1781.3	1828.5	1852.2	1878.8	1902.4
12.5°	1521.3	1534.6	1570.1	1581.9	1620.3	1645.4	1688.2	1717.8	1776.9	1807.9	1828.5
15°	1296.8	1351.5	1395.8	1449.0	1499.2	1546.4	1584.8	1638.0	1689.7	1713.3	1747.3
17.5°	1194.9	1220.0	1246.6	1273.2	1338.2	1422.4	1490.3	1547.9	1592.2	1623.2	1663.1
20°	1088.6	1113.7	1143.2	1168.3	1208.2	1268.8	1352.9	1451.9	1505.1	1537.6	1576.0
22.5°	1013.2	1036.9	1056.1	1078.2	1109.2	1153.5	1217.1	1339.7	1410.6	1450.4	1484.4
25°	932.0	961.5	982.2	998.5	1023.6	1072.3	1124.0	1193.4	1320.5	1351.5	1398.7
27.5°	875.9	884.7	908.4	933.5	958.6	985.2	1038.3	1097.4	1183.1	1251.0	1308.6
30°	809.4	831.6	853.7	864.1	886.2	924.6	957.1	1020.6	1087.1	1140.3	1209.7
32.5°	759.2	772.5	787.2	812.4	833.0	859.6	892.1	945.3	1001.4	1035.4	1088.6
35°	703.1	711.9	742.9	753.3	774.0	800.5	833.0	874.4	935.0	961.5	999.9
37.5°	649.9	670.6	679.4	703.1	722.3	748.8	772.5	819.7	859.6	890.6	926.1
40°	608.5	617.4	633.6	654.3	670.6	691.2	720.8	754.8	797.6	822.7	853.7
42.5°	558.3	565.7	586.4	598.2	624.8	644.0	661.7	703.1	741.5	760.7	791.7
45°	503.7	521.4	534.7	558.3	573.1	596.7	618.9	648.4	683.9	706.0	723.7
47.5°	456.4	474.1	487.4	509.6	533.2	543.5	567.2	598.2	630.7	648.4	673.5
50°	418.0	423.9	449.0	459.4	484.5	505.1	521.4	548.0	583.4	593.8	614.4
52.5°	381.1	385.5	401.7	415.0	437.2	454.9	475.6	500.7	530.2	546.5	562.7
55°	348.6	351.5	358.9	373.7	388.5	410.6	429.8	453.4	478.6	496.3	511.0
57.5°	311.7	317.6	323.5	332.3	347.1	367.8	388.5	410.6	431.3	443.1	462.3
60°	268.8	277.7	288.0	298.4	308.7	323.5	347.1	367.8	387.0	397.3	412.1
62.5°	223.0	240.8	249.6	261.4	270.3	283.6	301.3	324.9	338.2	351.5	363.3
65°	200.9	202.4	203.8	215.6	231.9	245.2	261.4	279.2	299.8	308.7	317.6
67.5°	178.7	180.2	183.1	184.6	190.5	205.3	223.0	242.2	258.5	264.4	273.2
70°	156.6	156.6	162.5	163.9	165.4	166.9	181.7	200.9	215.6	223.0	233.4
72.5°	132.9	134.4	137.4	138.8	141.8	144.7	149.2	159.5	177.2	184.6	196.4
75°	109.3	110.8	112.3	113.7	118.2	119.6	124.1	130.0	137.4	146.2	153.6
77.5°	87.1	87.1	88.6	91.6	94.5	96.0	100.4	103.4	106.3	110.8	116.7
80°	65.0	66.5	66.5	69.4	69.4	70.9	72.4	76.8	79.8	82.7	85.7
82.5°	44.3	47.3	47.3	47.3	48.7	50.2	51.7	51.7	54.6	56.1	60.6
85°	26.6	28.1	28.1	28.1	26.6	29.5	29.5	31.0	31.0	31.0	32.5
87.5°	10.3	8.9	10.3	10.3	10.3	11.8	10.3	10.3	11.8	13.3	13.3
90°	31.6	32.0	32.5	32.9	33.3	28.7	24.0	19.4	14.7	12.4	11.1
92.5°	30.3	30.1	29.9	29.7	29.5	29.3	29.1	28.8	28.6	28.5	27.7
95°	60.8	60.8	60.8	60.8	60.8	60.4	60.0	59.5	59.1	58.9	57.8
97.5°	95.0	95.0	95.0	95.0	95.0	94.2	93.3	92.5	91.6	91.2	90.3
100°	131.1	131.1	131.1	131.1	131.1	130.5	129.9	129.2	128.6	128.3	127.5
102.5°	170.9	170.7	170.5	170.3	170.1	169.3	168.4	167.6	166.7	166.3	165.7
105°	210.7	210.3	209.8	209.4	209.0	208.6	208.2	207.7	207.3	207.1	206.8
107.5°	252.6	252.4	252.2	252.0	251.8	251.8	251.8	251.8	251.8	251.8	251.4
110°	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	295.5	294.9

TEST NUMBER: P1009797

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	337.6	338.2	338.9	339.5	340.1	340.3	340.5	340.8	341.0	341.1	340.5
115°	383.0	383.2	383.5	383.7	383.9	384.3	384.7	385.2	385.6	385.8	385.2
117.5°	425.0	425.7	426.3	427.0	427.6	428.6	429.7	430.7	431.8	432.3	431.5
120°	469.4	469.4	469.4	469.4	469.4	471.1	472.8	474.5	476.2	477.0	476.2
122.5°	512.4	513.1	513.7	514.4	515.0	516.0	517.1	518.1	519.2	519.7	518.6
125°	556.1	556.8	557.4	558.1	558.7	559.3	559.9	560.6	561.2	561.5	560.6
127.5°	598.0	598.9	599.7	600.6	601.4	602.2	603.1	603.9	604.8	605.2	604.0
130°	642.5	642.9	643.4	643.8	644.2	644.6	645.0	645.5	645.9	646.1	644.7
132.5°	683.6	684.7	685.8	686.8	687.9	687.7	687.5	687.2	687.0	686.9	685.8
135°	726.9	727.1	727.4	727.6	727.8	727.4	727.0	726.5	726.1	725.9	724.7
137.5°	766.9	767.1	767.3	767.5	767.7	767.3	766.9	766.4	766.0	765.8	764.8
140°	807.6	807.6	807.6	807.6	807.6	806.6	805.5	804.5	803.4	802.9	801.9
142.5°	844.6	844.4	844.1	843.9	843.7	843.1	842.5	841.8	841.2	840.9	839.9
145°	881.6	881.4	881.2	881.0	880.8	879.5	878.3	877.0	875.7	875.1	874.4
147.5°	914.8	914.4	913.9	913.5	913.1	912.3	911.4	910.6	909.7	909.3	908.3
150°	946.0	945.4	944.7	944.1	943.5	942.7	941.8	941.0	940.1	939.7	939.1
152.5°	977.3	976.4	975.6	974.7	973.9	972.8	971.8	970.7	969.6	969.1	968.5
155°	1002.8	1001.7	1000.7	999.6	998.6	998.0	997.3	996.7	996.0	995.7	995.4
157.5°	1028.3	1026.8	1025.3	1023.8	1022.3	1021.9	1021.5	1021.0	1020.6	1020.4	1020.2
160°	1049.3	1048.0	1046.7	1045.5	1044.2	1044.0	1043.8	1043.5	1043.3	1043.2	1043.0
162.5°	1069.1	1067.6	1066.1	1064.7	1063.2	1063.0	1062.8	1062.5	1062.3	1062.2	1062.2
165°	1085.3	1083.8	1082.3	1080.8	1079.3	1079.3	1079.3	1079.3	1079.3	1079.3	1079.4
167.5°	1099.5	1098.0	1096.5	1095.1	1093.6	1093.6	1093.6	1093.6	1093.6	1093.6	1093.9
170°	1110.9	1109.4	1107.9	1106.5	1105.0	1105.2	1105.4	1105.6	1105.8	1105.9	1106.2
172.5°	1119.5	1118.0	1116.5	1115.0	1113.5	1113.7	1113.9	1114.2	1114.4	1114.5	1114.8
175°	1125.2	1123.7	1122.2	1120.7	1119.2	1119.6	1120.0	1120.5	1120.9	1121.1	1121.4
177.5°	1128.1	1126.8	1125.5	1124.3	1123.0	1123.4	1123.8	1124.3	1124.7	1124.9	1125.2
180°	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9	1125.9

TEST NUMBER: P1009797

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	2125.4	2125.4	2125.4	2125.4
2.5°	2087.0	2082.6	2109.2	2138.7
5°	2044.2	2051.6	2085.5	2126.9
7.5°	1999.9	2016.1	2056.0	2110.7
10°	1937.8	1967.4	2027.9	2084.1
12.5°	1877.3	1917.2	1974.8	2041.2
15°	1809.3	1853.7	1924.6	2004.3
17.5°	1734.0	1784.2	1866.9	1954.1
20°	1654.3	1720.7	1807.9	1902.4
22.5°	1565.6	1645.4	1735.5	1840.4
25°	1480.0	1567.1	1657.2	1778.3
27.5°	1395.8	1481.4	1581.9	1704.5
30°	1311.6	1389.9	1497.7	1629.1
32.5°	1221.5	1302.7	1416.5	1550.9
35°	1138.8	1220.0	1326.4	1459.3
37.5°	1050.2	1137.3	1239.2	1376.6
40°	946.8	1048.7	1147.6	1279.1
42.5°	861.1	968.9	1064.9	1189.0
45°	793.2	895.1	974.8	1095.9
47.5°	729.6	812.4	893.6	1005.8
50°	669.1	732.6	816.8	917.2
52.5°	607.1	661.7	734.1	828.6
55°	550.9	602.6	667.6	740.0
57.5°	499.2	536.2	601.1	666.1
60°	441.6	480.0	530.2	584.9
62.5°	392.9	422.4	469.7	515.5
65°	341.2	369.3	404.7	447.5
67.5°	293.9	319.0	347.1	381.1
70°	251.1	270.3	291.0	320.5
72.5°	205.3	226.0	245.2	268.8
75°	168.4	177.2	193.5	209.7
77.5°	130.0	141.8	150.7	163.9
80°	93.1	103.4	106.3	116.7
82.5°	62.0	67.9	73.9	76.8
85°	35.4	38.4	44.3	45.8
87.5°	13.3	14.8	17.7	20.7
90°	8.6	6.1	3.5	1.0
92.5°	26.0	24.3	22.6	20.9
95°	55.7	53.6	51.5	49.4
97.5°	88.4	86.5	84.6	82.7
100°	125.8	124.1	122.4	120.7
102.5°	164.4	163.1	161.9	160.6
105°	206.2	205.5	204.9	204.3
107.5°	250.5	249.7	248.8	248.0
110°	293.6	292.3	291.1	289.8

TEST NUMBER: P1009797

CATALOG NUMBER: S122RDIP-B1005D925UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	339.2	337.9	336.7	335.4
115°	383.9	382.6	381.3	380.0
117.5°	429.8	428.1	426.4	424.7
120°	474.5	472.8	471.1	469.4
122.5°	516.5	514.4	512.3	510.2
125°	558.7	556.8	554.9	553.0
127.5°	601.7	599.4	597.1	594.8
130°	642.0	639.2	636.5	633.7
132.5°	683.7	681.6	679.5	677.4
135°	722.4	720.1	717.7	715.4
137.5°	762.9	761.0	759.1	757.2
140°	800.0	798.1	796.2	794.3
142.5°	838.0	836.1	834.2	832.3
145°	872.9	871.4	869.9	868.4
147.5°	906.4	904.5	902.6	900.7
150°	937.8	936.5	935.3	934.0
152.5°	967.2	965.9	964.7	963.4
155°	994.8	994.1	993.5	992.9
157.5°	1019.8	1019.3	1018.9	1018.5
160°	1042.6	1042.1	1041.7	1041.3
162.5°	1062.2	1062.2	1062.2	1062.2
165°	1079.6	1079.9	1080.1	1080.3
167.5°	1094.5	1095.2	1095.8	1096.4
170°	1106.9	1107.5	1108.2	1108.8
172.5°	1115.4	1116.1	1116.7	1117.3
175°	1122.1	1122.7	1123.4	1124.0
177.5°	1125.9	1126.5	1127.2	1127.8
180°	1125.9	1125.9	1125.9	1125.9

(END OF REPORT)