

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009812

Luminaire Tested: S122RDIP-B290D1080UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009812
REPORT IS A COMBINATION OF REPORTS P988038 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B290D1080UB30-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4855.0 lumens
Efficiency: N/A
Efficacy: 101.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009812

CATALOG NUMBER: S122RDIP-B290D1080UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1009812

CATALOG NUMBER: S122RDIP-B290D1080UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	100	100	100	100	89	89	89	89	67	67	67	47	47	47	29	29	29	29	29	29
1	91	87	84	80	81	77	74	72	59	57	55	42	41	40	26	26	25	25	25	25
2	83	76	71	66	74	68	63	59	52	49	46	37	35	33	23	22	21	21	21	21
3	76	67	60	55	67	60	54	49	46	42	39	33	30	28	21	19	18	18	18	18
4	70	60	52	47	61	53	47	42	41	36	33	29	27	24	19	17	16	16	16	16
5	64	53	45	40	56	47	41	36	36	32	28	26	23	21	17	15	14	14	14	14
6	59	47	40	34	52	42	36	31	33	28	25	24	21	18	15	14	12	12	12	12
7	54	43	35	30	48	38	32	27	30	25	22	22	19	16	14	12	11	11	11	11
8	50	39	31	26	44	35	28	24	27	22	19	20	17	14	13	11	10	10	10	10
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9	9	9	9
10	43	32	25	21	38	29	23	19	22	18	15	17	14	12	11	9	8	8	8	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7736	7736	7736
5°	7748	7359	7305
10°	7672	6979	6750
15°	7566	6532	6117
20°	7427	6022	5454
25°	7284	5499	4849
30°	7092	4991	4187
35°	6903	4477	3620
40°	6713	3973	3034
45°	6491	3452	2524
50°	6261	2952	2056
55°	6022	2449	1632
60°	5744	1958	1234
65°	5425	1492	1004
70°	5037	1083	798
75°	4554	827	609
80°	3848	559	410
85°	2684	256	198

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6491 cd/sqm

TEST NUMBER: P1009812

CATALOG NUMBER: S122RDIP-B290D1080UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.8	0.9
10°-20°	125.7	2.6
20°-30°	176.5	3.6
30°-40°	192.4	4.0
40°-50°	176.8	3.6
50°-60°	138.9	2.9
60°-70°	90.4	1.9
70°-80°	46.5	1.0
80°-90°	15.8	0.3
90°-100°	85.1	1.8
100°-110°	270.5	5.6
110°-120°	462.9	9.5
120°-130°	608.8	12.5
130°-140°	683.4	14.1
140°-150°	670.1	13.8
150°-160°	562.1	11.6
160°-170°	372.8	7.7
170°-180°	130.3	2.7
0°-30°	348.0	7.2
0°-40°	540.4	11.1
0°-60°	856.2	17.6
0°-90°	1008.9	20.8
90°-120°	818.5	16.9
90°-150°	2780.8	57.3
90°-180°	3846.0	79.2
0°-180°	4855.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	489	489	489	489	489	
5°	489	486	481	485	483	46
15°	465	460	445	436	432	131
25°	422	408	378	360	354	194
35°	364	341	302	274	264	228
45°	297	268	221	190	179	230
55°	226	192	144	117	109	202
65°	153	117	77	62	61	151
75°	81	50	35	32	32	86
85°	19	10	8	8	8	22
90°	1	15	41	38	40	5
95°	60	72	74	74	72	67
105°	250	253	255	258	258	264
115°	464	471	469	468	464	459
125°	676	686	683	679	678	604
135°	874	887	889	888	885	675
145°	1061	1069	1076	1077	1073	663
155°	1213	1217	1220	1226	1222	558
165°	1320	1319	1319	1327	1321	372
175°	1373	1370	1368	1376	1369	130
180°	1376	1376	1376	1376	1376	

TEST NUMBER: P1009812

CATALOG NUMBER: S122RDIP-B290D1080UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	488.7	488.7	488.7	488.7	488.7
2.5°	490.9	488.7	483.8	488.2	487.3
5°	488.7	486.5	480.7	484.7	483.4
7.5°	484.7	482.0	475.8	477.6	475.4
10°	479.4	476.3	467.4	466.1	463.5
12.5°	472.7	468.8	456.8	454.2	449.3
15°	464.8	459.9	444.9	436.5	432.1
17.5°	455.5	448.4	429.8	420.1	413.0
20°	444.9	436.0	413.9	402.9	393.1
22.5°	433.4	423.2	397.6	382.5	375.9
25°	421.9	407.7	378.5	360.4	353.8
27.5°	408.2	393.1	360.9	340.1	329.9
30°	393.6	376.8	341.4	318.8	306.9
32.5°	379.4	359.1	322.8	296.3	285.2
35°	363.5	341.0	302.0	274.2	264.5
37.5°	348.0	323.7	282.6	252.1	241.0
40°	331.7	305.1	262.2	230.8	219.3
42.5°	314.9	286.6	241.9	209.2	198.1
45°	297.2	267.5	221.1	189.7	179.1
47.5°	280.4	249.0	201.2	169.8	160.1
50°	261.8	230.4	181.8	151.2	142.0
52.5°	243.7	210.5	163.2	134.0	125.6
55°	226.0	191.5	143.7	117.2	108.8
57.5°	207.8	172.5	126.5	101.7	94.6
60°	189.3	153.9	108.3	85.8	78.7
62.5°	171.1	135.8	92.9	71.6	68.1
65°	152.6	116.7	76.9	61.9	60.6
67.5°	134.9	99.1	61.9	54.4	53.1
70°	116.3	81.8	51.3	46.9	45.1
72.5°	98.6	65.9	42.9	39.4	38.5
75°	81.4	50.4	35.4	32.3	31.8
77.5°	64.1	35.8	27.9	26.1	25.2
80°	48.2	25.6	21.2	19.5	19.5
82.5°	33.6	17.2	14.6	13.7	13.7
85°	19.0	9.7	8.4	8.4	8.4
87.5°	7.1	3.5	3.5	3.1	3.1
90°	1.2	15.1	40.6	38.3	39.5
92.5°	25.5	34.8	36.0	37.1	37.1
95°	60.4	72.0	74.3	74.3	72.0
97.5°	101.0	111.4	116.1	116.1	116.1
100°	147.4	156.7	160.2	160.2	159.0
102.5°	196.2	203.2	207.8	209.0	207.8
105°	249.6	253.1	255.4	257.7	257.7
107.5°	303.0	307.6	307.6	308.8	303.0
110°	354.1	361.0	361.0	361.0	357.6

TEST NUMBER: P1009812

CATALOG NUMBER: S122RDIP-B290D1080UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	409.8	416.8	415.6	412.1	409.8
115°	464.4	471.3	469.0	467.8	464.4
117.5°	518.9	528.2	522.4	518.9	515.4
120°	573.5	582.8	573.5	573.5	570.0
122.5°	623.4	635.0	629.2	625.7	623.4
125°	675.6	686.1	682.6	679.1	678.0
127.5°	726.7	739.5	734.8	730.2	726.7
130°	774.3	789.4	787.1	784.8	780.1
132.5°	827.7	839.3	840.5	834.7	831.2
135°	874.2	886.9	889.2	888.1	884.6
137.5°	925.2	935.7	938.0	936.8	932.2
140°	970.5	981.0	986.8	986.8	982.1
142.5°	1016.9	1027.4	1030.9	1032.0	1027.4
145°	1061.1	1069.2	1076.1	1077.3	1072.7
147.5°	1100.5	1111.0	1115.6	1117.9	1113.3
150°	1141.2	1148.1	1152.8	1156.3	1152.8
152.5°	1177.1	1184.1	1189.9	1194.6	1189.9
155°	1213.1	1216.6	1220.1	1225.9	1222.4
157.5°	1244.5	1246.8	1249.1	1257.2	1251.4
160°	1272.3	1274.7	1275.8	1282.8	1278.1
162.5°	1297.9	1297.9	1299.0	1307.2	1301.4
165°	1319.9	1318.8	1318.8	1326.9	1321.1
167.5°	1339.7	1336.2	1336.2	1344.3	1338.5
170°	1354.8	1351.3	1350.1	1358.2	1351.3
172.5°	1365.2	1361.7	1360.6	1368.7	1361.7
175°	1373.3	1369.9	1367.5	1375.7	1368.7
177.5°	1378.0	1374.5	1372.2	1379.1	1372.2
180°	1375.7	1375.7	1375.7	1375.7	1375.7

(END OF REPORT)