

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010416

Luminaire Tested: S123DIP-B1000D1195UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010416
REPORT IS A COMBINATION OF REPORTS P989095 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D1195UB2750-4F0-XX-W2A-D_3500K
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8980.0 lumens
Efficiency: N/A
Efficacy: 109.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010416

CATALOG NUMBER: S123DIP-B1000D1195UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1010416

CATALOG NUMBER: S123DIP-B1000D1195UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50
1	95	91	86	83	87	83	79	76	68	66	63	55	53	51	42	41	40
2	86	79	72	67	78	72	66	62	59	55	52	48	45	42	37	35	33
3	79	69	61	55	71	63	56	51	52	47	43	42	38	35	32	30	28
4	72	61	53	46	65	56	48	43	46	41	36	37	33	30	29	26	24
5	66	54	46	39	60	49	42	37	41	35	31	33	29	26	26	23	20
6	60	48	40	34	55	44	37	32	37	31	27	30	26	22	23	20	18
7	56	43	35	30	51	40	33	28	33	28	24	27	23	20	21	18	16
8	52	39	31	26	47	36	29	24	30	25	21	25	20	17	19	16	14
9	48	36	28	23	44	33	26	22	28	22	19	23	19	16	18	15	13
10	45	33	25	21	41	30	24	19	25	20	17	21	17	14	17	14	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13426	13426	13426
5°	13463	13032	13021
10°	13337	12679	12583
15°	13160	12289	12116
20°	12910	11855	11616
25°	12602	11366	11098
30°	12287	10923	10578
35°	11931	10459	10154
40°	11594	10033	9706
45°	11220	9621	9337
50°	10848	9214	8937
55°	10439	8796	8568
60°	10037	8369	8190
65°	9624	7913	7749
70°	9003	7402	7293
75°	8217	6818	6823
80°	7302	6228	6287
85°	6397	5750	5902

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11220 cd/sqm

TEST NUMBER: P1010416

CATALOG NUMBER: S123DIP-B1000D1195UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.3	1.3
10°-20°	337.3	3.8
20°-30°	504.4	5.6
30°-40°	602.3	6.7
40°-50°	630.1	7.0
50°-60°	591.3	6.6
60°-70°	493.9	5.5
70°-80°	353.2	3.9
80°-90°	213.3	2.4
90°-100°	187.4	2.1
100°-110°	364.7	4.1
110°-120°	720.6	8.0
120°-130°	869.5	9.7
130°-140°	905.9	10.1
140°-150°	835.1	9.3
150°-160°	670.8	7.5
160°-170°	432.9	4.8
170°-180°	149.2	1.7
0°-30°	960.1	10.7
0°-40°	1562.3	17.4
0°-60°	2783.8	31.0
0°-90°	3844.1	42.8
90°-120°	1272.6	14.2
90°-150°	3883.0	43.2
90°-180°	5136.0	57.2
0°-180°	8980.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1247	1247	1247	1247	1247	
5°	1249	1246	1238	1249	1247	118
15°	1189	1193	1192	1205	1204	335
25°	1073	1087	1091	1109	1109	495
35°	924	946	963	984	989	578
45°	756	788	822	848	859	583
55°	576	621	670	706	717	516
65°	398	451	511	552	565	394
75°	216	280	348	393	409	231
85°	67	134	206	253	266	69
90°	19	97	182	232	248	17
95°	86	91	171	221	234	97
105°	358	404	357	189	204	379
115°	659	682	741	786	801	651
125°	923	932	976	1007	1019	825
135°	1147	1152	1172	1200	1203	883
145°	1321	1328	1330	1344	1349	827
155°	1454	1452	1453	1459	1452	670
165°	1533	1530	1529	1538	1530	433
175°	1570	1564	1565	1573	1564	149
180°	1570	1570	1570	1570	1570	

TEST NUMBER: P1010416

CATALOG NUMBER: S123DIP-B1000D1195UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1247.3	1247.3	1247.3	1247.3	1247.3
2.5°	1254.1	1250.0	1239.2	1250.0	1248.7
5°	1248.7	1246.0	1237.8	1248.7	1247.3
7.5°	1239.2	1239.2	1231.0	1244.6	1243.3
10°	1225.6	1228.3	1221.5	1235.1	1232.4
12.5°	1209.3	1213.4	1209.3	1221.5	1218.8
15°	1188.9	1193.0	1191.6	1205.2	1203.8
17.5°	1164.4	1172.6	1171.2	1183.5	1180.7
20°	1137.3	1145.4	1148.1	1160.4	1161.7
22.5°	1108.7	1116.9	1121.0	1137.3	1135.9
25°	1073.4	1087.0	1091.1	1108.7	1108.7
27.5°	1039.4	1054.4	1062.5	1077.5	1078.8
30°	1002.8	1020.4	1031.3	1047.6	1047.6
32.5°	962.0	982.4	997.3	1015.0	1019.1
35°	923.9	945.7	963.4	983.7	989.2
37.5°	883.2	907.6	928.0	951.1	955.2
40°	842.4	866.9	894.1	917.2	922.6
42.5°	797.6	828.8	857.4	883.2	891.3
45°	755.5	788.1	822.0	847.9	858.7
47.5°	710.6	747.3	785.4	813.9	822.0
50°	667.1	705.2	747.3	778.6	788.1
52.5°	620.9	661.7	709.3	741.9	754.1
55°	576.1	620.9	669.9	706.5	717.4
57.5°	532.6	578.8	631.8	668.5	680.7
60°	486.4	535.3	591.1	629.1	644.0
62.5°	443.0	493.2	553.0	591.1	604.6
65°	398.1	451.1	510.9	551.7	565.2
67.5°	353.3	409.0	468.8	513.6	524.5
70°	305.7	364.1	429.4	472.8	486.4
72.5°	262.2	320.7	388.6	433.4	447.0
75°	216.0	279.9	347.8	392.7	409.0
77.5°	176.6	240.5	308.4	356.0	368.2
80°	134.5	201.1	271.7	317.9	331.5
82.5°	97.8	165.8	237.8	284.0	297.6
85°	66.6	134.5	206.5	252.7	266.3
87.5°	40.8	108.7	178.0	224.2	237.8
90°	18.9	97.0	181.5	232.4	248.3
92.5°	43.1	94.5	173.0	226.0	239.3
95°	86.0	91.2	170.6	220.9	234.5
97.5°	143.0	159.3	163.7	213.7	228.5
100°	209.3	276.1	156.7	205.4	220.2
102.5°	284.9	338.1	196.4	195.9	211.8
105°	358.4	403.8	357.3	189.0	203.5
107.5°	435.1	474.1	547.4	404.4	264.0
110°	511.9	545.7	612.9	609.7	453.9

TEST NUMBER: P1010416

CATALOG NUMBER: S123DIP-B1000D1195UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	586.6	613.7	678.2	722.7	732.5
115°	658.6	681.9	741.3	785.6	801.2
117.5°	730.9	750.0	802.0	844.0	855.9
120°	796.0	813.3	861.7	902.2	911.7
122.5°	863.6	874.6	921.4	957.1	967.8
125°	923.0	932.3	976.4	1007.2	1019.0
127.5°	983.6	991.5	1031.4	1062.1	1069.2
130°	1039.6	1047.5	1079.4	1109.8	1115.7
132.5°	1091.8	1101.1	1125.0	1154.2	1160.2
135°	1146.6	1152.3	1171.9	1199.9	1203.2
137.5°	1193.3	1201.3	1213.1	1240.7	1245.1
140°	1238.6	1245.6	1253.1	1278.2	1282.6
142.5°	1281.8	1287.3	1290.8	1312.0	1315.3
145°	1321.4	1328.2	1330.5	1343.7	1349.1
147.5°	1358.5	1364.3	1366.6	1373.1	1372.6
150°	1393.5	1397.0	1399.3	1401.6	1400.8
152.5°	1424.9	1426.1	1427.3	1431.9	1426.1
155°	1454.1	1451.8	1452.9	1458.8	1451.8
157.5°	1477.4	1477.4	1476.3	1483.2	1473.9
160°	1498.4	1497.2	1496.1	1503.1	1494.9
162.5°	1518.2	1514.7	1513.6	1521.7	1514.7
165°	1533.4	1529.9	1528.7	1538.1	1529.9
167.5°	1546.2	1541.6	1541.6	1550.9	1541.6
170°	1556.7	1552.0	1552.0	1561.4	1552.0
172.5°	1563.7	1557.9	1559.0	1568.4	1557.9
175°	1569.5	1563.7	1564.9	1573.0	1563.7
177.5°	1571.9	1566.0	1567.2	1576.5	1564.9
180°	1569.5	1569.5	1569.5	1569.5	1569.5

(END OF REPORT)