

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010420

Luminaire Tested: S123DIP-B1000D1195UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010420
REPORT IS A COMBINATION OF REPORTS P989099 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D1195UB2750-4F0-XX-W2A-F_3000K
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8862.0 lumens
Efficiency: N/A
Efficacy: 108.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010420

CATALOG NUMBER: S123DIP-B1000D1195UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010420

CATALOG NUMBER: S123DIP-B1000D1195UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53
1	97	93	89	85	89	85	82	79	71	69	67	58	57	55	46	45	44
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	41	39	37
3	80	71	64	58	74	65	59	54	55	50	46	45	42	39	36	34	32
4	74	63	55	49	67	58	51	46	49	44	39	40	36	33	32	30	27
5	67	56	48	42	62	52	44	39	44	38	34	36	32	29	29	26	24
6	62	50	42	36	57	46	39	34	39	34	30	33	28	25	26	23	21
7	57	45	37	32	53	42	35	30	36	30	26	30	25	22	24	21	19
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17
9	50	37	30	25	45	35	28	23	30	24	21	25	21	18	20	17	15
10	46	34	27	22	43	32	25	21	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16937	16937	16937
5°	16979	16352	16328
10°	16828	15798	15636
15°	16593	15222	14883
20°	16326	14585	14137
25°	15978	13910	13339
30°	15598	13212	12499
35°	15200	12498	11666
40°	14784	11751	10845
45°	14325	11021	9988
50°	13859	10209	9129
55°	13262	9362	8257
60°	12647	8428	7329
65°	12067	7417	6363
70°	11235	6297	5234
75°	10035	4987	4062
80°	8665	3505	2873
85°	6762	1882	1438

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14325 cd/sqm

TEST NUMBER: P1010420

CATALOG NUMBER: S123DIP-B1000D1195UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.3	1.7
10°-20°	418.8	4.7
20°-30°	618.6	7.0
30°-40°	722.5	8.2
40°-50°	726.3	8.2
50°-60°	638.0	7.2
60°-70°	475.2	5.4
70°-80°	270.4	3.1
80°-90°	80.0	0.9
90°-100°	55.1	0.6
100°-110°	266.4	3.0
110°-120°	652.9	7.4
120°-130°	828.8	9.4
130°-140°	885.4	10.0
140°-150°	827.9	9.3
150°-160°	667.8	7.5
160°-170°	431.0	4.9
170°-180°	148.5	1.7
0°-30°	1185.8	13.4
0°-40°	1908.2	21.5
0°-60°	3272.5	36.9
0°-90°	4098.1	46.2
90°-120°	974.4	11.0
90°-150°	3516.6	39.7
90°-180°	4764.0	53.8
0°-180°	8862.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1574	1574	1574	1574	1574	
5°	1575	1568	1553	1567	1564	149
15°	1499	1494	1476	1487	1479	423
25°	1361	1353	1335	1337	1333	627
35°	1177	1169	1151	1143	1136	736
45°	965	959	942	925	919	745
55°	732	731	713	698	691	656
65°	499	492	479	468	464	493
75°	264	258	254	248	244	282
85°	70	68	68	65	65	75
90°	1	13	28	32	35	9
95°	71	23	36	44	44	85
105°	346	359	254	49	51	367
115°	649	656	666	678	683	641
125°	915	924	929	931	933	817
135°	1139	1146	1150	1154	1150	877
145°	1314	1322	1325	1327	1327	823
155°	1448	1445	1447	1452	1445	667
165°	1527	1523	1522	1531	1523	431
175°	1563	1557	1558	1566	1557	149
180°	1563	1563	1563	1563	1563	

TEST NUMBER: P1010420

CATALOG NUMBER: S123DIP-B1000D1195UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1573.5	1573.5	1573.5	1573.5	1573.5
2.5°	1580.2	1574.8	1559.9	1573.5	1572.1
5°	1574.8	1568.0	1553.2	1566.7	1564.0
7.5°	1562.6	1555.9	1541.0	1553.2	1551.8
10°	1546.4	1539.6	1522.0	1534.2	1531.5
12.5°	1524.7	1519.3	1503.1	1511.2	1509.9
15°	1499.0	1493.6	1476.0	1486.9	1478.7
17.5°	1470.6	1463.9	1446.3	1454.4	1451.7
20°	1438.2	1430.0	1412.5	1417.9	1413.8
22.5°	1401.6	1393.5	1375.9	1380.0	1374.6
25°	1361.0	1352.9	1335.3	1336.7	1332.6
27.5°	1319.1	1311.0	1292.0	1293.4	1289.3
30°	1273.1	1266.3	1247.4	1247.4	1237.9
32.5°	1227.1	1217.6	1204.1	1194.6	1190.6
35°	1177.0	1168.9	1151.3	1143.2	1136.5
37.5°	1127.0	1116.2	1098.6	1089.1	1085.0
40°	1074.2	1066.1	1047.2	1036.3	1030.9
42.5°	1021.5	1012.0	993.0	982.2	976.8
45°	964.6	959.2	941.6	925.4	918.6
47.5°	909.2	901.0	884.8	868.6	863.2
50°	852.3	845.6	828.0	813.1	805.0
52.5°	792.8	788.8	769.8	757.6	749.5
55°	731.9	730.6	713.0	698.1	691.3
57.5°	675.1	669.7	656.2	642.6	634.5
60°	612.9	611.5	595.3	583.1	576.3
62.5°	557.4	553.3	537.1	524.9	520.9
65°	499.2	492.5	478.9	468.1	464.1
67.5°	437.0	431.6	420.8	411.3	405.9
70°	381.5	373.4	365.3	355.8	349.1
72.5°	323.3	317.9	308.5	300.3	297.6
75°	263.8	258.4	254.4	247.6	243.5
77.5°	211.1	208.4	202.9	197.5	197.5
80°	159.6	155.6	152.9	151.5	151.5
82.5°	109.6	109.6	109.6	106.9	105.5
85°	70.4	67.6	67.6	64.9	64.9
87.5°	35.2	31.1	29.8	28.4	28.4
90°	1.2	12.8	27.9	32.5	34.8
92.5°	26.7	19.7	30.2	38.3	39.5
95°	70.8	23.2	36.0	44.1	44.1
97.5°	128.9	96.4	37.2	46.4	47.6
100°	196.2	219.4	38.3	47.6	48.8
102.5°	272.8	287.9	85.9	47.6	49.9
105°	346.0	358.7	254.3	48.8	51.1
107.5°	423.8	434.2	451.6	272.8	120.7
110°	501.5	510.8	523.6	485.3	319.3

TEST NUMBER: P1010420

CATALOG NUMBER: S123DIP-B1000D1195UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	575.8	584.0	596.7	607.2	604.9
115°	649.0	655.9	666.4	678.0	682.6
117.5°	721.0	729.1	734.9	744.2	745.3
120°	787.1	797.6	801.1	810.4	810.4
122.5°	854.5	862.6	867.2	873.0	874.2
125°	914.8	924.1	928.8	931.1	933.4
127.5°	975.2	984.5	990.3	993.8	991.5
130°	1030.9	1040.2	1044.9	1049.5	1047.2
132.5°	1084.3	1093.6	1097.1	1101.8	1098.3
135°	1138.9	1145.9	1150.5	1154.0	1150.5
137.5°	1185.3	1194.6	1197.0	1202.8	1200.4
140°	1231.8	1238.7	1242.2	1246.9	1244.5
142.5°	1274.7	1281.7	1285.2	1288.7	1285.2
145°	1314.2	1322.3	1324.7	1327.0	1327.0
147.5°	1352.5	1358.3	1360.6	1363.0	1357.2
150°	1387.3	1390.8	1393.2	1395.5	1392.0
152.5°	1418.7	1419.9	1421.0	1425.7	1419.9
155°	1447.7	1445.4	1446.6	1452.4	1445.4
157.5°	1470.9	1470.9	1469.8	1476.7	1467.5
160°	1491.8	1490.7	1489.5	1496.5	1488.4
162.5°	1511.6	1508.1	1506.9	1515.1	1508.1
165°	1526.7	1523.2	1522.0	1531.3	1523.2
167.5°	1539.4	1534.8	1534.8	1544.1	1534.8
170°	1549.9	1545.2	1545.2	1554.5	1545.2
172.5°	1556.8	1551.0	1552.2	1561.5	1551.0
175°	1562.7	1556.8	1558.0	1566.1	1556.8
177.5°	1565.0	1559.2	1560.3	1569.6	1558.0
180°	1562.7	1562.7	1562.7	1562.7	1562.7

(END OF REPORT)