

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009840

Luminaire Tested: S122RDIP-B290D330UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009840
REPORT IS A COMBINATION OF REPORTS P988078 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B290D330UB30-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2184.0 lumens
Efficiency: N/A
Efficacy: 97.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009840

CATALOG NUMBER: S122RDIP-B290D330UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1009840

CATALOG NUMBER: S122RDIP-B290D330UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	53	53	53	46		
1	97	93	89	86	89	86	83	80	72	70	67	59	57	56	47	46	45	40		
2	89	82	76	71	81	75	70	66	63	60	57	52	50	47	42	40	39	34		
3	81	72	65	60	75	67	61	56	56	52	48	47	43	41	38	35	33	29		
4	75	64	57	51	68	59	53	48	50	45	41	42	38	35	34	31	29	26		
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26	22		
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23	20		
7	59	47	39	34	54	43	37	32	37	32	28	31	27	24	26	23	20	18		
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	18	16		
9	51	39	32	27	47	36	30	25	31	26	22	26	22	20	22	19	17	15		
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	20	17	15	13		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7736	7736	7736
5°	7748	7359	7305
10°	7672	6979	6750
15°	7566	6532	6117
20°	7427	6022	5454
25°	7284	5499	4849
30°	7092	4991	4187
35°	6903	4477	3620
40°	6713	3973	3034
45°	6491	3452	2524
50°	6261	2952	2056
55°	6022	2449	1632
60°	5744	1958	1234
65°	5425	1492	1004
70°	5037	1083	798
75°	4554	827	609
80°	3848	559	410
85°	2684	256	198

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6491 cd/sqm

TEST NUMBER: P1009840

CATALOG NUMBER: S122RDIP-B290D330UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.8	2.1
10°-20°	125.7	5.8
20°-30°	176.5	8.1
30°-40°	192.4	8.8
40°-50°	176.8	8.1
50°-60°	138.9	6.4
60°-70°	90.4	4.1
70°-80°	46.5	2.1
80°-90°	13.1	0.6
90°-100°	26.1	1.2
100°-110°	82.8	3.8
110°-120°	141.8	6.5
120°-130°	186.4	8.5
130°-140°	209.3	9.6
140°-150°	205.2	9.4
150°-160°	172.1	7.9
160°-170°	114.2	5.2
170°-180°	39.9	1.8
0°-30°	348.0	15.9
0°-40°	540.4	24.7
0°-60°	856.2	39.2
0°-90°	1006.2	46.1
90°-120°	250.7	11.5
90°-150°	851.6	39.0
90°-180°	1178.0	53.9
0°-180°	2184.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	489	489	489	489	489	
5°	489	486	481	485	483	46
15°	465	460	445	436	432	131
25°	422	408	378	360	354	194
35°	364	341	302	274	264	228
45°	297	268	221	190	179	230
55°	226	192	144	117	109	202
65°	153	117	77	62	61	151
75°	81	50	35	32	32	86
85°	19	10	8	8	8	22
90°	0	5	12	12	12	2
95°	18	22	23	23	22	21
105°	76	78	78	79	79	81
115°	142	144	144	143	142	141
125°	207	210	209	208	208	185
135°	268	272	272	272	271	207
145°	325	327	330	330	328	203
155°	372	373	374	375	374	171
165°	404	404	404	406	405	114
175°	421	420	419	421	419	40
180°	421	421	421	421	421	

TEST NUMBER: P1009840

CATALOG NUMBER: S122RDIP-B290D330UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	488.7	488.7	488.7	488.7	488.7
2.5°	490.9	488.7	483.8	488.2	487.3
5°	488.7	486.5	480.7	484.7	483.4
7.5°	484.7	482.0	475.8	477.6	475.4
10°	479.4	476.3	467.4	466.1	463.5
12.5°	472.7	468.8	456.8	454.2	449.3
15°	464.8	459.9	444.9	436.5	432.1
17.5°	455.5	448.4	429.8	420.1	413.0
20°	444.9	436.0	413.9	402.9	393.1
22.5°	433.4	423.2	397.6	382.5	375.9
25°	421.9	407.7	378.5	360.4	353.8
27.5°	408.2	393.1	360.9	340.1	329.9
30°	393.6	376.8	341.4	318.8	306.9
32.5°	379.4	359.1	322.8	296.3	285.2
35°	363.5	341.0	302.0	274.2	264.5
37.5°	348.0	323.7	282.6	252.1	241.0
40°	331.7	305.1	262.2	230.8	219.3
42.5°	314.9	286.6	241.9	209.2	198.1
45°	297.2	267.5	221.1	189.7	179.1
47.5°	280.4	249.0	201.2	169.8	160.1
50°	261.8	230.4	181.8	151.2	142.0
52.5°	243.7	210.5	163.2	134.0	125.6
55°	226.0	191.5	143.7	117.2	108.8
57.5°	207.8	172.5	126.5	101.7	94.6
60°	189.3	153.9	108.3	85.8	78.7
62.5°	171.1	135.8	92.9	71.6	68.1
65°	152.6	116.7	76.9	61.9	60.6
67.5°	134.9	99.1	61.9	54.4	53.1
70°	116.3	81.8	51.3	46.9	45.1
72.5°	98.6	65.9	42.9	39.4	38.5
75°	81.4	50.4	35.4	32.3	31.8
77.5°	64.1	35.8	27.9	26.1	25.2
80°	48.2	25.6	21.2	19.5	19.5
82.5°	33.6	17.2	14.6	13.7	13.7
85°	19.0	9.7	8.4	8.4	8.4
87.5°	7.1	3.5	3.5	3.1	3.1
90°	0.4	4.6	12.4	11.7	12.1
92.5°	7.8	10.7	11.0	11.4	11.4
95°	18.5	22.0	22.8	22.8	22.0
97.5°	30.9	34.1	35.6	35.6	35.6
100°	45.1	48.0	49.1	49.1	48.7
102.5°	60.1	62.2	63.6	64.0	63.6
105°	76.4	77.5	78.2	78.9	78.9
107.5°	92.8	94.2	94.2	94.6	92.8
110°	108.4	110.6	110.6	110.6	109.5



TEST NUMBER: P1009840

CATALOG NUMBER: S122RDIP-B290D330UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	125.5	127.6	127.3	126.2	125.5
115°	142.2	144.3	143.6	143.3	142.2
117.5°	158.9	161.8	160.0	158.9	157.8
120°	175.6	178.5	175.6	175.6	174.6
122.5°	190.9	194.5	192.7	191.6	190.9
125°	206.9	210.1	209.0	208.0	207.6
127.5°	222.5	226.5	225.0	223.6	222.5
130°	237.1	241.7	241.0	240.3	238.9
132.5°	253.5	257.0	257.4	255.6	254.5
135°	267.7	271.6	272.3	272.0	270.9
137.5°	283.3	286.5	287.2	286.9	285.5
140°	297.2	300.4	302.2	302.2	300.8
142.5°	311.4	314.6	315.7	316.0	314.6
145°	324.9	327.4	329.6	329.9	328.5
147.5°	337.0	340.2	341.6	342.4	340.9
150°	349.5	351.6	353.0	354.1	353.0
152.5°	360.5	362.6	364.4	365.8	364.4
155°	371.5	372.6	373.6	375.4	374.3
157.5°	381.1	381.8	382.5	385.0	383.2
160°	389.6	390.3	390.7	392.8	391.4
162.5°	397.5	397.5	397.8	400.3	398.5
165°	404.2	403.9	403.9	406.3	404.6
167.5°	410.3	409.2	409.2	411.7	409.9
170°	414.9	413.8	413.5	415.9	413.8
172.5°	418.1	417.0	416.7	419.1	417.0
175°	420.6	419.5	418.8	421.3	419.1
177.5°	422.0	420.9	420.2	422.3	420.2
180°	421.3	421.3	421.3	421.3	421.3

(END OF REPORT)