

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009844

Luminaire Tested: S122RDIP-B290D330UB35-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009844
REPORT IS A COMBINATION OF REPORTS P988082 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B290D330UB35-4F0-XX-W2A-A4
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2398.0 lumens
Efficiency: N/A
Efficacy: 107.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009844

CATALOG NUMBER: S122RDIP-B290D330UB35-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1009844

CATALOG NUMBER: S122RDIP-B290D330UB35-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	53	53	53
1	98	94	90	87	90	86	83	80	72	70	68	59	58	57	47	47	46
2	89	83	77	72	82	76	71	67	64	61	58	53	51	48	43	41	40
3	82	73	66	61	75	68	62	57	57	53	49	48	44	42	39	36	35
4	76	65	58	52	69	61	54	49	51	47	43	43	39	37	35	33	31
5	70	59	51	45	64	54	48	43	46	41	37	39	35	32	32	29	27
6	64	53	45	40	59	49	42	38	42	37	33	36	32	29	29	27	24
7	60	48	41	35	55	45	38	33	39	33	30	33	29	26	27	24	22
8	56	44	37	31	51	41	34	30	35	30	27	30	26	23	25	22	20
9	52	40	33	28	48	38	31	27	33	28	24	28	24	21	23	20	18
10	49	37	30	26	45	35	29	24	30	25	22	26	22	19	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10112	10112	10112	10112
5°	10136	10742	10171	8581
10°	10024	11353	10096	7086
15°	9806	11356	9972	5323
20°	9545	9388	9752	4391
25°	9228	5866	9428	3736
30°	8823	3755	9063	3216
35°	8330	2887	8599	2752
40°	7782	2427	8114	2407
45°	7194	2065	7495	2021
50°	6593	1755	6901	1749
55°	5926	1525	6246	1504
60°	5335	1162	5617	1149
65°	4781	874	5066	992
70°	4170	699	4500	808
75°	3524	536	3849	612
80°	2802	364	3010	402
85°	1949	188	2133	198

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 9250 cd/sqm

TEST NUMBER: P1009844

CATALOG NUMBER: S122RDIP-B290D330UB35-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.6	2.5
10°-20°	169.1	7.1
20°-30°	217.7	9.1
30°-40°	206.5	8.6
40°-50°	177.0	7.4
50°-60°	134.8	5.6
60°-70°	85.0	3.5
70°-80°	42.4	1.8
80°-90°	12.1	0.5
90°-100°	72.4	3.0
100°-110°	254.9	10.6
110°-120°	267.7	11.2
120°-130°	220.2	9.2
130°-140°	176.9	7.4
140°-150°	133.6	5.6
150°-160°	93.9	3.9
160°-170°	55.3	2.3
170°-180°	18.0	0.8
0°-30°	447.4	18.7
0°-40°	653.9	27.3
0°-60°	965.7	40.3
0°-90°	1105.2	46.1
90°-120°	594.9	24.8
90°-150°	1125.6	46.9
90°-180°	1293.0	53.9
0°-180°	2398.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	639	639	639	639	639	
5°	639	711	642	568	639	61
15°	602	802	613	376	602	169
25°	534	428	546	273	534	245
35°	439	211	453	201	439	274
45°	329	146	343	143	329	254
55°	222	102	234	100	222	200
65°	134	53	142	60	134	133
75°	63	28	69	32	63	68
85°	14	8	15	8	14	16
90°	0	12	0	12	0	2
95°	12	41	12	41	12	13
105°	44	402	44	402	44	46
115°	77	529	77	529	77	76
125°	107	430	107	430	107	95
135°	126	356	126	356	126	97
145°	144	284	144	284	144	90
155°	163	239	163	239	163	75
165°	178	210	178	210	178	50
175°	185	189	185	189	185	18
180°	186	186	186	186	186	

TEST NUMBER: P1009844

CATALOG NUMBER: S122RDIP-B290D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8
2.5°	642.8	645.5	646.8	648.6	652.6	655.3	659.3	660.2	659.7	661.5	656.6
5°	639.3	645.1	650.4	654.8	661.9	666.4	671.3	677.0	678.4	685.0	681.0
7.5°	634.4	642.8	650.4	659.3	669.9	675.7	683.2	692.1	696.1	704.1	706.3
10°	626.4	638.4	651.3	660.6	675.2	685.5	692.6	706.8	716.1	728.1	726.3
12.5°	613.5	629.1	646.4	661.9	681.0	687.7	701.0	715.6	727.6	738.7	748.5
15°	602.4	620.2	639.3	658.4	680.1	692.6	705.9	725.0	737.8	757.4	765.8
17.5°	587.3	610.0	632.6	653.9	679.7	693.9	710.3	729.0	748.1	766.7	773.4
20°	571.8	596.2	620.6	649.5	678.8	692.6	709.4	732.5	751.2	765.8	765.8
22.5°	553.2	582.9	610.9	638.4	670.4	690.3	707.7	734.7	748.1	751.2	739.2
25°	534.5	564.3	594.9	629.1	665.5	683.2	702.8	728.1	732.5	720.1	689.0
27.5°	512.3	545.6	580.2	617.1	655.3	677.5	695.2	712.1	703.7	670.4	622.0
30°	489.7	525.6	564.7	599.8	645.9	666.4	681.5	686.3	659.7	605.5	542.9
32.5°	466.1	501.2	542.5	584.7	631.3	650.8	660.6	647.7	598.9	530.5	454.2
35°	438.6	478.1	521.2	565.1	611.3	626.0	631.7	600.2	537.6	449.3	373.4
37.5°	413.8	453.3	499.4	544.3	589.1	597.1	591.3	542.1	462.6	375.1	301.0
40°	384.5	426.6	471.9	522.1	558.9	561.2	546.9	483.0	384.5	302.3	256.6
42.5°	357.4	400.0	445.3	496.3	524.3	516.8	497.7	413.8	321.0	260.6	223.8
45°	329.4	369.8	418.6	463.9	483.9	466.1	437.3	348.1	269.5	224.2	195.8
47.5°	302.3	340.1	388.5	432.0	435.5	415.5	381.4	291.7	233.5	197.1	174.0
50°	275.7	313.4	358.7	394.7	391.1	363.6	325.0	253.5	202.9	174.0	154.9
52.5°	249.1	283.2	327.2	355.6	340.5	313.9	275.7	214.9	177.1	151.8	137.2
55°	222.4	254.4	292.1	315.6	291.7	261.0	234.0	184.2	153.6	133.2	122.1
57.5°	200.2	225.5	260.2	274.4	245.5	221.5	198.0	158.5	133.2	118.5	105.7
60°	175.8	198.9	227.3	235.7	206.0	186.5	166.5	134.1	114.1	101.2	92.8
62.5°	154.9	174.0	195.8	195.8	169.6	154.9	139.8	112.3	95.9	85.7	81.7
65°	134.5	148.3	163.8	162.0	139.8	127.0	115.0	92.8	80.4	73.3	69.3
67.5°	114.5	125.2	135.4	129.2	113.2	102.1	91.0	75.0	66.6	61.7	56.4
70°	96.3	104.8	110.1	104.3	88.3	79.0	71.0	60.4	53.7	47.5	44.4
72.5°	80.8	84.4	86.1	79.0	65.7	60.4	54.6	47.1	41.3	38.2	37.3
75°	63.0	66.1	64.8	59.5	48.4	44.4	40.0	34.6	33.3	31.5	30.6
77.5°	49.3	49.3	47.1	42.2	34.6	31.5	29.7	27.1	25.7	25.3	24.4
80°	35.1	34.6	33.3	28.0	23.5	21.8	21.8	20.0	19.5	18.6	18.6
82.5°	23.1	23.1	21.3	16.9	15.5	15.1	14.7	13.8	13.8	13.3	13.3
85°	13.8	12.9	10.7	9.3	8.9	8.9	8.4	8.0	8.4	8.0	8.0
87.5°	6.2	4.9	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
90°	0.4	1.4	2.9	3.6	4.3	4.8	5.4	7.1	9.6	11.8	12.1
92.5°	5.4	7.5	10.4	12.1	15.0	17.0	18.9	28.6	42.1	54.3	55.0
95°	12.5	13.9	17.5	20.7	26.4	30.7	35.0	51.4	82.5	123.9	139.9
97.5°	18.6	20.7	24.6	29.3	35.7	40.5	45.3	66.4	109.6	176.4	228.1
100°	27.5	28.6	31.8	37.5	44.6	49.6	54.6	73.5	117.1	194.2	282.0
102.5°	35.7	36.4	39.6	45.3	52.8	57.8	62.8	80.0	117.5	187.4	283.8
105°	43.6	45.0	47.5	52.8	60.7	65.7	70.7	87.5	119.2	178.1	264.5
107.5°	52.1	53.2	55.7	60.7	68.5	73.5	78.5	95.0	123.2	173.1	246.7
110°	60.7	62.1	64.3	68.9	76.4	81.6	86.8	102.5	128.2	171.7	234.5

TEST NUMBER: P1009844

CATALOG NUMBER: S122RDIP-B290D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	68.5	70.0	72.5	76.8	83.9	89.2	94.6	109.6	133.5	172.1	226.7
115°	76.8	78.5	80.7	85.0	92.1	96.9	101.7	117.1	138.9	173.5	221.3
117.5°	85.3	86.8	88.9	92.8	99.6	104.6	109.6	123.9	144.6	175.6	218.5
120°	93.2	94.6	96.7	100.0	107.1	112.1	117.1	131.0	150.3	177.8	216.0
122.5°	100.7	101.7	103.9	107.5	114.6	119.8	125.0	137.8	155.3	180.3	214.6
125°	107.1	108.2	110.3	114.6	121.7	126.7	131.7	144.6	160.7	182.8	212.8
127.5°	112.5	113.9	116.7	121.4	128.2	133.4	138.5	151.0	165.6	185.3	211.7
130°	117.1	118.5	122.1	127.1	134.2	139.2	144.2	156.7	170.3	188.1	211.0
132.5°	121.4	123.2	127.1	132.4	139.9	144.9	149.9	161.7	174.9	191.0	210.6
135°	125.7	127.1	131.4	136.7	144.9	149.9	154.9	166.4	178.9	193.1	210.3
137.5°	129.6	131.4	135.7	141.4	149.6	154.2	158.9	170.3	182.1	195.3	210.3
140°	134.2	135.7	139.9	145.7	153.5	158.2	162.8	173.5	184.6	196.7	209.9
142.5°	138.9	139.9	143.9	149.6	157.1	161.4	165.6	176.0	186.7	197.8	209.9
145°	143.5	144.9	148.5	153.9	161.0	165.0	168.9	178.5	188.5	198.5	209.2
147.5°	148.5	149.6	153.2	158.2	164.2	167.8	171.4	180.6	189.6	198.8	208.1
150°	153.5	154.6	157.4	162.1	167.4	170.6	173.9	182.1	190.3	198.5	207.1
152.5°	158.5	158.9	161.7	165.6	170.6	173.5	176.4	183.5	190.6	197.8	205.3
155°	163.1	163.5	165.6	169.6	173.5	176.2	178.9	184.9	191.0	197.1	203.1
157.5°	167.1	167.4	169.2	172.8	176.0	178.3	180.6	186.0	191.0	195.6	201.0
160°	171.0	171.4	172.8	175.6	178.5	180.4	182.4	186.7	191.0	194.6	198.8
162.5°	174.9	174.6	176.0	178.1	180.6	182.0	183.5	187.1	190.6	193.5	197.1
165°	177.8	177.4	178.1	180.3	182.1	183.1	184.2	187.4	189.9	192.1	194.6
167.5°	180.3	179.9	180.6	182.1	183.5	184.2	184.9	187.4	189.6	190.6	192.4
170°	182.8	182.1	182.4	183.5	184.2	184.8	185.3	187.1	188.9	189.6	190.6
172.5°	184.2	183.9	183.5	184.6	184.9	185.2	185.6	186.7	187.8	188.1	188.5
175°	185.3	184.9	184.6	185.3	185.3	185.4	185.6	186.4	187.1	186.7	187.1
177.5°	186.0	185.3	184.9	185.6	185.6	185.6	185.6	186.0	186.7	186.0	185.6
180°	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6

TEST NUMBER: P1009844

CATALOG NUMBER: S122RDIP-B290D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8
2.5°	661.5	662.4	663.7	669.9	670.8	672.6	671.7	671.7	672.1	671.3	671.7
5°	689.9	691.2	697.9	705.4	707.2	705.4	707.7	710.8	710.8	710.8	709.9
7.5°	716.5	721.4	729.0	740.1	742.3	744.5	748.5	745.8	746.7	750.7	749.4
10°	742.3	749.4	757.8	767.1	772.0	775.1	776.9	780.9	790.2	779.6	783.6
12.5°	766.7	776.9	785.8	796.0	799.6	803.5	804.9	808.4	808.4	808.0	811.1
15°	782.7	792.0	800.0	806.7	807.5	806.7	805.8	806.2	807.5	802.2	805.3
17.5°	786.2	787.1	789.8	787.1	787.6	778.2	772.9	771.6	759.2	759.6	769.8
20°	768.9	753.8	749.8	735.2	726.3	702.3	701.4	694.8	668.6	676.6	674.8
22.5°	721.4	695.7	661.5	644.6	636.2	610.9	591.3	577.6	568.3	558.9	554.9
25°	658.8	617.1	568.7	535.4	530.5	507.0	471.0	454.2	434.2	428.0	438.6
27.5°	578.0	523.9	469.3	418.2	408.9	387.6	369.4	357.4	334.3	333.0	333.8
30°	468.4	413.8	368.0	334.7	311.7	301.9	289.9	281.0	271.7	275.2	276.1
32.5°	384.9	333.0	290.3	272.6	261.9	255.7	245.5	239.7	235.7	234.4	234.0
35°	305.9	271.3	252.2	234.8	228.6	224.2	216.6	214.0	210.4	210.9	210.9
37.5°	261.9	233.1	218.9	210.0	204.2	202.0	197.1	194.4	192.2	191.3	192.7
40°	226.0	206.0	197.1	189.1	184.2	183.4	180.7	177.6	174.9	175.4	176.7
42.5°	199.8	188.2	177.6	171.4	167.8	166.5	164.3	162.0	162.0	160.7	160.3
45°	178.9	169.6	160.7	154.9	152.7	150.9	148.3	147.8	146.1	146.5	146.9
47.5°	160.3	152.7	146.1	140.3	138.1	137.6	135.0	133.2	133.2	132.7	132.3
50°	143.4	135.8	130.1	127.0	123.9	123.0	122.5	122.1	121.2	121.2	121.6
52.5°	129.6	122.1	117.6	115.0	113.2	112.3	112.3	111.9	111.9	111.9	111.4
55°	114.5	108.3	104.8	103.9	103.0	102.6	102.1	101.2	100.8	101.7	100.8
57.5°	100.3	98.1	95.0	94.1	91.9	91.9	90.6	89.7	88.8	89.7	89.7
60°	89.2	86.1	84.4	81.7	79.9	78.1	75.9	75.5	74.6	74.1	73.7
62.5°	77.7	75.0	70.6	66.6	63.9	62.2	61.3	60.8	60.8	60.4	60.4
65°	64.8	58.6	56.4	55.0	54.6	54.2	53.3	52.8	53.3	52.8	53.3
67.5°	50.6	49.7	48.4	47.5	47.1	46.6	46.6	46.2	46.2	46.2	46.2
70°	44.0	41.7	41.3	40.4	40.4	40.0	40.0	40.0	40.0	39.5	40.4
72.5°	36.4	35.1	34.6	34.2	34.2	34.2	33.7	33.7	33.7	33.3	33.7
75°	29.7	29.3	28.4	28.4	28.0	28.4	28.0	28.0	27.5	28.0	28.0
77.5°	24.0	23.5	23.1	23.1	22.6	22.6	22.6	22.6	22.6	22.6	23.1
80°	18.2	17.8	17.3	17.8	17.3	17.8	17.3	17.3	17.8	17.3	17.3
82.5°	13.3	12.9	12.9	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.4
85°	8.0	7.5	7.5	8.0	7.5	8.0	7.5	7.5	7.5	8.0	8.0
87.5°	3.6	4.0	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	4.0
90°	11.8	11.4	10.7	11.4	11.6	11.8	11.8	11.8	11.8	11.8	11.8
92.5°	46.1	36.1	30.7	26.8	25.4	23.9	23.6	22.1	22.5	21.8	22.5
95°	122.5	93.5	71.8	56.8	52.8	48.9	44.3	41.4	40.3	40.7	40.3
97.5°	229.9	191.4	152.8	116.7	106.0	95.3	81.4	74.3	70.3	68.2	70.3
100°	333.4	325.9	281.7	232.8	211.2	189.6	159.9	144.6	134.2	127.8	134.2
102.5°	372.0	414.1	412.7	380.2	357.0	333.8	301.0	272.0	258.5	249.2	258.5
105°	359.5	433.8	474.1	478.7	472.8	467.0	444.8	422.7	407.3	402.3	407.3
107.5°	333.1	412.7	472.7	507.7	514.8	521.9	521.6	518.4	513.7	505.5	513.7
110°	308.4	383.8	447.7	493.4	508.0	522.7	538.0	544.8	548.0	547.6	548.0

TEST NUMBER: P1009844

CATALOG NUMBER: S122RDIP-B290D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	291.3	357.4	418.0	467.7	485.0	502.3	525.1	537.6	544.4	546.9	544.4
115°	277.7	336.7	391.6	438.4	456.8	475.2	500.5	516.9	526.2	529.4	526.2
117.5°	268.5	319.5	368.8	412.3	429.8	447.3	473.4	490.9	500.5	503.0	500.5
120°	261.3	307.4	351.6	389.5	405.8	422.0	447.0	463.7	474.1	477.7	474.1
122.5°	255.3	297.7	337.4	372.7	387.0	401.3	423.0	439.5	448.4	451.2	448.4
125°	249.5	288.5	325.2	356.6	370.0	383.4	404.1	417.7	426.6	429.5	426.6
127.5°	244.2	279.2	313.1	343.1	355.6	368.1	386.3	399.1	407.0	409.1	407.0
130°	238.8	270.3	301.0	329.2	341.0	352.7	370.2	382.3	389.5	392.3	389.5
132.5°	234.5	261.7	289.5	314.9	325.8	336.7	353.8	365.9	372.4	374.9	372.4
135°	230.6	253.8	277.4	301.0	311.0	320.9	336.3	348.1	354.5	355.9	354.5
137.5°	227.8	247.4	267.8	287.0	296.0	304.9	319.5	329.9	335.6	337.7	335.6
140°	225.3	241.3	258.5	274.9	282.8	290.6	302.0	311.3	316.7	318.8	316.7
142.5°	222.8	236.3	250.3	263.8	270.0	276.3	287.0	295.2	299.9	299.9	299.9
145°	220.6	231.7	243.5	254.5	259.7	264.9	273.5	279.5	283.1	284.2	283.1
147.5°	218.5	228.1	237.8	246.7	250.6	254.5	262.0	267.0	269.5	270.3	269.5
150°	215.6	224.2	232.1	239.5	242.8	246.0	251.3	255.6	257.8	258.1	257.8
152.5°	213.1	220.3	227.4	233.5	236.2	238.8	242.8	246.3	247.8	247.8	247.8
155°	209.9	216.7	222.4	227.8	229.8	231.7	235.6	238.1	239.5	238.8	239.5
157.5°	207.1	212.4	217.4	222.1	223.7	225.3	228.1	230.3	231.0	231.0	231.0
160°	203.8	208.5	212.4	216.3	217.6	218.8	221.3	223.1	223.5	223.5	223.5
162.5°	201.0	204.6	207.8	211.0	211.9	212.8	215.3	216.3	216.7	216.3	216.7
165°	197.8	200.6	203.1	205.6	206.4	207.1	208.5	209.9	209.9	209.6	209.9
167.5°	194.6	196.7	198.8	200.6	201.4	202.1	202.8	203.5	203.5	203.1	203.5
170°	192.1	193.9	194.9	196.4	196.8	197.1	197.4	198.5	198.1	197.4	198.1
172.5°	189.6	190.6	191.4	192.4	192.6	192.8	193.1	193.5	193.1	192.8	193.1
175°	187.4	188.5	188.9	189.2	189.4	189.6	189.6	189.9	189.6	188.9	189.6
177.5°	186.0	186.7	186.7	187.1	187.1	187.1	187.1	187.1	186.7	186.0	186.7
180°	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6

TEST NUMBER: P1009844

CATALOG NUMBER: S122RDIP-B290D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8
2.5°	673.5	670.4	669.5	670.4	669.5	669.9	666.8	655.3	658.4	653.5	656.2
5°	711.7	709.0	703.2	702.3	701.4	700.6	696.1	685.9	681.9	675.2	674.8
7.5°	748.1	748.1	743.6	740.5	736.5	733.4	727.6	712.5	706.3	698.3	693.9
10°	784.0	772.5	777.4	774.2	764.5	762.7	752.1	743.2	731.2	723.2	716.1
12.5°	809.8	806.2	801.8	799.1	796.4	790.7	783.6	760.9	754.7	738.7	730.7
15°	808.9	806.7	808.0	808.0	807.1	805.8	800.0	783.6	772.9	757.4	743.6
17.5°	765.4	771.1	776.9	780.9	789.8	793.8	799.1	789.3	782.7	769.4	754.7
20°	689.5	703.7	720.5	724.1	732.1	755.6	766.3	774.7	777.4	772.9	760.9
22.5°	583.8	595.8	636.6	635.7	647.3	675.2	706.3	731.6	751.6	762.7	758.3
25°	457.3	474.1	495.9	512.3	550.1	591.8	630.4	670.8	705.4	736.1	743.6
27.5°	345.8	368.0	385.3	407.1	426.2	475.5	525.2	588.2	628.6	686.8	717.0
30°	279.7	289.9	307.2	317.4	326.7	364.5	420.9	483.0	554.0	621.1	673.0
32.5°	238.8	245.9	258.8	263.3	273.0	298.3	333.8	390.7	463.9	545.2	613.5
35°	214.4	222.0	224.6	228.6	236.6	252.6	277.0	318.3	384.5	463.9	545.6
37.5°	193.6	197.6	205.1	207.8	210.4	222.4	238.8	267.7	311.7	376.9	467.5
40°	178.9	181.1	185.1	187.3	189.1	197.6	212.2	231.7	264.1	313.9	397.3
42.5°	163.4	166.0	168.7	171.4	173.6	180.2	189.1	207.8	229.5	267.3	327.6
45°	148.3	150.1	153.2	154.9	158.0	163.4	171.4	184.2	203.8	227.7	276.6
47.5°	134.5	136.7	138.1	140.3	142.5	148.3	155.8	164.3	180.2	203.8	239.3
50°	122.1	124.7	126.5	127.0	128.7	134.1	140.3	149.6	159.8	178.0	209.1
52.5°	113.2	113.7	115.0	116.8	116.3	119.4	125.2	132.3	143.0	157.6	180.2
55°	103.0	104.3	105.2	105.7	105.7	108.3	111.4	118.1	126.5	138.5	157.6
57.5°	90.1	91.5	94.1	95.0	96.3	97.7	99.0	103.4	110.5	122.1	137.6
60°	76.8	77.7	80.4	82.1	83.0	86.6	88.3	91.9	95.9	104.3	119.0
62.5°	61.7	62.6	63.9	65.7	67.5	72.8	77.2	80.8	83.9	89.7	101.7
65°	53.7	54.2	55.0	55.5	55.9	58.2	62.2	67.0	72.8	77.2	84.4
67.5°	46.6	47.1	47.5	48.4	48.8	49.3	51.1	52.4	58.2	64.4	69.7
70°	40.0	40.8	41.3	41.3	41.7	42.6	43.5	45.3	47.1	50.2	56.8
72.5°	33.7	34.2	35.1	35.1	35.1	36.0	36.8	37.7	38.6	40.4	43.1
75°	28.0	28.9	28.9	28.9	29.3	29.3	30.2	31.1	32.0	33.3	34.2
77.5°	23.1	23.1	23.1	23.1	23.5	23.5	24.0	24.9	25.3	25.7	26.6
80°	17.3	17.8	17.8	17.8	18.2	18.2	18.2	19.1	19.5	19.5	20.4
82.5°	12.9	12.9	12.9	13.3	12.9	13.3	13.3	13.8	13.3	13.8	14.2
85°	8.0	8.0	8.0	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.9
87.5°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.4	4.0	4.0
90°	11.8	11.8	11.8	11.6	11.4	10.7	11.4	11.8	12.1	11.8	9.6
92.5°	22.1	23.6	23.9	25.4	26.8	30.7	36.1	46.1	55.0	54.3	42.1
95°	41.4	44.3	48.9	52.8	56.8	71.8	93.5	122.5	139.9	123.9	82.5
97.5°	74.3	81.4	95.3	106.0	116.7	152.8	191.4	229.9	228.1	176.4	109.6
100°	144.6	159.9	189.6	211.2	232.8	281.7	325.9	333.4	282.0	194.2	117.1
102.5°	272.0	301.0	333.8	357.0	380.2	412.7	414.1	372.0	283.8	187.4	117.5
105°	422.7	444.8	467.0	472.8	478.7	474.1	433.8	359.5	264.5	178.1	119.2
107.5°	518.4	521.6	521.9	514.8	507.7	472.7	412.7	333.1	246.7	173.1	123.2
110°	544.8	538.0	522.7	508.0	493.4	447.7	383.8	308.4	234.5	171.7	128.2

TEST NUMBER: P1009844

CATALOG NUMBER: S122RDIP-B290D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	537.6	525.1	502.3	485.0	467.7	418.0	357.4	291.3	226.7	172.1	133.5
115°	516.9	500.5	475.2	456.8	438.4	391.6	336.7	277.7	221.3	173.5	138.9
117.5°	490.9	473.4	447.3	429.8	412.3	368.8	319.5	268.5	218.5	175.6	144.6
120°	463.7	447.0	422.0	405.8	389.5	351.6	307.4	261.3	216.0	177.8	150.3
122.5°	439.5	423.0	401.3	387.0	372.7	337.4	297.7	255.3	214.6	180.3	155.3
125°	417.7	404.1	383.4	370.0	356.6	325.2	288.5	249.5	212.8	182.8	160.7
127.5°	399.1	386.3	368.1	355.6	343.1	313.1	279.2	244.2	211.7	185.3	165.6
130°	382.3	370.2	352.7	341.0	329.2	301.0	270.3	238.8	211.0	188.1	170.3
132.5°	365.9	353.8	336.7	325.8	314.9	289.5	261.7	234.5	210.6	191.0	174.9
135°	348.1	336.3	320.9	311.0	301.0	277.4	253.8	230.6	210.3	193.1	178.9
137.5°	329.9	319.5	304.9	296.0	287.0	267.8	247.4	227.8	210.3	195.3	182.1
140°	311.3	302.0	290.6	282.8	274.9	258.5	241.3	225.3	209.9	196.7	184.6
142.5°	295.2	287.0	276.3	270.0	263.8	250.3	236.3	222.8	209.9	197.8	186.7
145°	279.5	273.5	264.9	259.7	254.5	243.5	231.7	220.6	209.2	198.5	188.5
147.5°	267.0	262.0	254.5	250.6	246.7	237.8	228.1	218.5	208.1	198.8	189.6
150°	255.6	251.3	246.0	242.8	239.5	232.1	224.2	215.6	207.1	198.5	190.3
152.5°	246.3	242.8	238.8	236.2	233.5	227.4	220.3	213.1	205.3	197.8	190.6
155°	238.1	235.6	231.7	229.8	227.8	222.4	216.7	209.9	203.1	197.1	191.0
157.5°	230.3	228.1	225.3	223.7	222.1	217.4	212.4	207.1	201.0	195.6	191.0
160°	223.1	221.3	218.8	217.6	216.3	212.4	208.5	203.8	198.8	194.6	191.0
162.5°	216.3	215.3	212.8	211.9	211.0	207.8	204.6	201.0	197.1	193.5	190.6
165°	209.9	208.5	207.1	206.4	205.6	203.1	200.6	197.8	194.6	192.1	189.9
167.5°	203.5	202.8	202.1	201.4	200.6	198.8	196.7	194.6	192.4	190.6	189.6
170°	198.5	197.4	197.1	196.8	196.4	194.9	193.9	192.1	190.6	189.6	188.9
172.5°	193.5	193.1	192.8	192.6	192.4	191.4	190.6	189.6	188.5	188.1	187.8
175°	189.9	189.6	189.6	189.4	189.2	188.9	188.5	187.4	187.1	186.7	187.1
177.5°	187.1	187.1	187.1	187.1	187.1	186.7	186.7	186.0	185.6	186.0	186.7
180°	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6

TEST NUMBER: P1009844

CATALOG NUMBER: S122RDIP-B290D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8
2.5°	652.2	649.9	649.9	648.6	648.6	641.5	641.5	643.7	641.1	638.0	633.5
5°	669.0	664.1	662.8	661.0	655.3	646.4	642.8	641.5	636.2	629.5	622.0
7.5°	685.0	677.0	673.0	669.0	661.5	649.1	642.0	637.1	629.1	618.9	609.1
10°	700.6	690.3	680.1	675.2	664.6	649.1	638.8	630.9	619.3	605.5	591.8
12.5°	714.8	693.4	691.7	681.9	666.4	648.6	633.1	621.5	606.9	590.9	574.9
15°	727.2	705.4	694.8	685.9	665.5	643.3	626.9	612.6	593.1	574.9	555.4
17.5°	733.4	709.9	702.8	688.1	667.3	638.4	616.2	598.9	577.6	555.8	533.6
20°	739.6	712.1	700.6	690.3	661.9	629.1	604.2	584.2	560.7	535.0	510.5
22.5°	742.7	712.1	698.3	684.1	656.6	618.9	589.6	566.0	538.5	512.3	483.0
25°	737.4	709.4	693.0	678.4	647.3	606.4	572.7	546.1	516.8	487.0	457.3
27.5°	724.1	703.2	684.1	669.0	634.4	590.5	554.9	524.7	494.6	461.3	431.1
30°	699.2	689.9	674.8	657.9	620.2	576.2	534.1	503.0	469.7	436.4	404.9
32.5°	660.6	668.6	658.8	644.2	603.3	556.7	511.9	480.4	443.9	408.0	379.1
35°	613.5	642.0	636.6	626.4	585.6	535.8	491.0	452.8	416.4	380.0	351.2
37.5°	562.0	605.1	609.5	603.3	565.1	514.5	465.3	428.0	390.7	353.8	324.5
40°	491.5	557.6	571.8	574.5	543.8	488.8	437.3	400.9	364.0	328.1	292.6
42.5°	426.6	510.1	527.9	539.0	516.8	463.5	411.5	371.1	334.7	302.3	266.8
45°	365.8	452.8	481.7	495.9	486.1	434.6	380.9	343.2	309.9	280.1	245.9
47.5°	303.2	390.7	431.1	453.7	453.7	405.3	351.6	314.3	282.4	257.0	226.9
50°	261.5	334.3	376.0	405.8	413.8	375.6	325.0	288.6	258.4	230.9	207.8
52.5°	222.9	288.1	322.8	353.8	376.9	343.6	295.2	262.4	232.6	206.9	188.7
55°	192.7	241.5	273.0	307.2	333.0	311.2	266.4	234.4	208.7	187.3	171.8
57.5°	163.8	206.4	232.2	262.4	289.9	273.5	237.5	210.0	187.3	168.7	154.9
60°	139.4	174.0	194.0	217.5	251.7	240.2	210.4	185.1	166.9	150.1	138.5
62.5°	118.5	146.1	162.9	179.8	210.9	205.5	182.5	162.9	147.4	133.2	123.4
65°	97.2	119.9	133.2	147.8	172.7	174.9	156.3	142.5	128.3	115.9	107.0
67.5°	78.6	96.3	108.3	120.8	140.7	146.9	134.1	122.5	110.5	100.3	92.3
70°	63.5	75.9	84.8	94.6	111.0	118.5	111.9	103.9	94.1	85.7	78.6
72.5°	50.2	58.2	63.5	71.0	84.4	91.9	91.5	84.4	77.2	71.5	65.7
75°	36.8	43.1	47.5	52.4	63.0	70.1	71.9	68.8	61.7	57.3	52.8
77.5°	28.0	31.5	33.7	37.3	44.8	51.1	53.7	52.8	47.9	44.4	41.3
80°	21.3	22.2	23.1	24.4	30.6	36.4	38.2	37.7	35.1	33.7	30.2
82.5°	15.1	15.5	16.0	16.4	18.6	23.5	25.3	26.2	24.0	22.6	19.5
85°	8.9	9.3	9.3	10.2	10.7	12.0	15.1	15.1	14.7	12.9	12.4
87.5°	4.4	4.4	4.0	4.0	4.4	4.9	5.8	6.7	5.8	5.3	4.9
90°	7.1	5.4	4.8	4.3	3.6	2.9	1.4	0.4	1.4	2.9	3.6
92.5°	28.6	18.9	17.0	15.0	12.1	10.4	7.5	5.4	7.5	10.4	12.1
95°	51.4	35.0	30.7	26.4	20.7	17.5	13.9	12.5	13.9	17.5	20.7
97.5°	66.4	45.3	40.5	35.7	29.3	24.6	20.7	18.6	20.7	24.6	29.3
100°	73.5	54.6	49.6	44.6	37.5	31.8	28.6	27.5	28.6	31.8	37.5
102.5°	80.0	62.8	57.8	52.8	45.3	39.6	36.4	35.7	36.4	39.6	45.3
105°	87.5	70.7	65.7	60.7	52.8	47.5	45.0	43.6	45.0	47.5	52.8
107.5°	95.0	78.5	73.5	68.5	60.7	55.7	53.2	52.1	53.2	55.7	60.7
110°	102.5	86.8	81.6	76.4	68.9	64.3	62.1	60.7	62.1	64.3	68.9

TEST NUMBER: P1009844

CATALOG NUMBER: S122RDIP-B290D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	109.6	94.6	89.2	83.9	76.8	72.5	70.0	68.5	70.0	72.5	76.8
115°	117.1	101.7	96.9	92.1	85.0	80.7	78.5	76.8	78.5	80.7	85.0
117.5°	123.9	109.6	104.6	99.6	92.8	88.9	86.8	85.3	86.8	88.9	92.8
120°	131.0	117.1	112.1	107.1	100.0	96.7	94.6	93.2	94.6	96.7	100.0
122.5°	137.8	125.0	119.8	114.6	107.5	103.9	101.7	100.7	101.7	103.9	107.5
125°	144.6	131.7	126.7	121.7	114.6	110.3	108.2	107.1	108.2	110.3	114.6
127.5°	151.0	138.5	133.4	128.2	121.4	116.7	113.9	112.5	113.9	116.7	121.4
130°	156.7	144.2	139.2	134.2	127.1	122.1	118.5	117.1	118.5	122.1	127.1
132.5°	161.7	149.9	144.9	139.9	132.4	127.1	123.2	121.4	123.2	127.1	132.4
135°	166.4	154.9	149.9	144.9	136.7	131.4	127.1	125.7	127.1	131.4	136.7
137.5°	170.3	158.9	154.2	149.6	141.4	135.7	131.4	129.6	131.4	135.7	141.4
140°	173.5	162.8	158.2	153.5	145.7	139.9	135.7	134.2	135.7	139.9	145.7
142.5°	176.0	165.6	161.4	157.1	149.6	143.9	139.9	138.9	139.9	143.9	149.6
145°	178.5	168.9	165.0	161.0	153.9	148.5	144.9	143.5	144.9	148.5	153.9
147.5°	180.6	171.4	167.8	164.2	158.2	153.2	149.6	148.5	149.6	153.2	158.2
150°	182.1	173.9	170.6	167.4	162.1	157.4	154.6	153.5	154.6	157.4	162.1
152.5°	183.5	176.4	173.5	170.6	165.6	161.7	158.9	158.5	158.9	161.7	165.6
155°	184.9	178.9	176.2	173.5	169.6	165.6	163.5	163.1	163.5	165.6	169.6
157.5°	186.0	180.6	178.3	176.0	172.8	169.2	167.4	167.1	167.4	169.2	172.8
160°	186.7	182.4	180.4	178.5	175.6	172.8	171.4	171.0	171.4	172.8	175.6
162.5°	187.1	183.5	182.0	180.6	178.1	176.0	174.6	174.9	174.6	176.0	178.1
165°	187.4	184.2	183.1	182.1	180.3	178.1	177.4	177.8	177.4	178.1	180.3
167.5°	187.4	184.9	184.2	183.5	182.1	180.6	179.9	180.3	179.9	180.6	182.1
170°	187.1	185.3	184.8	184.2	183.5	182.4	182.1	182.8	182.1	182.4	183.5
172.5°	186.7	185.6	185.2	184.9	184.6	183.5	183.9	184.2	183.9	183.5	184.6
175°	186.4	185.6	185.4	185.3	185.3	184.6	184.9	185.3	184.9	184.6	185.3
177.5°	186.0	185.6	185.6	185.6	185.6	184.9	185.3	186.0	185.3	184.9	185.6
180°	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6

TEST NUMBER: P1009844

CATALOG NUMBER: S122RDIP-B290D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8
2.5°	631.7	632.2	633.5	629.5	623.3	620.6	612.6	611.3	610.0	610.0	611.3
5°	617.5	615.8	616.2	608.7	599.8	594.4	583.3	585.1	579.4	575.8	576.7
7.5°	602.0	597.1	596.7	586.9	575.8	566.0	554.5	551.8	546.5	540.3	537.6
10°	582.5	578.9	572.3	561.2	546.9	539.0	523.4	514.1	512.8	503.4	499.9
12.5°	562.5	556.3	549.6	534.1	518.1	505.2	493.7	483.5	476.4	468.4	463.0
15°	539.4	531.9	524.3	507.9	489.2	476.4	459.0	443.9	423.1	406.7	397.3
17.5°	514.1	505.7	495.4	477.2	459.0	441.3	409.3	391.6	376.9	367.1	361.4
20°	487.9	478.6	468.4	450.2	418.6	387.6	369.8	356.0	347.2	337.4	330.3
22.5°	460.4	450.6	439.5	411.1	377.8	356.0	342.3	329.4	316.5	311.2	307.7
25°	434.6	425.7	411.5	372.9	346.7	326.7	311.2	302.8	296.1	289.0	282.4
27.5°	408.0	391.6	371.6	339.2	322.8	302.3	291.2	285.0	273.5	268.6	265.5
30°	376.0	357.8	338.7	315.6	296.6	282.4	272.1	261.9	255.3	250.4	245.1
32.5°	343.6	326.3	314.3	290.3	276.1	261.5	251.7	245.5	235.7	232.6	230.4
35°	315.6	301.0	290.3	270.8	257.5	244.2	237.1	227.7	221.5	215.8	212.2
37.5°	288.1	280.1	269.0	252.6	238.4	227.7	218.0	214.9	206.4	203.3	199.8
40°	269.0	257.0	247.7	233.5	221.5	210.0	203.8	196.7	190.9	186.0	184.7
42.5°	245.9	237.1	231.7	216.2	203.8	197.1	189.6	181.6	177.1	173.1	168.3
45°	228.6	220.6	213.1	200.7	189.6	181.1	174.5	169.1	161.6	159.8	152.3
47.5°	210.4	202.4	196.7	184.2	174.0	166.0	161.2	154.1	147.8	143.8	140.3
50°	192.2	185.6	180.2	169.6	160.7	152.3	145.6	138.5	135.8	129.2	127.0
52.5°	174.9	170.5	164.7	154.5	145.6	138.5	131.4	125.6	121.6	118.1	115.4
55°	160.3	153.2	150.5	139.4	131.9	124.3	118.1	114.5	109.7	107.4	105.2
57.5°	143.8	139.8	135.4	127.0	118.5	111.4	107.0	101.7	99.0	96.3	94.6
60°	129.6	123.9	120.3	113.2	105.7	99.0	95.0	91.0	87.5	85.2	81.7
62.5°	113.2	108.8	106.5	99.0	92.8	86.6	83.0	79.0	76.4	72.4	67.9
65°	99.0	95.4	92.8	86.6	80.8	75.0	71.5	66.6	63.0	60.8	60.4
67.5°	86.6	83.9	79.9	74.1	68.4	63.9	59.9	55.9	55.5	54.6	54.6
70°	72.8	70.1	67.9	61.7	56.8	51.9	51.1	49.7	48.4	47.9	47.1
72.5°	60.8	58.6	55.9	50.6	45.7	44.4	43.5	42.6	41.3	40.8	40.4
75°	49.3	46.2	44.4	39.5	38.2	37.3	36.4	35.1	34.2	33.7	32.9
77.5°	37.7	34.6	34.6	32.0	31.1	29.7	28.9	28.0	27.5	26.6	26.6
80°	26.6	26.6	25.7	24.4	23.1	22.6	21.3	20.9	20.4	20.9	20.0
82.5°	19.5	17.8	17.8	16.9	16.0	15.5	14.7	14.7	14.2	14.2	14.2
85°	11.1	11.1	10.7	9.8	9.3	9.3	8.9	8.9	8.4	8.4	8.0
87.5°	4.4	4.0	4.4	4.0	4.0	3.6	3.6	3.6	3.1	3.6	3.1
90°	4.3	4.8	5.4	7.1	9.6	11.8	12.1	11.8	11.4	10.7	11.4
92.5°	15.0	17.0	18.9	28.6	42.1	54.3	55.0	46.1	36.1	30.7	26.8
95°	26.4	30.7	35.0	51.4	82.5	123.9	139.9	122.5	93.5	71.8	56.8
97.5°	35.7	40.5	45.3	66.4	109.6	176.4	228.1	229.9	191.4	152.8	116.7
100°	44.6	49.6	54.6	73.5	117.1	194.2	282.0	333.4	325.9	281.7	232.8
102.5°	52.8	57.8	62.8	80.0	117.5	187.4	283.8	372.0	414.1	412.7	380.2
105°	60.7	65.7	70.7	87.5	119.2	178.1	264.5	359.5	433.8	474.1	478.7
107.5°	68.5	73.5	78.5	95.0	123.2	173.1	246.7	333.1	412.7	472.7	507.7
110°	76.4	81.6	86.8	102.5	128.2	171.7	234.5	308.4	383.8	447.7	493.4

TEST NUMBER: P1009844

CATALOG NUMBER: S122RDIP-B290D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	83.9	89.2	94.6	109.6	133.5	172.1	226.7	291.3	357.4	418.0	467.7
115°	92.1	96.9	101.7	117.1	138.9	173.5	221.3	277.7	336.7	391.6	438.4
117.5°	99.6	104.6	109.6	123.9	144.6	175.6	218.5	268.5	319.5	368.8	412.3
120°	107.1	112.1	117.1	131.0	150.3	177.8	216.0	261.3	307.4	351.6	389.5
122.5°	114.6	119.8	125.0	137.8	155.3	180.3	214.6	255.3	297.7	337.4	372.7
125°	121.7	126.7	131.7	144.6	160.7	182.8	212.8	249.5	288.5	325.2	356.6
127.5°	128.2	133.4	138.5	151.0	165.6	185.3	211.7	244.2	279.2	313.1	343.1
130°	134.2	139.2	144.2	156.7	170.3	188.1	211.0	238.8	270.3	301.0	329.2
132.5°	139.9	144.9	149.9	161.7	174.9	191.0	210.6	234.5	261.7	289.5	314.9
135°	144.9	149.9	154.9	166.4	178.9	193.1	210.3	230.6	253.8	277.4	301.0
137.5°	149.6	154.2	158.9	170.3	182.1	195.3	210.3	227.8	247.4	267.8	287.0
140°	153.5	158.2	162.8	173.5	184.6	196.7	209.9	225.3	241.3	258.5	274.9
142.5°	157.1	161.4	165.6	176.0	186.7	197.8	209.9	222.8	236.3	250.3	263.8
145°	161.0	165.0	168.9	178.5	188.5	198.5	209.2	220.6	231.7	243.5	254.5
147.5°	164.2	167.8	171.4	180.6	189.6	198.8	208.1	218.5	228.1	237.8	246.7
150°	167.4	170.6	173.9	182.1	190.3	198.5	207.1	215.6	224.2	232.1	239.5
152.5°	170.6	173.5	176.4	183.5	190.6	197.8	205.3	213.1	220.3	227.4	233.5
155°	173.5	176.2	178.9	184.9	191.0	197.1	203.1	209.9	216.7	222.4	227.8
157.5°	176.0	178.3	180.6	186.0	191.0	195.6	201.0	207.1	212.4	217.4	222.1
160°	178.5	180.4	182.4	186.7	191.0	194.6	198.8	203.8	208.5	212.4	216.3
162.5°	180.6	182.0	183.5	187.1	190.6	193.5	197.1	201.0	204.6	207.8	211.0
165°	182.1	183.1	184.2	187.4	189.9	192.1	194.6	197.8	200.6	203.1	205.6
167.5°	183.5	184.2	184.9	187.4	189.6	190.6	192.4	194.6	196.7	198.8	200.6
170°	184.2	184.8	185.3	187.1	188.9	189.6	190.6	192.1	193.9	194.9	196.4
172.5°	184.9	185.2	185.6	186.7	187.8	188.1	188.5	189.6	190.6	191.4	192.4
175°	185.3	185.4	185.6	186.4	187.1	186.7	187.1	187.4	188.5	188.9	189.2
177.5°	185.6	185.6	185.6	186.0	186.7	186.0	185.6	186.0	186.7	186.7	187.1
180°	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6

TEST NUMBER: P1009844

CATALOG NUMBER: S122RDIP-B290D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8
2.5°	611.3	610.4	607.8	608.7	607.3	607.3	606.4	606.4	606.4	608.7	607.3
5°	578.0	574.9	571.8	570.5	569.1	567.8	567.8	567.4	571.4	570.5	574.0
7.5°	536.7	535.8	529.6	529.6	527.4	526.5	528.7	529.2	529.6	530.5	532.7
10°	499.9	497.7	488.8	489.7	488.3	486.6	487.9	487.0	490.1	491.0	490.1
12.5°	456.4	452.4	442.6	437.7	432.4	428.4	433.3	429.7	442.2	445.7	455.5
15°	398.7	391.1	384.5	384.5	379.6	376.0	378.2	382.2	384.9	388.9	390.7
17.5°	360.0	356.9	351.6	348.5	347.2	345.8	345.8	347.6	353.4	352.9	356.5
20°	327.2	325.4	322.8	318.8	317.4	316.5	316.5	316.5	320.5	324.1	326.3
22.5°	304.5	303.2	301.4	296.1	293.5	292.6	294.8	296.1	299.2	301.9	304.1
25°	281.9	278.8	275.7	273.9	272.6	272.6	273.5	273.9	275.2	276.6	279.2
27.5°	263.3	261.0	256.6	251.7	251.7	250.4	251.3	252.2	255.3	259.7	261.9
30°	242.4	242.0	240.2	238.4	236.6	235.7	237.5	238.8	239.3	241.5	241.5
32.5°	227.3	224.2	221.1	219.3	218.4	218.0	218.4	220.2	220.2	222.9	226.0
35°	212.2	210.4	207.3	204.2	203.3	201.1	202.9	204.7	207.8	209.1	210.4
37.5°	195.8	193.6	192.2	191.3	189.6	190.0	188.7	191.3	194.0	193.6	194.4
40°	183.4	179.4	175.4	174.9	174.5	174.0	174.0	174.5	176.2	178.0	180.7
42.5°	167.4	166.0	162.5	158.9	158.0	157.2	156.3	158.0	161.6	164.7	166.0
45°	150.9	149.2	148.3	145.6	143.8	143.4	142.5	144.7	147.8	149.2	150.1
47.5°	135.8	135.4	132.7	133.2	131.9	132.3	131.9	133.2	133.2	134.5	135.4
50°	125.6	124.3	123.0	122.1	120.8	120.8	120.3	120.8	122.5	124.3	123.9
52.5°	115.4	113.2	112.8	112.3	111.4	112.3	111.0	111.4	113.2	114.1	113.7
55°	103.4	103.0	102.1	101.2	100.8	100.3	100.3	100.3	102.1	103.4	103.9
57.5°	94.1	91.9	90.1	90.1	88.3	87.9	88.8	89.2	90.6	91.5	92.3
60°	81.2	80.4	77.7	76.4	73.7	73.3	73.3	75.0	77.2	80.4	81.2
62.5°	67.5	66.1	65.7	65.7	65.7	65.7	65.7	65.7	65.7	66.1	66.1
65°	59.9	60.4	59.9	59.5	59.9	59.9	59.5	59.5	59.5	59.9	60.4
67.5°	53.7	53.3	53.7	53.3	52.8	52.8	52.4	52.8	53.3	53.7	53.7
70°	46.6	46.6	46.2	46.6	46.2	45.7	45.3	45.3	46.2	46.6	46.6
72.5°	40.0	40.0	39.5	39.5	38.6	38.6	39.1	38.6	38.6	40.0	40.0
75°	33.3	32.9	32.4	32.4	32.0	32.0	32.0	31.5	32.4	32.4	32.9
77.5°	26.2	26.2	26.2	25.7	25.7	25.3	25.3	25.7	25.7	25.7	26.2
80°	20.0	20.0	20.0	19.5	19.1	19.1	19.1	19.1	19.1	19.5	19.1
82.5°	13.8	13.8	13.8	13.8	13.8	13.3	13.3	13.3	13.8	13.8	13.3
85°	8.4	8.0	8.4	8.4	8.0	8.4	8.0	8.0	7.5	7.5	8.0
87.5°	3.6	3.1	2.7	2.7	3.1	2.7	2.7	2.7	3.1	2.7	2.7
90°	11.6	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.6
92.5°	25.4	23.9	23.6	22.1	22.5	21.8	22.5	22.1	23.6	23.9	25.4
95°	52.8	48.9	44.3	41.4	40.3	40.7	40.3	41.4	44.3	48.9	52.8
97.5°	106.0	95.3	81.4	74.3	70.3	68.2	70.3	74.3	81.4	95.3	106.0
100°	211.2	189.6	159.9	144.6	134.2	127.8	134.2	144.6	159.9	189.6	211.2
102.5°	357.0	333.8	301.0	272.0	258.5	249.2	258.5	272.0	301.0	333.8	357.0
105°	472.8	467.0	444.8	422.7	407.3	402.3	407.3	422.7	444.8	467.0	472.8
107.5°	514.8	521.9	521.6	518.4	513.7	505.5	513.7	518.4	521.6	521.9	514.8
110°	508.0	522.7	538.0	544.8	548.0	547.6	548.0	544.8	538.0	522.7	508.0

TEST NUMBER: P1009844

CATALOG NUMBER: S122RDIP-B290D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	485.0	502.3	525.1	537.6	544.4	546.9	544.4	537.6	525.1	502.3	485.0
115°	456.8	475.2	500.5	516.9	526.2	529.4	526.2	516.9	500.5	475.2	456.8
117.5°	429.8	447.3	473.4	490.9	500.5	503.0	500.5	490.9	473.4	447.3	429.8
120°	405.8	422.0	447.0	463.7	474.1	477.7	474.1	463.7	447.0	422.0	405.8
122.5°	387.0	401.3	423.0	439.5	448.4	451.2	448.4	439.5	423.0	401.3	387.0
125°	370.0	383.4	404.1	417.7	426.6	429.5	426.6	417.7	404.1	383.4	370.0
127.5°	355.6	368.1	386.3	399.1	407.0	409.1	407.0	399.1	386.3	368.1	355.6
130°	341.0	352.7	370.2	382.3	389.5	392.3	389.5	382.3	370.2	352.7	341.0
132.5°	325.8	336.7	353.8	365.9	372.4	374.9	372.4	365.9	353.8	336.7	325.8
135°	311.0	320.9	336.3	348.1	354.5	355.9	354.5	348.1	336.3	320.9	311.0
137.5°	296.0	304.9	319.5	329.9	335.6	337.7	335.6	329.9	319.5	304.9	296.0
140°	282.8	290.6	302.0	311.3	316.7	318.8	316.7	311.3	302.0	290.6	282.8
142.5°	270.0	276.3	287.0	295.2	299.9	299.9	299.9	295.2	287.0	276.3	270.0
145°	259.7	264.9	273.5	279.5	283.1	284.2	283.1	279.5	273.5	264.9	259.7
147.5°	250.6	254.5	262.0	267.0	269.5	270.3	269.5	267.0	262.0	254.5	250.6
150°	242.8	246.0	251.3	255.6	257.8	258.1	257.8	255.6	251.3	246.0	242.8
152.5°	236.2	238.8	242.8	246.3	247.8	247.8	247.8	246.3	242.8	238.8	236.2
155°	229.8	231.7	235.6	238.1	239.5	238.8	239.5	238.1	235.6	231.7	229.8
157.5°	223.7	225.3	228.1	230.3	231.0	231.0	231.0	230.3	228.1	225.3	223.7
160°	217.6	218.8	221.3	223.1	223.5	223.5	223.5	223.1	221.3	218.8	217.6
162.5°	211.9	212.8	215.3	216.3	216.7	216.3	216.7	216.3	215.3	212.8	211.9
165°	206.4	207.1	208.5	209.9	209.9	209.6	209.9	209.9	208.5	207.1	206.4
167.5°	201.4	202.1	202.8	203.5	203.5	203.1	203.5	203.5	202.8	202.1	201.4
170°	196.8	197.1	197.4	198.5	198.1	197.4	198.1	198.5	197.4	197.1	196.8
172.5°	192.6	192.8	193.1	193.5	193.1	192.8	193.1	193.5	193.1	192.8	192.6
175°	189.4	189.6	189.6	189.9	189.6	188.9	189.6	189.9	189.6	189.6	189.4
177.5°	187.1	187.1	187.1	187.1	186.7	186.0	186.7	187.1	187.1	187.1	187.1
180°	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6

TEST NUMBER: P1009844

CATALOG NUMBER: S122RDIP-B290D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8	638.8
2.5°	608.7	610.9	610.0	605.1	610.0	611.3	614.0	616.6	618.4	621.1	623.3
5°	570.5	574.9	577.6	574.9	583.8	585.1	591.3	594.9	600.2	604.7	608.2
7.5°	534.5	538.1	543.4	544.3	549.6	555.8	564.7	573.6	582.0	586.5	590.5
10°	495.9	502.1	510.1	508.3	516.3	526.1	535.4	549.6	556.7	564.7	571.8
12.5°	457.3	461.3	471.9	475.5	487.0	494.6	507.4	516.3	534.1	543.4	549.6
15°	389.8	406.2	419.5	435.5	450.6	464.8	476.4	492.3	507.9	515.0	525.2
17.5°	359.2	366.7	374.7	382.7	402.2	427.5	447.9	465.3	478.6	487.9	499.9
20°	327.2	334.7	343.6	351.2	363.2	381.4	406.7	436.4	452.4	462.2	473.7
22.5°	304.5	311.7	317.4	324.1	333.4	346.7	365.8	402.7	424.0	436.0	446.2
25°	280.1	289.0	295.2	300.1	307.7	322.3	337.8	358.7	396.9	406.2	420.4
27.5°	263.3	265.9	273.0	280.6	288.1	296.1	312.1	329.9	355.6	376.0	393.3
30°	243.3	249.9	256.6	259.7	266.4	277.9	287.7	306.8	326.7	342.7	363.6
32.5°	228.2	232.2	236.6	244.2	250.4	258.4	268.1	284.1	301.0	311.2	327.2
35°	211.3	214.0	223.3	226.4	232.6	240.6	250.4	262.8	281.0	289.0	300.6
37.5°	195.3	201.6	204.2	211.3	217.1	225.1	232.2	246.4	258.4	267.7	278.4
40°	182.9	185.6	190.5	196.7	201.6	207.8	216.6	226.9	239.7	247.3	256.6
42.5°	167.8	170.0	176.2	179.8	187.8	193.6	198.9	211.3	222.9	228.6	238.0
45°	151.4	156.7	160.7	167.8	172.3	179.4	186.0	194.9	205.5	212.2	217.5
47.5°	137.2	142.5	146.5	153.2	160.3	163.4	170.5	179.8	189.6	194.9	202.4
50°	125.6	127.4	135.0	138.1	145.6	151.8	156.7	164.7	175.4	178.5	184.7
52.5°	114.5	115.9	120.8	124.7	131.4	136.7	143.0	150.5	159.4	164.3	169.1
55°	104.8	105.7	107.9	112.3	116.8	123.4	129.2	136.3	143.8	149.2	153.6
57.5°	93.7	95.4	97.2	99.9	104.3	110.5	116.8	123.4	129.6	133.2	139.0
60°	80.8	83.5	86.6	89.7	92.8	97.2	104.3	110.5	116.3	119.4	123.9
62.5°	67.0	72.4	75.0	78.6	81.2	85.2	90.6	97.7	101.7	105.7	109.2
65°	60.4	60.8	61.3	64.8	69.7	73.7	78.6	83.9	90.1	92.8	95.4
67.5°	53.7	54.2	55.0	55.5	57.3	61.7	67.0	72.8	77.7	79.5	82.1
70°	47.1	47.1	48.8	49.3	49.7	50.2	54.6	60.4	64.8	67.0	70.1
72.5°	40.0	40.4	41.3	41.7	42.6	43.5	44.8	47.9	53.3	55.5	59.0
75°	32.9	33.3	33.7	34.2	35.5	36.0	37.3	39.1	41.3	44.0	46.2
77.5°	26.2	26.2	26.6	27.5	28.4	28.9	30.2	31.1	32.0	33.3	35.1
80°	19.5	20.0	20.0	20.9	20.9	21.3	21.8	23.1	24.0	24.9	25.7
82.5°	13.3	14.2	14.2	14.2	14.7	15.1	15.5	15.5	16.4	16.9	18.2
85°	8.0	8.4	8.4	8.4	8.0	8.9	8.9	9.3	9.3	9.3	9.8
87.5°	3.1	2.7	3.1	3.1	3.1	3.6	3.1	3.1	3.6	4.0	4.0
90°	11.4	10.7	11.4	11.8	12.1	11.8	9.6	7.1	5.4	4.8	4.3
92.5°	26.8	30.7	36.1	46.1	55.0	54.3	42.1	28.6	18.9	17.0	15.0
95°	56.8	71.8	93.5	122.5	139.9	123.9	82.5	51.4	35.0	30.7	26.4
97.5°	116.7	152.8	191.4	229.9	228.1	176.4	109.6	66.4	45.3	40.5	35.7
100°	232.8	281.7	325.9	333.4	282.0	194.2	117.1	73.5	54.6	49.6	44.6
102.5°	380.2	412.7	414.1	372.0	283.8	187.4	117.5	80.0	62.8	57.8	52.8
105°	478.7	474.1	433.8	359.5	264.5	178.1	119.2	87.5	70.7	65.7	60.7
107.5°	507.7	472.7	412.7	333.1	246.7	173.1	123.2	95.0	78.5	73.5	68.5
110°	493.4	447.7	383.8	308.4	234.5	171.7	128.2	102.5	86.8	81.6	76.4

TEST NUMBER: P1009844

CATALOG NUMBER: S122RDIP-B290D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	467.7	418.0	357.4	291.3	226.7	172.1	133.5	109.6	94.6	89.2	83.9
115°	438.4	391.6	336.7	277.7	221.3	173.5	138.9	117.1	101.7	96.9	92.1
117.5°	412.3	368.8	319.5	268.5	218.5	175.6	144.6	123.9	109.6	104.6	99.6
120°	389.5	351.6	307.4	261.3	216.0	177.8	150.3	131.0	117.1	112.1	107.1
122.5°	372.7	337.4	297.7	255.3	214.6	180.3	155.3	137.8	125.0	119.8	114.6
125°	356.6	325.2	288.5	249.5	212.8	182.8	160.7	144.6	131.7	126.7	121.7
127.5°	343.1	313.1	279.2	244.2	211.7	185.3	165.6	151.0	138.5	133.4	128.2
130°	329.2	301.0	270.3	238.8	211.0	188.1	170.3	156.7	144.2	139.2	134.2
132.5°	314.9	289.5	261.7	234.5	210.6	191.0	174.9	161.7	149.9	144.9	139.9
135°	301.0	277.4	253.8	230.6	210.3	193.1	178.9	166.4	154.9	149.9	144.9
137.5°	287.0	267.8	247.4	227.8	210.3	195.3	182.1	170.3	158.9	154.2	149.6
140°	274.9	258.5	241.3	225.3	209.9	196.7	184.6	173.5	162.8	158.2	153.5
142.5°	263.8	250.3	236.3	222.8	209.9	197.8	186.7	176.0	165.6	161.4	157.1
145°	254.5	243.5	231.7	220.6	209.2	198.5	188.5	178.5	168.9	165.0	161.0
147.5°	246.7	237.8	228.1	218.5	208.1	198.8	189.6	180.6	171.4	167.8	164.2
150°	239.5	232.1	224.2	215.6	207.1	198.5	190.3	182.1	173.9	170.6	167.4
152.5°	233.5	227.4	220.3	213.1	205.3	197.8	190.6	183.5	176.4	173.5	170.6
155°	227.8	222.4	216.7	209.9	203.1	197.1	191.0	184.9	178.9	176.2	173.5
157.5°	222.1	217.4	212.4	207.1	201.0	195.6	191.0	186.0	180.6	178.3	176.0
160°	216.3	212.4	208.5	203.8	198.8	194.6	191.0	186.7	182.4	180.4	178.5
162.5°	211.0	207.8	204.6	201.0	197.1	193.5	190.6	187.1	183.5	182.0	180.6
165°	205.6	203.1	200.6	197.8	194.6	192.1	189.9	187.4	184.2	183.1	182.1
167.5°	200.6	198.8	196.7	194.6	192.4	190.6	189.6	187.4	184.9	184.2	183.5
170°	196.4	194.9	193.9	192.1	190.6	189.6	188.9	187.1	185.3	184.8	184.2
172.5°	192.4	191.4	190.6	189.6	188.5	188.1	187.8	186.7	185.6	185.2	184.9
175°	189.2	188.9	188.5	187.4	187.1	186.7	187.1	186.4	185.6	185.4	185.3
177.5°	187.1	186.7	186.7	186.0	185.6	186.0	186.7	186.0	185.6	185.6	185.6
180°	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6

TEST NUMBER: P1009844

CATALOG NUMBER: S122RDIP-B290D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	638.8	638.8	638.8	638.8
2.5°	627.3	626.0	634.0	642.8
5°	614.4	616.6	626.9	639.3
7.5°	601.1	606.0	618.0	634.4
10°	582.5	591.3	609.5	626.4
12.5°	564.3	576.2	593.6	613.5
15°	543.8	557.2	578.5	602.4
17.5°	521.2	536.3	561.2	587.3
20°	497.2	517.2	543.4	571.8
22.5°	470.6	494.6	521.6	553.2
25°	444.8	471.0	498.1	534.5
27.5°	419.5	445.3	475.5	512.3
30°	394.2	417.8	450.2	489.7
32.5°	367.1	391.6	425.7	466.1
35°	342.3	366.7	398.7	438.6
37.5°	315.6	341.8	372.5	413.8
40°	284.6	315.2	344.9	384.5
42.5°	258.8	291.2	320.1	357.4
45°	238.4	269.0	293.0	329.4
47.5°	219.3	244.2	268.6	302.3
50°	201.1	220.2	245.5	275.7
52.5°	182.5	198.9	220.6	249.1
55°	165.6	181.1	200.7	222.4
57.5°	150.1	161.2	180.7	200.2
60°	132.7	144.3	159.4	175.8
62.5°	118.1	127.0	141.2	154.9
65°	102.6	111.0	121.6	134.5
67.5°	88.3	95.9	104.3	114.5
70°	75.5	81.2	87.5	96.3
72.5°	61.7	67.9	73.7	80.8
75°	50.6	53.3	58.2	63.0
77.5°	39.1	42.6	45.3	49.3
80°	28.0	31.1	32.0	35.1
82.5°	18.6	20.4	22.2	23.1
85°	10.7	11.5	13.3	13.8
87.5°	4.0	4.4	5.3	6.2
90°	3.6	2.9	1.4	0.4
92.5°	12.1	10.4	7.5	5.4
95°	20.7	17.5	13.9	12.5
97.5°	29.3	24.6	20.7	18.6
100°	37.5	31.8	28.6	27.5
102.5°	45.3	39.6	36.4	35.7
105°	52.8	47.5	45.0	43.6
107.5°	60.7	55.7	53.2	52.1
110°	68.9	64.3	62.1	60.7

TEST NUMBER: P1009844

CATALOG NUMBER: S122RDIP-B290D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	76.8	72.5	70.0	68.5
115°	85.0	80.7	78.5	76.8
117.5°	92.8	88.9	86.8	85.3
120°	100.0	96.7	94.6	93.2
122.5°	107.5	103.9	101.7	100.7
125°	114.6	110.3	108.2	107.1
127.5°	121.4	116.7	113.9	112.5
130°	127.1	122.1	118.5	117.1
132.5°	132.4	127.1	123.2	121.4
135°	136.7	131.4	127.1	125.7
137.5°	141.4	135.7	131.4	129.6
140°	145.7	139.9	135.7	134.2
142.5°	149.6	143.9	139.9	138.9
145°	153.9	148.5	144.9	143.5
147.5°	158.2	153.2	149.6	148.5
150°	162.1	157.4	154.6	153.5
152.5°	165.6	161.7	158.9	158.5
155°	169.6	165.6	163.5	163.1
157.5°	172.8	169.2	167.4	167.1
160°	175.6	172.8	171.4	171.0
162.5°	178.1	176.0	174.6	174.9
165°	180.3	178.1	177.4	177.8
167.5°	182.1	180.6	179.9	180.3
170°	183.5	182.4	182.1	182.8
172.5°	184.6	183.5	183.9	184.2
175°	185.3	184.6	184.9	185.3
177.5°	185.6	184.9	185.3	186.0
180°	185.6	185.6	185.6	185.6

(END OF REPORT)