

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009852

Luminaire Tested: S122RDIP-B290D330UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009852
REPORT IS A COMBINATION OF REPORTS P988090 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B290D330UB40-4F0-XX-W2A-F1
Description: Define 2 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2171.0 lumens
Efficiency: N/A
Efficacy: 97.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009852

CATALOG NUMBER: S122RDIP-B290D330UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1009852

CATALOG NUMBER: S122RDIP-B290D330UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	53	53	53			46
1	97	93	89	86	89	86	83	80	72	70	67	59	57	56	47	46	45			40
2	89	82	76	71	81	75	70	66	63	60	57	52	50	47	42	40	39			34
3	81	72	65	60	75	67	61	56	56	52	48	47	43	41	38	35	33			29
4	75	64	57	51	68	59	53	48	50	45	41	42	38	35	34	31	29			26
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26			22
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23			20
7	59	47	39	34	54	43	37	32	37	32	28	31	27	24	26	23	20			18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	18			16
9	51	39	32	27	47	36	30	25	31	26	22	26	22	20	22	19	17			15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	20	17	15			13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7688	7688	7688
5°	7701	7315	7261
10°	7625	6937	6709
15°	7521	6492	6080
20°	7382	5987	5422
25°	7241	5467	4820
30°	7049	4961	4163
35°	6862	4450	3598
40°	6673	3950	3016
45°	6452	3432	2509
50°	6222	2934	2043
55°	5985	2435	1621
60°	5708	1947	1226
65°	5393	1485	997
70°	5006	1077	793
75°	4526	822	607
80°	3824	556	406
85°	2670	256	198

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6452 cd/sqm

TEST NUMBER: P1009852

CATALOG NUMBER: S122RDIP-B290D330UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.5	2.1
10°-20°	125.0	5.8
20°-30°	175.5	8.1
30°-40°	191.3	8.8
40°-50°	175.8	8.1
50°-60°	138.0	6.4
60°-70°	89.9	4.1
70°-80°	46.3	2.1
80°-90°	13.0	0.6
90°-100°	25.9	1.2
100°-110°	82.3	3.8
110°-120°	140.9	6.5
120°-130°	185.3	8.5
130°-140°	208.0	9.6
140°-150°	204.0	9.4
150°-160°	171.1	7.9
160°-170°	113.5	5.2
170°-180°	39.7	1.8
0°-30°	346.0	15.9
0°-40°	537.2	24.7
0°-60°	851.1	39.2
0°-90°	1000.2	46.1
90°-120°	249.2	11.5
90°-150°	846.5	39.0
90°-180°	1171.0	53.9
0°-180°	2171.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	486	486	486	486	486	
5°	486	484	478	482	480	46
15°	462	457	442	434	430	130
25°	419	405	376	358	352	193
35°	361	339	300	272	263	226
45°	295	266	220	189	178	228
55°	225	190	143	116	108	201
65°	152	116	76	62	60	150
75°	81	50	35	32	32	86
85°	19	10	8	8	8	22
90°	0	5	12	12	12	2
95°	18	22	23	23	22	21
105°	76	77	78	78	78	80
115°	141	144	143	142	141	140
125°	206	209	208	207	206	184
135°	266	270	271	270	269	206
145°	323	326	328	328	326	202
155°	369	370	371	373	372	170
165°	402	402	402	404	402	113
175°	418	417	416	419	417	40
180°	419	419	419	419	419	

TEST NUMBER: P1009852

CATALOG NUMBER: S122RDIP-B290D330UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	485.7	485.7	485.7	485.7	485.7
2.5°	487.9	485.7	480.9	485.3	484.4
5°	485.7	483.5	477.8	481.8	480.5
7.5°	481.8	479.2	473.0	474.8	472.6
10°	476.5	473.4	464.6	463.3	460.7
12.5°	469.9	466.0	454.1	451.5	446.6
15°	462.0	457.2	442.2	433.9	429.5
17.5°	452.8	445.7	427.3	417.6	410.6
20°	442.2	433.4	411.5	400.5	390.8
22.5°	430.8	420.7	395.2	380.2	373.7
25°	419.4	405.3	376.3	358.3	351.7
27.5°	405.7	390.8	358.7	338.0	327.9
30°	391.2	374.5	339.4	316.9	305.1
32.5°	377.2	356.9	320.9	294.5	283.5
35°	361.3	338.9	300.2	272.5	262.9
37.5°	346.0	321.8	280.9	250.6	239.6
40°	329.7	303.3	260.7	229.5	218.0
42.5°	313.0	284.9	240.5	207.9	196.9
45°	295.4	266.0	219.8	188.6	178.0
47.5°	278.7	247.5	200.0	168.8	159.1
50°	260.2	229.0	180.7	150.3	141.1
52.5°	242.2	209.2	162.2	133.2	124.8
55°	224.6	190.3	142.9	116.5	108.1
57.5°	206.6	171.4	125.7	101.1	94.1
60°	188.1	153.0	107.7	85.3	78.2
62.5°	170.1	135.0	92.3	71.2	67.7
65°	151.7	116.1	76.5	61.5	60.2
67.5°	134.1	98.5	61.5	54.1	52.8
70°	115.6	81.3	51.0	46.6	44.8
72.5°	98.0	65.5	42.6	39.1	38.2
75°	80.9	50.1	35.2	32.1	31.7
77.5°	63.7	35.6	27.7	25.9	25.1
80°	47.9	25.5	21.1	19.3	19.3
82.5°	33.4	17.1	14.5	13.6	13.6
85°	18.9	9.7	8.4	8.4	8.4
87.5°	7.0	3.5	3.5	3.1	3.1
90°	0.4	4.6	12.4	11.7	12.0
92.5°	7.8	10.6	11.0	11.3	11.3
95°	18.4	21.9	22.6	22.6	21.9
97.5°	30.7	33.9	35.3	35.3	35.3
100°	44.9	47.7	48.8	48.8	48.4
102.5°	59.7	61.8	63.3	63.6	63.3
105°	76.0	77.0	77.7	78.5	78.5
107.5°	92.2	93.6	93.6	94.0	92.2
110°	107.8	109.9	109.9	109.9	108.8

TEST NUMBER: P1009852

CATALOG NUMBER: S122RDIP-B290D330UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	124.7	126.9	126.5	125.5	124.7
115°	141.4	143.5	142.8	142.4	141.4
117.5°	158.0	160.8	159.0	158.0	156.9
120°	174.6	177.4	174.6	174.6	173.5
122.5°	189.8	193.3	191.5	190.5	189.8
125°	205.7	208.9	207.8	206.7	206.4
127.5°	221.2	225.1	223.7	222.3	221.2
130°	235.7	240.3	239.6	238.9	237.5
132.5°	252.0	255.5	255.9	254.1	253.0
135°	266.1	270.0	270.7	270.3	269.3
137.5°	281.7	284.8	285.5	285.2	283.8
140°	295.4	298.6	300.4	300.4	299.0
142.5°	309.6	312.8	313.8	314.2	312.8
145°	323.0	325.5	327.6	328.0	326.5
147.5°	335.0	338.2	339.6	340.3	338.9
150°	347.4	349.5	350.9	352.0	350.9
152.5°	358.3	360.5	362.2	363.6	362.2
155°	369.3	370.4	371.4	373.2	372.1
157.5°	378.8	379.5	380.3	382.7	381.0
160°	387.3	388.0	388.4	390.5	389.1
162.5°	395.1	395.1	395.4	397.9	396.2
165°	401.8	401.5	401.5	403.9	402.2
167.5°	407.8	406.8	406.8	409.2	407.5
170°	412.4	411.4	411.0	413.5	411.4
172.5°	415.6	414.5	414.2	416.7	414.5
175°	418.1	417.0	416.3	418.8	416.7
177.5°	419.5	418.4	417.7	419.8	417.7
180°	418.8	418.8	418.8	418.8	418.8

(END OF REPORT)