

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1009871

Luminaire Tested: S122RDIP-B290D530UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1009871
REPORT IS A COMBINATION OF REPORTS P988119 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B290D530UB30-4F0-XX-W2A-F4
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3078.4 lumens
Efficiency: N/A
Efficacy: 108.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1009871

CATALOG NUMBER: S122RDIP-B290D530UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1009871

CATALOG NUMBER: S122RDIP-B290D530UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	94	90	86	83	85	81	78	76	65	63	61	50	49	47	36	35	35
2	86	79	73	68	77	71	67	62	57	54	51	44	42	40	32	31	30
3	79	70	63	57	71	63	57	52	51	47	43	39	37	34	29	27	25
4	72	62	54	49	65	56	50	45	45	41	37	35	32	29	26	24	22
5	66	55	47	42	59	50	43	38	41	36	32	32	28	26	23	21	20
6	61	49	42	36	55	45	38	33	37	32	28	29	25	23	21	19	17
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	17	15
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	14	13
10	45	34	27	22	41	31	25	21	25	21	18	20	17	15	15	13	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7736	7736	7736
5°	7748	7359	7305
10°	7672	6979	6750
15°	7566	6532	6117
20°	7427	6022	5454
25°	7284	5499	4849
30°	7092	4991	4187
35°	6903	4477	3620
40°	6713	3973	3034
45°	6491	3452	2524
50°	6261	2952	2056
55°	6022	2449	1632
60°	5744	1958	1234
65°	5425	1492	1004
70°	5037	1083	798
75°	4554	827	609
80°	3848	559	410
85°	2684	256	198

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6491 cd/sqm

TEST NUMBER: P1009871

CATALOG NUMBER: S122RDIP-B290D530UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.8	1.5
10°-20°	125.7	4.1
20°-30°	176.5	5.7
30°-40°	192.4	6.3
40°-50°	176.8	5.7
50°-60°	138.9	4.5
60°-70°	90.4	2.9
70°-80°	46.5	1.5
80°-90°	13.8	0.4
90°-100°	120.5	3.9
100°-110°	407.2	13.2
110°-120°	428.0	13.9
120°-130°	352.0	11.4
130°-140°	282.8	9.2
140°-150°	213.7	6.9
150°-160°	150.2	4.9
160°-170°	88.4	2.9
170°-180°	28.8	0.9
0°-30°	348.0	11.3
0°-40°	540.4	17.6
0°-60°	856.2	27.8
0°-90°	1006.9	32.7
90°-120°	955.6	31.0
90°-150°	1804.1	58.6
90°-180°	2071.0	67.3
0°-180°	3078.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	489	489	489	489	489	
5°	489	486	481	485	483	46
15°	465	460	445	436	432	131
25°	422	408	378	360	354	194
35°	364	341	302	274	264	228
45°	297	268	221	190	179	230
55°	226	192	144	117	109	202
65°	153	117	77	62	61	151
75°	81	50	35	32	32	86
85°	19	10	8	8	8	22
90°	1	8	19	19	19	2
95°	20	49	224	85	65	21
105°	70	105	423	757	644	74
115°	123	155	354	731	847	122
125°	171	203	340	592	687	152
135°	201	240	336	498	570	155
145°	230	264	335	416	455	144
155°	261	282	325	368	382	120
165°	284	293	311	330	335	80
175°	296	297	299	303	302	28
180°	297	297	297	297	297	

TEST NUMBER: P1009871

CATALOG NUMBER: S122RDIP-B290D530UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	488.7	488.7	488.7	488.7	488.7
2.5°	490.9	488.7	483.8	488.2	487.3
5°	488.7	486.5	480.7	484.7	483.4
7.5°	484.7	482.0	475.8	477.6	475.4
10°	479.4	476.3	467.4	466.1	463.5
12.5°	472.7	468.8	456.8	454.2	449.3
15°	464.8	459.9	444.9	436.5	432.1
17.5°	455.5	448.4	429.8	420.1	413.0
20°	444.9	436.0	413.9	402.9	393.1
22.5°	433.4	423.2	397.6	382.5	375.9
25°	421.9	407.7	378.5	360.4	353.8
27.5°	408.2	393.1	360.9	340.1	329.9
30°	393.6	376.8	341.4	318.8	306.9
32.5°	379.4	359.1	322.8	296.3	285.2
35°	363.5	341.0	302.0	274.2	264.5
37.5°	348.0	323.7	282.6	252.1	241.0
40°	331.7	305.1	262.2	230.8	219.3
42.5°	314.9	286.6	241.9	209.2	198.1
45°	297.2	267.5	221.1	189.7	179.1
47.5°	280.4	249.0	201.2	169.8	160.1
50°	261.8	230.4	181.8	151.2	142.0
52.5°	243.7	210.5	163.2	134.0	125.6
55°	226.0	191.5	143.7	117.2	108.8
57.5°	207.8	172.5	126.5	101.7	94.6
60°	189.3	153.9	108.3	85.8	78.7
62.5°	171.1	135.8	92.9	71.6	68.1
65°	152.6	116.7	76.9	61.9	60.6
67.5°	134.9	99.1	61.9	54.4	53.1
70°	116.3	81.8	51.3	46.9	45.1
72.5°	98.6	65.9	42.9	39.4	38.5
75°	81.4	50.4	35.4	32.3	31.8
77.5°	64.1	35.8	27.9	26.1	25.2
80°	48.2	25.6	21.2	19.5	19.5
82.5°	33.6	17.2	14.6	13.7	13.7
85°	19.0	9.7	8.4	8.4	8.4
87.5°	7.1	3.5	3.5	3.1	3.1
90°	0.6	7.8	19.4	18.6	18.9
92.5°	8.6	27.2	88.0	40.6	34.9
95°	20.0	49.2	224.0	84.6	65.1
97.5°	29.7	64.8	365.1	169.7	109.1
100°	44.0	79.4	451.4	338.0	204.5
102.5°	57.1	92.6	454.2	571.4	398.8
105°	69.7	105.1	423.4	756.8	643.9
107.5°	83.4	117.7	394.8	823.9	809.1
110°	97.1	130.6	375.4	813.0	876.5

TEST NUMBER: P1009871

CATALOG NUMBER: S122RDIP-B290D530UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	109.7	142.9	362.8	776.2	875.3
115°	122.8	155.1	354.2	731.0	847.3
117.5°	136.6	167.4	349.7	687.9	805.1
120°	149.1	179.4	345.7	649.4	764.5
122.5°	161.1	191.7	343.4	619.4	722.2
125°	171.4	202.8	340.5	592.2	687.4
127.5°	180.0	213.4	338.8	569.1	654.8
130°	187.4	222.8	337.7	545.6	627.9
132.5°	194.3	232.0	337.1	521.3	599.9
135°	201.1	240.0	336.5	497.7	569.7
137.5°	207.4	246.8	336.5	473.6	540.5
140°	214.8	253.1	336.0	452.6	510.2
142.5°	222.3	258.2	336.0	432.2	479.9
145°	229.7	264.0	334.8	415.7	454.8
147.5°	237.7	268.6	333.1	401.1	432.5
150°	245.7	273.2	331.4	388.5	413.1
152.5°	253.7	277.7	328.5	378.0	396.5
155°	261.1	282.0	325.1	367.6	382.2
157.5°	267.4	285.4	321.7	358.0	369.7
160°	273.7	288.8	318.3	348.2	357.7
162.5°	280.0	291.4	315.4	339.1	346.2
165°	284.5	293.1	311.4	330.2	335.4
167.5°	288.5	294.8	308.0	322.2	325.1
170°	292.5	295.6	305.1	314.8	316.0
172.5°	294.8	296.6	301.7	308.2	308.5
175°	296.5	296.8	299.4	303.1	302.3
177.5°	297.7	297.1	297.1	299.4	297.7
180°	297.1	297.1	297.1	297.1	297.1

(END OF REPORT)